

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331990-930

Luminaire Tested: **S123DIP-S775D1025U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331990-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5611.2 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331990-930

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331990-930

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81		66	66	66		53	53	53	46
1	97	93	89	85	89	85	82	79	71	69	66		58	57	55		46	45	44	39
2	88	81	75	69	81	74	69	65	62	58	55		51	48	46		41	39	37	32
3	80	71	64	58	73	65	59	54	55	50	46		45	42	39		36	34	32	27
4	74	63	55	49	67	58	51	46	49	43	39		40	36	33		32	29	27	23
5	67	56	48	42	62	52	44	39	44	38	34		36	32	29		29	26	24	20
6	62	50	42	36	57	46	39	34	39	34	29		33	28	25		26	23	21	18
7	57	45	37	32	53	42	35	30	35	30	26		30	25	22		24	21	19	16
8	53	41	33	28	49	38	31	26	32	27	23		27	23	20		22	19	17	14
9	50	37	30	25	45	35	28	23	30	24	21		25	21	18		20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19		23	19	16		19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10687	10687	10687
5°	10737	10589	10662
10°	10665	10497	10563
15°	10541	10379	10398
20°	10394	10208	10219
25°	10200	10007	9987
30°	9984	9783	9708
35°	9759	9546	9423
40°	9524	9284	9140
45°	9266	9045	8824
50°	9008	8748	8505
55°	8668	8443	8188
60°	8325	8086	7830
65°	8023	7697	7457
70°	7578	7254	6930
75°	6924	6675	6392
80°	6248	5976	5926
85°	5483	5274	5064



TEST NUMBER: P331990-930

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.7
10°-20°	264.1	4.7
20°-30°	390.1	7.0
30°-40°	455.7	8.1
40°-50°	458.1	8.2
50°-60°	402.4	7.2
60°-70°	299.8	5.3
70°-80°	170.8	3.0
80°-90°	52.1	0.9
90°-100°	223.7	4.0
100°-110°	633.5	11.3
110°-120°	623.2	11.1
120°-130°	497.1	8.9
130°-140°	391.9	7.0
140°-150°	292.5	5.2
150°-160°	203.9	3.6
160°-170°	119.8	2.1
170°-180°	39.0	0.7
0°-30°	747.7	13.3
0°-40°	1203.3	21.4
0°-60°	2063.8	36.8
0°-90°	2586.6	46.1
90°-120°	1480.5	26.4
90°-150°	2662.0	47.4
90°-180°	3025.0	53.9
0°-180°	5611.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	994	989	980	988	987	94
15°	946	942	931	938	933	267
25°	859	853	843	843	841	395
35°	743	737	726	721	717	464
45°	609	605	594	584	580	470
55°	462	460	450	441	436	414
65°	315	310	302	296	293	311
75°	166	163	160	156	154	178
85°	44	43	43	41	41	49
90°	2	10	20	23	24	4
95°	28	90	483	141	94	30
105°	94	140	654	1144	1035	100
115°	167	208	500	1097	1259	165
125°	232	274	467	846	993	206
135°	272	324	461	697	805	210
145°	310	355	455	572	629	194
155°	352	380	440	500	522	162
165°	385	396	422	447	455	108
175°	401	402	404	410	409	38
180°	402	402	402	402	402	



TEST NUMBER: P331990-930

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	996.2	995.6	995.1	994.4	993.8	992.7	991.0	989.4	987.7	986.0	987.5
5°	993.7	992.7	991.8	990.8	989.9	988.4	986.3	984.2	982.1	980.0	981.9
7.5°	984.0	983.0	982.0	981.1	980.2	978.6	976.4	974.3	972.1	970.0	971.7
10°	975.8	974.8	973.9	972.9	972.0	970.3	967.8	965.3	962.9	960.4	962.1
12.5°	964.8	964.0	963.3	962.5	961.6	960.1	957.8	955.4	953.2	950.8	952.1
15°	945.9	945.1	944.4	943.6	942.8	941.3	938.7	936.3	933.8	931.4	932.9
17.5°	923.8	922.8	921.9	920.9	919.9	918.2	915.7	913.2	910.8	908.3	909.4
20°	907.4	906.3	905.2	904.1	902.9	901.1	898.6	896.2	893.7	891.2	892.0
22.5°	889.0	887.9	886.7	885.6	884.4	882.6	880.2	877.8	875.3	872.8	873.4
25°	858.8	857.7	856.6	855.4	854.3	852.5	849.9	847.5	845.1	842.6	842.8
27.5°	826.6	825.4	824.3	823.2	822.1	820.3	817.6	815.0	812.3	809.6	809.8
30°	803.3	802.3	801.4	800.5	799.5	797.7	795.1	792.4	789.8	787.1	787.1
32.5°	780.1	778.9	777.6	776.3	775.1	773.5	771.4	769.3	767.3	765.2	764.2
35°	742.7	741.6	740.5	739.3	738.2	736.4	733.9	731.4	729.0	726.5	725.4
37.5°	704.4	703.0	701.6	700.1	698.7	696.8	694.2	691.7	689.2	686.7	685.3
40°	677.8	676.7	675.6	674.4	673.3	671.4	668.7	666.1	663.4	660.7	659.3
42.5°	651.2	649.9	648.6	647.3	646.0	644.1	641.4	638.7	636.1	633.4	631.9
45°	608.7	607.9	607.2	606.4	605.6	604.1	601.5	599.1	596.6	594.2	591.9
47.5°	566.5	565.4	564.3	563.2	562.1	560.4	558.1	555.8	553.4	551.1	548.9
50°	537.9	536.9	535.9	535.0	534.0	532.3	529.9	527.4	524.9	522.4	520.4
52.5°	507.8	507.1	506.5	505.8	505.2	503.5	500.9	498.3	495.7	493.1	491.3
55°	461.9	461.6	461.5	461.3	461.1	459.7	457.3	454.9	452.3	449.9	447.8
57.5°	418.2	417.5	416.9	416.2	415.6	414.3	412.3	410.3	408.3	406.3	404.5
60°	386.7	386.5	386.4	386.1	386.0	384.7	382.5	380.2	377.9	375.6	373.9
62.5°	358.7	358.2	357.8	357.3	356.8	355.4	353.1	350.8	348.5	346.3	344.5
65°	315.0	314.1	313.1	312.2	311.2	309.8	307.9	306.0	304.1	302.2	300.7
67.5°	268.7	267.9	267.1	266.2	265.4	264.2	262.9	261.4	259.9	258.5	257.1
70°	240.8	239.6	238.5	237.3	236.2	235.1	233.9	232.8	231.6	230.5	229.2
72.5°	211.4	210.5	209.7	208.9	208.1	207.0	205.7	204.4	203.1	201.8	200.6
75°	166.5	165.7	164.9	164.2	163.5	162.7	162.2	161.6	161.0	160.5	159.6
77.5°	126.7	126.3	125.9	125.5	125.0	124.5	123.8	123.1	122.5	121.7	121.1
80°	100.8	100.2	99.6	99.1	98.5	98.0	97.6	97.3	96.9	96.4	96.3
82.5°	75.5	75.3	75.3	75.1	75.0	74.9	74.8	74.8	74.7	74.6	74.3
85°	44.4	44.0	43.6	43.3	42.9	42.7	42.7	42.7	42.7	42.7	42.3
87.5°	18.1	17.9	17.9	17.9	17.7	17.8	18.1	18.4	18.8	19.1	18.8
90°	1.6	3.3	4.9	7.3	9.0	10.6	13.0	15.5	17.9	20.4	19.6
92.5°	10.1	15.0	21.9	28.1	35.0	47.0	68.3	103.4	137.7	125.1	94.4
95°	27.6	30.1	39.1	52.9	74.0	105.8	175.0	296.2	429.7	482.6	391.4
97.5°	47.2	48.0	55.0	67.0	87.9	122.2	188.3	325.1	547.6	747.9	800.1
100°	60.3	61.1	66.8	78.1	97.7	129.4	186.4	306.8	520.8	770.7	931.0
102.5°	73.9	75.3	80.4	91.2	108.8	137.9	189.0	291.1	481.8	728.4	937.5
105°	94.4	96.9	101.7	111.5	126.9	152.2	196.2	280.0	433.7	654.3	887.9
107.5°	116.2	118.6	123.4	133.0	147.5	170.9	209.5	279.2	403.2	588.9	801.0
110°	131.8	134.3	138.4	147.3	161.1	183.9	220.5	282.4	391.4	551.8	746.2



TEST NUMBER: P331990-930

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.2	148.6	152.7	161.6	175.5	197.6	231.6	288.9	384.9	527.0	698.7
115°	166.8	170.1	175.0	183.1	197.0	218.9	249.8	299.5	382.5	500.5	641.3
117.5°	187.5	191.3	195.3	202.8	218.3	238.6	269.2	313.5	383.9	484.9	606.6
120°	201.8	204.2	208.3	216.5	232.0	252.3	281.6	323.9	386.5	477.7	588.4
122.5°	214.2	216.6	220.7	229.5	244.3	266.0	294.6	333.7	391.1	473.1	573.4
125°	232.0	233.6	238.5	247.4	262.9	284.9	313.3	349.1	397.9	467.2	554.2
127.5°	245.5	247.9	253.9	263.0	280.1	302.1	329.6	361.8	405.8	464.2	537.3
130°	253.9	256.3	263.7	273.5	290.5	312.5	339.3	370.3	411.0	462.3	528.2
132.5°	260.4	263.5	271.5	283.2	300.3	321.6	347.8	378.1	414.9	461.6	519.7
135°	271.8	275.1	284.1	296.2	313.3	335.3	360.5	388.2	420.8	460.6	508.7
137.5°	282.6	286.0	294.7	307.8	324.7	345.0	369.3	395.7	424.6	458.9	499.0
140°	289.8	293.8	301.9	315.0	331.3	351.6	375.2	399.6	427.2	458.2	493.2
142.5°	297.5	300.9	309.7	321.5	337.7	356.8	379.8	403.5	429.2	456.9	488.0
145°	310.1	312.5	319.8	332.1	345.8	364.6	385.7	407.7	430.5	454.9	480.9
147.5°	322.8	324.2	331.4	341.9	355.3	371.3	390.6	410.3	430.5	451.8	474.1
150°	331.3	332.1	338.5	349.1	360.5	375.2	393.9	411.0	430.5	449.2	469.5
152.5°	339.7	339.8	346.3	355.6	365.7	379.8	395.8	412.3	428.5	446.0	464.4
155°	352.4	352.4	357.3	365.4	374.4	385.7	399.6	412.6	426.4	440.3	456.6
157.5°	362.5	363.1	367.0	374.2	381.8	390.6	401.7	413.4	423.7	435.2	447.8
160°	370.3	370.3	373.6	380.0	385.7	393.9	403.7	413.4	422.4	431.3	441.9
162.5°	376.2	376.2	378.8	383.9	389.0	395.8	404.3	412.8	419.8	427.4	436.0
165°	384.9	384.1	385.7	389.8	393.1	398.8	405.3	411.0	415.9	421.6	428.0
167.5°	391.6	390.6	391.4	394.5	396.8	400.4	405.1	409.7	412.0	415.7	420.4
170°	395.5	393.9	394.7	397.1	398.8	400.4	404.5	407.7	409.4	411.8	415.9
172.5°	398.1	397.1	397.3	399.1	400.1	401.0	404.5	407.1	407.4	408.5	411.3
175°	401.2	400.4	399.6	401.2	401.2	402.0	403.7	405.3	404.5	404.5	406.1
177.5°	402.7	402.0	401.4	402.0	402.0	402.0	402.7	404.0	402.7	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331990-930

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	989.0	990.6	992.1	992.8	992.6	992.5	992.3	992.1
5°	983.8	985.7	987.7	988.4	988.0	987.7	987.2	986.8
7.5°	973.4	975.1	976.8	977.5	977.3	977.1	976.8	976.6
10°	963.8	965.5	967.2	967.9	967.5	967.1	966.8	966.4
12.5°	953.3	954.6	955.9	956.3	956.1	955.9	955.7	955.4
15°	934.4	935.9	937.4	937.6	936.5	935.3	934.3	933.1
17.5°	910.4	911.5	912.6	912.9	912.5	912.1	911.7	911.3
20°	892.8	893.5	894.3	894.4	893.8	893.2	892.7	892.1
22.5°	874.0	874.7	875.2	875.1	874.5	873.8	873.0	872.3
25°	842.9	843.2	843.3	843.2	842.6	842.0	841.5	840.9
27.5°	809.9	810.1	810.2	809.9	809.3	808.5	807.8	807.1
30°	787.1	787.1	787.1	786.4	785.1	783.7	782.4	781.1
32.5°	763.1	762.1	761.0	760.1	759.4	758.6	757.9	757.2
35°	724.2	723.1	721.9	720.9	719.9	719.0	718.0	717.1
37.5°	684.0	682.6	681.3	680.3	679.6	679.1	678.4	677.8
40°	657.7	656.2	654.7	653.5	652.8	652.0	651.3	650.5
42.5°	630.4	628.8	627.4	626.2	625.5	624.7	623.9	623.2
45°	589.6	587.3	585.1	583.4	582.5	581.6	580.6	579.7
47.5°	546.7	544.5	542.2	540.6	539.8	539.0	538.2	537.3
50°	518.3	516.2	514.1	512.5	511.4	510.2	509.1	507.9
52.5°	489.5	487.7	485.9	484.5	483.4	482.2	481.1	480.0
55°	445.7	443.6	441.6	440.0	439.0	438.1	437.2	436.3
57.5°	402.6	400.8	398.9	397.5	396.3	395.3	394.1	393.1
60°	372.2	370.5	368.8	367.5	366.5	365.6	364.6	363.7
62.5°	342.8	341.1	339.4	338.3	337.6	337.0	336.3	335.7
65°	299.1	297.7	296.1	295.1	294.5	293.9	293.3	292.8
67.5°	255.8	254.5	253.2	252.1	251.4	250.5	249.7	248.9
70°	227.9	226.5	225.2	224.0	223.1	222.2	221.2	220.2
72.5°	199.4	198.3	197.1	196.2	195.8	195.3	194.8	194.3
75°	158.6	157.7	156.7	156.0	155.4	154.8	154.3	153.7
77.5°	120.4	119.8	119.1	118.9	118.9	118.9	118.9	118.9
80°	96.1	95.9	95.7	95.6	95.6	95.6	95.6	95.6
82.5°	73.9	73.6	73.2	73.0	72.9	72.7	72.6	72.4
85°	41.9	41.6	41.2	41.0	41.0	41.0	41.0	41.0
87.5°	18.8	18.8	18.8	19.1	18.9	19.1	19.2	19.1
90°	20.4	21.2	22.0	23.6	22.7	23.6	24.4	23.6
92.5°	68.5	54.4	48.0	43.8	42.3	39.9	40.7	39.2
95°	292.9	198.6	155.5	126.1	110.7	103.4	97.7	94.4
97.5°	730.3	585.0	480.0	382.6	322.6	286.0	264.0	257.0
100°	959.5	893.6	798.3	682.8	600.6	541.2	509.5	510.3
102.5°	1035.7	1033.6	978.0	904.8	840.8	793.8	767.3	748.5
105°	1057.9	1139.4	1154.8	1133.7	1096.2	1065.3	1039.3	1035.2
107.5°	993.8	1126.0	1197.3	1226.3	1226.9	1216.5	1207.7	1200.2
110°	932.6	1082.4	1184.9	1241.9	1264.7	1271.2	1269.6	1268.0



TEST NUMBER: P331990-930

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	872.0	1025.1	1140.0	1213.2	1254.9	1275.0	1281.2	1281.6
115°	791.8	933.4	1053.0	1141.7	1202.8	1238.6	1254.9	1259.0
117.5°	733.8	856.0	963.4	1053.4	1117.0	1158.1	1181.5	1187.0
120°	703.1	813.0	910.7	992.9	1057.1	1102.7	1122.3	1127.2
122.5°	679.1	778.5	869.0	945.3	1002.5	1043.5	1064.9	1071.1
125°	647.0	735.7	813.8	878.9	931.0	966.8	987.2	992.9
127.5°	619.0	698.1	768.6	827.8	874.2	904.8	923.2	928.4
130°	601.4	674.7	740.5	795.9	839.0	868.4	885.4	891.9
132.5°	585.1	652.5	713.9	766.6	807.1	836.4	851.6	856.1
135°	563.1	620.9	673.8	720.2	760.1	784.5	799.2	804.9
137.5°	543.2	590.5	636.1	676.3	709.8	734.6	746.9	750.6
140°	531.4	572.9	612.0	647.0	677.9	700.7	713.7	712.9
142.5°	520.3	556.0	589.9	620.3	646.7	666.8	678.6	677.8
145°	507.0	533.9	559.9	583.5	603.8	620.9	627.5	629.1
147.5°	496.1	517.4	538.4	555.2	570.6	582.2	588.4	589.1
150°	488.3	507.0	524.1	539.6	551.8	560.7	565.6	565.6
152.5°	481.1	497.3	512.4	525.2	534.8	543.2	546.1	546.1
155°	470.3	483.4	495.6	505.4	512.7	519.2	520.8	521.6
157.5°	459.0	469.9	479.3	487.0	493.3	498.2	499.5	499.4
160°	452.5	461.5	469.5	475.2	480.9	485.8	485.8	485.0
162.5°	444.7	452.3	459.8	464.9	468.6	472.8	472.8	472.0
165°	434.6	439.4	445.2	449.2	452.5	455.8	454.9	454.9
167.5°	425.7	429.5	432.8	435.7	437.2	439.4	438.6	438.6
170°	420.0	422.4	425.6	427.2	428.0	429.7	428.8	428.8
172.5°	414.7	416.5	419.1	420.1	420.3	421.9	420.4	419.8
175°	407.7	408.5	410.2	410.2	410.2	411.0	410.2	409.4
177.5°	403.3	404.0	404.6	404.6	404.0	404.6	403.3	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

(END OF REPORT)