

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906088

Luminaire Tested: DFN2DIP-PN4F0-100D040US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906088
REPORT IS A COMBINATION OF REPORTS P899621 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-100D040US835-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13440.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 131.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906088

CATALOG NUMBER: DFN2DIP-PN4F0-100D040US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906088

CATALOG NUMBER: DFN2DIP-PN4F0-100D040US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78
1	103	99	95	91	98	94	90	87	85	82	80	77	74	72	69	67	66
2	94	86	80	74	89	82	76	71	74	70	66	67	64	61	61	58	55
3	86	76	68	62	81	72	65	60	66	60	55	59	55	51	54	50	47
4	79	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	41
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	36
6	67	54	46	40	63	52	44	38	47	41	36	43	38	34	39	35	31
7	62	49	41	35	58	47	39	34	43	37	32	39	34	30	36	31	28
8	57	45	37	31	54	43	35	30	39	33	28	36	31	27	33	29	25
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	31	26	23
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2840	2840	2840
5°	2845	2801	2820
10°	2822	2764	2782
15°	2780	2719	2723
20°	2724	2656	2663
25°	2668	2581	2593
30°	2599	2511	2503
35°	2532	2428	2409
40°	2451	2345	2319
45°	2369	2261	2227
50°	2281	2173	2121
55°	2187	2072	2023
60°	2082	1951	1911
65°	1968	1827	1779
70°	1821	1675	1637
75°	1619	1493	1507
80°	1375	1262	1257
85°	994	861	841

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2369 cd/sqm

TEST NUMBER: P906088

CATALOG NUMBER: DFN2DIP-PN4F0-100D040US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.2	2.7
10°-20°	1030.4	7.7
20°-30°	1514.3	11.3
30°-40°	1758.8	13.1
40°-50°	1756.6	13.1
50°-60°	1531.7	11.4
60°-70°	1132.3	8.4
70°-80°	640.6	4.8
80°-90°	172.7	1.3
90°-100°	78.3	0.6
100°-110°	248.7	1.9
110°-120°	425.6	3.2
120°-130°	559.8	4.2
130°-140°	628.3	4.7
140°-150°	616.2	4.6
150°-160°	516.9	3.8
160°-170°	342.8	2.6
170°-180°	119.8	0.9
0°-30°	2911.0	21.7
0°-40°	4669.7	34.7
0°-60°	7958.0	59.2
0°-90°	9903.6	73.7
90°-120°	752.7	5.6
90°-150°	2556.9	19.0
90°-180°	3536.0	26.3
0°-180°	13440.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3891	3891	3891	3891	3891	
5°	3891	3876	3835	3865	3858	369
15°	3704	3682	3633	3648	3630	1043
25°	3352	3323	3259	3266	3259	1543
35°	2892	2855	2795	2772	2754	1806
45°	2354	2327	2271	2230	2215	1816
55°	1781	1759	1714	1669	1650	1592
65°	1201	1179	1141	1108	1089	1188
75°	628	621	602	580	588	671
85°	153	150	146	135	131	171
90°	1	14	37	35	36	13
95°	56	66	68	68	66	62
105°	230	233	235	237	237	242
115°	427	433	431	430	427	422
125°	621	631	628	624	623	555
135°	804	815	818	816	814	621
145°	976	983	989	990	986	610
155°	1116	1119	1122	1127	1124	513
165°	1214	1212	1212	1220	1215	342
175°	1263	1260	1257	1265	1259	120
180°	1265	1265	1265	1265	1265	

TEST NUMBER: P906088

CATALOG NUMBER: DFN2DIP-PN4F0-100D040US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3891.1	3891.1	3891.1	3891.1	3891.1
2.5°	3913.7	3895.0	3853.7	3891.1	3883.9
5°	3891.1	3876.4	3835.1	3864.9	3857.7
7.5°	3864.9	3842.6	3801.3	3831.5	3824.0
10°	3824.0	3797.8	3752.9	3782.7	3771.6
12.5°	3767.6	3745.4	3700.5	3719.2	3711.6
15°	3704.1	3681.9	3633.0	3648.1	3629.5
17.5°	3625.5	3603.3	3554.4	3573.1	3554.4
20°	3539.3	3517.1	3464.7	3475.8	3461.1
22.5°	3453.6	3419.9	3371.0	3371.0	3363.5
25°	3352.4	3322.6	3259.1	3266.2	3259.1
27.5°	3240.0	3213.8	3165.4	3154.3	3135.6
30°	3128.1	3097.9	3041.9	3030.8	3015.7
32.5°	3008.2	2986.0	2926.0	2903.4	2888.3
35°	2892.3	2855.0	2795.0	2772.4	2753.7
37.5°	2761.3	2727.5	2667.6	2641.4	2622.7
40°	2626.7	2596.5	2536.6	2503.3	2488.2
42.5°	2495.7	2465.5	2406.0	2368.3	2346.1
45°	2353.6	2327.4	2271.0	2230.1	2215.1
47.5°	2215.1	2188.9	2128.9	2087.6	2065.4
50°	2069.0	2050.3	1997.9	1945.5	1926.9
52.5°	1926.9	1900.7	1852.2	1811.0	1784.8
55°	1781.2	1758.6	1713.7	1668.8	1650.2
57.5°	1635.1	1616.4	1567.6	1522.8	1507.7
60°	1489.0	1474.3	1421.9	1380.6	1369.5
62.5°	1346.9	1320.7	1283.4	1246.1	1231.0
65°	1201.2	1178.6	1141.3	1107.5	1088.9
67.5°	1051.6	1032.5	999.2	973.0	957.9
70°	913.0	897.9	864.2	838.0	823.3
72.5°	770.9	755.8	737.2	711.0	699.8
75°	628.4	621.3	602.2	580.0	587.5
77.5°	501.4	486.3	478.7	467.6	456.5
80°	374.3	370.4	362.8	351.7	344.2
82.5°	254.5	254.5	250.9	235.8	235.8
85°	153.2	149.7	146.1	134.6	131.0
87.5°	67.5	59.9	52.4	41.3	37.3
90°	1.1	13.7	37.4	35.1	36.2
92.5°	23.6	32.0	33.2	34.3	34.3
95°	55.7	66.4	68.3	68.3	66.4
97.5°	92.7	102.6	106.8	106.8	106.8
100°	135.4	144.2	147.2	147.2	146.1
102.5°	180.4	186.9	191.1	192.2	191.1
105°	229.6	232.6	234.9	236.8	236.8
107.5°	278.4	283.0	283.0	283.7	278.4
110°	325.7	331.8	331.8	331.8	328.8

TEST NUMBER: P906088

CATALOG NUMBER: DFN2DIP-PN4F0-100D040US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.8	383.3	382.1	379.1	376.8
115°	427.1	433.3	431.3	430.2	427.1
117.5°	477.1	485.5	480.2	477.1	474.1
120°	527.5	535.8	527.5	527.5	524.0
122.5°	573.2	583.9	578.6	575.5	573.2
125°	621.3	630.8	627.8	624.3	623.2
127.5°	668.2	680.0	675.8	671.2	668.2
130°	712.0	725.8	723.9	721.6	717.4
132.5°	761.2	771.9	772.7	767.3	764.3
135°	803.6	815.4	817.7	816.5	813.5
137.5°	850.9	860.4	862.3	861.5	857.0
140°	892.4	902.0	907.3	907.3	903.1
142.5°	935.2	944.7	947.7	948.9	944.7
145°	975.6	983.2	989.3	990.5	986.3
147.5°	1011.8	1021.3	1025.9	1027.8	1023.6
150°	1049.2	1055.7	1059.9	1063.3	1059.9
152.5°	1082.4	1088.8	1094.2	1098.4	1094.2
155°	1115.5	1118.6	1122.0	1127.4	1123.9
157.5°	1144.2	1146.4	1148.3	1156.0	1150.6
160°	1169.7	1172.0	1173.1	1179.6	1175.0
162.5°	1193.3	1193.3	1194.5	1201.7	1196.4
165°	1213.6	1212.4	1212.4	1220.0	1214.7
167.5°	1231.9	1228.4	1228.4	1236.1	1230.7
170°	1245.6	1242.5	1241.4	1249.0	1242.5
172.5°	1255.1	1252.1	1250.9	1258.6	1252.1
175°	1262.8	1259.7	1257.4	1265.0	1258.6
177.5°	1267.0	1263.9	1261.6	1268.1	1261.6
180°	1265.0	1265.0	1265.0	1265.0	1265.0

TEST NUMBER: P906088

CATALOG NUMBER: DFN2DIP-PN4F0-100D040US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.85	13.98	13.58	14.72	15.61	12.41	13.54	13.14	14.28	15.17
	3H	14.54	15.55	15.27	16.30	17.22	14.05	15.06	14.79	15.82	16.73
	4H	15.14	16.09	15.89	16.85	17.78	14.65	15.60	15.40	16.37	17.30
	6H	15.55	16.43	16.32	17.21	18.15	15.06	15.94	15.83	16.71	17.66
	8H	15.67	16.50	16.44	17.30	18.24	15.17	16.01	15.95	16.80	17.75
	12H	15.72	16.52	16.51	17.31	18.28	15.22	16.02	16.01	16.81	17.78
4H	2H	13.35	14.30	14.10	15.06	15.99	12.99	13.95	13.75	14.71	15.64
	3H	15.24	16.03	16.01	16.83	17.78	14.84	15.63	15.61	16.43	17.38
	4H	15.97	16.69	16.75	17.49	18.47	15.55	16.27	16.33	17.07	18.05
	6H	16.50	17.13	17.30	17.95	18.93	16.07	16.70	16.88	17.52	18.51
	8H	16.66	17.24	17.46	18.06	19.06	16.23	16.81	17.03	17.63	18.63
	12H	16.74	17.27	17.57	18.11	19.11	16.30	16.83	17.13	17.67	18.67
8H	4H	16.18	16.77	16.99	17.59	18.58	15.81	16.40	16.62	17.22	18.21
	6H	16.83	17.32	17.67	18.18	19.17	16.45	16.94	17.29	17.80	18.80
	8H	17.05	17.49	17.90	18.34	19.36	16.67	17.10	17.52	17.96	18.97
	12H	17.20	17.58	18.05	18.43	19.50	16.80	17.18	17.65	18.03	19.10
12H	4H	16.18	16.71	17.01	17.55	18.55	15.82	16.35	16.65	17.19	18.19
	6H	16.86	17.29	17.71	18.15	19.16	16.50	16.93	17.34	17.79	18.80
	8H	17.12	17.50	17.97	18.35	19.42	16.75	17.13	17.60	17.98	19.04