

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922696

Luminaire Tested: DFN2DIP-SQ2F0-080D060US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922696
REPORT IS A COMBINATION OF REPORTS P899817 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D060US940-FLLFLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11797.4 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922696

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922696

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89		77	77	77		65
1	100	96	92	88	93	89	86	83	78	75	73		67	66	64		58
2	91	84	77	72	85	78	73	68	68	64	61		59	56	53		51
3	83	73	66	60	77	69	62	57	60	55	51		52	48	45		45
4	76	65	57	51	71	61	54	48	54	48	43		47	42	39		40
5	70	58	50	44	65	55	47	42	48	42	38		42	37	34		36
6	64	52	44	38	60	49	42	36	43	37	33		38	33	29		33
7	60	47	39	33	56	44	37	32	39	33	29		35	30	26		30
8	55	43	35	30	52	40	33	28	36	30	26		32	27	23		28
9	52	39	32	26	48	37	30	25	33	27	23		29	24	21		26
10	48	36	29	24	45	34	27	23	30	25	21		27	22	19		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6103	6103	6103
5°	6103	6005	6051
10°	6043	5911	5960
15°	5943	5801	5824
20°	5813	5652	5684
25°	5683	5478	5524
30°	5522	5314	5323
35°	5368	5123	5111
40°	5182	4930	4909
45°	4995	4735	4701
50°	4791	4530	4462
55°	4576	4295	4239
60°	4332	4016	3985
65°	4065	3725	3685
70°	3725	3371	3359
75°	3259	2947	3047
80°	2692	2406	2474
85°	1818	1519	1555

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4995 cd/sqm

TEST NUMBER: P922696

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	2.2
10°-20°	735.1	6.2
20°-30°	1080.3	9.2
30°-40°	1254.7	10.6
40°-50°	1253.1	10.6
50°-60°	1092.7	9.3
60°-70°	807.7	6.8
70°-80°	457.0	3.9
80°-90°	125.4	1.1
90°-100°	104.7	0.9
100°-110°	332.7	2.8
110°-120°	569.3	4.8
120°-130°	748.8	6.3
130°-140°	840.5	7.1
140°-150°	824.2	7.0
150°-160°	691.4	5.9
160°-170°	458.5	3.9
170°-180°	160.3	1.4
0°-30°	2076.6	17.6
0°-40°	3331.3	28.2
0°-60°	5677.0	48.1
0°-90°	7067.2	59.9
90°-120°	1006.7	8.5
90°-150°	3420.1	29.0
90°-180°	4730.0	40.1
0°-180°	11797.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2776	2776	2776	2776	2776	
5°	2776	2765	2736	2757	2752	263
15°	2642	2626	2592	2602	2589	744
25°	2392	2370	2325	2330	2325	1100
35°	2063	2037	1994	1978	1964	1288
45°	1679	1660	1620	1591	1580	1296
55°	1271	1254	1222	1190	1177	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	122
90°	2	18	50	47	48	11
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	

TEST NUMBER: P922696

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2775.7	2775.7	2775.7	2775.7	2775.7
2.5°	2791.9	2778.6	2749.1	2775.7	2770.6
5°	2775.7	2765.3	2735.9	2757.1	2752.0
7.5°	2757.1	2741.2	2711.8	2733.3	2727.9
10°	2727.9	2709.2	2677.2	2698.4	2690.6
12.5°	2687.7	2671.8	2639.8	2653.1	2647.8
15°	2642.4	2626.5	2591.7	2602.5	2589.2
17.5°	2586.3	2570.4	2535.6	2549.0	2535.6
20°	2524.9	2509.0	2471.6	2479.6	2469.1
22.5°	2463.7	2439.6	2404.8	2404.8	2399.4
25°	2391.5	2370.3	2325.0	2330.0	2325.0
27.5°	2311.3	2292.7	2258.1	2250.1	2236.9
30°	2231.5	2209.9	2170.1	2162.1	2151.3
32.5°	2146.0	2130.1	2087.3	2071.2	2060.5
35°	2063.2	2036.7	1993.9	1977.7	1964.4
37.5°	1969.8	1945.7	1903.0	1884.3	1871.0
40°	1873.8	1852.3	1809.5	1785.7	1774.9
42.5°	1780.4	1758.8	1716.4	1689.4	1673.7
45°	1679.0	1660.3	1620.1	1590.9	1580.2
47.5°	1580.2	1561.5	1518.7	1489.2	1473.4
50°	1476.0	1462.7	1425.2	1387.9	1374.6
52.5°	1374.6	1355.8	1321.3	1291.9	1273.2
55°	1270.6	1254.5	1222.5	1190.5	1177.1
57.5°	1166.4	1153.2	1118.3	1086.3	1075.5
60°	1062.2	1051.8	1014.3	984.9	977.0
62.5°	960.8	942.2	915.5	888.9	878.2
65°	856.9	840.8	814.1	790.1	776.8
67.5°	750.1	736.6	712.7	694.1	683.3
70°	651.3	640.5	616.5	597.8	587.3
72.5°	549.9	539.2	525.8	507.2	499.3
75°	448.3	443.2	429.6	413.8	419.1
77.5°	357.7	346.9	341.5	333.6	325.7
80°	267.1	264.2	258.9	250.9	245.5
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.3	106.7	104.2	96.0	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7

TEST NUMBER: P922696

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1

TEST NUMBER: P922696

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.31	15.27	15.17	16.15	17.28	13.86	14.82	14.73	15.71	16.83
	3H	15.96	16.82	16.84	17.71	18.86	15.47	16.33	16.34	17.22	18.37
	4H	16.53	17.35	17.43	18.25	19.41	16.04	16.85	16.94	17.76	18.92
	6H	16.92	17.67	17.83	18.58	19.76	16.42	17.17	17.33	18.08	19.26
	8H	17.02	17.74	17.94	18.67	19.84	16.52	17.24	17.44	18.17	19.34
	12H	17.07	17.75	17.99	18.67	19.87	16.56	17.24	17.48	18.16	19.36
4H	2H	14.77	15.58	15.67	16.49	17.64	14.41	15.23	15.31	16.13	17.29
	3H	16.62	17.30	17.53	18.23	19.41	16.21	16.89	17.12	17.83	19.00
	4H	17.32	17.94	18.25	18.87	20.07	16.90	17.52	17.82	18.45	19.65
	6H	17.83	18.36	18.76	19.31	20.51	17.39	17.93	18.33	18.88	20.08
	8H	17.97	18.47	18.91	19.42	20.63	17.53	18.03	18.47	18.98	20.19
	12H	18.04	18.49	18.99	19.45	20.67	17.59	18.04	18.55	19.01	20.22
8H	4H	17.52	18.02	18.45	18.96	20.18	17.14	17.64	18.08	18.59	19.80
	6H	18.13	18.54	19.09	19.53	20.74	17.74	18.16	18.71	19.15	20.36
	8H	18.34	18.70	19.31	19.68	20.91	17.94	18.31	18.92	19.29	20.52
	12H	18.46	18.78	19.44	19.75	21.03	18.05	18.37	19.03	19.34	20.62
12H	4H	17.50	17.95	18.46	18.92	20.14	17.13	17.58	18.09	18.55	19.77
	6H	18.15	18.52	19.13	19.50	20.73	17.78	18.15	18.75	19.13	20.36
	8H	18.39	18.71	19.36	19.68	20.96	18.00	18.33	18.98	19.30	20.58