

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906412

Luminaire Tested: DFN2DIP-SQ3F0-060D040US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906412
REPORT IS A COMBINATION OF REPORTS P899865 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-060D040US835-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9480.0 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 83.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906412

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906412

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90		79	79	79		68
1	101	96	92	89	94	90	87	84	79	77	74		69	67	66		60
2	92	84	78	72	86	79	73	69	70	65	62		61	58	55		53
3	84	74	66	60	78	70	63	58	61	56	52		54	50	46		47
4	77	66	57	51	71	62	54	49	55	49	44		48	43	40		42
5	70	58	50	44	66	55	48	42	49	43	38		43	38	35		38
6	65	53	44	38	61	50	42	37	44	38	33		39	34	30		34
7	60	48	39	34	56	45	38	32	40	34	30		36	31	27		31
8	56	43	35	30	52	41	34	29	37	31	26		33	28	24		29
9	52	40	32	27	49	38	30	26	34	28	24		30	25	22		27
10	49	36	29	24	46	35	28	23	31	25	21		28	23	20		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2675	2675	2675
5°	2678	2636	2655
10°	2654	2599	2618
15°	2613	2554	2561
20°	2559	2493	2502
25°	2505	2420	2435
30°	2437	2352	2350
35°	2373	2272	2259
40°	2294	2192	2173
45°	2216	2111	2085
50°	2130	2026	1984
55°	2040	1927	1890
60°	1938	1811	1782
65°	1826	1689	1655
70°	1684	1542	1519
75°	1488	1365	1391
80°	1251	1139	1150
85°	880	754	753

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2216 cd/sqm

TEST NUMBER: P906412

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	2.3
10°-20°	618.3	6.5
20°-30°	908.6	9.6
30°-40°	1055.3	11.1
40°-50°	1054.0	11.1
50°-60°	919.0	9.7
60°-70°	679.4	7.2
70°-80°	384.4	4.1
80°-90°	105.0	1.1
90°-100°	78.3	0.8
100°-110°	248.7	2.6
110°-120°	425.6	4.5
120°-130°	559.8	5.9
130°-140°	628.3	6.6
140°-150°	616.2	6.5
150°-160°	516.9	5.5
160°-170°	342.8	3.6
170°-180°	119.8	1.3
0°-30°	1746.6	18.4
0°-40°	2801.8	29.6
0°-60°	4774.8	50.4
0°-90°	5943.6	62.7
90°-120°	752.7	7.9
90°-150°	2556.9	27.0
90°-180°	3536.0	37.3
0°-180°	9480.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	103
90°	1	14	37	35	36	9
95°	56	66	68	68	66	62
105°	230	233	235	237	237	242
115°	427	433	431	430	427	422
125°	621	631	628	624	623	555
135°	804	815	818	816	814	621
145°	976	983	989	990	986	610
155°	1116	1119	1122	1127	1124	513
165°	1214	1212	1212	1220	1215	342
175°	1263	1260	1257	1265	1259	120
180°	1265	1265	1265	1265	1265	

TEST NUMBER: P906412

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	1.1	13.7	37.4	35.1	36.2
92.5°	23.6	32.0	33.2	34.3	34.3
95°	55.7	66.4	68.3	68.3	66.4
97.5°	92.7	102.6	106.8	106.8	106.8
100°	135.4	144.2	147.2	147.2	146.1
102.5°	180.4	186.9	191.1	192.2	191.1
105°	229.6	232.6	234.9	236.8	236.8
107.5°	278.4	283.0	283.0	283.7	278.4
110°	325.7	331.8	331.8	331.8	328.8

TEST NUMBER: P906412

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.8	383.3	382.1	379.1	376.8
115°	427.1	433.3	431.3	430.2	427.1
117.5°	477.1	485.5	480.2	477.1	474.1
120°	527.5	535.8	527.5	527.5	524.0
122.5°	573.2	583.9	578.6	575.5	573.2
125°	621.3	630.8	627.8	624.3	623.2
127.5°	668.2	680.0	675.8	671.2	668.2
130°	712.0	725.8	723.9	721.6	717.4
132.5°	761.2	771.9	772.7	767.3	764.3
135°	803.6	815.4	817.7	816.5	813.5
137.5°	850.9	860.4	862.3	861.5	857.0
140°	892.4	902.0	907.3	907.3	903.1
142.5°	935.2	944.7	947.7	948.9	944.7
145°	975.6	983.2	989.3	990.5	986.3
147.5°	1011.8	1021.3	1025.9	1027.8	1023.6
150°	1049.2	1055.7	1059.9	1063.3	1059.9
152.5°	1082.4	1088.8	1094.2	1098.4	1094.2
155°	1115.5	1118.6	1122.0	1127.4	1123.9
157.5°	1144.2	1146.4	1148.3	1156.0	1150.6
160°	1169.7	1172.0	1173.1	1179.6	1175.0
162.5°	1193.3	1193.3	1194.5	1201.7	1196.4
165°	1213.6	1212.4	1212.4	1220.0	1214.7
167.5°	1231.9	1228.4	1228.4	1236.1	1230.7
170°	1245.6	1242.5	1241.4	1249.0	1242.5
172.5°	1255.1	1252.1	1250.9	1258.6	1252.1
175°	1262.8	1259.7	1257.4	1265.0	1258.6
177.5°	1267.0	1263.9	1261.6	1268.1	1261.6
180°	1265.0	1265.0	1265.0	1265.0	1265.0

TEST NUMBER: P906412

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.75	12.74	12.59	13.60	14.68	11.31	12.29	12.15	13.16	14.23
	3H	13.42	14.30	14.27	15.18	16.28	12.93	13.81	13.78	14.69	15.79
	4H	14.01	14.85	14.88	15.72	16.84	13.51	14.35	14.38	15.23	16.34
	6H	14.41	15.18	15.29	16.07	17.20	13.91	14.68	14.79	15.57	16.70
	8H	14.52	15.25	15.41	16.16	17.28	14.01	14.75	14.90	15.65	16.78
	12H	14.57	15.27	15.46	16.17	17.32	14.06	14.76	14.95	15.66	16.81
4H	2H	12.22	13.06	13.10	13.94	15.06	11.87	12.71	12.74	13.59	14.70
	3H	14.10	14.80	14.98	15.71	16.84	13.69	14.39	14.57	15.30	16.43
	4H	14.81	15.45	15.71	16.36	17.51	14.39	15.03	15.28	15.93	17.09
	6H	15.33	15.88	16.24	16.81	17.97	14.90	15.45	15.81	16.38	17.54
	8H	15.48	15.99	16.39	16.92	18.09	15.04	15.56	15.96	16.48	17.65
	12H	15.56	16.02	16.49	16.96	18.14	15.11	15.57	16.04	16.52	17.69
8H	4H	15.01	15.53	15.93	16.45	17.63	14.64	15.15	15.55	16.08	17.25
	6H	15.64	16.07	16.58	17.04	18.21	15.26	15.69	16.20	16.65	17.82
	8H	15.86	16.24	16.81	17.20	18.39	15.47	15.85	16.42	16.81	17.99
	12H	16.00	16.33	16.95	17.28	18.52	15.59	15.92	16.54	16.87	18.11
12H	4H	15.00	15.47	15.94	16.41	17.59	14.64	15.10	15.57	16.04	17.22
	6H	15.67	16.05	16.62	17.01	18.20	15.30	15.68	16.25	16.64	17.83
	8H	15.92	16.25	16.87	17.20	18.44	15.54	15.87	16.49	16.82	18.06