

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332299-935

Luminaire Tested: **S123RDIP-S560D1195U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332299-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5558.9 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.23
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332299-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P332299-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74		57	57	57		41
1	94	90	86	83	85	81	78	75	65	63	61		50	49	47		36
2	86	79	73	68	77	71	66	62	57	54	51		44	42	40		32
3	78	69	62	57	70	63	57	52	51	46	43		39	36	34		29
4	72	61	54	48	65	56	49	44	45	40	37		35	32	29		26
5	66	55	47	41	59	50	43	38	40	35	32		31	28	25		23
6	61	49	41	36	55	45	38	33	36	31	28		28	25	22		21
7	56	44	37	31	50	40	34	29	33	28	24		26	22	20		19
8	52	40	33	28	47	37	30	25	30	25	21		24	20	18		18
9	48	37	29	24	44	33	27	23	27	23	19		22	18	16		16
10	45	33	26	22	41	31	24	20	25	20	17		20	17	14		15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8753	8753	8753
5°	8787	8666	8715
10°	8737	8557	8528
15°	8643	8357	8269
20°	8514	8107	7918
25°	8381	7826	7574
30°	8206	7501	7091
35°	8025	7176	6646
40°	7859	6794	6097
45°	7640	6416	5602
50°	7400	5987	5047
55°	7156	5495	4530
60°	6928	4969	3961
65°	6635	4401	3393
70°	6266	3695	2738
75°	5731	2907	2578
80°	5114	2579	2368
85°	4323	2272	2112

TEST NUMBER: P332299-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	1.4
10°-20°	212.5	3.8
20°-30°	305.9	5.5
30°-40°	344.6	6.2
40°-50°	329.7	5.9
50°-60°	270.0	4.9
60°-70°	182.2	3.3
70°-80°	91.6	1.6
80°-90°	28.1	0.5
90°-100°	275.0	4.9
100°-110°	778.7	14.0
110°-120°	766.1	13.8
120°-130°	611.0	11.0
130°-140°	481.8	8.7
140°-150°	359.6	6.5
150°-160°	250.6	4.5
160°-170°	147.2	2.6
170°-180°	47.9	0.9
0°-30°	594.8	10.7
0°-40°	939.4	16.9
0°-60°	1539.1	27.7
0°-90°	1841.0	33.1
90°-120°	1819.8	32.7
90°-150°	3272.2	58.9
90°-180°	3718.0	66.9
0°-180°	5558.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	813	813	813	813	813	
5°	813	810	802	808	807	77
15°	776	768	750	747	742	218
25°	706	688	659	645	638	324
35°	611	586	546	519	506	382
45°	502	471	422	385	368	387
55°	381	348	293	256	241	342
65°	260	223	173	142	133	258
75°	138	106	70	64	62	147
85°	35	21	18	17	17	39
90°	2	12	25	28	29	4
95°	34	110	593	173	116	37
105°	116	172	804	1406	1272	123
115°	205	256	615	1349	1548	203
125°	285	337	574	1040	1220	253
135°	334	399	566	857	989	258
145°	381	437	559	703	773	239
155°	433	467	541	615	641	199
165°	473	487	518	550	559	133
175°	493	494	497	504	503	47
180°	494	494	494	494	494	

TEST NUMBER: P332299-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	815.9	815.4	814.9	814.4	814.0	813.0	811.7	810.2	808.8	807.4	808.7
5°	813.2	812.5	811.8	811.1	810.3	809.1	807.3	805.6	803.7	802.0	803.3
7.5°	805.7	804.9	804.1	803.3	802.5	801.0	798.7	796.4	794.1	791.9	792.6
10°	799.4	798.3	797.3	796.3	795.3	793.4	790.8	788.2	785.5	782.9	783.0
12.5°	790.4	789.3	788.1	787.0	785.8	783.7	780.4	777.2	774.0	770.8	770.7
15°	775.6	774.0	772.4	770.8	769.2	766.3	762.2	758.1	754.0	749.9	749.2
17.5°	757.0	755.2	753.3	751.4	749.5	746.0	740.7	735.6	730.3	725.1	723.6
20°	743.3	741.0	738.7	736.2	733.9	730.0	724.4	718.8	713.3	707.7	705.8
22.5°	728.0	725.3	722.6	719.9	717.2	712.9	707.0	701.0	695.2	689.2	686.8
25°	705.7	702.1	698.4	694.7	691.0	685.9	679.1	672.4	665.6	658.9	655.8
27.5°	678.6	674.6	670.5	666.5	662.5	656.7	649.2	641.7	634.2	626.7	622.4
30°	660.2	655.8	651.4	647.0	642.7	636.3	628.1	619.9	611.7	603.5	598.5
32.5°	641.7	636.8	631.8	626.8	621.8	615.0	606.3	597.6	588.9	580.2	574.8
35°	610.7	605.5	600.2	595.0	589.6	582.5	573.3	564.3	555.2	546.1	539.8
37.5°	579.4	573.5	567.7	561.7	555.9	548.1	538.4	528.7	519.0	509.3	502.1
40°	559.3	552.8	546.4	539.9	533.5	525.0	514.7	504.3	493.9	483.5	475.8
42.5°	536.6	530.1	523.7	517.3	510.8	502.2	491.5	480.7	469.9	459.2	450.8
45°	501.9	495.3	488.7	482.2	475.5	466.6	455.3	444.0	432.7	421.5	413.1
47.5°	467.2	459.9	452.7	445.5	438.2	429.0	417.7	406.4	395.1	383.8	374.8
50°	441.9	435.0	428.1	421.2	414.3	404.9	393.0	381.3	369.4	357.5	348.4
52.5°	419.2	411.7	404.2	396.7	389.3	379.7	367.9	356.2	344.4	332.7	323.2
55°	381.3	374.0	366.9	359.6	352.5	342.7	330.2	317.8	305.3	292.8	284.3
57.5°	346.1	338.3	330.5	322.6	314.8	304.6	292.1	279.7	267.1	254.6	246.6
60°	321.8	313.8	305.7	297.6	289.6	279.5	267.3	255.2	243.0	230.8	222.9
62.5°	297.6	289.6	281.5	273.4	265.4	255.2	243.1	230.9	218.7	206.6	199.1
65°	260.5	252.4	244.4	236.3	228.3	218.5	207.1	195.7	184.3	172.8	165.7
67.5°	223.4	215.3	207.2	199.0	190.9	181.3	170.3	159.4	148.4	137.4	132.1
70°	199.1	191.2	183.4	175.5	167.6	158.4	148.2	137.9	127.7	117.4	112.3
72.5°	174.9	167.1	159.3	151.5	143.7	135.2	125.9	116.5	107.2	97.9	93.7
75°	137.8	130.8	123.8	116.8	109.7	102.1	94.1	86.0	78.0	69.9	68.4
77.5°	104.1	97.7	91.4	85.0	78.6	72.8	67.7	62.5	57.3	52.1	51.3
80°	82.5	76.5	70.4	64.4	58.4	53.9	50.8	47.7	44.6	41.6	41.1
82.5°	61.9	56.7	51.5	46.3	41.1	37.8	36.3	35.0	33.5	32.0	31.6
85°	35.0	31.8	28.5	25.3	22.0	20.2	19.8	19.4	18.9	18.4	18.2
87.5°	13.1	12.1	11.3	10.6	9.7	9.5	10.1	10.7	11.3	11.9	11.5
90°	2.0	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0
92.5°	12.4	18.4	26.8	34.6	43.0	57.9	84.0	127.1	169.3	153.9	116.1
95°	34.0	37.0	48.0	65.0	91.0	130.0	215.1	364.1	528.2	593.2	481.1
97.5°	58.0	59.0	67.6	82.4	108.1	150.2	231.5	399.5	673.0	919.3	983.5
100°	74.0	75.0	82.1	96.0	120.0	159.0	229.1	377.1	640.2	947.4	1144.4
102.5°	90.8	92.6	98.8	112.0	133.6	169.4	232.3	357.9	592.2	895.4	1152.4
105°	116.1	119.1	125.0	137.1	156.0	187.1	241.1	344.1	533.2	804.3	1091.4
107.5°	142.8	145.9	151.6	163.4	181.2	210.1	257.5	343.1	495.6	723.8	984.6
110°	162.0	165.1	170.0	181.1	198.0	226.1	271.1	347.2	481.1	678.2	917.3

TEST NUMBER: P332299-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.7	182.7	187.7	198.6	215.7	242.9	284.7	355.2	473.2	647.8	858.9
115°	205.1	209.1	215.1	225.1	242.1	269.1	307.1	368.2	470.2	615.2	788.2
117.5°	230.5	235.1	240.0	249.3	268.3	293.3	330.9	385.3	472.0	596.0	745.6
120°	248.1	251.1	256.1	266.1	285.1	310.1	346.1	398.1	475.2	587.2	723.2
122.5°	263.3	266.3	271.3	282.1	300.3	326.9	362.1	410.2	480.8	581.6	704.8
125°	285.1	287.1	293.1	304.1	323.1	350.1	385.1	429.1	489.1	574.2	681.2
127.5°	301.7	304.7	312.1	323.3	344.3	371.3	405.1	444.8	498.8	570.6	660.5
130°	312.1	315.1	324.1	336.1	357.1	384.1	417.2	455.1	505.1	568.2	649.2
132.5°	320.1	323.9	333.7	348.1	369.1	395.4	427.6	464.8	510.0	567.4	638.9
135°	334.2	338.1	349.1	364.1	385.1	412.2	443.2	477.2	517.2	566.2	625.3
137.5°	347.3	351.5	362.3	378.3	399.2	424.1	453.9	486.4	522.0	564.0	613.4
140°	356.1	361.1	371.1	387.1	407.2	432.1	461.2	491.2	525.2	563.2	606.2
142.5°	365.8	370.0	380.7	395.1	415.2	438.6	466.7	495.9	527.6	561.6	599.8
145°	381.2	384.1	393.1	408.1	425.2	448.2	474.2	501.2	529.2	559.2	591.2
147.5°	396.7	398.6	407.3	420.3	436.8	456.3	480.2	504.4	529.2	555.4	582.8
150°	407.2	408.1	416.1	429.1	443.2	461.2	484.1	505.1	529.2	552.2	577.2
152.5°	417.6	417.8	425.8	437.1	449.5	466.7	486.6	506.8	526.8	548.2	570.8
155°	433.2	433.2	439.2	449.2	460.1	474.2	491.2	507.2	524.2	541.2	561.2
157.5°	445.6	446.3	451.2	459.9	469.3	480.2	493.8	508.2	520.8	535.0	550.4
160°	455.1	455.1	459.2	467.2	474.2	484.1	496.2	508.2	519.2	530.2	543.2
162.5°	462.4	462.4	465.5	472.0	478.2	486.6	497.0	507.4	516.0	525.4	536.0
165°	473.2	472.2	474.2	479.1	483.2	490.2	498.2	505.1	511.2	518.1	526.2
167.5°	481.4	480.2	481.1	485.0	487.8	492.1	498.0	503.6	506.4	511.0	516.8
170°	486.2	484.1	485.2	488.2	490.2	492.1	497.1	501.2	503.2	506.2	511.2
172.5°	489.4	488.2	488.4	490.6	491.8	493.0	497.1	500.4	500.8	502.1	505.6
175°	493.2	492.1	491.2	493.2	493.2	494.2	496.2	498.2	497.1	497.1	499.2
177.5°	495.0	494.2	493.4	494.2	494.2	494.2	495.0	496.5	495.0	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

TEST NUMBER: P332299-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	810.0	811.3	812.6	813.1	812.9	812.6	812.4	812.2
5°	804.6	806.0	807.3	807.8	807.5	807.2	806.9	806.6
7.5°	793.3	794.0	794.8	794.9	794.4	793.9	793.4	792.9
10°	783.2	783.3	783.4	783.2	782.5	781.7	781.0	780.2
12.5°	770.6	770.5	770.4	769.9	769.0	768.2	767.4	766.5
15°	748.5	747.7	747.0	746.1	745.0	744.1	743.0	742.0
17.5°	722.0	720.5	718.8	717.4	715.8	714.3	712.7	711.3
20°	703.9	702.0	700.1	698.3	696.5	694.7	692.9	691.2
22.5°	684.5	682.1	679.8	677.7	676.1	674.4	672.8	671.1
25°	652.7	649.6	646.6	644.2	642.7	641.0	639.4	637.7
27.5°	618.1	613.9	609.6	606.2	603.7	601.3	598.8	596.3
30°	593.5	588.5	583.6	579.9	577.6	575.2	572.8	570.5
32.5°	569.4	563.9	558.4	554.5	552.1	549.6	547.1	544.7
35°	533.5	527.2	520.9	516.4	513.8	511.2	508.5	505.8
37.5°	495.0	487.8	480.7	475.5	472.3	469.0	465.7	462.4
40°	468.2	460.5	453.0	447.5	444.1	440.7	437.4	433.9
42.5°	442.6	434.2	425.9	420.2	417.2	414.1	411.1	408.1
45°	404.8	396.4	388.1	382.1	378.6	375.1	371.5	368.0
47.5°	365.7	356.6	347.5	341.4	338.3	335.1	332.0	328.8
50°	339.3	330.2	321.2	314.9	311.5	308.2	304.8	301.4
52.5°	313.8	304.4	294.9	288.7	285.7	282.7	279.7	276.6
55°	275.9	267.3	258.8	253.1	250.2	247.3	244.4	241.4
57.5°	238.5	230.5	222.5	217.2	214.7	212.2	209.7	207.2
60°	215.0	207.1	199.1	194.0	191.5	189.0	186.5	184.0
62.5°	191.7	184.3	176.8	171.8	169.2	166.5	163.9	161.4
65°	158.4	151.3	144.0	139.7	138.1	136.5	134.8	133.2
67.5°	126.7	121.3	116.0	112.4	110.7	109.0	107.3	105.6
70°	107.1	102.0	96.9	93.5	91.9	90.3	88.7	87.0
72.5°	89.5	85.3	81.1	78.7	78.0	77.3	76.6	75.9
75°	67.0	65.5	64.1	63.2	62.9	62.6	62.3	62.0
77.5°	50.5	49.8	48.9	48.4	48.1	47.8	47.5	47.2
80°	40.6	40.2	39.8	39.4	39.2	38.8	38.6	38.2
82.5°	31.2	30.7	30.3	30.0	30.0	30.0	29.9	29.8
85°	17.9	17.6	17.3	17.1	17.1	17.1	17.1	17.1
87.5°	11.6	11.7	11.8	12.1	11.8	11.9	11.9	11.6
90°	25.0	26.0	27.0	29.0	28.0	29.0	30.0	29.0
92.5°	84.2	66.8	59.0	53.8	52.0	49.0	50.0	48.2
95°	360.2	244.1	191.1	155.1	136.0	127.1	120.0	116.1
97.5°	897.7	719.0	590.0	470.4	396.6	351.5	324.5	315.9
100°	1179.4	1098.4	981.4	839.3	738.2	665.2	626.2	627.2
102.5°	1273.1	1270.4	1202.2	1112.2	1033.5	975.8	943.1	920.2
105°	1300.5	1400.5	1419.5	1393.5	1347.5	1309.5	1277.5	1272.5
107.5°	1221.6	1384.1	1471.7	1507.4	1508.1	1495.3	1484.5	1475.3
110°	1146.4	1330.5	1456.6	1526.6	1554.5	1562.5	1560.6	1558.6

TEST NUMBER: P332299-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1071.9	1260.1	1401.3	1491.3	1542.6	1567.4	1574.9	1575.4
115°	973.4	1147.4	1294.4	1403.5	1478.5	1522.5	1542.6	1547.6
117.5°	901.9	1052.1	1184.2	1294.9	1373.1	1423.5	1452.3	1459.1
120°	864.3	999.4	1119.4	1220.5	1299.4	1355.5	1379.5	1385.5
122.5°	834.7	956.9	1068.2	1162.0	1232.3	1282.6	1309.1	1316.6
125°	795.3	904.3	1000.3	1080.4	1144.4	1188.4	1213.4	1220.5
127.5°	760.9	858.1	944.7	1017.5	1074.6	1112.2	1134.8	1141.2
130°	739.3	829.3	910.3	978.4	1031.4	1067.4	1088.4	1096.4
132.5°	719.3	802.1	877.5	942.4	992.1	1028.1	1046.8	1052.4
135°	692.2	763.3	828.3	885.3	934.4	964.3	982.3	989.4
137.5°	667.6	725.8	781.9	831.3	872.5	902.9	918.1	922.7
140°	653.2	704.2	752.3	795.3	833.3	861.3	877.3	876.3
142.5°	639.6	683.5	725.0	762.5	794.9	819.7	834.1	833.1
145°	623.2	656.3	688.3	717.2	742.3	763.3	771.3	773.3
147.5°	609.8	636.0	661.9	682.4	701.5	715.7	723.2	724.0
150°	600.2	623.2	644.2	663.2	678.2	689.2	695.3	695.3
152.5°	591.4	611.2	629.8	645.7	657.5	667.6	671.2	671.2
155°	578.2	594.2	609.2	621.2	630.3	638.3	640.2	641.2
157.5°	564.2	577.6	589.2	598.6	606.4	612.4	614.0	613.8
160°	556.2	567.2	577.2	584.2	591.2	597.2	597.2	596.2
162.5°	546.6	556.0	565.2	571.4	576.0	581.2	581.2	580.2
165°	534.2	540.2	547.2	552.2	556.2	560.2	559.2	559.2
167.5°	523.4	528.0	532.0	535.6	537.4	540.2	539.2	539.2
170°	516.2	519.2	523.1	525.2	526.2	528.2	527.2	527.2
172.5°	509.8	512.0	515.2	516.3	516.6	518.6	516.8	516.0
175°	501.2	502.1	504.2	504.2	504.2	505.1	504.2	503.2
177.5°	495.8	496.5	497.4	497.4	496.5	497.4	495.8	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

(END OF REPORT)