

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332017-840

Luminaire Tested: **S123DIP-S1000D585U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332017-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6302.4 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332017-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P332017-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66		
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	63	61	60	55		
2	92	85	78	73	87	80	74	69	71	66	63	63	59	56	55	52	50	46		
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39		
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	44	40	37	34		
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29		
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	36	31	28	26		
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	23	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18		
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	21	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139

TEST NUMBER: P332017-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	2.4
10°-20°	425.2	6.7
20°-30°	628.0	10.0
30°-40°	733.6	11.6
40°-50°	737.6	11.7
50°-60°	647.9	10.3
60°-70°	482.7	7.7
70°-80°	275.0	4.4
80°-90°	81.2	1.3
90°-100°	158.3	2.5
100°-110°	448.4	7.1
110°-120°	441.1	7.0
120°-130°	351.8	5.6
130°-140°	277.4	4.4
140°-150°	207.0	3.3
150°-160°	144.3	2.3
160°-170°	84.8	1.3
170°-180°	27.6	0.4
0°-30°	1203.8	19.1
0°-40°	1937.4	30.7
0°-60°	3322.8	52.7
0°-90°	4161.7	66.0
90°-120°	1047.8	16.6
90°-150°	1884.1	29.9
90°-180°	2141.0	34.0
0°-180°	6302.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	1	7	14	16	17	5
95°	20	64	342	100	67	21
105°	67	99	463	810	733	71
115°	118	147	354	777	891	117
125°	164	194	331	599	703	146
135°	192	230	326	493	570	149
145°	219	251	322	405	445	138
155°	249	269	312	354	369	115
165°	272	280	298	316	322	77
175°	284	284	286	290	290	27
180°	285	285	285	285	285	

TEST NUMBER: P332017-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.8	28.3	27.8	27.5	27.0	26.7	26.8	26.9	27.0	27.1	26.8
90°	1.1	2.3	3.4	5.2	6.4	7.5	9.2	10.9	12.6	14.4	13.8
92.5°	7.2	10.6	15.5	19.9	24.7	33.3	48.4	73.1	97.5	88.6	66.9
95°	19.6	21.3	27.7	37.5	52.4	74.8	123.8	209.6	304.2	341.5	277.0
97.5°	33.4	34.0	39.0	47.5	62.2	86.5	133.3	230.0	387.5	529.4	566.3
100°	42.6	43.2	47.3	55.3	69.1	91.6	131.9	217.1	368.6	545.4	658.9
102.5°	52.3	53.3	57.0	64.5	77.0	97.6	133.7	206.1	341.0	515.5	663.6
105°	66.9	68.6	72.0	78.9	89.9	107.8	138.9	198.1	307.0	463.1	628.4
107.5°	82.2	84.0	87.4	94.1	104.4	121.0	148.2	197.5	285.4	416.8	566.9
110°	93.3	95.0	98.0	104.2	114.0	130.2	156.1	199.9	277.0	390.5	528.2

TEST NUMBER: P332017-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	103.4	105.2	108.1	114.4	124.2	139.9	163.9	204.5	272.5	373.0	494.5
115°	118.1	120.4	123.8	129.6	139.4	154.9	176.8	212.0	270.7	354.3	453.9
117.5°	132.7	135.3	138.3	143.5	154.5	168.8	190.6	221.9	271.8	343.2	429.4
120°	142.9	144.6	147.4	153.2	164.2	178.5	199.2	229.2	273.6	338.1	416.5
122.5°	151.6	153.3	156.2	162.4	172.9	188.2	208.5	236.2	276.8	334.9	405.9
125°	164.2	165.3	168.7	175.1	186.0	201.6	221.8	247.1	281.7	330.6	392.2
127.5°	173.7	175.4	179.8	186.1	198.2	213.8	233.3	256.1	287.2	328.5	380.3
130°	179.8	181.5	186.6	193.5	205.6	221.2	240.1	262.1	290.8	327.2	373.9
132.5°	184.3	186.5	192.2	200.5	212.6	227.6	246.2	267.6	293.7	326.7	367.8
135°	192.4	194.7	201.1	209.6	221.8	237.3	255.2	274.8	297.8	326.0	360.0
137.5°	200.0	202.4	208.6	217.8	229.8	244.2	261.4	280.0	300.5	324.8	353.3
140°	205.1	207.9	213.7	222.9	234.4	248.8	265.5	282.9	302.4	324.3	349.0
142.5°	210.6	213.0	219.2	227.5	239.0	252.6	268.7	285.6	303.8	323.4	345.4
145°	219.4	221.2	226.4	235.0	244.8	258.0	273.1	288.6	304.7	321.9	340.4
147.5°	228.4	229.4	234.6	242.1	251.5	262.8	276.5	290.4	304.7	319.8	335.6
150°	234.4	235.0	239.6	247.1	255.2	265.5	278.8	290.8	304.7	317.9	332.3
152.5°	240.4	240.5	245.2	251.8	258.8	268.7	280.1	291.9	303.4	315.7	328.7
155°	249.4	249.4	252.9	258.6	265.0	273.1	282.9	292.1	301.8	311.6	323.2
157.5°	256.5	257.0	259.7	264.9	270.2	276.5	284.3	292.7	299.8	308.0	316.9
160°	262.1	262.1	264.4	269.0	273.1	278.8	285.7	292.7	298.9	305.3	312.8
162.5°	266.2	266.2	268.1	271.8	275.3	280.1	286.2	292.2	297.1	302.6	308.6
165°	272.5	271.9	273.1	275.9	278.2	282.3	286.8	290.8	294.4	298.4	303.0
167.5°	277.2	276.5	277.0	279.2	280.8	283.4	286.7	289.9	291.5	294.2	297.6
170°	279.9	278.8	279.3	281.0	282.3	283.4	286.3	288.6	289.7	291.4	294.4
172.5°	281.8	281.0	281.2	282.5	283.2	283.9	286.3	288.1	288.3	289.1	291.1
175°	284.0	283.4	282.9	284.0	284.0	284.6	285.7	286.8	286.3	286.3	287.4
177.5°	285.0	284.6	284.1	284.6	284.6	284.6	285.0	285.9	285.0	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6

TEST NUMBER: P332017-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	26.6	26.5	26.4	26.5	26.4	26.5	26.6	26.5
90°	14.4	14.9	15.6	16.7	16.2	16.7	17.3	16.7
92.5°	48.5	38.5	34.0	31.0	30.0	28.2	28.8	27.8
95°	207.3	140.6	110.0	89.3	78.4	73.1	69.1	66.9
97.5°	516.9	414.0	339.7	270.8	228.3	202.4	186.8	181.9
100°	679.1	632.5	565.0	483.2	425.1	383.0	360.6	361.1
102.5°	733.1	731.5	692.3	640.4	595.1	561.8	543.0	529.8
105°	748.8	806.4	817.4	802.3	775.9	754.0	735.6	732.7
107.5°	703.4	797.0	847.4	867.9	868.4	861.0	854.7	849.5
110°	660.0	766.1	838.7	879.0	895.1	899.7	898.6	897.4

TEST NUMBER: P332017-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	617.2	725.5	806.9	858.7	888.2	902.5	906.9	907.1
115°	560.5	660.7	745.4	808.1	851.3	876.7	888.2	891.1
117.5°	519.3	605.8	681.9	745.6	790.6	819.6	836.3	840.1
120°	497.7	575.4	644.5	702.8	748.2	780.5	794.3	797.8
122.5°	480.6	551.0	615.0	669.0	709.5	738.5	753.8	758.1
125°	457.9	520.7	576.0	622.1	658.9	684.3	698.7	702.8
127.5°	438.1	494.1	544.0	585.9	618.7	640.4	653.4	657.1
130°	425.7	477.5	524.1	563.3	593.9	614.6	626.7	631.3
132.5°	414.1	461.8	505.2	542.6	571.3	592.0	602.7	605.9
135°	398.6	439.5	477.0	509.8	538.0	555.2	565.6	569.7
137.5°	384.5	418.0	450.2	478.7	502.4	519.9	528.7	531.3
140°	376.2	405.5	433.1	457.9	479.8	495.9	505.1	504.5
142.5°	368.3	393.5	417.5	439.0	457.7	472.0	480.3	479.7
145°	358.8	377.9	396.3	413.0	427.4	439.5	444.1	445.2
147.5°	351.1	366.2	381.1	392.9	403.8	412.0	416.5	416.9
150°	345.6	358.8	370.9	381.9	390.5	396.9	400.3	400.3
152.5°	340.5	351.9	362.6	371.7	378.5	384.5	386.5	386.5
155°	333.0	342.1	350.8	357.7	362.8	367.5	368.6	369.2
157.5°	324.9	332.5	339.3	344.7	349.2	352.6	353.6	353.5
160°	320.2	326.6	332.3	336.4	340.4	343.9	343.9	343.3
162.5°	314.8	320.1	325.5	329.0	331.6	334.7	334.7	334.1
165°	307.6	311.0	315.1	317.9	320.2	322.6	321.9	321.9
167.5°	301.3	304.0	306.3	308.4	309.4	311.0	310.4	310.4
170°	297.2	298.9	301.2	302.4	303.0	304.2	303.6	303.6
172.5°	293.6	294.8	296.6	297.3	297.4	298.6	297.6	297.1
175°	288.6	289.1	290.3	290.3	290.3	290.8	290.3	289.7
177.5°	285.5	285.9	286.4	286.4	285.9	286.4	285.5	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6

(END OF REPORT)