

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332366-840

Luminaire Tested: **S123RDIP-S1165D585U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332366-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D585U840-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6982.9 lumens  
Efficiency: N/A  
Efficacy: 126.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	61	57
2	94	87	81	76	88	82	77	72	73	69	65	65	62	59	57	55	53	49
3	86	77	70	64	81	73	66	61	65	60	56	58	54	51	51	48	46	43
4	79	69	61	55	74	65	58	53	58	53	48	52	48	44	46	43	40	37
5	73	62	54	48	69	58	51	46	53	47	42	47	43	39	42	39	36	33
6	67	56	48	42	63	53	46	40	48	42	37	43	38	35	39	35	32	29
7	63	50	43	37	59	48	41	36	44	38	33	39	34	31	35	31	28	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	24
9	54	42	35	30	51	40	34	29	37	31	27	33	29	25	30	26	23	21
10	51	39	32	27	48	37	31	26	34	28	25	31	26	23	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19957	19957	19957	19957
5°	23791	20042	17650	20042
10°	29704	19928	15946	19928
15°	34867	19724	14540	19724
20°	38913	19420	13347	19420
25°	38292	19099	12613	19099
30°	27524	18804	11857	18804
35°	18378	18419	11369	18419
40°	13540	17956	10863	17956
45°	11357	17145	10368	17145
50°	10021	16083	9676	16083
55°	8788	14865	8728	14865
60°	7828	13702	7995	13702
65°	6872	12455	7440	12455
70°	5397	11339	6795	11339
75°	4754	9902	6209	9902
80°	4135	8412	6106	8412
85°	3335	6756	6472	6756



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.3	2.6
10°-20°	569.6	8.2
20°-30°	894.9	12.8
30°-40°	933.7	13.4
40°-50°	799.0	11.4
50°-60°	609.0	8.7
60°-70°	390.4	5.6
70°-80°	187.8	2.7
80°-90°	51.9	0.7
90°-100°	28.2	0.4
100°-110°	134.3	1.9
110°-120°	322.7	4.6
120°-130°	410.9	5.9
130°-140°	439.0	6.3
140°-150°	410.5	5.9
150°-160°	331.2	4.7
160°-170°	213.7	3.1
170°-180°	73.7	1.1
0°-30°	1646.9	23.6
0°-40°	2580.6	37.0
0°-60°	3988.6	57.1
0°-90°	4618.7	66.1
90°-120°	485.2	6.9
90°-150°	1745.7	25.0
90°-180°	2364.0	33.9
0°-180°	6982.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1854	1854	1854	1854	1854	
5°	2202	1855	1634	1855	2202	227
15°	3129	1770	1305	1770	3129	887
25°	3224	1608	1062	1608	3224	1386
35°	1399	1402	865	1402	1399	917
45°	746	1126	681	1126	746	587
55°	468	792	465	792	468	423
65°	270	489	292	489	270	265
75°	114	238	149	238	114	123
85°	27	55	52	55	27	31
90°	17	1	17	1	17	9
95°	22	35	22	35	22	18
105°	25	172	25	172	25	58
115°	339	322	339	322	339	313
125°	463	454	463	454	463	414
135°	571	565	571	565	571	440
145°	658	652	658	652	658	411
155°	717	718	717	718	717	331
165°	756	757	756	757	756	213
175°	772	775	772	775	772	74
180°	775	775	775	775	775	



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1974.8	1977.3	1969.0	1967.8	1958.2	1955.7	1955.7	1942.4	1934.1	1923.4	1917.0
5°	2201.8	2214.5	2208.2	2193.8	2170.0	2164.4	2149.4	2125.6	2098.6	2065.3	2049.4
7.5°	2485.3	2502.6	2496.0	2473.9	2448.9	2428.8	2386.2	2346.7	2291.3	2242.7	2201.1
10°	2717.7	2699.5	2685.1	2663.7	2640.7	2603.4	2559.0	2497.8	2427.2	2371.7	2309.8
12.5°	2891.6	2888.7	2870.5	2848.5	2816.0	2780.6	2725.9	2651.5	2569.4	2489.1	2418.3
15°	3128.9	3133.6	3121.7	3098.7	3052.6	2989.9	2907.4	2876.5	2759.0	2671.7	2584.3
17.5°	3293.0	3292.1	3290.4	3258.5	3211.6	3166.9	3090.4	3009.0	2902.7	2779.7	2662.0
20°	3397.1	3389.2	3390.8	3355.1	3320.1	3268.5	3193.9	3075.6	2988.4	2846.3	2724.8
22.5°	3394.6	3393.0	3399.0	3386.8	3361.4	3321.8	3263.2	3163.3	3051.9	2908.5	2771.9
25°	3224.1	3217.7	3255.1	3265.4	3305.9	3313.0	3295.5	3240.8	3135.2	2987.6	2818.5
27.5°	2698.4	2694.8	2764.1	2850.7	2960.6	3046.0	3128.6	3168.4	3135.2	3029.5	2860.1
30°	2214.5	2289.1	2324.0	2449.4	2589.1	2755.8	2901.8	3040.7	3074.8	3028.9	2889.9
32.5°	1838.6	1903.7	1932.9	2040.5	2170.7	2365.9	2585.0	2781.7	2920.6	2955.8	2872.2
35°	1398.6	1399.4	1466.0	1513.6	1634.3	1835.1	2047.8	2311.3	2573.2	2771.7	2792.3
37.5°	1116.0	1119.9	1160.2	1207.7	1298.2	1404.4	1591.7	1810.8	2113.3	2418.0	2596.6
40°	963.6	970.7	1000.9	1047.7	1112.8	1193.0	1339.0	1545.4	1797.8	2136.7	2413.7
42.5°	865.8	877.4	892.9	929.0	969.3	1044.4	1162.5	1321.9	1551.5	1871.9	2191.5
45°	746.1	752.5	764.4	781.0	817.5	869.9	949.3	1056.4	1247.0	1504.9	1824.7
47.5°	658.1	654.8	667.3	680.9	705.2	740.8	794.1	881.5	1017.4	1224.4	1495.7
50°	598.4	597.6	606.4	616.7	639.7	665.9	709.6	775.5	883.4	1054.9	1303.3
52.5°	542.6	545.6	551.8	564.6	581.3	602.5	641.7	689.1	781.8	929.8	1136.9
55°	468.3	470.7	479.4	486.6	498.5	519.9	544.5	584.2	647.7	750.8	921.5
57.5°	405.5	404.3	412.7	414.4	428.0	445.5	464.4	495.2	541.3	618.0	733.0
60°	363.6	361.1	368.3	373.9	381.0	395.3	411.1	441.3	477.9	534.2	632.6
62.5°	325.4	324.3	329.5	335.1	341.0	354.0	367.3	390.5	419.4	466.9	544.9
65°	269.8	272.3	274.6	277.0	280.1	288.1	300.8	316.7	336.6	369.9	426.3
67.5°	212.1	214.5	215.3	220.2	227.0	232.0	239.7	253.9	267.6	295.8	327.8
70°	171.5	170.7	171.5	173.8	182.6	191.3	201.6	212.0	220.7	240.4	267.5
72.5°	147.3	145.9	147.9	148.5	152.7	155.1	161.6	171.3	182.6	196.0	215.4
75°	114.3	114.3	114.3	114.3	117.4	119.1	121.5	123.8	127.7	134.1	148.5
77.5°	84.4	84.6	85.7	86.5	87.2	88.1	89.6	91.9	93.3	96.6	102.9
80°	66.7	67.5	66.7	67.5	67.5	69.1	69.9	72.2	73.0	77.0	79.4
82.5°	50.2	49.7	50.2	51.0	51.0	52.5	52.7	54.4	54.6	56.7	59.1
85°	27.0	25.4	27.0	26.2	27.8	26.2	27.0	28.6	28.6	29.4	32.5
87.5°	9.8	11.0	9.7	10.3	10.2	10.8	10.7	10.6	11.7	11.0	11.3
90°	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8	14.3	13.8	12.1
92.5°	19.1	19.0	18.8	18.7	18.5	18.0	17.2	16.4	15.6	14.7	13.5
95°	21.9	21.9	21.9	21.9	21.9	21.4	20.5	19.7	18.8	17.9	16.5
97.5°	23.7	23.6	23.4	23.3	23.2	22.6	21.6	20.6	19.6	18.6	27.8
100°	24.2	24.0	23.9	23.8	23.6	23.1	22.1	21.0	20.0	19.0	39.0
102.5°	24.6	24.4	24.2	23.9	23.7	25.2	28.4	31.5	34.7	37.9	59.7
105°	25.3	25.0	24.8	24.5	24.3	35.5	58.2	80.8	103.5	126.1	137.6
107.5°	79.6	96.6	113.7	130.8	147.9	164.7	181.4	197.9	214.6	231.2	229.3
110°	158.3	176.7	195.0	213.3	231.6	242.9	247.1	251.4	255.5	259.7	258.3



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.8	275.6	279.4	283.4	287.2	289.1	289.0	288.9	288.9	288.8	287.4
115°	338.7	338.2	337.7	337.1	336.6	335.8	334.5	333.2	331.9	330.6	329.4
117.5°	376.3	376.2	376.1	376.0	375.9	375.3	374.3	373.2	372.2	371.1	370.6
120°	402.0	402.0	402.0	402.0	402.0	401.5	400.5	399.5	398.5	397.4	397.1
122.5°	427.4	427.3	427.2	427.1	427.0	426.6	425.9	425.2	424.4	423.7	423.2
125°	463.1	462.8	462.6	462.3	462.1	461.8	461.5	461.3	461.0	460.8	460.3
127.5°	497.5	497.7	498.0	498.2	498.5	498.4	498.0	497.6	497.2	496.8	496.1
130°	519.6	519.8	520.1	520.3	520.6	520.4	519.9	519.4	518.9	518.4	517.9
132.5°	539.8	540.2	540.5	540.9	541.3	541.2	540.7	540.2	539.7	539.2	538.7
135°	570.8	571.2	571.6	572.0	572.3	572.3	572.0	571.6	571.2	570.8	570.3
137.5°	600.0	600.2	600.5	600.7	601.0	600.8	600.2	599.6	599.0	598.3	598.0
140°	617.4	617.7	617.9	618.2	618.4	618.3	617.8	617.3	616.8	616.3	615.9
142.5°	633.6	633.9	634.3	634.7	635.0	635.0	634.6	634.2	633.8	633.4	633.0
145°	658.3	658.3	658.3	658.3	658.3	658.2	657.9	657.7	657.4	657.2	656.9
147.5°	676.8	677.4	677.9	678.5	679.1	679.3	679.0	678.8	678.5	678.3	678.0
150°	690.6	690.9	691.4	691.8	692.2	692.2	692.0	691.7	691.5	691.2	690.9
152.5°	701.7	702.3	702.9	703.5	704.0	704.1	703.6	703.2	702.7	702.3	702.1
155°	717.1	717.9	718.6	719.4	720.1	720.2	719.6	718.9	718.3	717.7	717.5
157.5°	730.1	731.1	732.2	733.1	734.1	734.3	733.5	732.7	732.0	731.1	731.2
160°	738.4	739.3	740.2	741.1	741.9	742.0	741.2	740.5	739.7	739.0	739.1
162.5°	746.3	747.0	747.8	748.6	749.4	749.4	748.5	747.6	746.8	745.9	746.0
165°	755.7	756.6	757.5	758.4	759.3	759.2	758.2	757.2	756.2	755.1	755.3
167.5°	762.4	763.6	764.6	765.6	766.6	766.6	765.6	764.6	763.6	762.4	762.4
170°	766.6	767.7	768.7	769.7	770.7	770.7	769.7	768.7	767.7	766.6	766.6
172.5°	768.9	770.0	771.2	772.3	773.5	773.5	772.4	771.4	770.4	769.4	769.3
175°	772.3	773.5	774.5	775.5	776.5	776.6	775.7	774.8	773.9	773.0	772.8
177.5°	773.5	774.5	775.5	776.5	777.5	777.6	776.8	776.0	775.2	774.4	774.3
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1914.5	1912.6	1903.7	1893.5	1880.2	1871.3	1864.3	1860.5	1849.1	1835.1	1825.5
5°	2032.8	2008.9	1983.5	1952.6	1924.0	1894.6	1876.3	1854.9	1828.8	1799.4	1778.8
7.5°	2159.4	2112.7	2062.4	2010.5	1959.2	1913.2	1872.6	1837.8	1796.0	1753.9	1724.4
10°	2256.5	2188.3	2117.7	2045.4	1979.5	1917.6	1870.0	1823.2	1773.2	1724.7	1688.3
12.5°	2344.8	2254.9	2173.5	2084.8	2000.5	1926.5	1857.9	1802.8	1742.7	1691.1	1649.5
15°	2456.6	2364.5	2266.0	2131.1	2019.2	1925.6	1842.2	1770.0	1697.0	1633.5	1593.0
17.5°	2561.0	2422.5	2290.2	2177.7	2032.3	1915.2	1813.5	1727.2	1647.0	1579.6	1529.8
20°	2604.2	2470.0	2326.4	2182.7	2039.8	1908.9	1790.6	1695.4	1612.0	1535.8	1489.9
22.5°	2630.2	2478.3	2327.0	2172.6	2020.8	1884.8	1767.8	1663.0	1572.7	1500.3	1443.5
25°	2660.6	2479.6	2312.9	2160.5	2005.7	1858.2	1719.2	1608.1	1510.5	1433.5	1373.1
27.5°	2680.6	2467.7	2270.7	2101.3	1944.3	1797.3	1670.0	1552.2	1453.2	1371.7	1307.0
30°	2684.3	2458.1	2238.3	2055.0	1895.4	1760.5	1625.6	1512.9	1408.1	1321.5	1261.2
32.5°	2689.5	2434.7	2194.4	1999.7	1836.3	1702.7	1580.4	1472.8	1365.5	1280.3	1218.7
35°	2668.5	2421.7	2128.0	1904.1	1740.6	1611.2	1501.0	1401.7	1296.2	1213.6	1150.9
37.5°	2578.3	2370.1	2059.1	1796.5	1625.6	1505.7	1415.8	1329.3	1232.5	1143.5	1084.4
40°	2487.5	2319.3	2005.7	1731.1	1552.6	1429.5	1348.6	1277.9	1184.3	1100.9	1037.4
42.5°	2352.3	2250.1	1954.9	1662.5	1470.0	1351.4	1283.1	1216.9	1134.7	1050.1	990.4
45°	2104.2	2117.7	1851.0	1553.3	1355.6	1236.6	1172.4	1126.3	1053.3	983.4	922.3
47.5°	1793.0	1919.2	1728.9	1436.9	1235.2	1123.5	1067.2	1027.0	977.9	909.3	853.5
50°	1589.8	1770.0	1631.1	1358.9	1159.6	1048.5	992.9	960.4	917.6	863.5	810.4
52.5°	1402.5	1596.0	1513.0	1271.8	1077.7	976.1	921.8	895.0	861.0	810.2	762.1
55°	1143.8	1339.8	1320.8	1140.5	954.8	863.5	822.3	792.1	769.1	731.0	693.0
57.5°	925.1	1111.1	1120.8	994.5	846.6	756.4	720.8	698.1	683.1	654.4	619.1
60°	787.4	958.1	991.4	896.2	769.1	689.7	654.8	636.5	624.7	601.7	574.6
62.5°	673.1	818.3	856.1	787.5	694.8	620.6	593.2	575.6	567.5	547.6	523.8
65°	515.1	635.8	672.3	634.2	585.7	526.2	504.0	489.0	481.8	470.7	453.2
67.5°	387.4	475.2	515.3	488.5	471.0	433.3	419.2	411.1	404.8	397.2	382.5
70°	311.1	376.2	417.5	410.3	396.1	376.2	365.9	360.3	354.0	347.7	335.0
72.5°	250.1	295.0	333.7	337.3	325.6	321.6	312.6	310.2	306.4	298.7	291.8
75°	165.9	196.8	223.8	234.2	238.9	242.9	238.9	238.1	237.3	231.0	227.0
77.5°	108.8	125.4	142.4	160.1	167.4	172.9	174.1	177.0	174.9	171.6	169.7
80°	83.3	87.4	99.2	114.3	126.2	131.0	134.1	135.7	134.9	134.1	131.0
82.5°	60.5	63.8	69.4	80.0	90.0	98.0	99.9	99.6	101.3	101.8	99.2
85°	32.5	33.3	34.9	36.6	42.1	50.8	53.2	54.7	56.4	56.4	51.6
87.5°	12.2	11.3	12.2	11.9	13.6	13.9	17.5	20.4	21.3	19.1	19.3
90°	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	12.2	11.0	9.7	9.3	9.6	10.0	10.4	10.7	10.4	10.0	9.6
95°	15.0	13.6	12.2	14.1	19.4	24.6	29.9	35.1	29.9	24.6	19.4
97.5°	37.0	46.2	55.4	61.2	63.5	65.9	68.3	70.6	68.3	65.9	63.5
100°	59.0	78.9	98.9	107.6	105.0	102.5	99.9	97.4	99.9	102.5	105.0
102.5°	81.5	103.3	125.1	135.1	133.3	131.5	129.6	127.7	129.6	131.5	133.3
105°	149.2	160.7	172.2	177.2	175.8	174.5	173.1	171.7	173.1	174.5	175.8
107.5°	227.5	225.7	223.9	222.5	221.4	220.3	219.0	217.9	219.0	220.3	221.4
110°	256.9	255.5	254.2	252.9	251.9	250.9	249.8	248.8	249.8	250.9	251.9





TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	286.0	284.6	283.2	282.0	281.0	280.1	279.2	278.3	279.2	280.1	281.0
115°	328.3	327.2	326.0	325.1	324.3	323.5	322.8	321.9	322.8	323.5	324.3
117.5°	370.0	369.4	368.8	368.0	367.1	366.2	365.2	364.3	365.2	366.2	367.1
120°	396.7	396.3	395.9	395.2	393.9	392.8	391.6	390.5	391.6	392.8	393.9
122.5°	422.7	422.2	421.7	421.0	420.1	419.1	418.2	417.3	418.2	419.1	420.1
125°	459.8	459.3	458.8	458.0	457.0	456.0	454.9	453.8	454.9	456.0	457.0
127.5°	495.5	494.8	494.2	493.4	492.4	491.4	490.4	489.4	490.4	491.4	492.4
130°	517.4	516.8	516.3	515.5	514.5	513.5	512.5	511.5	512.5	513.5	514.5
132.5°	538.3	537.9	537.5	536.7	535.7	534.7	533.7	532.7	533.7	534.7	535.7
135°	569.8	569.3	568.8	568.2	567.3	566.5	565.8	565.0	565.8	566.5	567.3
137.5°	597.7	597.4	597.2	596.5	595.6	594.6	593.7	592.7	593.7	594.6	595.6
140°	615.5	615.1	614.8	614.2	613.4	612.7	611.9	611.1	611.9	612.7	613.4
142.5°	632.6	632.2	631.8	631.3	630.5	629.8	628.9	628.1	628.9	629.8	630.5
145°	656.7	656.4	656.2	655.6	654.7	653.8	652.9	652.0	652.9	653.8	654.7
147.5°	677.7	677.5	677.2	676.8	676.2	675.7	675.1	674.5	675.1	675.7	676.2
150°	690.6	690.4	690.1	689.8	689.4	689.0	688.7	688.3	688.7	689.0	689.4
152.5°	702.0	701.8	701.7	701.5	701.3	701.0	700.9	700.7	700.9	701.0	701.3
155°	717.4	717.3	717.2	717.2	717.5	717.7	718.0	718.2	718.0	717.7	717.5
157.5°	731.4	731.5	731.6	731.7	731.7	731.7	731.8	731.8	731.8	731.7	731.7
160°	739.2	739.3	739.5	739.6	739.7	739.9	740.0	740.1	740.0	739.9	739.7
162.5°	746.2	746.3	746.4	746.6	747.0	747.3	747.6	748.0	747.6	747.3	747.0
165°	755.4	755.5	755.6	755.9	756.3	756.7	757.0	757.4	757.0	756.7	756.3
167.5°	762.4	762.4	762.4	762.8	763.3	763.8	764.3	764.8	764.3	763.8	763.3
170°	766.6	766.6	766.6	766.9	767.4	767.9	768.4	768.9	768.4	767.9	767.4
172.5°	769.2	769.1	769.0	769.2	769.8	770.4	771.1	771.7	771.1	770.4	769.8
175°	772.7	772.5	772.4	772.7	773.4	774.0	774.7	775.3	774.7	774.0	773.4
177.5°	774.2	774.1	774.0	774.2	774.7	775.2	775.7	776.2	775.7	775.2	774.7
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1822.4	1814.1	1808.5	1795.7	1787.5	1778.6	1769.7	1775.4	1774.7	1774.1	1774.1
5°	1761.3	1743.0	1726.4	1705.0	1691.4	1674.8	1662.0	1660.4	1663.7	1652.5	1646.2
7.5°	1700.6	1675.7	1652.0	1628.4	1603.4	1583.4	1570.7	1564.9	1556.8	1549.9	1542.9
10°	1658.1	1628.7	1605.7	1576.3	1549.3	1525.5	1510.5	1500.2	1494.6	1489.0	1478.7
12.5°	1614.3	1585.6	1556.2	1523.0	1497.3	1469.7	1458.3	1446.8	1436.1	1430.0	1415.8
15°	1550.1	1512.9	1481.9	1446.9	1418.4	1391.4	1375.5	1352.5	1349.3	1341.4	1327.1
17.5°	1485.8	1445.3	1402.7	1376.7	1344.5	1316.5	1292.3	1284.5	1261.8	1253.2	1240.9
20°	1435.0	1397.8	1365.2	1331.1	1284.2	1258.1	1239.0	1228.7	1210.4	1199.3	1191.3
22.5°	1391.2	1353.3	1315.7	1275.9	1237.3	1207.9	1194.0	1177.9	1167.9	1152.4	1143.8
25°	1328.7	1287.4	1242.1	1199.3	1171.5	1149.3	1127.1	1112.8	1098.5	1091.4	1075.5
27.5°	1256.0	1212.8	1170.5	1138.0	1103.9	1082.0	1061.9	1049.1	1032.0	1020.0	1011.2
30°	1216.0	1165.2	1128.6	1099.3	1055.6	1035.0	1020.0	1004.1	991.4	978.7	970.0
32.5°	1169.6	1123.3	1088.6	1052.3	1018.9	996.2	976.7	962.8	952.0	939.9	931.2
35°	1096.9	1058.0	1022.3	985.8	961.2	938.2	915.1	903.2	892.9	881.8	873.9
37.5°	1031.2	994.8	960.9	926.2	895.8	877.1	858.5	849.4	835.5	828.0	819.9
40°	990.6	954.8	918.4	885.0	853.2	839.0	822.3	808.8	796.1	790.5	781.8
42.5°	946.1	910.4	879.6	843.7	817.7	798.3	782.9	768.2	758.6	750.5	745.6
45°	880.2	848.5	818.3	782.6	758.0	741.3	723.9	710.3	701.7	696.1	687.3
47.5°	816.3	784.6	753.9	722.8	698.9	679.9	662.5	653.1	641.5	634.7	628.7
50°	769.9	741.3	708.8	680.2	656.4	637.3	623.1	611.2	600.9	592.1	588.1
52.5°	727.4	696.9	668.8	642.1	617.0	595.4	582.4	569.9	562.1	552.1	547.5
55°	657.2	627.8	604.0	577.8	553.2	534.9	519.1	508.0	500.1	489.0	482.6
57.5°	591.3	565.0	536.5	513.8	488.5	473.0	459.9	444.8	435.2	426.4	420.2
60°	546.8	516.7	492.1	470.7	448.5	428.6	416.7	404.8	394.5	385.8	380.2
62.5°	500.5	474.1	450.8	427.5	407.2	389.9	376.1	366.1	357.0	351.4	345.9
65°	429.4	408.8	385.0	365.9	346.9	334.2	323.1	314.3	308.0	304.0	299.2
67.5°	364.0	344.0	323.2	304.5	291.8	282.1	274.8	267.3	264.2	259.0	255.9
70°	321.4	300.8	282.6	268.3	255.6	248.4	243.7	238.1	234.9	228.6	225.4
72.5°	275.1	260.1	247.0	235.3	225.1	218.6	212.6	205.7	200.7	193.7	190.5
75°	216.7	203.2	192.9	184.9	178.5	169.9	161.2	154.0	151.6	149.3	148.5
77.5°	160.5	151.9	144.4	137.7	129.9	123.5	121.6	120.0	119.6	118.3	118.3
80°	126.2	118.3	112.7	104.7	100.0	100.0	100.0	98.5	99.2	99.2	99.2
82.5°	93.8	86.5	83.5	80.7	79.7	80.3	80.3	80.7	80.2	81.4	80.8
85°	48.4	49.2	50.8	50.0	50.8	50.8	52.4	51.6	52.4	50.8	52.4
87.5°	18.9	21.1	22.1	23.0	24.0	23.7	24.4	24.5	25.2	25.4	25.4
90°	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8	15.3	15.9	16.3
92.5°	9.3	9.7	11.0	12.2	13.5	14.7	15.6	16.4	17.2	18.0	18.5
95°	14.1	12.2	13.6	15.0	16.5	17.9	18.8	19.7	20.5	21.4	21.9
97.5°	61.2	55.4	46.2	37.0	27.8	18.6	19.6	20.6	21.6	22.6	23.2
100°	107.6	98.9	78.9	59.0	39.0	19.0	20.0	21.0	22.1	23.1	23.6
102.5°	135.1	125.1	103.3	81.5	59.7	37.9	34.7	31.5	28.4	25.2	23.7
105°	177.2	172.2	160.7	149.2	137.6	126.1	103.5	80.8	58.2	35.5	24.3
107.5°	222.5	223.9	225.7	227.5	229.3	231.2	214.6	197.9	181.4	164.7	147.9
110°	252.9	254.2	255.5	256.9	258.3	259.7	255.5	251.4	247.1	242.9	231.6



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	282.0	283.2	284.6	286.0	287.4	288.8	288.9	288.9	289.0	289.1	287.2
115°	325.1	326.0	327.2	328.3	329.4	330.6	331.9	333.2	334.5	335.8	336.6
117.5°	368.0	368.8	369.4	370.0	370.6	371.1	372.2	373.2	374.3	375.3	375.9
120°	395.2	395.9	396.3	396.7	397.1	397.4	398.5	399.5	400.5	401.5	402.0
122.5°	421.0	421.7	422.2	422.7	423.2	423.7	424.4	425.2	425.9	426.6	427.0
125°	458.0	458.8	459.3	459.8	460.3	460.8	461.0	461.3	461.5	461.8	462.1
127.5°	493.4	494.2	494.8	495.5	496.1	496.8	497.2	497.6	498.0	498.4	498.5
130°	515.5	516.3	516.8	517.4	517.9	518.4	518.9	519.4	519.9	520.4	520.6
132.5°	536.7	537.5	537.9	538.3	538.7	539.2	539.7	540.2	540.7	541.2	541.3
135°	568.2	568.8	569.3	569.8	570.3	570.8	571.2	571.6	572.0	572.3	572.3
137.5°	596.5	597.2	597.4	597.7	598.0	598.3	599.0	599.6	600.2	600.8	601.0
140°	614.2	614.8	615.1	615.5	615.9	616.3	616.8	617.3	617.8	618.3	618.4
142.5°	631.3	631.8	632.2	632.6	633.0	633.4	633.8	634.2	634.6	635.0	635.0
145°	655.6	656.2	656.4	656.7	656.9	657.2	657.4	657.7	657.9	658.2	658.3
147.5°	676.8	677.2	677.5	677.7	678.0	678.3	678.5	678.8	679.0	679.3	679.1
150°	689.8	690.1	690.4	690.6	690.9	691.2	691.5	691.7	692.0	692.2	692.2
152.5°	701.5	701.7	701.8	702.0	702.1	702.3	702.7	703.2	703.6	704.1	704.0
155°	717.2	717.2	717.3	717.4	717.5	717.7	718.3	718.9	719.6	720.2	720.1
157.5°	731.7	731.6	731.5	731.4	731.2	731.1	732.0	732.7	733.5	734.3	734.1
160°	739.6	739.5	739.3	739.2	739.1	739.0	739.7	740.5	741.2	742.0	741.9
162.5°	746.6	746.4	746.3	746.2	746.0	745.9	746.8	747.6	748.5	749.4	749.4
165°	755.9	755.6	755.5	755.4	755.3	755.1	756.2	757.2	758.2	759.2	759.3
167.5°	762.8	762.4	762.4	762.4	762.4	762.4	763.6	764.6	765.6	766.6	766.6
170°	766.9	766.6	766.6	766.6	766.6	766.6	767.7	768.7	769.7	770.7	770.7
172.5°	769.2	769.0	769.1	769.2	769.3	769.4	770.4	771.4	772.4	773.5	773.5
175°	772.7	772.4	772.5	772.7	772.8	773.0	773.9	774.8	775.7	776.6	776.5
177.5°	774.2	774.0	774.1	774.2	774.3	774.4	775.2	776.0	776.8	777.6	777.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1766.6	1765.8	1766.6	1763.9	1766.6	1765.8	1766.6	1774.1	1774.1	1774.7	1775.4
5°	1643.8	1643.1	1640.6	1633.5	1640.6	1643.1	1643.8	1646.2	1652.5	1663.7	1660.4
7.5°	1536.6	1535.5	1528.5	1528.7	1528.5	1535.5	1536.6	1542.9	1549.9	1556.8	1564.9
10°	1473.2	1473.9	1464.4	1458.9	1464.4	1473.9	1473.2	1478.7	1489.0	1494.6	1500.2
12.5°	1411.6	1408.0	1400.3	1394.1	1400.3	1408.0	1411.6	1415.8	1430.0	1436.1	1446.8
15°	1330.3	1322.3	1303.3	1304.8	1303.3	1322.3	1330.3	1327.1	1341.4	1349.3	1352.5
17.5°	1234.6	1228.7	1228.4	1217.3	1228.4	1228.7	1234.6	1240.9	1253.2	1261.8	1284.5
20°	1178.7	1174.7	1176.3	1165.2	1176.3	1174.7	1178.7	1191.3	1199.3	1210.4	1228.7
22.5°	1134.9	1130.8	1124.2	1120.7	1124.2	1130.8	1134.9	1143.8	1152.4	1167.9	1177.9
25°	1070.8	1064.4	1058.0	1062.0	1058.0	1064.4	1070.8	1075.5	1091.4	1098.5	1112.8
27.5°	1006.6	1001.9	995.5	994.7	995.5	1001.9	1006.6	1011.2	1020.0	1032.0	1049.1
30°	965.9	961.2	958.1	954.0	958.1	961.2	965.9	970.0	978.7	991.4	1004.1
32.5°	924.7	923.7	918.1	917.3	918.1	923.7	924.7	931.2	939.9	952.0	962.8
35°	870.7	866.0	864.3	865.2	864.3	866.0	870.7	873.9	881.8	892.9	903.2
37.5°	819.4	813.0	810.2	807.4	810.2	813.0	819.4	819.9	828.0	835.5	849.4
40°	782.6	776.3	774.7	773.1	774.7	776.3	782.6	781.8	790.5	796.1	808.8
42.5°	741.3	738.8	737.8	735.0	737.8	738.8	741.3	745.6	750.5	758.6	768.2
45°	685.0	684.2	679.4	681.1	679.4	684.2	685.0	687.3	696.1	701.7	710.3
47.5°	625.6	622.1	618.7	621.0	618.7	622.1	625.6	628.7	634.7	641.5	653.1
50°	585.0	583.4	576.2	577.8	576.2	583.4	585.0	588.1	592.1	600.9	611.2
52.5°	544.3	538.3	535.6	534.6	535.6	538.3	544.3	547.5	552.1	562.1	569.9
55°	477.1	469.9	466.7	465.1	466.7	469.9	477.1	482.6	489.0	500.1	508.0
57.5°	411.0	409.1	406.6	408.3	406.6	409.1	411.0	420.2	426.4	435.2	444.8
60°	372.2	372.2	372.2	371.4	372.2	372.2	372.2	380.2	385.8	394.5	404.8
62.5°	342.4	340.5	339.9	341.0	339.9	340.5	342.4	345.9	351.4	357.0	366.1
65°	296.9	296.1	292.9	292.1	292.9	296.1	296.9	299.2	304.0	308.0	314.3
67.5°	253.9	251.0	250.0	248.9	250.0	251.0	253.9	255.9	259.0	264.2	267.3
70°	221.5	219.8	215.1	215.9	215.1	219.8	221.5	225.4	228.6	234.9	238.1
72.5°	186.5	184.9	184.0	182.9	184.0	184.9	186.5	190.5	193.7	200.7	205.7
75°	147.6	146.8	146.0	149.3	146.0	146.8	147.6	148.5	149.3	151.6	154.0
77.5°	118.3	118.3	118.8	117.4	118.8	118.3	118.3	118.3	118.3	119.6	120.0
80°	99.2	99.2	98.5	98.5	98.5	99.2	99.2	99.2	99.2	99.2	98.5
82.5°	79.6	80.2	80.7	79.4	80.7	80.2	79.6	80.8	81.4	80.2	80.7
85°	52.4	51.6	53.2	52.4	53.2	51.6	52.4	52.4	50.8	52.4	51.6
87.5°	26.8	25.5	25.7	26.4	25.7	25.5	26.8	25.4	25.4	25.2	24.5
90°	16.6	16.8	17.1	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8
92.5°	18.7	18.8	19.0	19.1	19.0	18.8	18.7	18.5	18.0	17.2	16.4
95°	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.4	20.5	19.7
97.5°	23.3	23.4	23.6	23.7	23.6	23.4	23.3	23.2	22.6	21.6	20.6
100°	23.8	23.9	24.0	24.2	24.0	23.9	23.8	23.6	23.1	22.1	21.0
102.5°	23.9	24.2	24.4	24.6	24.4	24.2	23.9	23.7	25.2	28.4	31.5
105°	24.5	24.8	25.0	25.3	25.0	24.8	24.5	24.3	35.5	58.2	80.8
107.5°	130.8	113.7	96.6	79.6	96.6	113.7	130.8	147.9	164.7	181.4	197.9
110°	213.3	195.0	176.7	158.3	176.7	195.0	213.3	231.6	242.9	247.1	251.4



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	283.4	279.4	275.6	271.8	275.6	279.4	283.4	287.2	289.1	289.0	288.9
115°	337.1	337.7	338.2	338.7	338.2	337.7	337.1	336.6	335.8	334.5	333.2
117.5°	376.0	376.1	376.2	376.3	376.2	376.1	376.0	375.9	375.3	374.3	373.2
120°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	401.5	400.5	399.5
122.5°	427.1	427.2	427.3	427.4	427.3	427.2	427.1	427.0	426.6	425.9	425.2
125°	462.3	462.6	462.8	463.1	462.8	462.6	462.3	462.1	461.8	461.5	461.3
127.5°	498.2	498.0	497.7	497.5	497.7	498.0	498.2	498.5	498.4	498.0	497.6
130°	520.3	520.1	519.8	519.6	519.8	520.1	520.3	520.6	520.4	519.9	519.4
132.5°	540.9	540.5	540.2	539.8	540.2	540.5	540.9	541.3	541.2	540.7	540.2
135°	572.0	571.6	571.2	570.8	571.2	571.6	572.0	572.3	572.3	572.0	571.6
137.5°	600.7	600.5	600.2	600.0	600.2	600.5	600.7	601.0	600.8	600.2	599.6
140°	618.2	617.9	617.7	617.4	617.7	617.9	618.2	618.4	618.3	617.8	617.3
142.5°	634.7	634.3	633.9	633.6	633.9	634.3	634.7	635.0	635.0	634.6	634.2
145°	658.3	658.3	658.3	658.3	658.3	658.3	658.3	658.3	658.2	657.9	657.7
147.5°	678.5	677.9	677.4	676.8	677.4	677.9	678.5	679.1	679.3	679.0	678.8
150°	691.8	691.4	690.9	690.6	690.9	691.4	691.8	692.2	692.2	692.0	691.7
152.5°	703.5	702.9	702.3	701.7	702.3	702.9	703.5	704.0	704.1	703.6	703.2
155°	719.4	718.6	717.9	717.1	717.9	718.6	719.4	720.1	720.2	719.6	718.9
157.5°	733.1	732.2	731.1	730.1	731.1	732.2	733.1	734.1	734.3	733.5	732.7
160°	741.1	740.2	739.3	738.4	739.3	740.2	741.1	741.9	742.0	741.2	740.5
162.5°	748.6	747.8	747.0	746.3	747.0	747.8	748.6	749.4	749.4	748.5	747.6
165°	758.4	757.5	756.6	755.7	756.6	757.5	758.4	759.3	759.2	758.2	757.2
167.5°	765.6	764.6	763.6	762.4	763.6	764.6	765.6	766.6	766.6	765.6	764.6
170°	769.7	768.7	767.7	766.6	767.7	768.7	769.7	770.7	770.7	769.7	768.7
172.5°	772.3	771.2	770.0	768.9	770.0	771.2	772.3	773.5	773.5	772.4	771.4
175°	775.5	774.5	773.5	772.3	773.5	774.5	775.5	776.5	776.6	775.7	774.8
177.5°	776.5	775.5	774.5	773.5	774.5	775.5	776.5	777.5	777.6	776.8	776.0
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1769.7	1778.6	1787.5	1795.7	1808.5	1814.1	1822.4	1825.5	1835.1	1849.1	1860.5
5°	1662.0	1674.8	1691.4	1705.0	1726.4	1743.0	1761.3	1778.8	1799.4	1828.8	1854.9
7.5°	1570.7	1583.4	1603.4	1628.4	1652.0	1675.7	1700.6	1724.4	1753.9	1796.0	1837.8
10°	1510.5	1525.5	1549.3	1576.3	1605.7	1628.7	1658.1	1688.3	1724.7	1773.2	1823.2
12.5°	1458.3	1469.7	1497.3	1523.0	1556.2	1585.6	1614.3	1649.5	1691.1	1742.7	1802.8
15°	1375.5	1391.4	1418.4	1446.9	1481.9	1512.9	1550.1	1593.0	1633.5	1697.0	1770.0
17.5°	1292.3	1316.5	1344.5	1376.7	1402.7	1445.3	1485.8	1529.8	1579.6	1647.0	1727.2
20°	1239.0	1258.1	1284.2	1331.1	1365.2	1397.8	1435.0	1489.9	1535.8	1612.0	1695.4
22.5°	1194.0	1207.9	1237.3	1275.9	1315.7	1353.3	1391.2	1443.5	1500.3	1572.7	1663.0
25°	1127.1	1149.3	1171.5	1199.3	1242.1	1287.4	1328.7	1373.1	1433.5	1510.5	1608.1
27.5°	1061.9	1082.0	1103.9	1138.0	1170.5	1212.8	1256.0	1307.0	1371.7	1453.2	1552.2
30°	1020.0	1035.0	1055.6	1099.3	1128.6	1165.2	1216.0	1261.2	1321.5	1408.1	1512.9
32.5°	976.7	996.2	1018.9	1052.3	1088.6	1123.3	1169.6	1218.7	1280.3	1365.5	1472.8
35°	915.1	938.2	961.2	985.8	1022.3	1058.0	1096.9	1150.9	1213.6	1296.2	1401.7
37.5°	858.5	877.1	895.8	926.2	960.9	994.8	1031.2	1084.4	1143.5	1232.5	1329.3
40°	822.3	839.0	853.2	885.0	918.4	954.8	990.6	1037.4	1100.9	1184.3	1277.9
42.5°	782.9	798.3	817.7	843.7	879.6	910.4	946.1	990.4	1050.1	1134.7	1216.9
45°	723.9	741.3	758.0	782.6	818.3	848.5	880.2	922.3	983.4	1053.3	1126.3
47.5°	662.5	679.9	698.9	722.8	753.9	784.6	816.3	853.5	909.3	977.9	1027.0
50°	623.1	637.3	656.4	680.2	708.8	741.3	769.9	810.4	863.5	917.6	960.4
52.5°	582.4	595.4	617.0	642.1	668.8	696.9	727.4	762.1	810.2	861.0	895.0
55°	519.1	534.9	553.2	577.8	604.0	627.8	657.2	693.0	731.0	769.1	792.1
57.5°	459.9	473.0	488.5	513.8	536.5	565.0	591.3	619.1	654.4	683.1	698.1
60°	416.7	428.6	448.5	470.7	492.1	516.7	546.8	574.6	601.7	624.7	636.5
62.5°	376.1	389.9	407.2	427.5	450.8	474.1	500.5	523.8	547.6	567.5	575.6
65°	323.1	334.2	346.9	365.9	385.0	408.8	429.4	453.2	470.7	481.8	489.0
67.5°	274.8	282.1	291.8	304.5	323.2	344.0	364.0	382.5	397.2	404.8	411.1
70°	243.7	248.4	255.6	268.3	282.6	300.8	321.4	335.0	347.7	354.0	360.3
72.5°	212.6	218.6	225.1	235.3	247.0	260.1	275.1	291.8	298.7	306.4	310.2
75°	161.2	169.9	178.5	184.9	192.9	203.2	216.7	227.0	231.0	237.3	238.1
77.5°	121.6	123.5	129.9	137.7	144.4	151.9	160.5	169.7	171.6	174.9	177.0
80°	100.0	100.0	100.0	104.7	112.7	118.3	126.2	131.0	134.1	134.9	135.7
82.5°	80.3	80.3	79.7	80.7	83.5	86.5	93.8	99.2	101.8	101.3	99.6
85°	52.4	50.8	50.8	50.0	50.8	49.2	48.4	51.6	56.4	56.4	54.7
87.5°	24.4	23.7	24.0	23.0	22.1	21.1	18.9	19.3	19.1	21.3	20.4
90°	14.3	13.8	12.1	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6
92.5°	15.6	14.7	13.5	12.2	11.0	9.7	9.3	9.6	10.0	10.4	10.7
95°	18.8	17.9	16.5	15.0	13.6	12.2	14.1	19.4	24.6	29.9	35.1
97.5°	19.6	18.6	27.8	37.0	46.2	55.4	61.2	63.5	65.9	68.3	70.6
100°	20.0	19.0	39.0	59.0	78.9	98.9	107.6	105.0	102.5	99.9	97.4
102.5°	34.7	37.9	59.7	81.5	103.3	125.1	135.1	133.3	131.5	129.6	127.7
105°	103.5	126.1	137.6	149.2	160.7	172.2	177.2	175.8	174.5	173.1	171.7
107.5°	214.6	231.2	229.3	227.5	225.7	223.9	222.5	221.4	220.3	219.0	217.9
110°	255.5	259.7	258.3	256.9	255.5	254.2	252.9	251.9	250.9	249.8	248.8



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	288.9	288.8	287.4	286.0	284.6	283.2	282.0	281.0	280.1	279.2	278.3
115°	331.9	330.6	329.4	328.3	327.2	326.0	325.1	324.3	323.5	322.8	321.9
117.5°	372.2	371.1	370.6	370.0	369.4	368.8	368.0	367.1	366.2	365.2	364.3
120°	398.5	397.4	397.1	396.7	396.3	395.9	395.2	393.9	392.8	391.6	390.5
122.5°	424.4	423.7	423.2	422.7	422.2	421.7	421.0	420.1	419.1	418.2	417.3
125°	461.0	460.8	460.3	459.8	459.3	458.8	458.0	457.0	456.0	454.9	453.8
127.5°	497.2	496.8	496.1	495.5	494.8	494.2	493.4	492.4	491.4	490.4	489.4
130°	518.9	518.4	517.9	517.4	516.8	516.3	515.5	514.5	513.5	512.5	511.5
132.5°	539.7	539.2	538.7	538.3	537.9	537.5	536.7	535.7	534.7	533.7	532.7
135°	571.2	570.8	570.3	569.8	569.3	568.8	568.2	567.3	566.5	565.8	565.0
137.5°	599.0	598.3	598.0	597.7	597.4	597.2	596.5	595.6	594.6	593.7	592.7
140°	616.8	616.3	615.9	615.5	615.1	614.8	614.2	613.4	612.7	611.9	611.1
142.5°	633.8	633.4	633.0	632.6	632.2	631.8	631.3	630.5	629.8	628.9	628.1
145°	657.4	657.2	656.9	656.7	656.4	656.2	655.6	654.7	653.8	652.9	652.0
147.5°	678.5	678.3	678.0	677.7	677.5	677.2	676.8	676.2	675.7	675.1	674.5
150°	691.5	691.2	690.9	690.6	690.4	690.1	689.8	689.4	689.0	688.7	688.3
152.5°	702.7	702.3	702.1	702.0	701.8	701.7	701.5	701.3	701.0	700.9	700.7
155°	718.3	717.7	717.5	717.4	717.3	717.2	717.2	717.5	717.7	718.0	718.2
157.5°	732.0	731.1	731.2	731.4	731.5	731.6	731.7	731.7	731.7	731.8	731.8
160°	739.7	739.0	739.1	739.2	739.3	739.5	739.6	739.7	739.9	740.0	740.1
162.5°	746.8	745.9	746.0	746.2	746.3	746.4	746.6	747.0	747.3	747.6	748.0
165°	756.2	755.1	755.3	755.4	755.5	755.6	755.9	756.3	756.7	757.0	757.4
167.5°	763.6	762.4	762.4	762.4	762.4	762.4	762.8	763.3	763.8	764.3	764.8
170°	767.7	766.6	766.6	766.6	766.6	766.6	766.9	767.4	767.9	768.4	768.9
172.5°	770.4	769.4	769.3	769.2	769.1	769.0	769.2	769.8	770.4	771.1	771.7
175°	773.9	773.0	772.8	772.7	772.5	772.4	772.7	773.4	774.0	774.7	775.3
177.5°	775.2	774.4	774.3	774.2	774.1	774.0	774.2	774.7	775.2	775.7	776.2
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1864.3	1871.3	1880.2	1893.5	1903.7	1912.6	1914.5	1917.0	1923.4	1934.1	1942.4
5°	1876.3	1894.6	1924.0	1952.6	1983.5	2008.9	2032.8	2049.4	2065.3	2098.6	2125.6
7.5°	1872.6	1913.2	1959.2	2010.5	2062.4	2112.7	2159.4	2201.1	2242.7	2291.3	2346.7
10°	1870.0	1917.6	1979.5	2045.4	2117.7	2188.3	2256.5	2309.8	2371.7	2427.2	2497.8
12.5°	1857.9	1926.5	2000.5	2084.8	2173.5	2254.9	2344.8	2418.3	2489.1	2569.4	2651.5
15°	1842.2	1925.6	2019.2	2131.1	2266.0	2364.5	2456.6	2584.3	2671.7	2759.0	2876.5
17.5°	1813.5	1915.2	2032.3	2177.7	2290.2	2422.5	2561.0	2662.0	2779.7	2902.7	3009.0
20°	1790.6	1908.9	2039.8	2182.7	2326.4	2470.0	2604.2	2724.8	2846.3	2988.4	3075.6
22.5°	1767.8	1884.8	2020.8	2172.6	2327.0	2478.3	2630.2	2771.9	2908.5	3051.9	3163.3
25°	1719.2	1858.2	2005.7	2160.5	2312.9	2479.6	2660.6	2818.5	2987.6	3135.2	3240.8
27.5°	1670.0	1797.3	1944.3	2101.3	2270.7	2467.7	2680.6	2860.1	3029.5	3135.2	3168.4
30°	1625.6	1760.5	1895.4	2055.0	2238.3	2458.1	2684.3	2889.9	3028.9	3074.8	3040.7
32.5°	1580.4	1702.7	1836.3	1999.7	2194.4	2434.7	2689.5	2872.2	2955.8	2920.6	2781.7
35°	1501.0	1611.2	1740.6	1904.1	2128.0	2421.7	2668.5	2792.3	2771.7	2573.2	2311.3
37.5°	1415.8	1505.7	1625.6	1796.5	2059.1	2370.1	2578.3	2596.6	2418.0	2113.3	1810.8
40°	1348.6	1429.5	1552.6	1731.1	2005.7	2319.3	2487.5	2413.7	2136.7	1797.8	1545.4
42.5°	1283.1	1351.4	1470.0	1662.5	1954.9	2250.1	2352.3	2191.5	1871.9	1551.5	1321.9
45°	1172.4	1236.6	1355.6	1553.3	1851.0	2117.7	2104.2	1824.7	1504.9	1247.0	1056.4
47.5°	1067.2	1123.5	1235.2	1436.9	1728.9	1919.2	1793.0	1495.7	1224.4	1017.4	881.5
50°	992.9	1048.5	1159.6	1358.9	1631.1	1770.0	1589.8	1303.3	1054.9	883.4	775.5
52.5°	921.8	976.1	1077.7	1271.8	1513.0	1596.0	1402.5	1136.9	929.8	781.8	689.1
55°	822.3	863.5	954.8	1140.5	1320.8	1339.8	1143.8	921.5	750.8	647.7	584.2
57.5°	720.8	756.4	846.6	994.5	1120.8	1111.1	925.1	733.0	618.0	541.3	495.2
60°	654.8	689.7	769.1	896.2	991.4	958.1	787.4	632.6	534.2	477.9	441.3
62.5°	593.2	620.6	694.8	787.5	856.1	818.3	673.1	544.9	466.9	419.4	390.5
65°	504.0	526.2	585.7	634.2	672.3	635.8	515.1	426.3	369.9	336.6	316.7
67.5°	419.2	433.3	471.0	488.5	515.3	475.2	387.4	327.8	295.8	267.6	253.9
70°	365.9	376.2	396.1	410.3	417.5	376.2	311.1	267.5	240.4	220.7	212.0
72.5°	312.6	321.6	325.6	337.3	333.7	295.0	250.1	215.4	196.0	182.6	171.3
75°	238.9	242.9	238.9	234.2	223.8	196.8	165.9	148.5	134.1	127.7	123.8
77.5°	174.1	172.9	167.4	160.1	142.4	125.4	108.8	102.9	96.6	93.3	91.9
80°	134.1	131.0	126.2	114.3	99.2	87.4	83.3	79.4	77.0	73.0	72.2
82.5°	99.9	98.0	90.0	80.0	69.4	63.8	60.5	59.1	56.7	54.6	54.4
85°	53.2	50.8	42.1	36.6	34.9	33.3	32.5	32.5	29.4	28.6	28.6
87.5°	17.5	13.9	13.6	11.9	12.2	11.3	12.2	11.3	11.0	11.7	10.6
90°	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8
92.5°	10.4	10.0	9.6	9.3	9.7	11.0	12.2	13.5	14.7	15.6	16.4
95°	29.9	24.6	19.4	14.1	12.2	13.6	15.0	16.5	17.9	18.8	19.7
97.5°	68.3	65.9	63.5	61.2	55.4	46.2	37.0	27.8	18.6	19.6	20.6
100°	99.9	102.5	105.0	107.6	98.9	78.9	59.0	39.0	19.0	20.0	21.0
102.5°	129.6	131.5	133.3	135.1	125.1	103.3	81.5	59.7	37.9	34.7	31.5
105°	173.1	174.5	175.8	177.2	172.2	160.7	149.2	137.6	126.1	103.5	80.8
107.5°	219.0	220.3	221.4	222.5	223.9	225.7	227.5	229.3	231.2	214.6	197.9
110°	249.8	250.9	251.9	252.9	254.2	255.5	256.9	258.3	259.7	255.5	251.4





TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	279.2	280.1	281.0	282.0	283.2	284.6	286.0	287.4	288.8	288.9	288.9
115°	322.8	323.5	324.3	325.1	326.0	327.2	328.3	329.4	330.6	331.9	333.2
117.5°	365.2	366.2	367.1	368.0	368.8	369.4	370.0	370.6	371.1	372.2	373.2
120°	391.6	392.8	393.9	395.2	395.9	396.3	396.7	397.1	397.4	398.5	399.5
122.5°	418.2	419.1	420.1	421.0	421.7	422.2	422.7	423.2	423.7	424.4	425.2
125°	454.9	456.0	457.0	458.0	458.8	459.3	459.8	460.3	460.8	461.0	461.3
127.5°	490.4	491.4	492.4	493.4	494.2	494.8	495.5	496.1	496.8	497.2	497.6
130°	512.5	513.5	514.5	515.5	516.3	516.8	517.4	517.9	518.4	518.9	519.4
132.5°	533.7	534.7	535.7	536.7	537.5	537.9	538.3	538.7	539.2	539.7	540.2
135°	565.8	566.5	567.3	568.2	568.8	569.3	569.8	570.3	570.8	571.2	571.6
137.5°	593.7	594.6	595.6	596.5	597.2	597.4	597.7	598.0	598.3	599.0	599.6
140°	611.9	612.7	613.4	614.2	614.8	615.1	615.5	615.9	616.3	616.8	617.3
142.5°	628.9	629.8	630.5	631.3	631.8	632.2	632.6	633.0	633.4	633.8	634.2
145°	652.9	653.8	654.7	655.6	656.2	656.4	656.7	656.9	657.2	657.4	657.7
147.5°	675.1	675.7	676.2	676.8	677.2	677.5	677.7	678.0	678.3	678.5	678.8
150°	688.7	689.0	689.4	689.8	690.1	690.4	690.6	690.9	691.2	691.5	691.7
152.5°	700.9	701.0	701.3	701.5	701.7	701.8	702.0	702.1	702.3	702.7	703.2
155°	718.0	717.7	717.5	717.2	717.2	717.3	717.4	717.5	717.7	718.3	718.9
157.5°	731.8	731.7	731.7	731.7	731.6	731.5	731.4	731.2	731.1	732.0	732.7
160°	740.0	739.9	739.7	739.6	739.5	739.3	739.2	739.1	739.0	739.7	740.5
162.5°	747.6	747.3	747.0	746.6	746.4	746.3	746.2	746.0	745.9	746.8	747.6
165°	757.0	756.7	756.3	755.9	755.6	755.5	755.4	755.3	755.1	756.2	757.2
167.5°	764.3	763.8	763.3	762.8	762.4	762.4	762.4	762.4	762.4	763.6	764.6
170°	768.4	767.9	767.4	766.9	766.6	766.6	766.6	766.6	766.6	767.7	768.7
172.5°	771.1	770.4	769.8	769.2	769.0	769.1	769.2	769.3	769.4	770.4	771.4
175°	774.7	774.0	773.4	772.7	772.4	772.5	772.7	772.8	773.0	773.9	774.8
177.5°	775.7	775.2	774.7	774.2	774.0	774.1	774.2	774.3	774.4	775.2	776.0
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1955.7	1955.7	1958.2	1967.8	1969.0	1977.3	1974.8
5°	2149.4	2164.4	2170.0	2193.8	2208.2	2214.5	2201.8
7.5°	2386.2	2428.8	2448.9	2473.9	2496.0	2502.6	2485.3
10°	2559.0	2603.4	2640.7	2663.7	2685.1	2699.5	2717.7
12.5°	2725.9	2780.6	2816.0	2848.5	2870.5	2888.7	2891.6
15°	2907.4	2989.9	3052.6	3098.7	3121.7	3133.6	3128.9
17.5°	3090.4	3166.9	3211.6	3258.5	3290.4	3292.1	3293.0
20°	3193.9	3268.5	3320.1	3355.1	3390.8	3389.2	3397.1
22.5°	3263.2	3321.8	3361.4	3386.8	3399.0	3393.0	3394.6
25°	3295.5	3313.0	3305.9	3265.4	3255.1	3217.7	3224.1
27.5°	3128.6	3046.0	2960.6	2850.7	2764.1	2694.8	2698.4
30°	2901.8	2755.8	2589.1	2449.4	2324.0	2289.1	2214.5
32.5°	2585.0	2365.9	2170.7	2040.5	1932.9	1903.7	1838.6
35°	2047.8	1835.1	1634.3	1513.6	1466.0	1399.4	1398.6
37.5°	1591.7	1404.4	1298.2	1207.7	1160.2	1119.9	1116.0
40°	1339.0	1193.0	1112.8	1047.7	1000.9	970.7	963.6
42.5°	1162.5	1044.4	969.3	929.0	892.9	877.4	865.8
45°	949.3	869.9	817.5	781.0	764.4	752.5	746.1
47.5°	794.1	740.8	705.2	680.9	667.3	654.8	658.1
50°	709.6	665.9	639.7	616.7	606.4	597.6	598.4
52.5°	641.7	602.5	581.3	564.6	551.8	545.6	542.6
55°	544.5	519.9	498.5	486.6	479.4	470.7	468.3
57.5°	464.4	445.5	428.0	414.4	412.7	404.3	405.5
60°	411.1	395.3	381.0	373.9	368.3	361.1	363.6
62.5°	367.3	354.0	341.0	335.1	329.5	324.3	325.4
65°	300.8	288.1	280.1	277.0	274.6	272.3	269.8
67.5°	239.7	232.0	227.0	220.2	215.3	214.5	212.1
70°	201.6	191.3	182.6	173.8	171.5	170.7	171.5
72.5°	161.6	155.1	152.7	148.5	147.9	145.9	147.3
75°	121.5	119.1	117.4	114.3	114.3	114.3	114.3
77.5°	89.6	88.1	87.2	86.5	85.7	84.6	84.4
80°	69.9	69.1	67.5	67.5	66.7	67.5	66.7
82.5°	52.7	52.5	51.0	51.0	50.2	49.7	50.2
85°	27.0	26.2	27.8	26.2	27.0	25.4	27.0
87.5°	10.7	10.8	10.2	10.3	9.7	11.0	9.8
90°	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	17.2	18.0	18.5	18.7	18.8	19.0	19.1
95°	20.5	21.4	21.9	21.9	21.9	21.9	21.9
97.5°	21.6	22.6	23.2	23.3	23.4	23.6	23.7
100°	22.1	23.1	23.6	23.8	23.9	24.0	24.2
102.5°	28.4	25.2	23.7	23.9	24.2	24.4	24.6
105°	58.2	35.5	24.3	24.5	24.8	25.0	25.3
107.5°	181.4	164.7	147.9	130.8	113.7	96.6	79.6
110°	247.1	242.9	231.6	213.3	195.0	176.7	158.3



TEST NUMBER: P332366-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	289.0	289.1	287.2	283.4	279.4	275.6	271.8
115°	334.5	335.8	336.6	337.1	337.7	338.2	338.7
117.5°	374.3	375.3	375.9	376.0	376.1	376.2	376.3
120°	400.5	401.5	402.0	402.0	402.0	402.0	402.0
122.5°	425.9	426.6	427.0	427.1	427.2	427.3	427.4
125°	461.5	461.8	462.1	462.3	462.6	462.8	463.1
127.5°	498.0	498.4	498.5	498.2	498.0	497.7	497.5
130°	519.9	520.4	520.6	520.3	520.1	519.8	519.6
132.5°	540.7	541.2	541.3	540.9	540.5	540.2	539.8
135°	572.0	572.3	572.3	572.0	571.6	571.2	570.8
137.5°	600.2	600.8	601.0	600.7	600.5	600.2	600.0
140°	617.8	618.3	618.4	618.2	617.9	617.7	617.4
142.5°	634.6	635.0	635.0	634.7	634.3	633.9	633.6
145°	657.9	658.2	658.3	658.3	658.3	658.3	658.3
147.5°	679.0	679.3	679.1	678.5	677.9	677.4	676.8
150°	692.0	692.2	692.2	691.8	691.4	690.9	690.6
152.5°	703.6	704.1	704.0	703.5	702.9	702.3	701.7
155°	719.6	720.2	720.1	719.4	718.6	717.9	717.1
157.5°	733.5	734.3	734.1	733.1	732.2	731.1	730.1
160°	741.2	742.0	741.9	741.1	740.2	739.3	738.4
162.5°	748.5	749.4	749.4	748.6	747.8	747.0	746.3
165°	758.2	759.2	759.3	758.4	757.5	756.6	755.7
167.5°	765.6	766.6	766.6	765.6	764.6	763.6	762.4
170°	769.7	770.7	770.7	769.7	768.7	767.7	766.6
172.5°	772.4	773.5	773.5	772.3	771.2	770.0	768.9
175°	775.7	776.6	776.5	775.5	774.5	773.5	772.3
177.5°	776.8	777.6	777.5	776.5	775.5	774.5	773.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3

(END OF REPORT)