

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906912

Luminaire Tested: DFN2DIP-SQ4F0-120D160US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906912
REPORT IS A COMBINATION OF REPORTS P900215 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D160US835-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26041.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 239.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906912

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906912

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3276	3276	3276
5°	3282	3231	3253
10°	3255	3188	3210
15°	3207	3137	3142
20°	3142	3064	3073
25°	3078	2978	2992
30°	2997	2897	2890
35°	2921	2802	2781
40°	2827	2706	2678
45°	2733	2610	2572
50°	2630	2509	2449
55°	2523	2392	2337
60°	2401	2254	2209
65°	2269	2110	2057
70°	2100	1935	1894
75°	1867	1726	1745
80°	1586	1460	1458
85°	1146	999	980

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3982 cd/sqm

TEST NUMBER: P906912

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.5	1.7
10°-20°	1236.5	4.7
20°-30°	1817.2	7.0
30°-40°	2110.5	8.1
40°-50°	2107.9	8.1
50°-60°	1838.0	7.1
60°-70°	1358.7	5.2
70°-80°	768.7	3.0
80°-90°	217.3	0.8
90°-100°	313.1	1.2
100°-110°	995.0	3.8
110°-120°	1702.7	6.5
120°-130°	2239.3	8.6
130°-140°	2513.5	9.7
140°-150°	2464.8	9.5
150°-160°	2067.6	7.9
160°-170°	1371.2	5.3
170°-180°	479.3	1.8
0°-30°	3493.1	13.4
0°-40°	5603.7	21.5
0°-60°	9549.6	36.7
0°-90°	11894.4	45.7
90°-120°	3010.8	11.6
90°-150°	10228.5	39.3
90°-180°	14147.0	54.3
0°-180°	26041.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4669	4669	4669	4669	4669	
5°	4669	4652	4602	4638	4629	443
15°	4445	4418	4360	4378	4355	1252
25°	4023	3987	3911	3920	3911	1851
35°	3471	3426	3354	3327	3304	2167
45°	2824	2793	2725	2676	2658	2180
55°	2137	2110	2056	2003	1980	1911
65°	1442	1414	1370	1329	1307	1425
75°	754	746	723	696	705	805
85°	184	180	175	162	157	205
90°	5	55	150	140	145	25
95°	223	266	273	273	266	248
105°	918	931	940	947	947	969
115°	1709	1733	1726	1721	1709	1690
125°	2485	2523	2511	2498	2493	2221
135°	3214	3262	3271	3266	3254	2485
145°	3903	3933	3958	3962	3945	2438
155°	4462	4475	4488	4510	4496	2054
165°	4855	4850	4850	4880	4859	1369
175°	5051	5039	5030	5061	5035	480
180°	5061	5061	5061	5061	5061	

TEST NUMBER: P906912

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4669.3	4669.3	4669.3	4669.3	4669.3
2.5°	4696.4	4674.0	4624.5	4669.3	4660.7
5°	4669.3	4651.6	4602.1	4637.8	4629.2
7.5°	4637.8	4611.1	4561.6	4597.8	4588.8
10°	4588.8	4557.3	4503.5	4539.2	4525.9
12.5°	4521.1	4494.4	4440.6	4463.0	4453.9
15°	4444.9	4418.2	4359.6	4377.7	4355.3
17.5°	4350.6	4323.9	4265.3	4287.7	4265.3
20°	4247.2	4220.5	4157.7	4171.0	4153.4
22.5°	4144.3	4103.8	4045.2	4045.2	4036.2
25°	4022.8	3987.1	3910.9	3919.5	3910.9
27.5°	3888.0	3856.6	3798.5	3785.1	3762.8
30°	3753.7	3717.5	3650.3	3637.0	3618.9
32.5°	3609.8	3583.2	3511.2	3484.1	3466.0
35°	3470.7	3426.0	3354.0	3326.9	3304.5
37.5°	3313.5	3273.1	3201.1	3169.7	3147.3
40°	3152.1	3115.9	3043.9	3003.9	2985.8
42.5°	2994.9	2958.7	2887.2	2842.0	2815.3
45°	2824.3	2792.9	2725.2	2676.2	2658.1
47.5°	2658.1	2626.6	2554.7	2505.2	2478.5
50°	2482.8	2460.4	2397.5	2334.6	2312.2
52.5°	2312.2	2280.8	2222.7	2173.1	2141.7
55°	2137.4	2110.3	2056.4	2002.6	1980.2
57.5°	1962.1	1939.7	1881.1	1827.3	1809.2
60°	1786.8	1769.2	1706.3	1656.8	1643.4
62.5°	1616.3	1584.8	1540.1	1495.3	1477.2
65°	1441.5	1414.3	1369.5	1329.0	1306.7
67.5°	1261.9	1239.0	1199.0	1167.6	1149.5
70°	1095.6	1077.5	1037.0	1005.6	988.0
72.5°	925.1	907.0	884.6	853.2	839.8
75°	754.1	745.5	722.6	696.0	705.0
77.5°	601.6	583.5	574.5	561.1	547.8
80°	449.2	444.4	435.4	422.1	413.0
82.5°	305.3	305.3	301.1	283.0	283.0
85°	183.9	179.6	175.3	161.5	157.2
87.5°	81.0	71.9	62.9	49.5	44.8
90°	4.6	54.9	149.5	140.4	144.9
92.5°	94.6	128.2	132.7	137.3	137.3
95°	222.7	265.5	273.1	273.1	265.5
97.5°	370.7	410.4	427.2	427.2	427.2
100°	541.6	576.7	588.9	588.9	584.3
102.5°	721.6	747.6	764.3	768.9	764.3
105°	918.4	930.6	939.8	947.4	947.4
107.5°	1113.7	1132.0	1132.0	1135.1	1113.7
110°	1302.9	1327.3	1327.3	1327.3	1315.1

TEST NUMBER: P906912

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1507.3	1533.3	1528.7	1516.5	1507.3
115°	1708.7	1733.1	1725.5	1720.9	1708.7
117.5°	1908.6	1942.1	1920.8	1908.6	1896.4
120°	2110.0	2143.5	2110.0	2110.0	2096.2
122.5°	2293.0	2335.8	2314.4	2302.2	2293.0
125°	2485.3	2523.4	2511.2	2497.5	2492.9
127.5°	2672.9	2720.2	2703.4	2685.1	2672.9
130°	2848.4	2903.3	2895.7	2886.5	2869.7
132.5°	3045.2	3087.9	3090.9	3069.6	3057.4
135°	3214.5	3261.8	3271.0	3266.4	3254.2
137.5°	3403.7	3441.8	3449.5	3446.4	3428.1
140°	3570.0	3608.1	3629.5	3629.5	3612.7
142.5°	3740.9	3779.0	3791.2	3795.8	3779.0
145°	3902.6	3933.1	3957.5	3962.1	3945.3
147.5°	4047.5	4085.7	4104.0	4111.6	4094.8
150°	4197.0	4223.0	4239.8	4253.5	4239.8
152.5°	4329.8	4355.7	4377.1	4393.8	4377.1
155°	4462.5	4474.7	4488.4	4509.8	4496.1
157.5°	4576.9	4586.1	4593.7	4624.2	4602.9
160°	4679.1	4688.3	4692.9	4718.8	4700.5
162.5°	4773.7	4773.7	4778.3	4807.3	4785.9
165°	4854.6	4850.0	4850.0	4880.5	4859.2
167.5°	4927.8	4914.1	4914.1	4944.6	4923.2
170°	4982.7	4970.5	4966.0	4996.5	4970.5
172.5°	5020.9	5008.7	5004.1	5034.6	5008.7
175°	5051.4	5039.2	5030.0	5060.6	5034.6
177.5°	5068.2	5056.0	5046.8	5072.8	5046.8
180°	5060.6	5060.6	5060.6	5060.6	5060.6

TEST NUMBER: P906912

CATALOG NUMBER: DFN2DIP-SQ4F0-120D160US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.99	11.82	11.99	12.82	14.15	10.55	11.37	11.54	12.38	13.71
	3H	12.65	13.39	13.66	14.41	15.76	12.16	12.90	13.17	13.92	15.27
	4H	13.24	13.94	14.26	14.96	16.32	12.75	13.45	13.77	14.47	15.83
	6H	13.64	14.29	14.67	15.31	16.68	13.14	13.79	14.17	14.81	16.18
	8H	13.75	14.36	14.78	15.40	16.77	13.25	13.86	14.28	14.90	16.27
	12H	13.80	14.38	14.84	15.41	16.81	13.29	13.87	14.33	14.90	16.30
4H	2H	11.45	12.15	12.47	13.17	14.53	11.09	11.79	12.12	12.81	14.17
	3H	13.32	13.90	14.35	14.95	16.32	12.91	13.49	13.94	14.54	15.91
	4H	14.03	14.57	15.07	15.60	17.00	13.61	14.14	14.65	15.18	16.58
	6H	14.55	15.01	15.60	16.07	17.46	14.12	14.58	15.17	15.64	17.03
	8H	14.70	15.13	15.75	16.18	17.59	14.26	14.69	15.31	15.75	17.15
	12H	14.77	15.16	15.84	16.23	17.64	14.32	14.71	15.39	15.78	17.19
8H	4H	14.23	14.66	15.28	15.71	17.12	13.85	14.28	14.90	15.33	16.74
	6H	14.86	15.22	15.93	16.31	17.72	14.48	14.83	15.55	15.93	17.33
	8H	15.08	15.40	16.16	16.48	17.90	14.69	15.00	15.77	16.08	17.51
	12H	15.22	15.49	16.30	16.57	18.03	14.81	15.08	15.89	16.16	17.62
12H	4H	14.21	14.60	15.28	15.67	17.08	13.84	14.23	14.91	15.30	16.71
	6H	14.89	15.20	15.97	16.28	17.71	14.52	14.83	15.60	15.91	17.33
	8H	15.13	15.41	16.22	16.48	17.95	14.75	15.03	15.84	16.10	17.57

END OF REPORT