

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332024-940

Luminaire Tested: **S123DIP-S1000D805U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332024-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6536.9 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332024-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332024-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37	33
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15193	15193	15193
5°	15263	15055	15159
10°	15162	14924	15017
15°	14985	14755	14782
20°	14778	14513	14528
25°	14500	14226	14197
30°	14194	13908	13801
35°	13875	13571	13397
40°	13541	13198	12995
45°	13172	12858	12543
50°	12804	12439	12092
55°	12322	12003	11639
60°	11834	11496	11130
65°	11405	10942	10603
70°	10770	10313	9854
75°	9844	9491	9087
80°	8877	8498	8424
85°	7793	7497	7188



TEST NUMBER: P332024-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	2.0
10°-20°	375.4	5.7
20°-30°	554.6	8.5
30°-40°	647.8	9.9
40°-50°	651.3	10.0
50°-60°	572.1	8.8
60°-70°	426.2	6.5
70°-80°	242.8	3.7
80°-90°	72.3	1.1
90°-100°	34.1	0.5
100°-110°	162.6	2.5
110°-120°	390.6	6.0
120°-130°	497.3	7.6
130°-140°	531.4	8.1
140°-150°	496.9	7.6
150°-160°	400.8	6.1
160°-170°	258.7	4.0
170°-180°	89.2	1.4
0°-30°	1062.9	16.3
0°-40°	1710.7	26.2
0°-60°	2934.1	44.9
0°-90°	3675.4	56.2
90°-120°	587.3	9.0
90°-150°	2112.9	32.3
90°-180°	2862.0	43.8
0°-180°	6536.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1413	1406	1393	1405	1403	134
15°	1345	1339	1324	1333	1326	379
25°	1221	1213	1198	1199	1195	562
35°	1056	1048	1033	1026	1020	660
45°	865	860	845	831	824	668
55°	657	655	640	627	620	588
65°	448	441	430	420	416	442
75°	237	232	228	222	218	253
85°	63	61	61	58	58	69
90°	1	8	17	19	21	5
95°	42	16	22	26	26	53
105°	208	212	153	36	31	220
115°	390	394	400	407	410	385
125°	549	555	558	559	560	490
135°	684	688	691	693	691	526
145°	789	794	795	797	797	494
155°	869	868	869	872	868	400
165°	917	915	914	919	915	259
175°	938	935	936	940	935	89
180°	938	938	938	938	938	



TEST NUMBER: P332024-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1416.3	1415.5	1414.6	1413.7	1412.9	1411.2	1408.9	1406.5	1404.2	1401.8	1403.9
5°	1412.6	1411.3	1410.0	1408.6	1407.3	1405.2	1402.2	1399.2	1396.2	1393.3	1396.0
7.5°	1398.8	1397.5	1396.2	1394.8	1393.5	1391.2	1388.2	1385.1	1382.1	1378.9	1381.3
10°	1387.2	1385.9	1384.5	1383.1	1381.8	1379.4	1375.9	1372.3	1368.9	1365.4	1367.8
12.5°	1371.6	1370.6	1369.4	1368.2	1367.2	1364.9	1361.6	1358.3	1355.0	1351.7	1353.5
15°	1344.7	1343.6	1342.6	1341.5	1340.4	1338.1	1334.6	1331.1	1327.6	1324.1	1326.2
17.5°	1313.4	1312.0	1310.6	1309.2	1307.8	1305.4	1301.8	1298.3	1294.9	1291.3	1292.8
20°	1290.1	1288.5	1286.9	1285.2	1283.6	1281.0	1277.6	1274.1	1270.6	1267.0	1268.1
22.5°	1263.9	1262.3	1260.7	1259.0	1257.4	1254.9	1251.3	1247.9	1244.4	1240.8	1241.7
25°	1220.9	1219.3	1217.7	1216.1	1214.4	1211.9	1208.4	1204.9	1201.4	1197.8	1198.1
27.5°	1175.1	1173.5	1171.9	1170.4	1168.8	1166.1	1162.3	1158.6	1154.8	1151.0	1151.2
30°	1142.0	1140.7	1139.3	1138.0	1136.7	1134.1	1130.3	1126.5	1122.8	1119.0	1119.0
32.5°	1109.0	1107.2	1105.5	1103.7	1101.9	1099.6	1096.6	1093.8	1090.8	1087.9	1086.4
35°	1055.9	1054.3	1052.7	1051.1	1049.4	1046.9	1043.3	1039.8	1036.3	1032.8	1031.2
37.5°	1001.5	999.4	997.4	995.3	993.3	990.5	986.9	983.4	979.8	976.2	974.3
40°	963.7	962.0	960.4	958.8	957.2	954.5	950.7	946.9	943.2	939.3	937.2
42.5°	925.8	923.9	922.1	920.2	918.5	915.6	911.9	908.1	904.3	900.5	898.4
45°	865.3	864.2	863.2	862.1	861.0	858.7	855.2	851.7	848.2	844.7	841.5
47.5°	805.4	803.8	802.3	800.7	799.2	796.7	793.4	790.1	786.8	783.5	780.3
50°	764.6	763.2	761.9	760.5	759.2	756.8	753.2	749.8	746.3	742.8	739.8
52.5°	721.8	720.9	720.1	719.2	718.2	715.9	712.2	708.5	704.7	701.0	698.5
55°	656.6	656.3	656.0	655.8	655.5	653.6	650.1	646.6	643.1	639.6	636.6
57.5°	594.4	593.5	592.6	591.7	590.8	588.9	586.1	583.3	580.5	577.7	575.1
60°	549.7	549.5	549.2	548.9	548.7	547.0	543.7	540.5	537.3	534.0	531.5
62.5°	510.0	509.3	508.5	507.8	507.2	505.2	501.9	498.7	495.5	492.2	489.8
65°	447.8	446.5	445.1	443.8	442.5	440.4	437.7	435.1	432.3	429.6	427.5
67.5°	382.1	380.8	379.7	378.5	377.3	375.7	373.6	371.6	369.5	367.5	365.6
70°	342.2	340.6	339.0	337.4	335.8	334.1	332.5	330.9	329.3	327.7	325.8
72.5°	300.5	299.3	298.1	296.9	295.8	294.3	292.4	290.6	288.7	286.9	285.3
75°	236.7	235.6	234.5	233.4	232.4	231.4	230.6	229.8	229.0	228.2	226.9
77.5°	180.1	179.5	178.9	178.3	177.7	176.9	176.0	175.0	174.1	173.1	172.2
80°	143.2	142.4	141.6	140.8	140.0	139.3	138.8	138.2	137.7	137.1	136.9
82.5°	107.3	107.1	107.0	106.8	106.6	106.5	106.4	106.3	106.2	106.1	105.6
85°	63.1	62.6	62.1	61.5	61.0	60.7	60.7	60.7	60.7	60.7	60.1
87.5°	25.4	25.1	24.7	24.3	24.1	24.0	24.2	24.3	24.5	24.7	24.6
90°	0.7	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4
92.5°	12.9	12.6	12.1	11.7	11.2	11.8	13.3	14.8	16.3	17.8	18.8
95°	42.5	36.2	29.8	23.5	17.1	14.8	16.5	18.2	19.9	21.6	22.7
97.5°	85.4	82.7	79.8	77.0	74.1	67.1	55.9	44.8	33.6	22.5	23.7
100°	117.8	120.9	124.0	127.1	130.2	119.7	95.5	71.3	47.2	23.0	24.3
102.5°	154.6	156.9	159.1	161.3	163.5	151.5	125.1	98.6	72.2	45.8	42.0
105°	207.8	209.5	211.2	212.9	214.5	208.5	194.5	180.6	166.6	152.7	125.3
107.5°	263.8	265.2	266.5	267.9	269.2	271.0	273.2	275.4	277.6	279.8	259.8
110°	301.1	302.4	303.6	304.9	306.1	307.6	309.3	311.0	312.7	314.4	309.3



TEST NUMBER: P332024-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.9	338.0	339.1	340.2	341.3	342.7	344.5	346.2	347.9	349.6	349.6
115°	389.7	390.7	391.6	392.5	393.4	394.6	396.0	397.3	398.8	400.2	401.7
117.5°	440.9	442.0	443.2	444.3	445.4	446.4	447.1	447.8	448.5	449.2	450.5
120°	472.7	474.0	475.5	476.8	478.2	479.2	479.7	480.1	480.5	481.0	482.2
122.5°	505.0	506.1	507.3	508.5	509.6	510.4	511.0	511.7	512.2	512.8	513.7
125°	549.4	550.5	551.8	553.0	554.3	555.3	555.9	556.4	557.1	557.7	558.0
127.5°	592.3	593.5	594.8	596.0	597.3	598.2	599.0	599.8	600.5	601.2	601.7
130°	619.0	620.3	621.5	622.8	624.0	624.9	625.5	626.2	626.8	627.4	628.0
132.5°	644.7	646.0	647.2	648.5	649.7	650.5	651.0	651.5	652.0	652.6	653.2
135°	683.9	684.8	685.7	686.7	687.6	688.4	689.0	689.6	690.3	690.9	691.3
137.5°	717.4	718.5	719.7	720.9	722.0	722.8	723.2	723.5	723.8	724.2	725.0
140°	739.7	740.6	741.5	742.4	743.4	744.0	744.6	745.0	745.5	745.9	746.5
142.5°	760.3	761.3	762.1	763.1	764.0	764.7	765.2	765.6	766.1	766.6	767.0
145°	789.2	790.2	791.3	792.4	793.5	794.2	794.5	794.8	795.1	795.4	795.8
147.5°	816.4	817.1	817.8	818.5	819.2	819.7	820.0	820.3	820.6	820.9	821.3
150°	833.0	833.6	834.0	834.5	834.9	835.4	835.6	836.0	836.2	836.6	836.9
152.5°	848.1	848.4	848.6	848.8	849.0	849.2	849.4	849.5	849.8	850.0	850.5
155°	869.3	869.1	868.7	868.4	868.1	868.0	868.2	868.3	868.4	868.6	869.4
157.5°	885.7	885.7	885.7	885.6	885.6	885.6	885.4	885.3	885.1	884.9	885.9
160°	895.8	895.6	895.5	895.4	895.2	895.0	894.9	894.7	894.6	894.4	895.4
162.5°	905.3	904.9	904.5	904.1	903.7	903.4	903.2	903.1	902.9	902.8	903.8
165°	916.8	916.2	915.8	915.3	914.9	914.5	914.4	914.3	914.1	913.9	915.2
167.5°	925.7	925.1	924.4	923.8	923.2	922.8	922.8	922.8	922.8	922.8	924.1
170°	930.7	930.1	929.4	928.8	928.2	927.9	927.9	927.9	927.9	927.9	929.2
172.5°	934.0	933.3	932.6	931.7	931.0	930.8	930.9	930.9	931.1	931.2	932.5
175°	938.3	937.5	936.8	936.0	935.2	935.0	935.0	935.2	935.4	935.6	936.7
177.5°	939.4	938.9	938.3	937.6	937.0	936.7	936.8	937.0	937.1	937.2	938.3
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332024-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1406.0	1408.3	1410.4	1411.4	1411.1	1411.0	1410.7	1410.5
5°	1398.6	1401.3	1404.1	1405.2	1404.6	1404.1	1403.6	1403.0
7.5°	1383.8	1386.3	1388.7	1389.7	1389.4	1389.1	1388.8	1388.4
10°	1370.2	1372.6	1375.1	1376.0	1375.5	1374.9	1374.4	1373.9
12.5°	1355.3	1357.1	1358.9	1359.6	1359.3	1359.0	1358.6	1358.3
15°	1328.4	1330.5	1332.8	1333.0	1331.4	1329.7	1328.1	1326.5
17.5°	1294.3	1295.8	1297.4	1297.8	1297.3	1296.6	1296.0	1295.5
20°	1269.2	1270.3	1271.4	1271.5	1270.7	1269.9	1269.1	1268.3
22.5°	1242.6	1243.4	1244.3	1244.2	1243.2	1242.2	1241.2	1240.1
25°	1198.4	1198.7	1199.0	1198.7	1197.8	1197.0	1196.2	1195.4
27.5°	1151.5	1151.6	1151.9	1151.5	1150.5	1149.4	1148.4	1147.4
30°	1119.0	1119.0	1119.0	1118.0	1116.2	1114.3	1112.4	1110.4
32.5°	1084.9	1083.4	1081.9	1080.6	1079.6	1078.5	1077.5	1076.5
35°	1029.6	1028.0	1026.4	1024.8	1023.5	1022.2	1020.8	1019.5
37.5°	972.4	970.4	968.5	967.1	966.3	965.4	964.5	963.7
40°	935.0	932.9	930.8	929.1	928.0	926.9	925.9	924.8
42.5°	896.2	894.0	891.9	890.3	889.2	888.1	887.1	886.0
45°	838.2	835.0	831.8	829.5	828.1	826.8	825.5	824.0
47.5°	777.1	774.0	770.8	768.7	767.4	766.2	765.1	763.8
50°	736.8	733.9	730.8	728.6	727.0	725.3	723.7	722.1
52.5°	695.9	693.4	690.9	688.8	687.2	685.5	683.9	682.3
55°	633.6	630.7	627.8	625.5	624.2	622.9	621.5	620.2
57.5°	572.4	569.8	567.1	565.0	563.5	561.9	560.4	558.7
60°	529.1	526.7	524.3	522.5	521.0	519.7	518.4	517.0
62.5°	487.4	485.0	482.5	480.9	479.9	479.0	478.1	477.2
65°	425.3	423.1	421.0	419.5	418.7	417.9	417.1	416.3
67.5°	363.7	361.9	360.0	358.5	357.3	356.1	355.0	353.9
70°	323.9	322.0	320.1	318.5	317.2	315.8	314.5	313.1
72.5°	283.6	281.9	280.2	279.0	278.3	277.6	277.0	276.3
75°	225.5	224.1	222.7	221.7	220.9	220.1	219.3	218.5
77.5°	171.2	170.3	169.4	169.0	169.0	169.0	169.0	169.0
80°	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9
82.5°	105.1	104.6	104.2	103.8	103.5	103.3	103.2	102.9
85°	59.6	59.0	58.5	58.2	58.2	58.2	58.2	58.2
87.5°	24.5	24.4	24.3	24.3	24.3	24.4	24.5	24.6
90°	18.0	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	19.8	20.8	21.8	22.4	22.6	22.7	22.9	23.2
95°	23.8	24.9	25.9	26.5	26.5	26.5	26.5	26.5
97.5°	25.0	26.1	27.4	28.1	28.3	28.4	28.5	28.7
100°	25.5	26.8	28.0	28.6	28.8	29.0	29.2	29.2
102.5°	38.2	34.3	30.5	28.7	29.0	29.2	29.5	29.9
105°	97.8	70.4	43.0	29.4	29.8	30.1	30.4	30.7
107.5°	239.6	219.5	199.4	179.0	158.4	137.7	117.0	96.3
110°	304.2	299.1	294.0	280.4	258.2	236.0	213.8	191.7



TEST NUMBER: P332024-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	349.7	349.8	349.9	347.6	343.0	338.2	333.6	329.0
115°	403.2	404.8	406.4	407.4	408.0	408.7	409.3	409.9
117.5°	451.7	453.0	454.1	454.9	455.0	455.1	455.2	455.4
120°	483.5	484.7	486.0	486.6	486.6	486.6	486.6	486.6
122.5°	514.5	515.4	516.3	516.7	516.9	517.0	517.2	517.3
125°	558.3	558.7	558.9	559.3	559.5	559.9	560.2	560.5
127.5°	602.2	602.7	603.2	603.2	603.0	602.7	602.4	602.1
130°	628.7	629.3	629.9	630.1	629.7	629.5	629.1	628.8
132.5°	653.7	654.3	655.0	655.1	654.7	654.2	653.8	653.4
135°	691.8	692.2	692.7	692.7	692.2	691.8	691.3	690.9
137.5°	725.7	726.4	727.2	727.4	727.1	726.7	726.5	726.1
140°	747.2	747.8	748.4	748.6	748.2	748.0	747.6	747.3
142.5°	767.6	768.0	768.6	768.6	768.1	767.7	767.3	766.9
145°	796.0	796.4	796.7	796.8	796.8	796.8	796.8	796.8
147.5°	821.5	821.9	822.2	822.0	821.3	820.6	819.8	819.1
150°	837.1	837.5	837.8	837.8	837.2	836.8	836.3	835.9
152.5°	851.0	851.6	852.2	852.1	851.4	850.7	850.0	849.3
155°	870.2	870.9	871.7	871.6	870.8	869.8	868.9	867.9
157.5°	886.8	887.7	888.7	888.5	887.3	886.1	884.9	883.7
160°	896.3	897.2	898.1	898.0	897.0	895.9	894.8	893.8
162.5°	904.9	906.0	907.0	907.0	906.1	905.1	904.2	903.2
165°	916.4	917.7	918.9	919.0	917.9	916.8	915.7	914.6
167.5°	925.3	926.6	927.8	927.8	926.6	925.3	924.1	922.8
170°	930.3	931.6	932.8	932.8	931.6	930.3	929.2	927.9
172.5°	933.7	935.0	936.2	936.1	934.8	933.4	932.0	930.7
175°	937.7	938.8	939.9	939.8	938.6	937.4	936.1	934.9
177.5°	939.2	940.2	941.2	941.1	939.9	938.6	937.4	936.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3

(END OF REPORT)