

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906929

Luminaire Tested: DFN2DIP-SQ4F0-140D090US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906929
REPORT IS A COMBINATION OF REPORTS P901647 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D090US835-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22770.0 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 210.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906929

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906929

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	100	96	92	88	94	90	86	83	78	76	74	68	66	64	58	57	56
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	51	49	47
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	27	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3822	3822	3822
5°	3828	3770	3796
10°	3797	3720	3745
15°	3741	3659	3666
20°	3666	3575	3585
25°	3591	3474	3491
30°	3497	3380	3371
35°	3408	3269	3244
40°	3298	3157	3124
45°	3188	3045	3001
50°	3069	2927	2858
55°	2943	2791	2727
60°	2802	2629	2577
65°	2647	2462	2400
70°	2450	2258	2210
75°	2178	2014	2036
80°	1850	1704	1701
85°	1337	1165	1143

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3188 cd/sqm

TEST NUMBER: P906929

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.7	2.3
10°-20°	1442.6	6.3
20°-30°	2120.0	9.3
30°-40°	2462.3	10.8
40°-50°	2459.3	10.8
50°-60°	2144.4	9.4
60°-70°	1585.2	7.0
70°-80°	896.9	3.9
80°-90°	242.0	1.1
90°-100°	100.2	0.4
100°-110°	373.4	1.6
110°-120°	990.2	4.3
120°-130°	1642.4	7.2
130°-140°	1744.6	7.7
140°-150°	1621.4	7.1
150°-160°	1303.5	5.7
160°-170°	840.0	3.7
170°-180°	289.1	1.3
0°-30°	4075.3	17.9
0°-40°	6537.6	28.7
0°-60°	11141.3	48.9
0°-90°	13865.3	60.9
90°-120°	1463.7	6.4
90°-150°	6472.0	28.4
90°-180°	8905.0	39.1
0°-180°	22770.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5448	5448	5448	5448	5448	
5°	5448	5427	5369	5411	5401	517
15°	5186	5155	5086	5107	5081	1461
25°	4693	4652	4563	4573	4563	2160
35°	4049	3997	3913	3881	3855	2529
45°	3295	3258	3180	3122	3101	2543
55°	2494	2462	2399	2336	2310	2229
65°	1682	1650	1598	1550	1524	1663
75°	880	870	843	812	822	939
85°	214	210	204	188	183	239
90°	2	26	44	55	59	21
95°	143	70	86	97	94	169
105°	668	734	134	158	167	714
115°	1264	1301	1356	338	180	1244
125°	1787	1815	1857	1873	1879	1594
135°	2211	2246	2266	2288	2284	1708
145°	2565	2563	2600	2615	2604	1604
155°	2824	2805	2831	2844	2826	1301
165°	2976	2963	2969	2985	2969	841
175°	3044	3028	3033	3048	3026	290
180°	3037	3037	3037	3037	3037	

TEST NUMBER: P906929

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5447.5	5447.5	5447.5	5447.5	5447.5
2.5°	5479.1	5453.0	5395.2	5447.5	5437.5
5°	5447.5	5426.9	5369.1	5410.8	5400.8
7.5°	5410.8	5379.7	5321.9	5364.1	5353.5
10°	5353.5	5316.9	5254.1	5295.8	5280.2
12.5°	5274.6	5243.5	5180.7	5206.8	5196.3
15°	5185.7	5154.6	5086.2	5107.4	5081.2
17.5°	5075.7	5044.6	4976.2	5002.3	4976.2
20°	4955.1	4924.0	4850.6	4866.2	4845.6
22.5°	4835.0	4787.8	4719.4	4719.4	4708.9
25°	4693.3	4651.6	4562.7	4572.7	4562.7
27.5°	4536.0	4499.4	4431.6	4416.0	4389.9
30°	4379.3	4337.1	4258.7	4243.2	4222.0
32.5°	4211.5	4180.4	4096.4	4064.8	4043.6
35°	4049.2	3997.0	3913.0	3881.4	3855.2
37.5°	3865.8	3818.6	3734.6	3698.0	3671.8
40°	3677.4	3635.2	3551.2	3504.6	3483.4
42.5°	3494.0	3451.8	3368.4	3315.6	3284.5
45°	3295.0	3258.4	3179.5	3122.2	3101.1
47.5°	3101.1	3064.4	2980.5	2922.7	2891.6
50°	2896.6	2870.5	2797.1	2723.7	2697.6
52.5°	2697.6	2660.9	2593.1	2535.3	2498.7
55°	2493.7	2462.0	2399.2	2336.4	2310.3
57.5°	2289.1	2263.0	2194.7	2131.9	2110.7
60°	2084.6	2064.1	1990.7	1932.9	1917.3
62.5°	1885.7	1849.0	1796.7	1744.5	1723.4
65°	1681.7	1650.0	1597.8	1550.5	1524.4
67.5°	1472.2	1445.5	1398.8	1362.1	1341.0
70°	1278.2	1257.1	1209.9	1173.2	1152.6
72.5°	1079.3	1058.1	1032.0	995.4	979.8
75°	879.8	869.8	843.1	812.0	822.5
77.5°	701.9	680.8	670.2	654.7	639.1
80°	524.1	518.5	508.0	492.4	481.8
82.5°	356.2	356.2	351.2	330.1	330.1
85°	214.5	209.5	204.5	188.4	183.4
87.5°	94.5	83.9	73.4	57.8	52.2
90°	2.1	26.4	43.8	55.1	59.2
92.5°	55.1	46.2	52.7	57.2	59.2
95°	142.8	70.2	85.6	96.8	94.5
97.5°	257.1	77.0	112.0	118.7	120.8
100°	389.1	88.0	125.3	142.8	147.2
102.5°	534.0	529.8	129.7	153.7	160.5
105°	668.1	734.2	134.1	158.2	167.0
107.5°	824.2	879.0	138.6	162.6	171.5
110°	973.7	1019.7	384.7	164.9	173.6

TEST NUMBER: P906929

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1114.4	1153.8	1116.5	169.1	175.9
115°	1263.7	1301.0	1356.1	338.5	180.3
117.5°	1393.4	1437.3	1474.8	1160.4	584.6
120°	1538.5	1571.4	1611.1	1637.4	1340.7
122.5°	1661.5	1696.7	1740.8	1753.8	1756.2
125°	1786.7	1815.4	1857.2	1872.6	1879.1
127.5°	1901.0	1931.8	1965.0	1986.9	1989.0
130°	2008.8	2044.1	2068.1	2092.3	2090.3
132.5°	2118.7	2147.4	2171.4	2191.3	2189.2
135°	2211.1	2246.3	2265.9	2288.1	2283.7
137.5°	2307.7	2334.0	2356.2	2378.1	2371.6
140°	2402.1	2419.9	2443.9	2463.7	2452.8
142.5°	2481.5	2496.9	2525.3	2542.8	2531.9
145°	2565.0	2562.6	2600.0	2615.4	2604.4
147.5°	2637.3	2630.8	2668.1	2679.1	2670.4
150°	2707.8	2692.4	2727.6	2740.6	2729.7
152.5°	2767.0	2749.5	2782.4	2795.7	2780.3
155°	2824.2	2804.6	2830.9	2844.0	2826.5
157.5°	2870.4	2852.9	2872.7	2888.1	2870.4
160°	2910.0	2896.7	2910.0	2923.1	2907.7
162.5°	2945.0	2931.9	2942.9	2958.3	2938.5
165°	2975.8	2962.7	2969.3	2984.7	2969.3
167.5°	3000.1	2986.8	2993.5	3008.9	2989.1
170°	3019.9	3006.6	3011.0	3026.4	3006.6
172.5°	3033.0	3019.9	3024.3	3039.7	3019.9
175°	3043.9	3028.5	3033.0	3048.3	3026.4
177.5°	3048.3	3033.0	3035.3	3050.7	3030.9
180°	3037.4	3037.4	3037.4	3037.4	3037.4

TEST NUMBER: P906929

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.89	13.86	13.75	14.74	15.85	12.45	13.42	13.30	14.30	15.40
	3H	14.56	15.43	15.43	16.32	17.46	14.07	14.94	14.94	15.83	16.97
	4H	15.16	15.98	16.05	16.88	18.02	14.67	15.49	15.55	16.38	17.53
	6H	15.57	16.33	16.47	17.23	18.38	15.07	15.83	15.97	16.73	17.88
	8H	15.68	16.40	16.58	17.32	18.48	15.18	15.90	16.08	16.82	17.97
	12H	15.73	16.42	16.64	17.33	18.51	15.22	15.91	16.13	16.82	18.00
4H	2H	13.37	14.19	14.26	15.08	16.23	13.01	13.83	13.90	14.73	15.87
	3H	15.25	15.93	16.15	16.86	18.02	14.84	15.52	15.74	16.45	17.61
	4H	15.97	16.59	16.88	17.52	18.70	15.54	16.17	16.46	17.09	18.28
	6H	16.49	17.03	17.42	17.98	19.17	16.06	16.60	16.99	17.55	18.73
	8H	16.65	17.15	17.58	18.09	19.29	16.21	16.72	17.14	17.66	18.86
	12H	16.73	17.18	17.68	18.14	19.35	16.28	16.73	17.23	17.69	18.90
8H	4H	16.17	16.68	17.10	17.62	18.82	15.80	16.30	16.73	17.24	18.44
	6H	16.81	17.23	17.77	18.21	19.41	16.43	16.85	17.39	17.83	19.03
	8H	17.04	17.41	18.01	18.38	19.60	16.65	17.02	17.61	17.99	19.20
	12H	17.18	17.50	18.15	18.47	19.73	16.77	17.09	17.74	18.06	19.32
12H	4H	16.16	16.62	17.11	17.58	18.78	15.80	16.25	16.75	17.21	18.41
	6H	16.85	17.22	17.81	18.19	19.40	16.47	16.84	17.44	17.82	19.03
	8H	17.10	17.42	18.07	18.39	19.65	16.72	17.04	17.69	18.01	19.27