

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906972

Luminaire Tested: DFN2DIP-SQ4F0-160D110US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906972
REPORT IS A COMBINATION OF REPORTS P900165 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D110US835-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25575.0 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 249.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906972

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906972

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	89	94	90	87	84	79	76	74	69	67	65	59	58	57
2	92	84	78	72	85	79	73	69	69	65	61	60	57	54	52	50	48
3	84	74	66	60	78	69	63	57	61	56	52	53	49	46	46	43	41
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	41	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	37	34	31
6	65	52	44	38	60	49	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	25	22
9	52	39	32	27	49	37	30	26	33	28	24	30	25	21	26	22	19
10	49	36	29	24	46	34	28	23	31	25	21	28	23	19	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4368	4368	4368
5°	4375	4308	4338
10°	4340	4251	4280
15°	4276	4182	4190
20°	4190	4086	4097
25°	4104	3970	3990
30°	3996	3863	3853
35°	3894	3736	3708
40°	3769	3608	3570
45°	3644	3480	3429
50°	3507	3346	3266
55°	3364	3190	3116
60°	3202	3005	2945
65°	3025	2814	2742
70°	2800	2581	2525
75°	2489	2302	2327
80°	2114	1947	1944
85°	1528	1332	1306

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3644 cd/sqm

TEST NUMBER: P906972

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	586.0	2.3
10°-20°	1648.7	6.4
20°-30°	2422.9	9.5
30°-40°	2814.1	11.0
40°-50°	2810.6	11.0
50°-60°	2450.7	9.6
60°-70°	1811.6	7.1
70°-80°	1025.0	4.0
80°-90°	280.4	1.1
90°-100°	215.3	0.8
100°-110°	684.0	2.7
110°-120°	1170.5	4.6
120°-130°	1539.4	6.0
130°-140°	1727.9	6.8
140°-150°	1694.4	6.6
150°-160°	1421.4	5.6
160°-170°	942.6	3.7
170°-180°	329.5	1.3
0°-30°	4657.5	18.2
0°-40°	7471.6	29.2
0°-60°	12732.9	49.8
0°-90°	15849.9	62.0
90°-120°	2069.8	8.1
90°-150°	7031.6	27.5
90°-180°	9725.0	38.0
0°-180°	25575.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6226	6226	6226	6226	6226	
5°	6226	6202	6136	6184	6172	591
15°	5926	5891	5813	5837	5807	1669
25°	5364	5316	5214	5226	5214	2468
35°	4628	4568	4472	4436	4406	2890
45°	3766	3724	3634	3568	3544	2906
55°	2850	2814	2742	2670	2640	2548
65°	1922	1886	1826	1772	1742	1900
75°	1005	994	964	928	940	1073
85°	245	239	234	215	210	273
90°	3	38	103	96	100	25
95°	153	182	188	188	182	170
105°	631	640	646	651	651	666
115°	1175	1191	1186	1183	1175	1162
125°	1708	1735	1726	1717	1714	1527
135°	2210	2242	2249	2246	2237	1708
145°	2683	2704	2721	2724	2712	1676
155°	3068	3076	3086	3100	3091	1412
165°	3337	3334	3334	3355	3340	941
175°	3473	3464	3458	3479	3461	330
180°	3479	3479	3479	3479	3479	

TEST NUMBER: P906972

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6225.7	6225.7	6225.7	6225.7	6225.7
2.5°	6261.9	6232.0	6166.0	6225.7	6214.2
5°	6225.7	6202.2	6136.1	6183.8	6172.3
7.5°	6183.8	6148.2	6082.1	6130.4	6118.3
10°	6118.3	6076.4	6004.7	6052.3	6034.5
12.5°	6028.2	5992.6	5920.8	5950.7	5938.6
15°	5926.5	5891.0	5812.8	5837.0	5807.1
17.5°	5800.8	5765.2	5687.1	5716.9	5687.1
20°	5662.9	5627.4	5543.5	5561.3	5537.8
22.5°	5525.8	5471.8	5393.6	5393.6	5381.6
25°	5363.8	5316.2	5214.5	5226.0	5214.5
27.5°	5184.0	5142.1	5064.6	5046.9	5017.0
30°	5004.9	4956.7	4867.1	4849.3	4825.2
32.5°	4813.1	4777.6	4681.6	4645.4	4621.3
35°	4627.7	4568.0	4472.0	4435.8	4406.0
37.5°	4418.1	4364.1	4268.2	4226.2	4196.4
40°	4202.7	4154.5	4058.6	4005.2	3981.1
42.5°	3993.2	3944.9	3849.6	3789.3	3753.7
45°	3765.8	3723.8	3633.7	3568.2	3544.1
47.5°	3544.1	3502.2	3406.3	3340.2	3304.7
50°	3310.4	3280.5	3196.7	3112.8	3083.0
52.5°	3083.0	3041.1	2963.6	2897.5	2855.6
55°	2849.9	2813.7	2741.9	2670.1	2640.3
57.5°	2616.2	2586.3	2508.2	2436.4	2412.3
60°	2382.4	2358.9	2275.1	2209.0	2191.2
62.5°	2155.0	2113.1	2053.4	1993.7	1969.6
65°	1921.9	1885.7	1826.0	1772.1	1742.2
67.5°	1682.5	1652.0	1598.7	1556.7	1532.6
70°	1460.8	1436.7	1382.7	1340.8	1317.3
72.5°	1233.4	1209.3	1179.5	1137.5	1119.8
75°	1005.4	994.0	963.5	927.9	940.0
77.5°	802.2	778.1	766.0	748.2	730.4
80°	598.9	592.6	580.5	562.7	550.7
82.5°	407.1	407.1	401.4	377.3	377.3
85°	245.2	239.4	233.7	215.3	209.6
87.5°	108.0	95.9	83.8	66.1	59.7
90°	3.1	37.8	102.8	96.5	99.6
92.5°	65.0	88.1	91.2	94.4	94.4
95°	153.1	182.5	187.7	187.7	182.5
97.5°	254.9	282.1	293.7	293.7	293.7
100°	372.3	396.4	404.8	404.8	401.7
102.5°	496.1	513.9	525.5	528.6	525.5
105°	631.4	639.8	646.1	651.3	651.3
107.5°	765.6	778.2	778.2	780.3	765.6
110°	895.7	912.5	912.5	912.5	904.1

TEST NUMBER: P906972

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1036.2	1054.0	1050.9	1042.5	1036.2
115°	1174.7	1191.4	1186.2	1183.1	1174.7
117.5°	1312.1	1335.1	1320.4	1312.1	1303.7
120°	1450.5	1473.6	1450.5	1450.5	1441.1
122.5°	1576.4	1605.7	1591.0	1582.6	1576.4
125°	1708.5	1734.7	1726.3	1716.9	1713.7
127.5°	1837.5	1870.0	1858.5	1845.9	1837.5
130°	1958.1	1995.9	1990.6	1984.3	1972.8
132.5°	2093.4	2122.8	2124.9	2110.2	2101.8
135°	2209.8	2242.3	2248.6	2245.5	2237.1
137.5°	2339.9	2366.1	2371.3	2369.2	2356.7
140°	2454.2	2480.4	2495.1	2495.1	2483.6
142.5°	2571.7	2597.9	2606.3	2609.4	2597.9
145°	2682.8	2703.8	2720.6	2723.7	2712.2
147.5°	2782.5	2808.7	2821.3	2826.5	2815.0
150°	2885.3	2903.1	2914.6	2924.1	2914.6
152.5°	2976.5	2994.3	3009.0	3020.6	3009.0
155°	3067.8	3076.1	3085.6	3100.3	3090.8
157.5°	3146.4	3152.7	3157.9	3178.9	3164.2
160°	3216.7	3223.0	3226.1	3244.0	3231.4
162.5°	3281.7	3281.7	3284.9	3304.8	3290.1
165°	3337.3	3334.1	3334.1	3355.1	3340.4
167.5°	3387.6	3378.2	3378.2	3399.2	3384.5
170°	3425.4	3417.0	3413.9	3434.8	3417.0
172.5°	3451.6	3443.2	3440.1	3461.1	3443.2
175°	3472.6	3464.2	3457.9	3478.9	3461.1
177.5°	3484.1	3475.7	3469.4	3487.3	3469.4
180°	3478.9	3478.9	3478.9	3478.9	3478.9

TEST NUMBER: P906972

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.44	14.42	14.29	15.29	16.38	13.00	13.98	13.85	14.85	15.94
	3H	15.12	16.00	15.98	16.88	17.99	14.63	15.51	15.49	16.38	17.50
	4H	15.71	16.54	16.59	17.43	18.56	15.22	16.05	16.09	16.94	18.06
	6H	16.12	16.89	17.01	17.78	18.92	15.62	16.39	16.51	17.28	18.42
	8H	16.23	16.96	17.13	17.87	19.01	15.73	16.46	16.63	17.37	18.51
	12H	16.29	16.98	17.19	17.89	19.05	15.78	16.47	16.68	17.38	18.54
4H	2H	13.92	14.75	14.80	15.64	16.76	13.56	14.40	14.44	15.28	16.41
	3H	15.80	16.49	16.69	17.41	18.55	15.39	16.09	16.28	17.00	18.15
	4H	16.52	17.16	17.43	18.07	19.24	16.10	16.73	17.00	17.64	18.81
	6H	17.05	17.60	17.97	18.53	19.70	16.62	17.16	17.53	18.10	19.27
	8H	17.20	17.71	18.12	18.65	19.83	16.77	17.28	17.69	18.21	19.39
	12H	17.28	17.75	18.22	18.69	19.88	16.83	17.30	17.77	18.25	19.43
8H	4H	16.73	17.24	17.65	18.17	19.35	16.35	16.86	17.27	17.79	18.98
	6H	17.37	17.79	18.32	18.77	19.95	16.99	17.41	17.93	18.38	19.56
	8H	17.59	17.97	18.55	18.93	20.13	17.20	17.58	18.16	18.54	19.74
	12H	17.74	18.07	18.70	19.02	20.27	17.32	17.65	18.28	18.61	19.86
12H	4H	16.72	17.18	17.66	18.13	19.32	16.35	16.81	17.29	17.76	18.95
	6H	17.40	17.78	18.36	18.74	19.94	17.03	17.40	17.99	18.37	19.57
	8H	17.65	17.98	18.61	18.94	20.19	17.27	17.60	18.23	18.56	19.81