

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904346

Luminaire Tested: DFN2DIP-TR2F0-060D030US830-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904346
REPORT IS A COMBINATION OF REPORTS P900240 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-060D030US830-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7309.4 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 81.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904346

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904346

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5213	5213	5213
5°	5214	5119	5154
10°	5154	5007	4978
15°	5076	4830	4710
20°	4974	4591	4385
25°	4870	4326	4071
30°	4733	4054	3677
35°	4598	3764	3330
40°	4460	3464	2934
45°	4301	3134	2576
50°	4137	2801	2227
55°	3963	2447	1891
60°	3762	2079	1548
65°	3531	1707	1384
70°	3250	1358	1240
75°	2896	1175	1111
80°	2387	953	936
85°	1567	592	660

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4301 cd/sqm

TEST NUMBER: P904346

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.1	3.0
10°-20°	601.3	8.2
20°-30°	844.3	11.6
30°-40°	920.3	12.6
40°-50°	845.9	11.6
50°-60°	664.3	9.1
60°-70°	432.4	5.9
70°-80°	222.6	3.0
80°-90°	59.4	0.8
90°-100°	55.3	0.8
100°-110°	175.8	2.4
110°-120°	300.9	4.1
120°-130°	395.7	5.4
130°-140°	444.2	6.1
140°-150°	435.6	6.0
150°-160°	365.4	5.0
160°-170°	242.3	3.3
170°-180°	84.7	1.2
0°-30°	1664.7	22.8
0°-40°	2585.0	35.4
0°-60°	4095.1	56.0
0°-90°	4809.5	65.8
90°-120°	532.1	7.3
90°-150°	1807.5	24.7
90°-180°	2500.0	34.2
0°-180°	7309.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2067	626
25°	2018	1950	1811	1724	1692	928
35°	1739	1631	1445	1312	1265	1088
45°	1421	1280	1058	907	857	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	1	10	26	25	26	7
95°	39	47	48	48	47	44
105°	162	164	166	167	167	171
115°	302	306	305	304	302	299
125°	439	446	444	441	440	392
135°	568	576	578	577	575	439
145°	690	695	699	700	697	431
155°	789	791	793	797	795	363
165°	858	857	857	862	859	242
175°	893	890	889	894	890	85
180°	894	894	894	894	894	

TEST NUMBER: P904346

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2337.3	2337.3	2337.3	2337.3	2337.3
2.5°	2347.9	2337.3	2313.9	2335.2	2331.0
5°	2337.3	2326.8	2299.1	2318.3	2312.0
7.5°	2318.3	2305.6	2276.1	2284.3	2273.8
10°	2292.8	2278.0	2235.9	2229.4	2216.8
12.5°	2261.3	2242.1	2184.9	2172.4	2149.0
15°	2223.1	2199.7	2127.9	2087.7	2066.6
17.5°	2178.7	2144.8	2055.9	2009.4	1975.6
20°	2127.9	2085.5	1979.8	1927.0	1880.4
22.5°	2072.9	2024.2	1901.5	1829.7	1798.0
25°	2018.0	1950.2	1810.6	1724.0	1692.1
27.5°	1952.5	1880.4	1726.0	1626.5	1577.9
30°	1882.6	1802.0	1632.9	1525.1	1467.9
32.5°	1814.9	1717.5	1544.3	1417.2	1364.2
35°	1738.8	1630.9	1444.8	1311.5	1264.8
37.5°	1664.7	1548.2	1351.7	1205.6	1152.8
40°	1586.4	1459.6	1254.2	1104.1	1049.1
42.5°	1506.1	1370.7	1157.1	1000.4	947.7
45°	1421.4	1279.6	1057.7	907.3	856.6
47.5°	1341.1	1191.0	962.5	812.2	765.7
50°	1252.3	1102.1	869.4	723.3	679.1
52.5°	1165.4	1006.7	780.5	640.9	600.8
55°	1080.8	915.9	687.4	560.6	520.4
57.5°	994.2	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.4	368.1	296.2	289.7
67.5°	645.2	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.7
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.6
80°	230.5	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	0.8	9.7	26.4	24.8	25.6
92.5°	16.7	22.6	23.5	24.2	24.2
95°	39.4	46.9	48.3	48.3	46.9
97.5°	65.5	72.5	75.5	75.5	75.5
100°	95.7	101.9	104.1	104.1	103.3
102.5°	127.5	132.1	135.1	135.9	135.1
105°	162.3	164.5	166.1	167.4	167.4
107.5°	196.8	200.0	200.0	200.6	196.8
110°	230.3	234.6	234.6	234.6	232.4

TEST NUMBER: P904346

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.4	271.0	270.1	268.0	266.4
115°	302.0	306.2	304.9	304.2	302.0
117.5°	337.2	343.2	339.4	337.2	335.1
120°	372.9	378.8	372.9	372.9	370.4
122.5°	405.2	412.7	409.0	406.8	405.2
125°	439.2	445.9	443.7	441.3	440.5
127.5°	472.3	480.7	477.8	474.5	472.3
130°	503.3	513.0	511.7	510.1	507.1
132.5°	538.1	545.6	546.2	542.4	540.3
135°	568.1	576.4	578.1	577.2	575.0
137.5°	601.4	608.2	609.5	609.1	605.8
140°	630.8	637.6	641.4	641.4	638.4
142.5°	661.1	667.8	670.0	670.8	667.8
145°	689.7	695.0	699.4	700.1	697.2
147.5°	715.3	722.0	725.2	726.6	723.6
150°	741.7	746.3	749.2	751.7	749.2
152.5°	765.2	769.7	773.5	776.5	773.5
155°	788.6	790.7	793.1	796.9	794.6
157.5°	808.8	810.4	811.8	817.2	813.4
160°	826.9	828.5	829.3	833.9	830.7
162.5°	843.6	843.6	844.4	849.5	845.7
165°	857.9	857.1	857.1	862.4	858.7
167.5°	870.8	868.4	868.4	873.7	870.0
170°	880.5	878.4	877.6	883.0	878.4
172.5°	887.2	885.1	884.3	889.7	885.1
175°	892.7	890.5	888.9	894.3	889.7
177.5°	895.6	893.4	891.8	896.5	891.8
180°	894.3	894.3	894.3	894.3	894.3

TEST NUMBER: P904346

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.12	15.09	14.93	15.93	16.96	10.10	11.08	10.91	11.91	12.94
	3H	15.78	16.66	16.61	17.50	18.56	11.28	12.16	12.11	13.00	14.06
	4H	16.38	17.20	17.23	18.05	19.12	11.73	12.55	12.57	13.40	14.47
	6H	16.79	17.55	17.65	18.41	19.49	12.04	12.80	12.90	13.66	14.74
	8H	16.91	17.63	17.78	18.51	19.59	12.13	12.85	13.00	13.73	14.81
	12H	16.97	17.66	17.84	18.52	19.63	12.17	12.86	13.04	13.73	14.84
4H	2H	14.15	14.97	15.00	15.82	16.89	10.70	11.52	11.55	12.37	13.44
	3H	15.96	16.65	16.82	17.53	18.62	12.04	12.73	12.90	13.61	14.69
	4H	16.64	17.27	17.52	18.15	19.26	12.58	13.21	13.46	14.09	15.20
	6H	17.14	17.68	18.03	18.58	19.70	12.99	13.53	13.88	14.43	15.55
	8H	17.31	17.81	18.20	18.71	19.84	13.12	13.62	14.01	14.52	15.64
	12H	17.40	17.85	18.31	18.77	19.90	13.18	13.63	14.09	14.55	15.68
8H	4H	16.62	17.12	17.51	18.02	19.14	12.86	13.36	13.75	14.26	15.39
	6H	17.16	17.58	18.08	18.52	19.65	13.36	13.78	14.28	14.72	15.84
	8H	17.37	17.73	18.29	18.67	19.81	13.54	13.91	14.47	14.84	15.98
	12H	17.49	17.82	18.43	18.74	19.94	13.65	13.98	14.58	14.90	16.10
12H	4H	16.58	17.03	17.49	17.94	19.08	12.87	13.32	13.78	14.24	15.37
	6H	17.14	17.51	18.07	18.44	19.58	13.40	13.77	14.33	14.71	15.85
	8H	17.35	17.67	18.28	18.60	19.79	13.61	13.93	14.54	14.86	16.05