

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907008

Luminaire Tested: DFN2DIP-TR2F0-030D020US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907008
REPORT IS A COMBINATION OF REPORTS P900223 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D020US835-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4740.0 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 40.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907008

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907008

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2604	2604	2604
5°	2604	2561	2580
10°	2579	2521	2541
15°	2537	2474	2482
20°	2482	2410	2421
25°	2427	2336	2352
30°	2359	2266	2266
35°	2295	2184	2175
40°	2216	2102	2088
45°	2137	2019	1998
50°	2050	1931	1895
55°	1960	1830	1800
60°	1856	1712	1690
65°	1744	1587	1560
70°	1600	1436	1420
75°	1403	1255	1285
80°	1163	1023	1039
85°	793	645	645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2137 cd/sqm

TEST NUMBER: P907008

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	2.3
10°-20°	309.1	6.5
20°-30°	454.3	9.6
30°-40°	527.6	11.1
40°-50°	527.0	11.1
50°-60°	459.5	9.7
60°-70°	339.7	7.2
70°-80°	192.2	4.1
80°-90°	52.5	1.1
90°-100°	39.1	0.8
100°-110°	124.4	2.6
110°-120°	212.8	4.5
120°-130°	279.9	5.9
130°-140°	314.2	6.6
140°-150°	308.1	6.5
150°-160°	258.4	5.5
160°-170°	171.4	3.6
170°-180°	59.9	1.3
0°-30°	873.3	18.4
0°-40°	1400.9	29.6
0°-60°	2387.4	50.4
0°-90°	2971.8	62.7
90°-120°	376.3	7.9
90°-150°	1278.5	27.0
90°-180°	1768.0	37.3
0°-180°	4740.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1167	1167	1167	1167	1167	
5°	1167	1163	1150	1160	1157	111
15°	1111	1105	1090	1094	1089	313
25°	1006	997	978	980	978	463
35°	868	856	838	832	826	542
45°	706	698	681	669	664	545
55°	534	528	514	501	495	478
65°	360	354	342	332	327	356
75°	188	186	181	174	176	201
85°	46	45	44	40	39	51
90°	1	7	19	18	18	5
95°	28	33	34	34	33	31
105°	115	116	118	118	118	121
115°	214	217	216	215	214	211
125°	311	315	314	312	312	278
135°	402	408	409	408	407	311
145°	488	492	495	495	493	305
155°	558	559	561	564	562	257
165°	607	606	606	610	607	171
175°	631	630	629	632	629	60
180°	632	632	632	632	632	

TEST NUMBER: P907008

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1167.3	1167.3	1167.3	1167.3	1167.3
2.5°	1174.1	1168.5	1156.1	1167.3	1165.2
5°	1167.3	1162.9	1150.5	1159.5	1157.3
7.5°	1159.5	1152.8	1140.4	1149.5	1147.2
10°	1147.2	1139.3	1125.9	1134.8	1131.5
12.5°	1130.3	1123.6	1110.2	1115.7	1113.5
15°	1111.2	1104.6	1089.9	1094.4	1088.8
17.5°	1087.6	1081.0	1066.3	1071.9	1066.3
20°	1061.8	1055.1	1039.4	1042.7	1038.3
22.5°	1036.1	1026.0	1011.3	1011.3	1009.0
25°	1005.7	996.8	977.7	979.9	977.7
27.5°	972.0	964.1	949.6	946.3	940.7
30°	938.4	929.4	912.6	909.2	904.7
32.5°	902.5	895.8	877.8	871.0	866.5
35°	867.7	856.5	838.5	831.7	826.1
37.5°	828.4	818.3	800.3	792.4	786.8
40°	788.0	779.0	761.0	751.0	746.5
42.5°	748.7	739.7	721.8	710.5	703.8
45°	706.1	698.2	681.3	669.0	664.5
47.5°	664.5	656.7	638.7	626.3	619.6
50°	620.7	615.1	599.4	583.7	578.1
52.5°	578.1	570.2	555.7	543.3	535.4
55°	534.4	527.6	514.1	500.7	495.1
57.5°	490.5	484.9	470.3	456.8	452.3
60°	446.7	442.3	426.6	414.2	410.9
62.5°	404.1	396.2	385.0	373.8	369.3
65°	360.4	353.6	342.4	332.3	326.7
67.5°	315.5	309.8	299.7	291.9	287.4
70°	273.9	269.4	259.3	251.4	247.0
72.5°	231.3	226.7	221.1	213.3	210.0
75°	188.5	186.4	180.7	174.0	176.3
77.5°	150.4	145.9	143.6	140.3	137.0
80°	112.3	111.1	108.8	105.5	103.3
82.5°	76.3	76.3	75.3	70.7	70.7
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	0.6	6.9	18.7	17.5	18.1
92.5°	11.8	16.0	16.6	17.2	17.2
95°	27.8	33.2	34.1	34.1	33.2
97.5°	46.3	51.3	53.4	53.4	53.4
100°	67.7	72.1	73.6	73.6	73.0
102.5°	90.2	93.4	95.5	96.1	95.5
105°	114.8	116.3	117.5	118.4	118.4
107.5°	139.2	141.5	141.5	141.9	139.2
110°	162.9	165.9	165.9	165.9	164.4

TEST NUMBER: P907008

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.4	191.6	191.1	189.5	188.4
115°	213.6	216.6	215.7	215.1	213.6
117.5°	238.6	242.8	240.1	238.6	237.0
120°	263.7	267.9	263.7	263.7	262.0
122.5°	286.6	291.9	289.3	287.8	286.6
125°	310.6	315.4	313.9	312.2	311.6
127.5°	334.1	340.0	337.9	335.6	334.1
130°	356.0	362.9	361.9	360.8	358.7
132.5°	380.6	386.0	386.3	383.7	382.1
135°	401.8	407.7	408.8	408.3	406.7
137.5°	425.4	430.2	431.2	430.8	428.5
140°	446.2	451.0	453.7	453.7	451.6
142.5°	467.6	472.3	473.9	474.4	472.3
145°	487.8	491.6	494.7	495.2	493.1
147.5°	505.9	510.7	513.0	513.9	511.8
150°	524.6	527.8	529.9	531.6	529.9
152.5°	541.2	544.4	547.1	549.2	547.1
155°	557.8	559.3	561.0	563.7	562.0
157.5°	572.1	573.2	574.2	578.0	575.3
160°	584.9	586.0	586.6	589.8	587.5
162.5°	596.7	596.7	597.2	600.9	598.2
165°	606.8	606.2	606.2	610.0	607.4
167.5°	615.9	614.2	614.2	618.0	615.4
170°	622.8	621.3	620.7	624.5	621.3
172.5°	627.6	626.0	625.5	629.3	626.0
175°	631.4	629.9	628.7	632.5	629.3
177.5°	633.5	632.0	630.8	634.0	630.8
180°	632.5	632.5	632.5	632.5	632.5

TEST NUMBER: P907008

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US835-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.56	12.55	12.40	13.41	14.49	11.14	12.13	11.98	12.99	14.07
	3H	13.21	14.10	14.06	14.97	16.07	12.75	13.63	13.60	14.51	15.61
	4H	13.79	14.62	14.66	15.50	16.62	13.33	14.17	14.20	15.04	16.16
	6H	14.17	14.95	15.06	15.83	16.96	13.71	14.49	14.60	15.37	16.50
	8H	14.27	15.01	15.16	15.91	17.04	13.82	14.55	14.70	15.46	16.58
	12H	14.32	15.02	15.21	15.92	17.07	13.85	14.56	14.75	15.45	16.61
4H	2H	12.03	12.87	12.90	13.75	14.86	11.69	12.53	12.56	13.41	14.52
	3H	13.88	14.58	14.76	15.49	16.62	13.50	14.20	14.38	15.11	16.24
	4H	14.58	15.22	15.48	16.13	17.28	14.19	14.82	15.08	15.73	16.89
	6H	15.08	15.63	15.99	16.56	17.72	14.69	15.24	15.60	16.17	17.33
	8H	15.22	15.74	16.14	16.66	17.83	14.82	15.34	15.74	16.27	17.44
	12H	15.29	15.76	16.22	16.70	17.88	14.89	15.35	15.82	16.29	17.47
8H	4H	14.78	15.29	15.69	16.22	17.39	14.43	14.94	15.34	15.87	17.04
	6H	15.39	15.81	16.33	16.78	17.95	15.03	15.46	15.98	16.43	17.60
	8H	15.59	15.97	16.54	16.93	18.12	15.24	15.61	16.19	16.57	17.76
	12H	15.71	16.05	16.67	17.00	18.24	15.35	15.68	16.30	16.63	17.87
12H	4H	14.77	15.23	15.70	16.17	17.35	14.42	14.89	15.36	15.83	17.01
	6H	15.41	15.79	16.36	16.75	17.94	15.07	15.45	16.02	16.41	17.60
	8H	15.64	15.98	16.60	16.93	18.16	15.30	15.63	16.25	16.58	17.82