

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332299-940

Luminaire Tested: **S123RDIP-S560D1195U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332299-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5757.1 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332299-940

CATALOG NUMBER: S123RDIP-S560D1195U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P332299-940

CATALOG NUMBER: S123RDIP-S560D1195U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74		57	57	57		41
1	94	90	86	83	85	81	78	75	65	63	61		50	49	47		36
2	86	79	73	68	77	71	66	62	57	54	51		44	42	40		32
3	78	69	62	57	70	63	57	52	51	46	43		39	36	34		29
4	72	61	54	48	65	56	49	44	45	40	37		35	32	29		26
5	66	55	47	41	59	50	43	38	40	35	32		31	28	25		23
6	61	49	41	36	55	45	38	33	36	31	28		28	25	22		21
7	56	44	37	31	50	40	34	29	33	28	24		26	22	20		19
8	52	40	33	28	47	37	30	25	30	25	21		24	20	18		18
9	48	37	29	24	44	33	27	23	27	23	19		22	18	16		16
10	45	33	26	22	41	31	24	20	25	20	17		20	17	14		15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9065	9065	9065
5°	9100	8975	9027
10°	9049	8862	8833
15°	8952	8655	8564
20°	8818	8395	8200
25°	8679	8105	7845
30°	8499	7768	7343
35°	8311	7432	6884
40°	8140	7035	6315
45°	7913	6645	5801
50°	7663	6199	5228
55°	7409	5692	4692
60°	7175	5147	4103
65°	6872	4559	3512
70°	6493	3827	2839
75°	5939	3011	2670
80°	5294	2672	2455
85°	4471	2359	2186

TEST NUMBER: P332299-940

CATALOG NUMBER: S123RDIP-S560D1195U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.4
10°-20°	220.1	3.8
20°-30°	316.9	5.5
30°-40°	356.9	6.2
40°-50°	341.4	5.9
50°-60°	279.6	4.9
60°-70°	188.7	3.3
70°-80°	94.9	1.6
80°-90°	29.1	0.5
90°-100°	284.8	4.9
100°-110°	806.5	14.0
110°-120°	793.4	13.8
120°-130°	632.8	11.0
130°-140°	498.9	8.7
140°-150°	372.4	6.5
150°-160°	259.6	4.5
160°-170°	152.5	2.6
170°-180°	49.6	0.9
0°-30°	616.0	10.7
0°-40°	972.9	16.9
0°-60°	1594.0	27.7
0°-90°	1906.6	33.1
90°-120°	1884.7	32.7
90°-150°	3388.9	58.9
90°-180°	3851.0	66.9
0°-180°	5757.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	842	839	831	836	835	80
15°	803	795	777	773	768	226
25°	731	713	682	668	660	336
35°	632	607	566	537	524	396
45°	520	488	436	399	381	401
55°	395	360	303	265	250	354
65°	270	231	179	147	138	267
75°	143	110	72	66	64	152
85°	36	22	19	18	18	41
90°	2	12	26	29	30	4
95°	35	114	614	179	120	38
105°	120	178	833	1457	1318	128
115°	212	265	637	1397	1603	210
125°	295	349	595	1077	1264	262
135°	346	413	586	887	1025	267
145°	395	452	579	728	801	247
155°	449	484	560	637	664	206
165°	490	504	537	569	579	138
175°	511	511	515	522	521	48
180°	512	512	512	512	512	

TEST NUMBER: P332299-940

CATALOG NUMBER: S123RDIP-S560D1195U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	845.0	844.5	844.0	843.5	843.0	842.0	840.6	839.1	837.7	836.2	837.6
5°	842.2	841.5	840.7	840.0	839.2	837.9	836.1	834.3	832.4	830.6	832.0
7.5°	834.5	833.7	832.8	832.0	831.2	829.6	827.2	824.8	822.4	820.1	820.8
10°	827.9	826.8	825.7	824.7	823.7	821.7	819.0	816.3	813.5	810.8	810.9
12.5°	818.6	817.4	816.2	815.0	813.9	811.6	808.2	804.9	801.6	798.3	798.2
15°	803.3	801.6	800.0	798.3	796.7	793.6	789.4	785.2	780.9	776.7	775.9
17.5°	784.0	782.1	780.2	778.2	776.2	772.6	767.1	761.8	756.3	751.0	749.4
20°	769.8	767.4	765.0	762.5	760.1	756.0	750.2	744.5	738.7	732.9	730.9
22.5°	753.9	751.2	748.4	745.6	742.8	738.3	732.2	726.0	720.0	713.8	711.3
25°	730.8	727.1	723.3	719.5	715.7	710.3	703.3	696.3	689.4	682.4	679.2
27.5°	702.8	698.7	694.5	690.3	686.1	680.1	672.3	664.6	656.8	649.1	644.6
30°	683.8	679.2	674.7	670.1	665.6	659.0	650.5	642.0	633.5	625.0	619.8
32.5°	664.6	659.5	654.3	649.2	644.0	636.9	627.9	618.9	609.9	600.9	595.3
35°	632.5	627.1	621.6	616.2	610.6	603.2	593.8	584.4	575.0	565.6	559.0
37.5°	600.0	594.0	587.9	581.8	575.7	567.7	557.6	547.6	537.5	527.4	520.0
40°	579.3	572.6	565.9	559.2	552.5	543.8	533.1	522.3	511.5	500.7	492.8
42.5°	555.7	549.0	542.4	535.7	529.1	520.1	509.0	497.8	486.7	475.5	466.9
45°	519.8	513.0	506.1	499.4	492.5	483.2	471.5	459.9	448.2	436.5	427.8
47.5°	483.8	476.4	468.9	461.4	453.9	444.3	432.6	420.9	409.2	397.5	388.2
50°	457.6	450.5	443.4	436.2	429.1	419.4	407.1	394.8	382.5	370.2	360.8
52.5°	434.2	426.4	418.7	410.9	403.2	393.2	381.0	368.9	356.7	344.6	334.7
55°	394.8	387.4	380.0	372.5	365.1	354.9	342.0	329.1	316.2	303.3	294.4
57.5°	358.5	350.4	342.2	334.1	326.0	315.5	302.6	289.6	276.6	263.7	255.4
60°	333.3	325.0	316.6	308.3	300.0	289.4	276.9	264.3	251.6	239.1	230.9
62.5°	308.2	299.9	291.5	283.1	274.8	264.3	251.7	239.2	226.5	213.9	206.3
65°	269.8	261.4	253.2	244.8	236.4	226.3	214.5	202.7	190.8	179.0	171.6
67.5°	231.4	223.0	214.5	206.1	197.7	187.8	176.4	165.1	153.7	142.3	136.8
70°	206.3	198.0	189.9	181.7	173.5	164.1	153.5	142.9	132.2	121.6	116.3
72.5°	181.1	173.1	165.0	156.9	148.8	140.0	130.4	120.6	111.0	101.4	97.0
75°	142.8	135.5	128.2	120.9	113.6	105.8	97.5	89.1	80.8	72.4	70.9
77.5°	107.8	101.2	94.6	88.0	81.4	75.4	70.1	64.7	59.3	53.9	53.1
80°	85.4	79.2	72.9	66.7	60.5	55.8	52.6	49.4	46.2	43.1	42.5
82.5°	64.1	58.7	53.3	48.0	42.5	39.1	37.6	36.2	34.7	33.2	32.7
85°	36.2	32.9	29.5	26.2	22.8	21.0	20.5	20.1	19.6	19.1	18.8
87.5°	13.6	12.6	11.7	11.0	10.1	9.8	10.4	11.1	11.7	12.3	11.9
90°	2.1	4.1	6.2	9.4	11.4	13.5	16.6	19.7	22.8	25.9	24.9
92.5°	12.8	19.1	27.7	35.8	44.6	59.9	87.0	131.6	175.3	159.3	120.2
95°	35.2	38.3	49.8	67.3	94.3	134.6	222.7	377.1	547.1	614.4	498.3
97.5°	60.1	61.1	70.0	85.3	111.9	155.6	239.8	413.8	697.1	952.1	1018.6
100°	76.7	77.7	85.0	99.4	124.3	164.7	237.3	390.6	663.1	981.1	1185.3
102.5°	94.1	95.9	102.4	116.0	138.4	175.5	240.6	370.7	613.3	927.3	1193.5
105°	120.2	123.3	129.5	142.0	161.6	193.8	249.7	356.4	552.2	832.9	1130.3
107.5°	147.9	151.1	157.0	169.2	187.7	217.6	266.7	355.3	513.3	749.7	1019.7
110°	167.8	170.9	176.1	187.5	205.1	234.2	280.8	359.5	498.3	702.4	950.0

TEST NUMBER: P332299-940

CATALOG NUMBER: S123RDIP-S560D1195U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.1	189.2	194.4	205.7	223.4	251.6	294.9	367.8	490.1	670.9	889.6
115°	212.4	216.5	222.7	233.1	250.7	278.7	318.1	381.3	487.0	637.1	816.4
117.5°	238.7	243.4	248.6	258.2	277.9	303.8	342.7	399.0	488.8	617.2	772.2
120°	256.9	260.0	265.2	275.6	295.2	321.2	358.5	412.3	492.1	608.1	749.0
122.5°	272.7	275.8	281.0	292.1	311.0	338.6	375.1	424.8	497.9	602.4	730.0
125°	295.2	297.4	303.5	315.0	334.7	362.6	398.9	444.4	506.6	594.7	705.5
127.5°	312.5	315.6	323.2	334.8	356.6	384.6	419.5	460.7	516.6	590.9	684.0
130°	323.2	326.4	335.6	348.1	369.9	397.8	432.0	471.4	523.2	588.4	672.3
132.5°	331.5	335.5	345.6	360.5	382.3	409.5	442.8	481.3	528.2	587.6	661.6
135°	346.1	350.2	361.6	377.1	398.9	426.9	459.0	494.2	535.7	586.4	647.6
137.5°	359.7	364.1	375.2	391.8	413.4	439.3	470.1	503.7	540.6	584.1	635.3
140°	368.8	374.0	384.3	400.9	421.7	447.5	477.6	508.7	543.9	583.3	627.9
142.5°	378.8	383.2	394.3	409.2	430.0	454.2	483.4	513.6	546.4	581.7	621.2
145°	394.8	397.8	407.2	422.7	440.3	464.1	491.1	519.1	548.0	579.2	612.3
147.5°	410.9	412.8	421.9	435.3	452.4	472.6	497.3	522.4	548.0	575.2	603.6
150°	421.7	422.7	431.0	444.4	459.0	477.6	501.4	523.2	548.0	571.9	597.8
152.5°	432.5	432.7	441.0	452.7	465.6	483.4	503.9	524.9	545.5	567.8	591.2
155°	448.6	448.6	454.9	465.2	476.5	491.1	508.7	525.3	542.9	560.5	581.2
157.5°	461.5	462.3	467.3	476.4	486.1	497.3	511.4	526.3	539.4	554.1	570.0
160°	471.4	471.4	475.5	483.8	491.1	501.4	513.9	526.3	537.7	549.1	562.6
162.5°	478.8	478.8	482.1	488.8	495.3	503.9	514.7	525.5	534.4	544.1	555.1
165°	490.1	489.0	491.1	496.2	500.4	507.7	515.9	523.2	529.4	536.6	544.9
167.5°	498.6	497.3	498.3	502.3	505.2	509.7	515.8	521.6	524.4	529.2	535.2
170°	503.5	501.4	502.5	505.6	507.7	509.7	514.9	519.1	521.1	524.2	529.4
172.5°	506.8	505.6	505.8	508.1	509.3	510.6	514.9	518.3	518.6	520.0	523.6
175°	510.8	509.7	508.7	510.8	510.8	511.8	513.9	515.9	514.9	514.9	517.0
177.5°	512.6	511.8	511.0	511.8	511.8	511.8	512.6	514.2	512.6	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8

TEST NUMBER: P332299-940

CATALOG NUMBER: S123RDIP-S560D1195U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	838.9	840.3	841.6	842.1	841.9	841.6	841.4	841.2
5°	833.3	834.7	836.1	836.6	836.3	836.0	835.7	835.4
7.5°	821.6	822.3	823.1	823.2	822.7	822.2	821.7	821.2
10°	811.1	811.3	811.4	811.1	810.4	809.6	808.9	808.1
12.5°	798.1	798.0	797.9	797.4	796.5	795.6	794.8	793.9
15°	775.2	774.4	773.6	772.7	771.6	770.6	769.5	768.5
17.5°	747.8	746.2	744.5	743.0	741.4	739.8	738.2	736.6
20°	729.0	727.0	725.1	723.2	721.3	719.5	717.6	715.9
22.5°	708.9	706.4	704.0	701.9	700.2	698.5	696.8	695.1
25°	676.0	672.8	669.7	667.2	665.6	663.9	662.2	660.5
27.5°	640.2	635.8	631.3	627.9	625.3	622.8	620.2	617.6
30°	614.7	609.5	604.4	600.6	598.2	595.8	593.3	590.8
32.5°	589.7	584.0	578.4	574.3	571.8	569.2	566.6	564.1
35°	552.5	546.0	539.5	534.8	532.1	529.4	526.6	523.9
37.5°	512.6	505.2	497.8	492.5	489.1	485.7	482.3	478.9
40°	484.9	477.0	469.1	463.4	459.9	456.5	453.0	449.4
42.5°	458.3	449.7	441.0	435.2	432.0	428.9	425.8	422.7
45°	419.2	410.5	401.9	395.7	392.1	388.4	384.8	381.1
47.5°	378.7	369.3	359.9	353.6	350.4	347.1	343.8	340.5
50°	351.4	342.0	332.6	326.1	322.6	319.1	315.7	312.2
52.5°	325.0	315.2	305.4	299.0	295.9	292.7	289.6	286.5
55°	285.7	276.9	268.0	262.2	259.1	256.1	253.1	250.0
57.5°	247.0	238.7	230.4	225.0	222.4	219.8	217.2	214.6
60°	222.7	214.5	206.3	200.9	198.3	195.7	193.1	190.6
62.5°	198.5	190.8	183.1	177.9	175.2	172.5	169.8	167.1
65°	164.1	156.7	149.2	144.6	143.0	141.3	139.6	137.9
67.5°	131.3	125.6	120.1	116.5	114.7	112.9	111.1	109.3
70°	110.9	105.7	100.3	96.8	95.1	93.5	91.8	90.2
72.5°	92.6	88.4	84.0	81.5	80.8	80.1	79.4	78.6
75°	69.4	67.9	66.3	65.5	65.1	64.8	64.5	64.2
77.5°	52.3	51.5	50.6	50.1	49.8	49.5	49.2	48.9
80°	42.1	41.6	41.2	40.8	40.6	40.2	39.9	39.6
82.5°	32.3	31.8	31.4	31.1	31.0	31.0	30.9	30.9
85°	18.5	18.2	17.9	17.7	17.7	17.7	17.7	17.7
87.5°	12.0	12.1	12.2	12.5	12.2	12.3	12.3	12.0
90°	25.9	26.9	28.0	30.1	29.0	30.1	31.1	30.1
92.5°	87.2	69.2	61.1	55.7	53.9	50.7	51.8	49.9
95°	373.0	252.8	197.9	160.6	140.9	131.6	124.3	120.2
97.5°	929.7	744.7	611.1	487.1	410.7	364.1	336.1	327.2
100°	1221.5	1137.6	1016.4	869.2	764.6	688.9	648.5	649.6
102.5°	1318.5	1315.7	1245.1	1151.8	1070.4	1010.6	976.8	953.0
105°	1346.8	1450.5	1470.2	1443.2	1395.5	1356.2	1323.0	1317.9
107.5°	1265.2	1433.4	1524.2	1561.1	1561.9	1548.6	1537.5	1527.9
110°	1187.3	1378.0	1508.5	1581.0	1610.0	1618.3	1616.2	1614.2

TEST NUMBER: P332299-940

CATALOG NUMBER: S123RDIP-S560D1195U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1110.2	1305.0	1451.3	1544.5	1597.6	1623.3	1631.1	1631.6
115°	1008.1	1188.3	1340.6	1453.6	1531.2	1576.8	1597.6	1602.8
117.5°	934.1	1089.7	1226.5	1341.0	1422.1	1474.3	1504.1	1511.2
120°	895.1	1035.0	1159.3	1264.0	1345.8	1403.8	1428.7	1434.9
122.5°	864.4	991.0	1106.3	1203.5	1276.2	1328.4	1355.8	1363.6
125°	823.7	936.6	1036.0	1118.9	1185.3	1230.8	1256.7	1264.0
127.5°	788.0	888.7	978.4	1053.8	1112.9	1151.8	1175.3	1181.9
130°	765.6	858.9	942.8	1013.3	1068.2	1105.5	1127.2	1135.5
132.5°	744.9	830.7	908.8	976.0	1027.5	1064.8	1084.1	1089.9
135°	716.9	790.5	857.8	916.9	967.7	998.7	1017.4	1024.7
137.5°	691.4	751.7	809.8	860.9	903.7	935.1	950.8	955.6
140°	676.5	729.3	779.1	823.7	863.0	892.1	908.6	907.6
142.5°	662.5	707.8	750.9	789.7	823.2	848.9	863.8	862.8
145°	645.4	679.7	712.8	742.8	768.7	790.5	798.8	800.8
147.5°	631.6	658.7	685.5	706.8	726.5	741.2	749.0	749.8
150°	621.6	645.4	667.2	686.9	702.4	713.8	720.1	720.1
152.5°	612.5	633.0	652.3	668.7	680.9	691.4	695.2	695.2
155°	598.8	615.4	631.0	643.4	652.7	661.0	663.1	664.1
157.5°	584.3	598.2	610.2	619.9	628.0	634.3	635.9	635.7
160°	576.0	587.5	597.8	605.0	612.3	618.5	618.5	617.5
162.5°	566.1	575.9	585.3	591.7	596.6	601.9	601.9	600.9
165°	553.2	559.5	566.7	571.9	576.0	580.1	579.2	579.2
167.5°	542.1	546.8	551.0	554.7	556.5	559.5	558.4	558.4
170°	534.6	537.7	541.8	543.9	544.9	547.1	546.0	546.0
172.5°	528.0	530.2	533.6	534.8	535.0	537.1	535.2	534.4
175°	519.1	520.0	522.2	522.2	522.2	523.2	522.2	521.1
177.5°	513.4	514.2	515.1	515.1	514.2	515.1	513.4	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8

(END OF REPORT)