

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332275-940

Luminaire Tested: **S123RDIP-S560D365U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332275-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3075.0 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332275-940

CATALOG NUMBER: S123RDIP-S560D365U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P332275-940

CATALOG NUMBER: S123RDIP-S560D365U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	89	94	91	87	84	80	77	75	69	68	66	60	59	57
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	39	37
5	71	60	51	46	67	56	49	44	50	44	40	44	39	36	39	35	32
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	28	25
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21
10	49	37	30	25	46	36	29	24	32	26	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9065	9065	9065
5°	9100	8975	9027
10°	9049	8862	8833
15°	8952	8655	8564
20°	8818	8395	8200
25°	8679	8105	7845
30°	8499	7768	7343
35°	8311	7432	6884
40°	8140	7035	6315
45°	7913	6645	5801
50°	7663	6199	5228
55°	7409	5692	4692
60°	7175	5147	4103
65°	6872	4559	3512
70°	6493	3827	2839
75°	5939	3011	2670
80°	5294	2672	2455
85°	4471	2359	2186

TEST NUMBER: P332275-940

CATALOG NUMBER: S123RDIP-S560D365U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	2.6
10°-20°	220.1	7.2
20°-30°	316.9	10.3
30°-40°	356.9	11.6
40°-50°	341.4	11.1
50°-60°	279.6	9.1
60°-70°	188.7	6.1
70°-80°	94.9	3.1
80°-90°	26.3	0.9
90°-100°	86.6	2.8
100°-110°	245.3	8.0
110°-120°	241.3	7.8
120°-130°	192.5	6.3
130°-140°	151.8	4.9
140°-150°	113.3	3.7
150°-160°	78.9	2.6
160°-170°	46.4	1.5
170°-180°	15.1	0.5
0°-30°	616.0	20.0
0°-40°	972.9	31.6
0°-60°	1594.0	51.8
0°-90°	1903.8	61.9
90°-120°	573.2	18.6
90°-150°	1030.7	33.5
90°-180°	1171.0	38.1
0°-180°	3075.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	842	839	831	836	835	80
15°	803	795	777	773	768	226
25°	731	713	682	668	660	336
35°	632	607	566	537	524	396
45°	520	488	436	399	381	401
55°	395	360	303	265	250	354
65°	270	231	179	147	138	267
75°	143	110	72	66	64	152
85°	36	22	19	18	18	41
90°	1	4	8	9	9	3
95°	11	35	187	55	37	12
105°	37	54	253	443	401	39
115°	65	80	194	425	488	64
125°	90	106	181	328	384	80
135°	105	126	178	270	312	81
145°	120	138	176	221	244	75
155°	136	147	170	194	202	63
165°	149	153	163	173	176	42
175°	155	156	157	159	158	15
180°	156	156	156	156	156	

TEST NUMBER: P332275-940

CATALOG NUMBER: S123RDIP-S560D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	845.0	844.5	844.0	843.5	843.0	842.0	840.6	839.1	837.7	836.2	837.6
5°	842.2	841.5	840.7	840.0	839.2	837.9	836.1	834.3	832.4	830.6	832.0
7.5°	834.5	833.7	832.8	832.0	831.2	829.6	827.2	824.8	822.4	820.1	820.8
10°	827.9	826.8	825.7	824.7	823.7	821.7	819.0	816.3	813.5	810.8	810.9
12.5°	818.6	817.4	816.2	815.0	813.9	811.6	808.2	804.9	801.6	798.3	798.2
15°	803.3	801.6	800.0	798.3	796.7	793.6	789.4	785.2	780.9	776.7	775.9
17.5°	784.0	782.1	780.2	778.2	776.2	772.6	767.1	761.8	756.3	751.0	749.4
20°	769.8	767.4	765.0	762.5	760.1	756.0	750.2	744.5	738.7	732.9	730.9
22.5°	753.9	751.2	748.4	745.6	742.8	738.3	732.2	726.0	720.0	713.8	711.3
25°	730.8	727.1	723.3	719.5	715.7	710.3	703.3	696.3	689.4	682.4	679.2
27.5°	702.8	698.7	694.5	690.3	686.1	680.1	672.3	664.6	656.8	649.1	644.6
30°	683.8	679.2	674.7	670.1	665.6	659.0	650.5	642.0	633.5	625.0	619.8
32.5°	664.6	659.5	654.3	649.2	644.0	636.9	627.9	618.9	609.9	600.9	595.3
35°	632.5	627.1	621.6	616.2	610.6	603.2	593.8	584.4	575.0	565.6	559.0
37.5°	600.0	594.0	587.9	581.8	575.7	567.7	557.6	547.6	537.5	527.4	520.0
40°	579.3	572.6	565.9	559.2	552.5	543.8	533.1	522.3	511.5	500.7	492.8
42.5°	555.7	549.0	542.4	535.7	529.1	520.1	509.0	497.8	486.7	475.5	466.9
45°	519.8	513.0	506.1	499.4	492.5	483.2	471.5	459.9	448.2	436.5	427.8
47.5°	483.8	476.4	468.9	461.4	453.9	444.3	432.6	420.9	409.2	397.5	388.2
50°	457.6	450.5	443.4	436.2	429.1	419.4	407.1	394.8	382.5	370.2	360.8
52.5°	434.2	426.4	418.7	410.9	403.2	393.2	381.0	368.9	356.7	344.6	334.7
55°	394.8	387.4	380.0	372.5	365.1	354.9	342.0	329.1	316.2	303.3	294.4
57.5°	358.5	350.4	342.2	334.1	326.0	315.5	302.6	289.6	276.6	263.7	255.4
60°	333.3	325.0	316.6	308.3	300.0	289.4	276.9	264.3	251.6	239.1	230.9
62.5°	308.2	299.9	291.5	283.1	274.8	264.3	251.7	239.2	226.5	213.9	206.3
65°	269.8	261.4	253.2	244.8	236.4	226.3	214.5	202.7	190.8	179.0	171.6
67.5°	231.4	223.0	214.5	206.1	197.7	187.8	176.4	165.1	153.7	142.3	136.8
70°	206.3	198.0	189.9	181.7	173.5	164.1	153.5	142.9	132.2	121.6	116.3
72.5°	181.1	173.1	165.0	156.9	148.8	140.0	130.4	120.6	111.0	101.4	97.0
75°	142.8	135.5	128.2	120.9	113.6	105.8	97.5	89.1	80.8	72.4	70.9
77.5°	107.8	101.2	94.6	88.0	81.4	75.4	70.1	64.7	59.3	53.9	53.1
80°	85.4	79.2	72.9	66.7	60.5	55.8	52.6	49.4	46.2	43.1	42.5
82.5°	64.1	58.7	53.3	48.0	42.5	39.1	37.6	36.2	34.7	33.2	32.7
85°	36.2	32.9	29.5	26.2	22.8	21.0	20.5	20.1	19.6	19.1	18.8
87.5°	13.2	12.0	10.8	9.6	8.5	7.9	8.1	8.3	8.5	8.6	8.5
90°	0.6	1.2	1.9	2.9	3.5	4.1	5.1	6.0	7.0	7.8	7.6
92.5°	3.9	5.8	8.5	10.9	13.6	18.2	26.5	40.0	53.3	48.4	36.6
95°	10.7	11.7	15.2	20.5	28.7	40.9	67.8	114.7	166.4	186.9	151.6
97.5°	18.3	18.5	21.3	25.9	34.1	47.3	72.9	125.8	212.0	289.6	309.8
100°	23.4	23.6	25.9	30.2	37.8	50.1	72.1	118.8	201.7	298.5	360.5
102.5°	28.6	29.2	31.1	35.3	42.1	53.4	73.2	112.7	186.5	282.0	363.0
105°	36.6	37.5	39.4	43.2	49.1	58.9	76.0	108.4	168.0	253.3	343.8
107.5°	45.0	45.9	47.8	51.5	57.1	66.2	81.1	108.1	156.1	228.0	310.1
110°	51.0	52.0	53.6	57.1	62.4	71.2	85.4	109.3	151.6	213.7	289.0

TEST NUMBER: P332275-940

CATALOG NUMBER: S123RDIP-S560D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	56.6	57.5	59.1	62.6	67.9	76.5	89.7	111.9	149.0	204.0	270.5
115°	64.6	65.9	67.8	70.9	76.2	84.8	96.8	115.9	148.1	193.8	248.3
117.5°	72.6	74.0	75.6	78.6	84.5	92.4	104.2	121.4	148.6	187.7	234.9
120°	78.1	79.1	80.7	83.8	89.8	97.6	109.1	125.4	149.7	184.9	227.8
122.5°	82.9	83.9	85.4	88.9	94.6	103.0	114.0	129.2	151.4	183.2	222.0
125°	89.8	90.4	92.3	95.8	101.7	110.3	121.4	135.2	154.1	180.8	214.6
127.5°	95.1	95.9	98.4	101.8	108.4	117.0	127.6	140.1	157.1	179.8	208.0
130°	98.4	99.2	102.1	105.8	112.5	121.0	131.4	143.4	159.2	179.0	204.5
132.5°	100.9	102.0	105.1	109.7	116.3	124.6	134.6	146.4	160.7	178.7	201.3
135°	105.2	106.5	109.9	114.7	121.4	129.8	139.6	150.3	162.9	178.3	197.0
137.5°	109.4	110.8	114.1	119.1	125.7	133.6	143.0	153.2	164.4	177.6	193.2
140°	112.2	113.8	116.9	122.0	128.2	136.2	145.3	154.7	165.4	177.5	190.9
142.5°	115.2	116.5	119.9	124.5	130.8	138.1	147.0	156.2	166.2	176.9	189.0
145°	120.0	121.0	123.9	128.6	133.9	141.2	149.4	157.8	166.7	176.1	186.2
147.5°	125.0	125.6	128.3	132.4	137.6	143.7	151.2	158.9	166.7	175.0	183.6
150°	128.2	128.6	131.1	135.2	139.6	145.3	152.5	159.2	166.7	174.0	181.8
152.5°	131.5	131.6	134.1	137.7	141.6	147.0	153.3	159.6	165.9	172.7	179.8
155°	136.4	136.4	138.3	141.5	145.0	149.4	154.7	159.8	165.1	170.5	176.7
157.5°	140.4	140.6	142.1	144.9	147.8	151.2	155.5	160.1	164.1	168.5	173.3
160°	143.4	143.4	144.6	147.1	149.4	152.5	156.3	160.1	163.5	167.0	171.1
162.5°	145.6	145.6	146.7	148.6	150.6	153.3	156.6	159.8	162.6	165.5	168.8
165°	149.0	148.7	149.4	151.0	152.2	154.4	156.9	159.2	161.0	163.3	165.8
167.5°	151.6	151.2	151.6	152.8	153.6	155.1	156.9	158.6	159.5	161.0	162.8
170°	153.1	152.5	152.8	153.7	154.4	155.1	156.6	157.8	158.5	159.4	161.0
172.5°	154.2	153.7	153.8	154.5	154.9	155.2	156.6	157.7	157.7	158.2	159.3
175°	155.3	155.1	154.7	155.3	155.3	155.7	156.3	156.9	156.6	156.6	157.2
177.5°	156.0	155.7	155.4	155.7	155.7	155.7	156.0	156.4	156.0	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7

TEST NUMBER: P332275-940

CATALOG NUMBER: S123RDIP-S560D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	838.9	840.3	841.6	842.1	841.9	841.6	841.4	841.2
5°	833.3	834.7	836.1	836.6	836.3	836.0	835.7	835.4
7.5°	821.6	822.3	823.1	823.2	822.7	822.2	821.7	821.2
10°	811.1	811.3	811.4	811.1	810.4	809.6	808.9	808.1
12.5°	798.1	798.0	797.9	797.4	796.5	795.6	794.8	793.9
15°	775.2	774.4	773.6	772.7	771.6	770.6	769.5	768.5
17.5°	747.8	746.2	744.5	743.0	741.4	739.8	738.2	736.6
20°	729.0	727.0	725.1	723.2	721.3	719.5	717.6	715.9
22.5°	708.9	706.4	704.0	701.9	700.2	698.5	696.8	695.1
25°	676.0	672.8	669.7	667.2	665.6	663.9	662.2	660.5
27.5°	640.2	635.8	631.3	627.9	625.3	622.8	620.2	617.6
30°	614.7	609.5	604.4	600.6	598.2	595.8	593.3	590.8
32.5°	589.7	584.0	578.4	574.3	571.8	569.2	566.6	564.1
35°	552.5	546.0	539.5	534.8	532.1	529.4	526.6	523.9
37.5°	512.6	505.2	497.8	492.5	489.1	485.7	482.3	478.9
40°	484.9	477.0	469.1	463.4	459.9	456.5	453.0	449.4
42.5°	458.3	449.7	441.0	435.2	432.0	428.9	425.8	422.7
45°	419.2	410.5	401.9	395.7	392.1	388.4	384.8	381.1
47.5°	378.7	369.3	359.9	353.6	350.4	347.1	343.8	340.5
50°	351.4	342.0	332.6	326.1	322.6	319.1	315.7	312.2
52.5°	325.0	315.2	305.4	299.0	295.9	292.7	289.6	286.5
55°	285.7	276.9	268.0	262.2	259.1	256.1	253.1	250.0
57.5°	247.0	238.7	230.4	225.0	222.4	219.8	217.2	214.6
60°	222.7	214.5	206.3	200.9	198.3	195.7	193.1	190.6
62.5°	198.5	190.8	183.1	177.9	175.2	172.5	169.8	167.1
65°	164.1	156.7	149.2	144.6	143.0	141.3	139.6	137.9
67.5°	131.3	125.6	120.1	116.5	114.7	112.9	111.1	109.3
70°	110.9	105.7	100.3	96.8	95.1	93.5	91.8	90.2
72.5°	92.6	88.4	84.0	81.5	80.8	80.1	79.4	78.6
75°	69.4	67.9	66.3	65.5	65.1	64.8	64.5	64.2
77.5°	52.3	51.5	50.6	50.1	49.8	49.5	49.2	48.9
80°	42.1	41.6	41.2	40.8	40.6	40.2	39.9	39.6
82.5°	32.3	31.8	31.4	31.1	31.0	31.0	30.9	30.9
85°	18.5	18.2	17.9	17.7	17.7	17.7	17.7	17.7
87.5°	8.5	8.4	8.3	8.3	8.1	8.1	8.0	7.8
90°	7.8	8.2	8.5	9.1	8.8	9.1	9.5	9.1
92.5°	26.6	21.0	18.5	16.9	16.4	15.4	15.8	15.2
95°	113.4	76.9	60.2	48.9	42.9	40.0	37.8	36.6
97.5°	282.8	226.5	185.8	148.2	124.9	110.8	102.2	99.5
100°	371.5	346.0	309.2	264.4	232.6	209.6	197.2	197.6
102.5°	401.0	400.2	378.7	350.4	325.6	307.4	297.1	289.8
105°	409.7	441.1	447.1	439.0	424.5	412.5	402.4	400.8
107.5°	384.8	436.0	463.6	474.8	475.1	471.0	467.6	464.8
110°	361.1	419.1	458.8	480.9	489.7	492.2	491.6	491.0

TEST NUMBER: P332275-940

CATALOG NUMBER: S123RDIP-S560D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	337.7	396.9	441.4	469.8	485.9	493.7	496.1	496.2
115°	306.6	361.4	407.8	442.1	465.7	479.6	485.9	487.5
117.5°	284.1	331.4	373.0	407.9	432.6	448.4	457.4	459.6
120°	272.2	314.8	352.6	384.4	409.3	427.0	434.5	436.4
122.5°	263.0	301.4	336.4	366.0	388.2	404.0	412.3	414.7
125°	250.5	284.9	315.1	340.4	360.5	374.3	382.3	384.4
127.5°	239.7	270.3	297.6	320.6	338.5	350.4	357.5	359.4
130°	232.8	261.3	286.8	308.2	324.9	336.3	342.9	345.4
132.5°	226.6	252.6	276.4	296.9	312.5	323.9	329.8	331.5
135°	218.0	240.4	260.9	278.8	294.4	303.8	309.4	311.7
137.5°	210.3	228.6	246.3	261.9	274.8	284.5	289.2	290.7
140°	205.8	221.9	236.9	250.5	262.5	271.3	276.3	276.1
142.5°	201.5	215.3	228.4	240.1	250.4	258.2	262.7	262.4
145°	196.4	206.7	216.8	226.0	233.8	240.4	243.0	243.6
147.5°	192.1	200.4	208.5	215.0	221.0	225.4	227.8	228.1
150°	189.0	196.4	203.0	208.9	213.7	217.1	219.0	219.0
152.5°	186.3	192.5	198.4	203.4	207.1	210.3	211.4	211.4
155°	182.2	187.2	191.9	195.6	198.5	201.1	201.7	202.0
157.5°	177.7	181.9	185.6	188.6	191.0	192.9	193.4	193.3
160°	175.2	178.7	181.8	184.0	186.2	188.2	188.2	187.8
162.5°	172.2	175.1	178.1	180.0	181.5	183.1	183.1	182.8
165°	168.3	170.1	172.4	174.0	175.2	176.5	176.1	176.1
167.5°	164.9	166.3	167.6	168.7	169.2	170.1	169.9	169.9
170°	162.6	163.5	164.8	165.4	165.8	166.4	166.0	166.0
172.5°	160.6	161.3	162.3	162.6	162.7	163.4	162.8	162.6
175°	157.8	158.2	158.8	158.8	158.8	159.2	158.8	158.5
177.5°	156.1	156.4	156.7	156.7	156.4	156.7	156.1	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7

(END OF REPORT)