

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831595

Luminaire Tested: S123DIP-S775D1025U850-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831595
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U850-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7841.0 lumens
Efficiency: N/A
Efficacy: 151.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 51.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

Luminous Intensity Polar Plot



TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	49	49
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	59	51	45	64	55	48	43	47	42	38	40	36	33	33	31	28
6	65	53	45	40	60	49	43	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	26	23	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	24	21	19
10	49	37	30	26	45	35	29	24	31	26	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	26337	26337	26337	26337	26337
5°	33309	31437	26573	21414	19678
10°	33632	34649	26397	17070	14917
15°	25331	32169	26216	14456	12615
20°	17649	26032	25882	12641	11458
25°	13459	20018	25312	11631	10747
30°	11642	15904	24401	10916	10174
35°	10801	13428	23349	10399	9772
40°	10227	12045	21874	9908	9636
45°	9887	11149	19998	9523	9575
50°	9716	10438	17777	9173	9525
55°	9355	9918	15597	8843	9567
60°	9020	9362	13444	8531	9410
65°	8474	8835	11596	8199	9225
70°	7827	8164	9863	7648	8683
75°	7083	7320	8451	7107	7935
80°	5839	6403	6688	6192	6688
85°	4631	5187	4903	5261	5323

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°

Vertical Angle: 45°

Luminance: 22832 cd/sqm

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.3	3.0
10°-20°	575.5	7.3
20°-30°	681.4	8.7
30°-40°	685.1	8.7
40°-50°	628.6	8.0
50°-60°	518.8	6.6
60°-70°	367.0	4.7
70°-80°	195.9	2.5
80°-90°	52.7	0.7
90°-100°	90.7	1.2
100°-110°	274.6	3.5
110°-120°	467.4	6.0
120°-130°	614.9	7.8
130°-140°	691.2	8.8
140°-150°	679.5	8.7
150°-160°	572.1	7.3
160°-170°	380.9	4.9
170°-180°	133.4	1.7
0°-30°	1488.2	19.0
0°-40°	2173.3	27.7
0°-60°	3320.7	42.4
0°-90°	3936.3	50.2
90°-120°	832.7	10.6
90°-150°	2818.3	35.9
90°-180°	3905.0	49.8
0°-180°	7841.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2447	2447	2447	2447	2447	
5°	3083	2910	2459	1982	1821	294
15°	2273	2887	2353	1297	1132	628
25°	1133	1686	2131	979	905	535
35°	822	1022	1777	791	744	517
45°	650	732	1314	626	629	503
55°	498	528	831	471	510	446
65°	333	347	455	322	362	331
75°	170	176	203	171	191	179
85°	38	42	40	43	43	42
90°	33	27	1	27	33	18
95°	86	82	65	82	86	87
105°	264	261	249	261	264	279
115°	472	472	470	472	472	467
125°	681	690	689	690	681	609
135°	892	899	893	899	892	686
145°	1084	1089	1084	1089	1084	677
155°	1239	1242	1241	1242	1239	571
165°	1347	1348	1352	1348	1347	380
175°	1400	1402	1406	1402	1400	133
180°	1409	1409	1409	1409	1409	

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2758.0	2755.1	2752.3	2738.1	2723.9	2717.1	2710.3	2689.8	2669.4	2646.7	2624.0
5°	3082.7	3090.6	3098.6	3089.5	3080.4	3052.6	3024.8	2987.9	2951.0	2909.5	2868.1
7.5°	3232.6	3237.1	3241.6	3236.0	3230.3	3222.9	3215.5	3182.6	3149.7	3107.1	3064.5
10°	3077.0	3087.2	3097.4	3119.6	3141.7	3166.7	3191.7	3187.1	3182.6	3170.1	3157.6
12.5°	2735.2	2747.7	2760.2	2804.5	2848.8	2905.6	2962.3	3011.2	3060.0	3094.0	3128.1
15°	2273.1	2307.8	2342.4	2382.7	2423.0	2506.5	2589.9	2692.7	2795.4	2886.8	2978.2
17.5°	1872.3	1885.4	1898.4	1941.6	1984.7	2089.8	2194.8	2313.4	2432.1	2583.7	2735.2
20°	1540.8	1552.7	1564.6	1621.4	1678.2	1760.5	1842.8	1976.2	2109.6	2272.6	2435.5
22.5°	1294.4	1313.1	1331.9	1363.6	1395.4	1474.4	1553.3	1671.9	1790.6	1970.5	2150.5
25°	1133.2	1146.8	1160.4	1179.7	1199.0	1262.0	1325.0	1422.7	1520.3	1685.5	1850.7
27.5°	1023.0	1028.7	1034.4	1053.7	1073.0	1113.9	1154.7	1238.8	1322.8	1463.0	1603.2
30°	936.7	940.7	944.7	961.7	978.7	1006.6	1034.4	1095.1	1155.9	1279.6	1403.4
32.5°	876.5	879.4	882.2	895.3	908.3	928.2	948.1	992.4	1036.6	1138.8	1241.0
35°	822.0	823.8	825.5	835.1	844.8	859.5	874.3	907.8	941.3	1021.9	1102.5
37.5°	774.4	776.6	778.9	784.6	790.3	803.3	816.4	843.1	869.7	931.6	993.5
40°	727.8	731.8	735.8	739.7	743.7	754.5	765.3	785.7	806.2	857.2	908.3
42.5°	688.1	692.0	696.0	697.7	699.4	705.7	711.9	730.6	749.4	787.4	825.5
45°	649.5	651.2	652.9	654.6	656.3	661.4	666.5	683.0	699.4	732.4	765.3
47.5°	614.3	614.3	614.3	615.4	616.5	621.1	625.6	637.5	649.5	675.0	700.6
50°	580.2	580.2	580.2	578.5	576.8	579.6	582.5	591.6	600.6	623.3	646.1
52.5°	539.3	539.3	539.3	539.9	540.5	540.5	540.5	548.4	556.4	576.8	597.2
55°	498.5	500.7	503.0	501.3	499.6	500.7	501.9	507.0	512.1	528.5	545.0
57.5°	457.6	458.7	459.8	459.3	458.7	459.3	459.8	464.4	468.9	481.4	493.9
60°	419.0	419.0	419.0	417.8	416.7	417.8	419.0	421.2	423.5	434.9	446.2
62.5°	375.8	376.4	377.0	377.5	378.1	377.0	375.8	378.7	381.5	390.0	398.5
65°	332.7	333.2	333.8	335.5	337.2	336.1	335.0	337.8	340.6	346.9	353.1
67.5°	294.1	292.9	291.8	292.4	292.9	294.6	296.3	296.9	297.5	304.3	311.1
70°	248.7	249.8	250.9	250.4	249.8	250.4	250.9	252.6	254.3	259.4	264.6
72.5°	207.8	208.4	208.9	208.9	208.9	210.1	211.2	212.9	214.6	217.4	220.3
75°	170.3	170.3	170.3	171.4	172.6	173.2	173.7	173.7	173.7	176.0	178.3
77.5°	129.4	132.3	135.1	134.5	134.0	135.1	136.3	138.0	139.7	140.8	141.9
80°	94.2	94.2	94.2	94.8	95.4	97.1	98.8	99.9	101.1	103.3	105.6
82.5°	60.2	60.7	61.3	63.0	64.7	65.9	67.0	68.7	70.4	70.4	70.4
85°	37.5	36.3	35.2	36.3	37.5	38.6	39.7	40.3	40.9	42.0	43.1
87.5°	18.2	18.2	18.2	18.2	18.2	18.7	19.3	19.3	19.3	19.3	19.3
90°	33.2	32.7	32.2	31.7	31.2	30.5	29.5	28.5	27.6	26.6	23.4
92.5°	47.6	48.1	48.6	49.1	49.6	49.4	48.7	48.0	47.2	46.5	45.0
95°	86.3	86.3	86.3	86.3	86.3	85.9	84.9	83.9	82.9	81.9	80.0
97.5°	124.0	124.2	124.5	124.7	125.0	124.5	123.2	122.0	120.8	119.6	118.1
100°	168.3	167.8	167.3	166.8	166.3	165.7	164.9	164.2	163.5	162.7	161.5
102.5°	213.7	213.9	214.1	214.4	214.6	214.4	213.7	212.9	212.2	211.4	209.7
105°	263.5	263.0	262.5	262.0	261.5	261.3	261.3	261.3	261.3	261.3	259.0
107.5°	314.4	314.6	314.9	315.1	315.4	315.1	314.4	313.7	312.9	312.2	311.2
110°	366.4	366.9	367.4	367.9	368.4	368.1	367.2	366.2	365.2	364.2	363.7

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	421.8	421.8	421.8	421.8	421.8	421.2	419.9	418.7	417.5	416.2	416.2
115°	471.6	471.8	472.1	472.3	472.6	472.6	472.3	472.1	471.8	471.6	472.1
117.5°	522.5	523.2	524.0	524.7	525.5	525.8	525.8	525.8	525.8	525.8	526.3
120°	576.8	577.2	577.7	578.2	578.7	579.1	579.3	579.6	579.8	580.1	581.3
122.5°	628.8	629.5	630.3	631.0	631.7	632.5	633.2	633.9	634.7	635.4	635.9
125°	680.8	681.8	682.8	683.8	684.7	685.7	686.7	687.7	688.7	689.7	690.2
127.5°	732.8	733.8	734.8	735.8	736.8	738.0	739.5	741.0	742.4	743.9	744.4
130°	783.8	785.5	787.2	788.9	790.7	792.0	793.0	794.0	795.0	795.9	796.7
132.5°	836.9	838.1	839.4	840.6	841.8	843.1	844.3	845.5	846.7	848.0	848.5
135°	892.3	892.7	893.2	893.7	894.2	895.0	895.9	896.9	897.9	898.9	899.1
137.5°	941.0	941.7	942.4	943.2	943.9	944.9	946.1	947.4	948.6	949.8	949.1
140°	988.6	990.3	992.0	993.7	995.5	996.4	996.7	996.9	997.2	997.4	997.2
142.5°	1037.3	1038.5	1039.7	1041.0	1042.2	1042.9	1043.2	1043.4	1043.7	1043.9	1043.4
145°	1083.8	1084.7	1085.7	1086.7	1087.7	1088.3	1088.6	1088.8	1089.1	1089.3	1088.6
147.5°	1125.8	1127.3	1128.8	1130.3	1131.7	1132.5	1132.5	1132.5	1132.5	1132.5	1131.7
150°	1165.7	1167.2	1168.6	1170.1	1171.6	1172.3	1172.3	1172.3	1172.3	1172.3	1171.8
152.5°	1204.4	1205.7	1206.9	1208.1	1209.4	1209.7	1209.2	1208.7	1208.2	1207.8	1207.5
155°	1238.7	1240.5	1242.2	1243.9	1245.6	1246.0	1245.0	1244.0	1243.1	1242.1	1241.8
157.5°	1270.9	1272.3	1273.8	1275.3	1276.8	1277.0	1276.0	1275.0	1274.0	1273.1	1272.8
160°	1301.8	1302.8	1303.8	1304.8	1305.8	1305.7	1304.4	1303.2	1302.0	1300.7	1300.7
162.5°	1325.1	1326.8	1328.5	1330.3	1332.0	1332.2	1331.0	1329.8	1328.5	1327.3	1327.1
165°	1347.2	1349.0	1350.7	1352.4	1354.1	1354.2	1352.8	1351.3	1349.8	1348.3	1348.3
167.5°	1367.2	1368.6	1370.1	1371.6	1373.1	1373.1	1371.6	1370.1	1368.6	1367.2	1366.9
170°	1381.6	1383.3	1385.0	1386.7	1388.4	1388.4	1386.7	1385.0	1383.3	1381.6	1381.6
172.5°	1392.6	1394.3	1396.1	1397.8	1399.5	1399.6	1398.2	1396.7	1395.2	1393.7	1393.7
175°	1400.4	1402.1	1403.8	1405.5	1407.3	1407.4	1405.9	1404.4	1403.0	1401.5	1401.5
177.5°	1404.8	1406.5	1408.2	1410.0	1411.7	1411.8	1410.3	1408.9	1407.4	1405.9	1405.9
180°	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2617.2	2610.3	2585.4	2560.4	2532.0	2503.6	2482.6	2461.6	2430.4	2399.2	2373.6
5°	2836.3	2804.5	2751.7	2698.9	2627.4	2555.8	2507.6	2459.3	2394.6	2329.9	2278.2
7.5°	3010.0	2955.5	2881.7	2807.9	2714.2	2620.6	2532.0	2443.4	2344.7	2245.9	2165.3
10°	3120.7	3083.8	2998.7	2913.5	2788.0	2662.6	2538.8	2415.1	2287.9	2160.7	2054.0
12.5°	3131.5	3134.9	3056.6	2978.2	2836.3	2694.4	2543.9	2393.5	2233.4	2073.3	1949.0
15°	3036.7	3095.2	3052.0	3008.9	2865.8	2722.8	2537.7	2352.6	2168.1	1983.6	1840.0
17.5°	2860.7	2986.2	2992.4	2998.7	2855.6	2712.5	2507.6	2302.6	2093.7	1884.8	1733.8
20°	2620.6	2805.6	2869.2	2932.8	2816.4	2700.0	2479.8	2259.5	2025.6	1791.7	1633.3
22.5°	2375.3	2600.1	2716.5	2832.9	2746.6	2660.3	2425.8	2191.4	1944.4	1697.5	1536.8
25°	2096.0	2341.3	2520.1	2698.9	2646.1	2593.3	2362.3	2131.2	1868.3	1605.5	1441.4
27.5°	1852.4	2101.7	2317.4	2533.1	2521.8	2510.4	2281.1	2051.7	1782.6	1513.5	1355.1
30°	1635.6	1867.8	2109.1	2350.3	2378.2	2406.0	2184.6	1963.2	1693.5	1423.8	1271.1
32.5°	1443.7	1646.4	1905.2	2164.1	2218.6	2273.1	2073.3	1873.5	1606.6	1339.8	1192.8
35°	1286.4	1470.4	1729.3	1988.1	2056.3	2124.4	1950.7	1776.9	1516.9	1256.9	1116.7
37.5°	1147.3	1301.2	1553.8	1806.5	1889.9	1973.4	1817.8	1662.3	1418.7	1175.2	1046.3
40°	1032.1	1155.9	1388.1	1620.3	1716.8	1813.3	1685.0	1556.7	1325.6	1094.6	975.9
42.5°	935.6	1045.7	1256.4	1467.0	1559.5	1652.0	1543.6	1435.2	1229.7	1024.2	915.7
45°	853.3	941.3	1132.6	1323.9	1411.9	1499.9	1406.8	1313.7	1132.6	951.5	850.4
47.5°	776.1	851.6	1015.1	1178.6	1256.9	1335.3	1262.6	1189.9	1036.6	883.4	792.0
50°	706.8	767.5	910.6	1053.7	1121.8	1189.9	1125.8	1061.6	935.6	809.6	730.1
52.5°	646.6	696.0	815.8	935.6	994.1	1052.5	997.5	942.4	842.5	742.6	673.3
55°	587.0	629.0	732.9	836.8	876.5	916.3	873.7	831.1	750.5	669.9	611.4
57.5°	531.4	568.8	654.0	739.2	769.8	800.5	761.9	723.3	662.5	601.8	553.0
60°	476.9	507.5	578.5	649.5	668.2	686.9	655.7	624.5	581.9	539.3	495.6
62.5°	426.4	454.2	507.0	559.8	572.3	584.7	560.9	537.1	504.7	472.3	438.3
65°	374.1	395.1	438.3	481.4	489.4	497.3	476.3	455.3	430.9	406.5	381.5
67.5°	325.9	340.6	375.8	411.0	411.6	412.2	395.1	378.1	364.5	350.8	331.0
70°	278.7	292.9	316.2	339.5	340.1	340.6	327.0	313.4	303.2	292.9	278.2
72.5°	230.5	240.7	258.3	275.9	274.8	273.6	265.1	256.6	248.7	240.7	229.9
75°	186.8	195.3	207.2	219.1	215.7	212.3	207.8	203.2	196.4	189.6	182.8
77.5°	147.0	152.1	159.0	165.8	163.5	161.2	157.3	153.3	148.2	143.1	140.2
80°	107.9	110.1	114.7	119.2	118.1	116.9	112.4	107.9	106.7	105.6	101.6
82.5°	73.2	76.1	77.2	78.3	77.8	77.2	73.8	70.4	69.3	68.1	67.6
85°	43.7	44.3	44.8	45.4	43.7	42.0	40.9	39.7	39.7	39.7	39.2
87.5°	19.9	20.4	20.4	20.4	19.9	19.3	18.2	17.0	17.6	18.2	18.2
90°	20.2	17.0	13.8	10.9	8.5	6.0	3.6	1.1	3.6	6.0	8.5
92.5°	43.5	42.1	40.6	39.1	37.6	36.2	34.7	33.2	34.7	36.2	37.6
95°	78.0	76.0	74.0	72.2	70.5	68.8	67.0	65.3	67.0	68.8	70.5
97.5°	116.6	115.1	113.7	112.3	111.1	109.8	108.6	107.4	108.6	109.8	111.1
100°	160.3	159.0	157.8	156.5	155.0	153.5	152.0	150.6	152.0	153.5	155.0
102.5°	208.0	206.3	204.6	203.3	202.6	201.8	201.1	200.4	201.1	201.8	202.6
105°	256.8	254.6	252.4	251.0	250.6	250.1	249.6	249.1	249.6	250.1	250.6
107.5°	310.2	309.2	308.2	307.6	307.4	307.1	306.9	306.6	306.9	307.1	307.4
110°	363.2	362.7	362.2	361.7	361.3	360.8	360.3	359.8	360.3	360.8	361.3

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.2	416.2	416.2	416.1	415.9	415.6	415.4	415.1	415.4	415.6	415.9
115°	472.6	473.1	473.6	473.4	472.7	472.0	471.2	470.5	471.2	472.0	472.7
117.5°	526.8	527.3	527.8	527.9	527.7	527.4	527.2	526.9	527.2	527.4	527.7
120°	582.5	583.8	585.0	584.9	583.4	581.9	580.4	579.0	580.4	581.9	583.4
122.5°	636.4	636.9	637.4	637.1	636.2	635.2	634.2	633.2	634.2	635.2	636.2
125°	690.7	691.1	691.6	691.5	690.8	690.0	689.3	688.6	689.3	690.0	690.8
127.5°	744.9	745.4	745.9	745.4	743.9	742.4	741.0	739.5	741.0	742.4	743.9
130°	797.4	798.2	798.9	798.3	796.3	794.3	792.4	790.4	792.4	794.3	796.3
132.5°	849.0	849.4	849.9	849.2	847.2	845.3	843.3	841.3	843.3	845.3	847.2
135°	899.4	899.6	899.9	899.3	897.8	896.3	894.8	893.4	894.8	896.3	897.8
137.5°	948.3	947.6	946.9	945.9	944.7	943.4	942.2	941.0	942.2	943.4	944.7
140°	996.9	996.7	996.4	995.7	994.5	993.2	992.0	990.8	992.0	993.2	994.5
142.5°	1042.9	1042.4	1041.9	1041.1	1039.9	1038.6	1037.4	1036.2	1037.4	1038.6	1039.9
145°	1087.8	1087.1	1086.3	1085.7	1085.2	1084.7	1084.3	1083.8	1084.3	1084.7	1085.2
147.5°	1131.0	1130.3	1129.5	1128.7	1127.7	1126.7	1125.7	1124.7	1125.7	1126.7	1127.7
150°	1171.3	1170.9	1170.4	1169.9	1169.4	1168.9	1168.4	1167.9	1168.4	1168.9	1169.4
152.5°	1207.3	1207.0	1206.8	1206.3	1205.5	1204.8	1204.1	1203.3	1204.1	1204.8	1205.5
155°	1241.6	1241.3	1241.1	1241.0	1241.0	1241.0	1241.0	1241.0	1241.0	1241.0	1241.0
157.5°	1272.6	1272.3	1272.1	1272.1	1272.3	1272.6	1272.8	1273.1	1272.8	1272.6	1272.3
160°	1300.7	1300.7	1300.7	1301.0	1301.5	1302.0	1302.5	1303.0	1302.5	1302.0	1301.5
162.5°	1326.8	1326.6	1326.3	1326.6	1327.3	1328.0	1328.8	1329.5	1328.8	1328.0	1327.3
165°	1348.3	1348.3	1348.3	1348.7	1349.4	1350.2	1350.9	1351.7	1350.9	1350.2	1349.4
167.5°	1366.7	1366.4	1366.2	1366.5	1367.5	1368.5	1369.5	1370.5	1369.5	1368.5	1367.5
170°	1381.6	1381.6	1381.6	1382.0	1383.0	1384.0	1385.0	1386.0	1385.0	1384.0	1383.0
172.5°	1393.7	1393.7	1393.7	1394.2	1395.2	1396.2	1397.2	1398.2	1397.2	1396.2	1395.2
175°	1401.5	1401.5	1401.5	1402.0	1403.0	1403.9	1404.9	1405.9	1404.9	1403.9	1403.0
177.5°	1405.9	1405.9	1405.9	1406.4	1407.4	1408.4	1409.4	1410.3	1409.4	1408.4	1407.4
180°	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2348.1	2325.9	2303.8	2286.8	2269.7	2240.8	2211.8	2205.0	2198.2	2188.5	2178.9
5°	2226.6	2172.1	2117.6	2068.7	2019.9	1981.9	1943.9	1918.9	1893.9	1875.7	1857.6
7.5°	2084.6	2002.9	1921.1	1863.2	1805.3	1750.3	1695.2	1677.6	1660.0	1636.2	1612.3
10°	1947.3	1857.0	1766.7	1691.2	1615.7	1561.8	1507.8	1486.3	1464.7	1434.6	1404.5
12.5°	1824.6	1725.8	1627.1	1551.0	1474.9	1422.7	1370.5	1339.2	1308.0	1291.0	1273.9
15°	1696.3	1590.7	1485.1	1414.7	1344.3	1297.2	1250.1	1222.9	1195.6	1179.1	1162.7
17.5°	1582.8	1478.3	1373.9	1306.3	1238.8	1195.6	1152.5	1128.6	1104.8	1092.3	1079.8
20°	1474.9	1372.7	1270.5	1204.7	1138.8	1103.6	1068.4	1053.1	1037.8	1027.6	1017.3
22.5°	1376.1	1275.7	1175.2	1119.0	1062.8	1034.4	1006.0	995.2	984.4	975.9	967.4
25°	1277.4	1187.7	1098.0	1050.3	1002.6	979.3	956.0	945.2	934.5	925.9	917.4
27.5°	1196.7	1111.0	1025.3	984.4	943.5	925.4	907.2	898.7	890.2	882.2	874.3
30°	1118.4	1041.8	965.1	929.9	894.7	878.3	861.8	853.3	844.8	837.4	830.0
32.5°	1045.7	979.9	914.0	881.7	849.3	835.7	822.0	811.8	801.6	795.9	790.3
35°	976.5	917.4	858.4	831.7	805.0	791.4	777.8	769.3	760.7	756.2	751.7
37.5°	917.4	864.6	811.8	786.3	760.7	747.7	734.6	727.2	719.9	718.2	716.5
40°	857.2	811.8	766.4	741.4	716.5	705.1	693.7	689.2	684.7	683.5	682.4
42.5°	807.3	763.0	718.7	696.0	673.3	663.7	654.0	651.7	649.5	651.2	652.9
45°	749.4	712.5	675.6	654.6	633.6	625.6	617.7	616.0	614.3	617.7	621.1
47.5°	700.6	666.5	632.4	612.6	592.7	587.0	581.3	580.8	580.2	584.7	589.3
50°	650.6	617.7	584.7	568.8	553.0	547.8	542.7	544.4	546.1	553.5	560.9
52.5°	604.0	573.4	542.7	528.0	513.2	509.8	506.4	510.4	514.3	522.3	530.2
55°	553.0	525.1	497.3	486.0	474.6	471.2	467.8	475.7	483.7	491.1	498.5
57.5°	504.1	479.7	455.3	445.1	434.9	434.3	433.7	441.1	448.5	456.4	464.4
60°	451.9	431.5	411.0	403.1	395.1	396.3	397.4	405.9	414.4	420.7	426.9
62.5°	404.2	387.2	370.1	362.8	355.4	358.2	361.1	369.6	378.1	385.5	392.9
65°	356.5	342.3	328.1	323.0	317.9	321.9	325.9	333.2	340.6	345.7	350.8
67.5°	311.1	299.2	287.3	283.3	279.3	283.3	287.3	294.6	302.0	307.1	312.2
70°	263.4	253.8	244.1	241.3	238.4	243.0	247.5	253.8	260.0	265.1	270.2
72.5°	219.1	211.8	204.4	203.8	203.2	207.2	211.2	217.4	223.7	227.1	230.5
75°	176.0	172.0	168.0	167.5	166.9	170.9	174.9	178.3	181.7	184.5	187.3
77.5°	137.4	134.0	130.6	131.1	131.7	134.5	137.4	140.8	144.2	145.9	147.6
80°	97.6	96.5	95.4	96.5	97.6	99.9	102.2	104.5	106.7	107.9	109.0
82.5°	67.0	65.9	64.7	66.4	68.1	69.8	71.5	73.2	74.9	75.5	76.1
85°	38.6	40.3	42.0	42.0	42.0	42.6	43.1	43.7	44.3	43.7	43.1
87.5°	18.2	18.7	19.3	19.3	19.3	19.9	20.4	20.4	20.4	19.9	19.3
90°	10.9	13.8	17.0	20.2	23.4	26.6	27.6	28.5	29.5	30.5	31.2
92.5°	39.1	40.6	42.1	43.5	45.0	46.5	47.2	48.0	48.7	49.4	49.6
95°	72.2	74.0	76.0	78.0	80.0	81.9	82.9	83.9	84.9	85.9	86.3
97.5°	112.3	113.7	115.1	116.6	118.1	119.6	120.8	122.0	123.2	124.5	125.0
100°	156.5	157.8	159.0	160.3	161.5	162.7	163.5	164.2	164.9	165.7	166.3
102.5°	203.3	204.6	206.3	208.0	209.7	211.4	212.2	212.9	213.7	214.4	214.6
105°	251.0	252.4	254.6	256.8	259.0	261.3	261.3	261.3	261.3	261.3	261.5
107.5°	307.6	308.2	309.2	310.2	311.2	312.2	312.9	313.7	314.4	315.1	315.4
110°	361.7	362.2	362.7	363.2	363.7	364.2	365.2	366.2	367.2	368.1	368.4

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	416.1	416.2	416.2	416.2	416.2	416.2	417.5	418.7	419.9	421.2	421.8
115°	473.4	473.6	473.1	472.6	472.1	471.6	471.8	472.1	472.3	472.6	472.6
117.5°	527.9	527.8	527.3	526.8	526.3	525.8	525.8	525.8	525.8	525.8	525.5
120°	584.9	585.0	583.8	582.5	581.3	580.1	579.8	579.6	579.3	579.1	578.7
122.5°	637.1	637.4	636.9	636.4	635.9	635.4	634.7	633.9	633.2	632.5	631.7
125°	691.5	691.6	691.1	690.7	690.2	689.7	688.7	687.7	686.7	685.7	684.7
127.5°	745.4	745.9	745.4	744.9	744.4	743.9	742.4	741.0	739.5	738.0	736.8
130°	798.3	798.9	798.2	797.4	796.7	795.9	795.0	794.0	793.0	792.0	790.7
132.5°	849.2	849.9	849.4	849.0	848.5	848.0	846.7	845.5	844.3	843.1	841.8
135°	899.3	899.9	899.6	899.4	899.1	898.9	897.9	896.9	895.9	895.0	894.2
137.5°	945.9	946.9	947.6	948.3	949.1	949.8	948.6	947.4	946.1	944.9	943.9
140°	995.7	996.4	996.7	996.9	997.2	997.4	997.2	996.9	996.7	996.4	995.5
142.5°	1041.1	1041.9	1042.4	1042.9	1043.4	1043.9	1043.7	1043.4	1043.2	1042.9	1042.2
145°	1085.7	1086.3	1087.1	1087.8	1088.6	1089.3	1089.1	1088.8	1088.6	1088.3	1087.7
147.5°	1128.7	1129.5	1130.3	1131.0	1131.7	1132.5	1132.5	1132.5	1132.5	1132.5	1131.7
150°	1169.9	1170.4	1170.9	1171.3	1171.8	1172.3	1172.3	1172.3	1172.3	1172.3	1171.6
152.5°	1206.3	1206.8	1207.0	1207.3	1207.5	1207.8	1208.2	1208.7	1209.2	1209.7	1209.4
155°	1241.0	1241.1	1241.3	1241.6	1241.8	1242.1	1243.1	1244.0	1245.0	1246.0	1245.6
157.5°	1272.1	1272.1	1272.3	1272.6	1272.8	1273.1	1274.0	1275.0	1276.0	1277.0	1276.8
160°	1301.0	1300.7	1300.7	1300.7	1300.7	1300.7	1302.0	1303.2	1304.4	1305.7	1305.8
162.5°	1326.6	1326.3	1326.6	1326.8	1327.1	1327.3	1328.5	1329.8	1331.0	1332.2	1332.0
165°	1348.7	1348.3	1348.3	1348.3	1348.3	1348.3	1349.8	1351.3	1352.8	1354.2	1354.1
167.5°	1366.5	1366.2	1366.4	1366.7	1366.9	1367.2	1368.6	1370.1	1371.6	1373.1	1373.1
170°	1382.0	1381.6	1381.6	1381.6	1381.6	1381.6	1383.3	1385.0	1386.7	1388.4	1388.4
172.5°	1394.2	1393.7	1393.7	1393.7	1393.7	1393.7	1395.2	1396.7	1398.2	1399.6	1399.5
175°	1402.0	1401.5	1401.5	1401.5	1401.5	1401.5	1403.0	1404.4	1405.9	1407.4	1407.3
177.5°	1406.4	1405.9	1405.9	1405.9	1405.9	1405.9	1407.4	1408.9	1410.3	1411.8	1411.7
180°	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2	1409.2

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2446.8	2446.8	2446.8	2446.8
2.5°	2174.9	2170.9	2155.0	2139.1
5°	1843.9	1830.3	1825.8	1821.2
7.5°	1611.2	1610.0	1586.2	1562.3
10°	1406.2	1407.9	1386.4	1364.8
12.5°	1259.8	1245.6	1243.9	1242.2
15°	1149.6	1136.6	1134.3	1132.0
17.5°	1071.8	1063.9	1061.6	1059.4
20°	1012.8	1008.3	1004.3	1000.3
22.5°	961.7	956.0	952.6	949.2
25°	912.3	907.2	906.1	904.9
27.5°	868.0	861.8	861.8	861.8
30°	826.0	822.0	820.3	818.6
32.5°	786.9	783.4	783.4	783.4
35°	749.9	748.2	746.0	743.7
37.5°	716.5	716.5	715.3	714.2
40°	684.1	685.8	685.8	685.8
42.5°	654.6	656.3	656.3	656.3
45°	623.9	626.8	627.9	629.0
47.5°	593.8	598.4	599.5	600.6
50°	564.3	567.7	568.3	568.8
52.5°	534.2	538.2	541.0	543.9
55°	502.4	506.4	508.1	509.8
57.5°	468.4	472.3	472.9	473.5
60°	430.9	434.9	436.0	437.1
62.5°	395.1	397.4	398.5	399.7
65°	354.3	357.7	359.9	362.2
67.5°	315.1	317.9	317.9	317.9
70°	271.4	272.5	274.2	275.9
72.5°	231.1	231.6	231.6	231.6
75°	188.5	189.6	190.2	190.8
77.5°	148.2	148.7	148.7	148.7
80°	108.4	107.9	107.9	107.9
82.5°	74.4	72.7	72.7	72.7
85°	42.6	42.0	42.6	43.1
87.5°	19.3	19.3	19.3	19.3
90°	31.7	32.2	32.7	33.2
92.5°	49.1	48.6	48.1	47.6
95°	86.3	86.3	86.3	86.3
97.5°	124.7	124.5	124.2	124.0
100°	166.8	167.3	167.8	168.3
102.5°	214.4	214.1	213.9	213.7
105°	262.0	262.5	263.0	263.5
107.5°	315.1	314.9	314.6	314.4
110°	367.9	367.4	366.9	366.4

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	421.8	421.8	421.8	421.8
115°	472.3	472.1	471.8	471.6
117.5°	524.7	524.0	523.2	522.5
120°	578.2	577.7	577.2	576.8
122.5°	631.0	630.3	629.5	628.8
125°	683.8	682.8	681.8	680.8
127.5°	735.8	734.8	733.8	732.8
130°	788.9	787.2	785.5	783.8
132.5°	840.6	839.4	838.1	836.9
135°	893.7	893.2	892.7	892.3
137.5°	943.2	942.4	941.7	941.0
140°	993.7	992.0	990.3	988.6
142.5°	1041.0	1039.7	1038.5	1037.3
145°	1086.7	1085.7	1084.7	1083.8
147.5°	1130.3	1128.8	1127.3	1125.8
150°	1170.1	1168.6	1167.2	1165.7
152.5°	1208.1	1206.9	1205.7	1204.4
155°	1243.9	1242.2	1240.5	1238.7
157.5°	1275.3	1273.8	1272.3	1270.9
160°	1304.8	1303.8	1302.8	1301.8
162.5°	1330.3	1328.5	1326.8	1325.1
165°	1352.4	1350.7	1349.0	1347.2
167.5°	1371.6	1370.1	1368.6	1367.2
170°	1386.7	1385.0	1383.3	1381.6
172.5°	1397.8	1396.1	1394.3	1392.6
175°	1405.5	1403.8	1402.1	1400.4
177.5°	1410.0	1408.2	1406.5	1404.8
180°	1409.2	1409.2	1409.2	1409.2

TEST NUMBER: P831595

CATALOG NUMBER: S123DIP-S775D1025U850-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.95	15.78	15.91	16.75	18.02	17.19	18.01	18.15	18.99	20.26
	3H	16.60	17.34	17.57	18.32	19.61	18.61	19.35	19.58	20.33	21.63
	4H	17.17	17.87	18.16	18.86	20.16	19.06	19.76	20.05	20.74	22.05
	6H	17.54	18.18	18.54	19.18	20.49	19.33	19.98	20.33	20.97	22.28
	8H	17.64	18.25	18.64	19.26	20.57	19.39	20.01	20.40	21.01	22.33
	12H	17.68	18.26	18.69	19.26	20.60	19.41	19.99	20.42	21.00	22.33
4H	2H	15.52	16.22	16.52	17.21	18.51	17.35	18.05	18.34	19.03	20.34
	3H	17.35	17.93	18.35	18.95	20.26	18.96	19.55	19.97	20.56	21.88
	4H	18.04	18.58	19.05	19.58	20.92	19.55	20.08	20.56	21.09	22.43
	6H	18.52	18.98	19.54	20.01	21.34	19.95	20.41	20.97	21.44	22.77
	8H	18.65	19.08	19.68	20.10	21.46	20.06	20.49	21.08	21.51	22.86
	12H	18.72	19.10	19.76	20.14	21.50	20.10	20.49	21.14	21.53	22.88
8H	4H	18.31	18.74	19.33	19.76	21.11	19.65	20.08	20.67	21.10	22.45
	6H	18.90	19.25	19.94	20.31	21.66	20.15	20.50	21.20	21.57	22.92
	8H	19.10	19.41	20.16	20.46	21.83	20.33	20.64	21.38	21.69	23.06
	12H	19.23	19.50	20.28	20.54	21.95	20.43	20.70	21.49	21.75	23.16
12H	4H	18.31	18.69	19.35	19.73	21.09	19.62	20.01	20.66	21.05	22.40
	6H	18.95	19.26	20.00	20.31	21.68	20.16	20.47	21.22	21.53	22.89
	8H	19.18	19.45	20.24	20.50	21.91	20.36	20.63	21.42	21.68	23.09

END OF REPORT