

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331700

Luminaire Tested: **SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P331700
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6393.3 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19
8	54	43	35	30	50	40	33	28	33	28	25	28	24	21	22	20	18
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.3	2.2
10°-20°	388.0	6.1
20°-30°	500.0	7.8
30°-40°	475.2	7.4
40°-50°	407.1	6.4
50°-60°	310.0	4.8
60°-70°	196.0	3.1
70°-80°	97.9	1.5
80°-90°	31.0	0.5
90°-100°	87.2	1.4
100°-110°	270.9	4.2
110°-120°	463.1	7.2
120°-130°	608.9	9.5
130°-140°	683.5	10.7
140°-150°	670.1	10.5
150°-160°	562.1	8.8
160°-170°	372.8	5.8
170°-180°	130.3	2.0
0°-30°	1027.3	16.1
0°-40°	1502.5	23.5
0°-60°	2219.6	34.7
0°-90°	2544.4	39.8
90°-120°	821.2	12.8
90°-150°	2783.7	43.5
90°-180°	3849.0	60.2
0°-180°	6393.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	21
90°	40	1	40	1	40	18
95°	72	60	72	60	72	80
105°	258	250	258	250	258	271
115°	465	465	465	465	465	459
125°	678	676	678	676	678	605
135°	885	875	885	875	885	681
145°	1073	1062	1073	1062	1073	670
155°	1223	1214	1223	1214	1223	563
165°	1322	1321	1322	1321	1322	373
175°	1370	1374	1370	1374	1370	130
180°	1376	1376	1376	1376	1376	

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	14.4	14.8	14.7	14.7	14.6	14.7	14.8	15.3	15.0	15.5	13.9
90°	39.5	39.2	39.0	38.7	38.5	38.6	39.1	39.6	40.1	40.7	35.0
92.5°	37.6	37.6	37.5	37.5	37.4	37.4	37.2	37.1	37.0	36.9	35.6
95°	72.0	72.5	73.1	73.6	74.1	74.3	74.3	74.3	74.3	74.3	73.8
97.5°	124.8	124.8	124.9	124.9	125.0	125.0	125.0	125.0	125.0	125.0	124.0
100°	159.1	159.4	159.7	159.9	160.2	160.3	160.3	160.3	160.3	160.3	159.5
102.5°	198.2	198.4	198.7	198.9	199.2	199.2	199.0	198.8	198.6	198.4	197.4
105°	257.9	257.9	257.9	257.9	257.9	257.6	257.1	256.6	256.1	255.5	255.0
107.5°	314.1	315.3	316.5	317.7	318.8	319.3	319.1	318.9	318.7	318.5	318.5
110°	357.8	358.5	359.3	360.1	360.9	361.3	361.3	361.3	361.3	361.3	361.3

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	399.6	400.2	400.7	401.3	401.9	402.5	403.1	403.7	404.3	404.9	405.1
115°	464.6	465.4	466.2	467.0	467.7	468.2	468.5	468.8	469.0	469.3	469.8
117.5°	526.7	527.4	528.2	529.0	529.8	530.5	531.1	531.7	532.3	532.9	534.4
120°	570.3	571.1	571.9	572.7	573.4	573.8	573.8	573.8	573.8	573.8	575.9
122.5°	613.1	613.7	614.2	614.8	615.4	615.9	616.6	617.2	617.8	618.4	619.9
125°	678.4	678.6	678.9	679.1	679.4	679.9	680.7	681.5	682.2	683.0	683.8
127.5°	737.8	738.7	739.5	740.3	741.1	742.0	742.9	743.9	744.8	745.7	746.7
130°	780.6	781.6	782.6	783.7	784.7	785.5	786.0	786.5	787.0	787.6	788.1
132.5°	821.5	822.3	823.1	824.0	824.8	825.8	826.9	828.0	829.2	830.3	830.2
135°	885.1	885.9	886.7	887.4	888.2	888.7	889.0	889.3	889.5	889.8	889.3
137.5°	942.7	943.8	944.8	945.8	946.9	947.5	947.7	947.9	948.1	948.3	947.6
140°	982.7	983.7	984.8	985.8	986.8	987.3	987.3	987.3	987.3	987.3	986.1
142.5°	1018.9	1020.0	1021.0	1022.0	1023.1	1023.5	1023.3	1023.1	1022.9	1022.7	1021.8
145°	1073.3	1074.3	1075.4	1076.4	1077.4	1077.8	1077.6	1077.3	1077.0	1076.8	1075.2
147.5°	1121.9	1122.8	1123.8	1124.8	1125.8	1126.0	1125.4	1124.9	1124.3	1123.7	1122.7
150°	1153.5	1154.2	1155.0	1155.8	1156.6	1156.6	1155.8	1155.0	1154.2	1153.5	1152.4
152.5°	1183.2	1184.2	1185.2	1186.1	1187.1	1187.1	1186.1	1185.2	1184.2	1183.2	1182.0
155°	1223.1	1223.9	1224.7	1225.5	1226.2	1226.0	1224.7	1223.4	1222.1	1220.8	1220.1
157.5°	1257.5	1258.8	1260.0	1261.2	1262.5	1262.2	1260.5	1258.7	1257.0	1255.2	1254.7
160°	1278.9	1279.9	1281.0	1282.0	1283.0	1282.8	1281.2	1279.7	1278.1	1276.6	1276.3
162.5°	1297.5	1298.7	1300.0	1301.2	1302.4	1302.2	1300.4	1298.7	1296.9	1295.2	1294.9
165°	1321.9	1323.2	1324.5	1325.8	1327.0	1326.8	1325.0	1323.2	1321.4	1319.6	1319.6
167.5°	1341.9	1343.2	1344.5	1345.9	1347.2	1347.0	1345.2	1343.4	1341.6	1339.8	1339.8
170°	1352.1	1353.6	1355.2	1356.7	1358.3	1358.1	1356.3	1354.5	1352.7	1350.9	1351.2
172.5°	1360.4	1362.0	1363.5	1365.1	1366.6	1366.5	1364.7	1362.9	1361.1	1359.3	1359.5
175°	1369.5	1371.1	1372.6	1374.2	1375.7	1375.6	1373.8	1372.0	1370.2	1368.3	1368.9
177.5°	1373.7	1374.9	1376.2	1377.4	1378.6	1378.6	1377.4	1376.2	1374.9	1373.7	1374.1
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	12.8	12.1	10.9	9.7	9.4	9.2	10.7	12.1	11.1	10.5	10.3
90°	29.3	23.6	17.9	13.6	10.5	7.4	4.3	1.2	4.3	7.4	10.5
92.5°	34.3	32.9	31.6	29.8	27.5	25.2	22.9	20.7	22.9	25.2	27.5
95°	73.3	72.8	72.3	70.7	68.1	65.6	63.0	60.4	63.0	65.6	68.1
97.5°	123.0	122.0	121.1	119.4	117.2	114.9	112.6	110.4	112.6	114.9	117.2
100°	158.7	158.0	157.2	155.8	153.7	151.7	149.6	147.5	149.6	151.7	153.7
102.5°	196.4	195.5	194.5	193.2	191.5	189.9	188.2	186.6	188.2	189.9	191.5
105°	254.5	254.0	253.5	252.8	252.1	251.3	250.5	249.7	250.5	251.3	252.1
107.5°	318.5	318.5	318.5	317.9	316.8	315.7	314.5	313.4	314.5	315.7	316.8
110°	361.3	361.3	361.3	360.5	358.9	357.4	355.8	354.3	355.8	357.4	358.9

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	405.3	405.5	405.8	405.1	403.5	402.0	400.4	398.9	400.4	402.0	403.5
115°	470.3	470.8	471.3	470.8	469.3	467.7	466.2	464.6	466.2	467.7	469.3
117.5°	535.8	537.3	538.7	538.4	536.3	534.3	532.2	530.1	532.2	534.3	536.3
120°	578.0	580.0	582.1	582.1	580.0	578.0	575.9	573.8	575.9	578.0	580.0
122.5°	621.3	622.8	624.2	623.7	621.2	618.7	616.3	613.8	616.3	618.7	621.2
125°	684.6	685.3	686.1	685.3	683.0	680.7	678.4	676.0	678.4	680.7	683.0
127.5°	747.6	748.5	749.5	748.4	745.5	742.6	739.6	736.7	739.6	742.6	745.5
130°	788.6	789.1	789.6	788.2	784.8	781.5	778.1	774.8	778.1	781.5	784.8
132.5°	830.1	830.0	829.9	828.5	825.7	823.0	820.3	817.5	820.3	823.0	825.7
135°	888.7	888.2	887.7	886.0	883.2	880.4	877.5	874.7	877.5	880.4	883.2
137.5°	947.0	946.3	945.6	944.1	941.8	939.5	937.2	934.8	937.2	939.5	941.8
140°	984.8	983.5	982.2	980.4	978.1	975.7	973.4	971.1	973.4	975.7	978.1
142.5°	1020.9	1020.0	1019.1	1017.5	1015.2	1012.9	1010.6	1008.3	1010.6	1012.9	1015.2
145°	1073.7	1072.1	1070.6	1068.9	1067.1	1065.3	1063.5	1061.7	1063.5	1065.3	1067.1
147.5°	1121.7	1120.6	1119.6	1118.0	1115.8	1113.6	1111.5	1109.3	1111.5	1113.6	1115.8
150°	1151.4	1150.4	1149.3	1148.0	1146.5	1144.9	1143.4	1141.8	1143.4	1144.9	1146.5
152.5°	1180.7	1179.5	1178.2	1176.8	1175.3	1173.7	1172.2	1170.6	1172.2	1173.7	1175.3
155°	1219.3	1218.5	1217.7	1217.0	1216.2	1215.4	1214.6	1213.9	1214.6	1215.4	1216.2
157.5°	1254.3	1253.8	1253.3	1252.9	1252.3	1251.8	1251.3	1250.8	1251.3	1251.8	1252.3
160°	1276.1	1275.8	1275.5	1275.2	1274.6	1274.1	1273.6	1273.1	1273.6	1274.1	1274.6
162.5°	1294.6	1294.4	1294.1	1294.0	1293.8	1293.7	1293.6	1293.5	1293.6	1293.7	1293.8
165°	1319.6	1319.6	1319.6	1319.7	1319.9	1320.2	1320.5	1320.7	1320.5	1320.2	1319.9
167.5°	1339.9	1339.9	1340.0	1340.4	1341.2	1341.9	1342.7	1343.5	1342.7	1341.9	1341.2
170°	1351.4	1351.7	1352.0	1352.5	1353.2	1354.0	1354.8	1355.6	1354.8	1354.0	1353.2
172.5°	1359.8	1360.1	1360.3	1360.8	1361.6	1362.4	1363.2	1363.9	1363.2	1362.4	1361.6
175°	1369.4	1369.9	1370.4	1371.1	1371.8	1372.6	1373.4	1374.2	1373.4	1372.6	1371.8
177.5°	1374.5	1374.9	1375.3	1375.9	1376.5	1377.1	1377.7	1378.3	1377.7	1377.1	1376.5
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5



TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	10.5	10.9	11.3	12.4	13.5	14.3	14.2	13.6	13.5	13.4	13.0
90°	13.6	17.9	23.6	29.3	35.0	40.7	40.1	39.6	39.1	38.6	38.5
92.5°	29.8	31.6	32.9	34.3	35.6	36.9	37.0	37.1	37.2	37.4	37.4
95°	70.7	72.3	72.8	73.3	73.8	74.3	74.3	74.3	74.3	74.3	74.1
97.5°	119.4	121.1	122.0	123.0	124.0	125.0	125.0	125.0	125.0	125.0	125.0
100°	155.8	157.2	158.0	158.7	159.5	160.3	160.3	160.3	160.3	160.3	160.2
102.5°	193.2	194.5	195.5	196.4	197.4	198.4	198.6	198.8	199.0	199.2	199.2
105°	252.8	253.5	254.0	254.5	255.0	255.5	256.1	256.6	257.1	257.6	257.9
107.5°	317.9	318.5	318.5	318.5	318.5	318.5	318.7	318.9	319.1	319.3	318.8
110°	360.5	361.3	361.3	361.3	361.3	361.3	361.3	361.3	361.3	361.3	360.9

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	405.1	405.8	405.5	405.3	405.1	404.9	404.3	403.7	403.1	402.5	401.9
115°	470.8	471.3	470.8	470.3	469.8	469.3	469.0	468.8	468.5	468.2	467.7
117.5°	538.4	538.7	537.3	535.8	534.4	532.9	532.3	531.7	531.1	530.5	529.8
120°	582.1	582.1	580.0	578.0	575.9	573.8	573.8	573.8	573.8	573.8	573.4
122.5°	623.7	624.2	622.8	621.3	619.9	618.4	617.8	617.2	616.6	615.9	615.4
125°	685.3	686.1	685.3	684.6	683.8	683.0	682.2	681.5	680.7	679.9	679.4
127.5°	748.4	749.5	748.5	747.6	746.7	745.7	744.8	743.9	742.9	742.0	741.1
130°	788.2	789.6	789.1	788.6	788.1	787.6	787.0	786.5	786.0	785.5	784.7
132.5°	828.5	829.9	830.0	830.1	830.2	830.3	829.2	828.0	826.9	825.8	824.8
135°	886.0	887.7	888.2	888.7	889.3	889.8	889.5	889.3	889.0	888.7	888.2
137.5°	944.1	945.6	946.3	947.0	947.6	948.3	948.1	947.9	947.7	947.5	946.9
140°	980.4	982.2	983.5	984.8	986.1	987.3	987.3	987.3	987.3	987.3	986.8
142.5°	1017.5	1019.1	1020.0	1020.9	1021.8	1022.7	1022.9	1023.1	1023.3	1023.5	1023.1
145°	1068.9	1070.6	1072.1	1073.7	1075.2	1076.8	1077.0	1077.3	1077.6	1077.8	1077.4
147.5°	1118.0	1119.6	1120.6	1121.7	1122.7	1123.7	1124.3	1124.9	1125.4	1126.0	1125.8
150°	1148.0	1149.3	1150.4	1151.4	1152.4	1153.5	1154.2	1155.0	1155.8	1156.6	1156.6
152.5°	1176.8	1178.2	1179.5	1180.7	1182.0	1183.2	1184.2	1185.2	1186.1	1187.1	1187.1
155°	1217.0	1217.7	1218.5	1219.3	1220.1	1220.8	1222.1	1223.4	1224.7	1226.0	1226.2
157.5°	1252.9	1253.3	1253.8	1254.3	1254.7	1255.2	1257.0	1258.7	1260.5	1262.2	1262.5
160°	1275.2	1275.5	1275.8	1276.1	1276.3	1276.6	1278.1	1279.7	1281.2	1282.8	1283.0
162.5°	1294.0	1294.1	1294.4	1294.6	1294.9	1295.2	1296.9	1298.7	1300.4	1302.2	1302.4
165°	1319.7	1319.6	1319.6	1319.6	1319.6	1319.6	1321.4	1323.2	1325.0	1326.8	1327.0
167.5°	1340.4	1340.0	1339.9	1339.9	1339.8	1339.8	1341.6	1343.4	1345.2	1347.0	1347.2
170°	1352.5	1352.0	1351.7	1351.4	1351.2	1350.9	1352.7	1354.5	1356.3	1358.1	1358.3
172.5°	1360.8	1360.3	1360.1	1359.8	1359.5	1359.3	1361.1	1362.9	1364.7	1366.5	1366.6
175°	1371.1	1370.4	1369.9	1369.4	1368.9	1368.3	1370.2	1372.0	1373.8	1375.6	1375.7
177.5°	1375.9	1375.3	1374.9	1374.5	1374.1	1373.7	1374.9	1376.2	1377.4	1378.6	1378.6
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	13.1	12.7	13.2	12.8	13.2	12.7	13.1	13.0	13.4	13.5	13.6
90°	38.7	39.0	39.2	39.5	39.2	39.0	38.7	38.5	38.6	39.1	39.6
92.5°	37.5	37.5	37.6	37.6	37.6	37.5	37.5	37.4	37.4	37.2	37.1
95°	73.6	73.1	72.5	72.0	72.5	73.1	73.6	74.1	74.3	74.3	74.3
97.5°	124.9	124.9	124.8	124.8	124.8	124.9	124.9	125.0	125.0	125.0	125.0
100°	159.9	159.7	159.4	159.1	159.4	159.7	159.9	160.2	160.3	160.3	160.3
102.5°	198.9	198.7	198.4	198.2	198.4	198.7	198.9	199.2	199.2	199.0	198.8
105°	257.9	257.9	257.9	257.9	257.9	257.9	257.9	257.9	257.6	257.1	256.6
107.5°	317.7	316.5	315.3	314.1	315.3	316.5	317.7	318.8	319.3	319.1	318.9
110°	360.1	359.3	358.5	357.8	358.5	359.3	360.1	360.9	361.3	361.3	361.3

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	401.3	400.7	400.2	399.6	400.2	400.7	401.3	401.9	402.5	403.1	403.7
115°	467.0	466.2	465.4	464.6	465.4	466.2	467.0	467.7	468.2	468.5	468.8
117.5°	529.0	528.2	527.4	526.7	527.4	528.2	529.0	529.8	530.5	531.1	531.7
120°	572.7	571.9	571.1	570.3	571.1	571.9	572.7	573.4	573.8	573.8	573.8
122.5°	614.8	614.2	613.7	613.1	613.7	614.2	614.8	615.4	615.9	616.6	617.2
125°	679.1	678.9	678.6	678.4	678.6	678.9	679.1	679.4	679.9	680.7	681.5
127.5°	740.3	739.5	738.7	737.8	738.7	739.5	740.3	741.1	742.0	742.9	743.9
130°	783.7	782.6	781.6	780.6	781.6	782.6	783.7	784.7	785.5	786.0	786.5
132.5°	824.0	823.1	822.3	821.5	822.3	823.1	824.0	824.8	825.8	826.9	828.0
135°	887.4	886.7	885.9	885.1	885.9	886.7	887.4	888.2	888.7	889.0	889.3
137.5°	945.8	944.8	943.8	942.7	943.8	944.8	945.8	946.9	947.5	947.7	947.9
140°	985.8	984.8	983.7	982.7	983.7	984.8	985.8	986.8	987.3	987.3	987.3
142.5°	1022.0	1021.0	1020.0	1018.9	1020.0	1021.0	1022.0	1023.1	1023.5	1023.3	1023.1
145°	1076.4	1075.4	1074.3	1073.3	1074.3	1075.4	1076.4	1077.4	1077.8	1077.6	1077.3
147.5°	1124.8	1123.8	1122.8	1121.9	1122.8	1123.8	1124.8	1125.8	1126.0	1125.4	1124.9
150°	1155.8	1155.0	1154.2	1153.5	1154.2	1155.0	1155.8	1156.6	1156.6	1155.8	1155.0
152.5°	1186.1	1185.2	1184.2	1183.2	1184.2	1185.2	1186.1	1187.1	1187.1	1186.1	1185.2
155°	1225.5	1224.7	1223.9	1223.1	1223.9	1224.7	1225.5	1226.2	1226.0	1224.7	1223.4
157.5°	1261.2	1260.0	1258.8	1257.5	1258.8	1260.0	1261.2	1262.5	1262.2	1260.5	1258.7
160°	1282.0	1281.0	1279.9	1278.9	1279.9	1281.0	1282.0	1283.0	1282.8	1281.2	1279.7
162.5°	1301.2	1300.0	1298.7	1297.5	1298.7	1300.0	1301.2	1302.4	1302.2	1300.4	1298.7
165°	1325.8	1324.5	1323.2	1321.9	1323.2	1324.5	1325.8	1327.0	1326.8	1325.0	1323.2
167.5°	1345.9	1344.5	1343.2	1341.9	1343.2	1344.5	1345.9	1347.2	1347.0	1345.2	1343.4
170°	1356.7	1355.2	1353.6	1352.1	1353.6	1355.2	1356.7	1358.3	1358.1	1356.3	1354.5
172.5°	1365.1	1363.5	1362.0	1360.4	1362.0	1363.5	1365.1	1366.6	1366.5	1364.7	1362.9
175°	1374.2	1372.6	1371.1	1369.5	1371.1	1372.6	1374.2	1375.7	1375.6	1373.8	1372.0
177.5°	1377.4	1376.2	1374.9	1373.7	1374.9	1376.2	1377.4	1378.6	1378.6	1377.4	1376.2
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	14.2	14.3	13.5	12.4	11.3	10.9	10.5	10.3	10.5	11.1	12.1
90°	40.1	40.7	35.0	29.3	23.6	17.9	13.6	10.5	7.4	4.3	1.2
92.5°	37.0	36.9	35.6	34.3	32.9	31.6	29.8	27.5	25.2	22.9	20.7
95°	74.3	74.3	73.8	73.3	72.8	72.3	70.7	68.1	65.6	63.0	60.4
97.5°	125.0	125.0	124.0	123.0	122.0	121.1	119.4	117.2	114.9	112.6	110.4
100°	160.3	160.3	159.5	158.7	158.0	157.2	155.8	153.7	151.7	149.6	147.5
102.5°	198.6	198.4	197.4	196.4	195.5	194.5	193.2	191.5	189.9	188.2	186.6
105°	256.1	255.5	255.0	254.5	254.0	253.5	252.8	252.1	251.3	250.5	249.7
107.5°	318.7	318.5	318.5	318.5	318.5	318.5	317.9	316.8	315.7	314.5	313.4
110°	361.3	361.3	361.3	361.3	361.3	361.3	360.5	358.9	357.4	355.8	354.3

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	404.3	404.9	405.1	405.3	405.5	405.8	405.1	403.5	402.0	400.4	398.9
115°	469.0	469.3	469.8	470.3	470.8	471.3	470.8	469.3	467.7	466.2	464.6
117.5°	532.3	532.9	534.4	535.8	537.3	538.7	538.4	536.3	534.3	532.2	530.1
120°	573.8	573.8	575.9	578.0	580.0	582.1	582.1	580.0	578.0	575.9	573.8
122.5°	617.8	618.4	619.9	621.3	622.8	624.2	623.7	621.2	618.7	616.3	613.8
125°	682.2	683.0	683.8	684.6	685.3	686.1	685.3	683.0	680.7	678.4	676.0
127.5°	744.8	745.7	746.7	747.6	748.5	749.5	748.4	745.5	742.6	739.6	736.7
130°	787.0	787.6	788.1	788.6	789.1	789.6	788.2	784.8	781.5	778.1	774.8
132.5°	829.2	830.3	830.2	830.1	830.0	829.9	828.5	825.7	823.0	820.3	817.5
135°	889.5	889.8	889.3	888.7	888.2	887.7	886.0	883.2	880.4	877.5	874.7
137.5°	948.1	948.3	947.6	947.0	946.3	945.6	944.1	941.8	939.5	937.2	934.8
140°	987.3	987.3	986.1	984.8	983.5	982.2	980.4	978.1	975.7	973.4	971.1
142.5°	1022.9	1022.7	1021.8	1020.9	1020.0	1019.1	1017.5	1015.2	1012.9	1010.6	1008.3
145°	1077.0	1076.8	1075.2	1073.7	1072.1	1070.6	1068.9	1067.1	1065.3	1063.5	1061.7
147.5°	1124.3	1123.7	1122.7	1121.7	1120.6	1119.6	1118.0	1115.8	1113.6	1111.5	1109.3
150°	1154.2	1153.5	1152.4	1151.4	1150.4	1149.3	1148.0	1146.5	1144.9	1143.4	1141.8
152.5°	1184.2	1183.2	1182.0	1180.7	1179.5	1178.2	1176.8	1175.3	1173.7	1172.2	1170.6
155°	1222.1	1220.8	1220.1	1219.3	1218.5	1217.7	1217.0	1216.2	1215.4	1214.6	1213.9
157.5°	1257.0	1255.2	1254.7	1254.3	1253.8	1253.3	1252.9	1252.3	1251.8	1251.3	1250.8
160°	1278.1	1276.6	1276.3	1276.1	1275.8	1275.5	1275.2	1274.6	1274.1	1273.6	1273.1
162.5°	1296.9	1295.2	1294.9	1294.6	1294.4	1294.1	1294.0	1293.8	1293.7	1293.6	1293.5
165°	1321.4	1319.6	1319.6	1319.6	1319.6	1319.6	1319.7	1319.9	1320.2	1320.5	1320.7
167.5°	1341.6	1339.8	1339.8	1339.9	1339.9	1340.0	1340.4	1341.2	1341.9	1342.7	1343.5
170°	1352.7	1350.9	1351.2	1351.4	1351.7	1352.0	1352.5	1353.2	1354.0	1354.8	1355.6
172.5°	1361.1	1359.3	1359.5	1359.8	1360.1	1360.3	1360.8	1361.6	1362.4	1363.2	1363.9
175°	1370.2	1368.3	1368.9	1369.4	1369.9	1370.4	1371.1	1371.8	1372.6	1373.4	1374.2
177.5°	1374.9	1373.7	1374.1	1374.5	1374.9	1375.3	1375.9	1376.5	1377.1	1377.7	1378.3
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.7	9.2	9.4	9.7	10.9	12.1	12.8	13.9	15.5	15.0	15.3
90°	4.3	7.4	10.5	13.6	17.9	23.6	29.3	35.0	40.7	40.1	39.6
92.5°	22.9	25.2	27.5	29.8	31.6	32.9	34.3	35.6	36.9	37.0	37.1
95°	63.0	65.6	68.1	70.7	72.3	72.8	73.3	73.8	74.3	74.3	74.3
97.5°	112.6	114.9	117.2	119.4	121.1	122.0	123.0	124.0	125.0	125.0	125.0
100°	149.6	151.7	153.7	155.8	157.2	158.0	158.7	159.5	160.3	160.3	160.3
102.5°	188.2	189.9	191.5	193.2	194.5	195.5	196.4	197.4	198.4	198.6	198.8
105°	250.5	251.3	252.1	252.8	253.5	254.0	254.5	255.0	255.5	256.1	256.6
107.5°	314.5	315.7	316.8	317.9	318.5	318.5	318.5	318.5	318.5	318.7	318.9
110°	355.8	357.4	358.9	360.5	361.3	361.3	361.3	361.3	361.3	361.3	361.3

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	400.4	402.0	403.5	405.1	405.8	405.5	405.3	405.1	404.9	404.3	403.7
115°	466.2	467.7	469.3	470.8	471.3	470.8	470.3	469.8	469.3	469.0	468.8
117.5°	532.2	534.3	536.3	538.4	538.7	537.3	535.8	534.4	532.9	532.3	531.7
120°	575.9	578.0	580.0	582.1	582.1	580.0	578.0	575.9	573.8	573.8	573.8
122.5°	616.3	618.7	621.2	623.7	624.2	622.8	621.3	619.9	618.4	617.8	617.2
125°	678.4	680.7	683.0	685.3	686.1	685.3	684.6	683.8	683.0	682.2	681.5
127.5°	739.6	742.6	745.5	748.4	749.5	748.5	747.6	746.7	745.7	744.8	743.9
130°	778.1	781.5	784.8	788.2	789.6	789.1	788.6	788.1	787.6	787.0	786.5
132.5°	820.3	823.0	825.7	828.5	829.9	830.0	830.1	830.2	830.3	829.2	828.0
135°	877.5	880.4	883.2	886.0	887.7	888.2	888.7	889.3	889.8	889.5	889.3
137.5°	937.2	939.5	941.8	944.1	945.6	946.3	947.0	947.6	948.3	948.1	947.9
140°	973.4	975.7	978.1	980.4	982.2	983.5	984.8	986.1	987.3	987.3	987.3
142.5°	1010.6	1012.9	1015.2	1017.5	1019.1	1020.0	1020.9	1021.8	1022.7	1022.9	1023.1
145°	1063.5	1065.3	1067.1	1068.9	1070.6	1072.1	1073.7	1075.2	1076.8	1077.0	1077.3
147.5°	1111.5	1113.6	1115.8	1118.0	1119.6	1120.6	1121.7	1122.7	1123.7	1124.3	1124.9
150°	1143.4	1144.9	1146.5	1148.0	1149.3	1150.4	1151.4	1152.4	1153.5	1154.2	1155.0
152.5°	1172.2	1173.7	1175.3	1176.8	1178.2	1179.5	1180.7	1182.0	1183.2	1184.2	1185.2
155°	1214.6	1215.4	1216.2	1217.0	1217.7	1218.5	1219.3	1220.1	1220.8	1222.1	1223.4
157.5°	1251.3	1251.8	1252.3	1252.9	1253.3	1253.8	1254.3	1254.7	1255.2	1257.0	1258.7
160°	1273.6	1274.1	1274.6	1275.2	1275.5	1275.8	1276.1	1276.3	1276.6	1278.1	1279.7
162.5°	1293.6	1293.7	1293.8	1294.0	1294.1	1294.4	1294.6	1294.9	1295.2	1296.9	1298.7
165°	1320.5	1320.2	1319.9	1319.7	1319.6	1319.6	1319.6	1319.6	1319.6	1321.4	1323.2
167.5°	1342.7	1341.9	1341.2	1340.4	1340.0	1339.9	1339.9	1339.8	1339.8	1341.6	1343.4
170°	1354.8	1354.0	1353.2	1352.5	1352.0	1351.7	1351.4	1351.2	1350.9	1352.7	1354.5
172.5°	1363.2	1362.4	1361.6	1360.8	1360.3	1360.1	1359.8	1359.5	1359.3	1361.1	1362.9
175°	1373.4	1372.6	1371.8	1371.1	1370.4	1369.9	1369.4	1368.9	1368.3	1370.2	1372.0
177.5°	1377.7	1377.1	1376.5	1375.9	1375.3	1374.9	1374.5	1374.1	1373.7	1374.9	1376.2
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5

TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	14.8	14.7	14.6	14.7	14.7	14.8	14.4
90°	39.1	38.6	38.5	38.7	39.0	39.2	39.5
92.5°	37.2	37.4	37.4	37.5	37.5	37.6	37.6
95°	74.3	74.3	74.1	73.6	73.1	72.5	72.0
97.5°	125.0	125.0	125.0	124.9	124.9	124.8	124.8
100°	160.3	160.3	160.2	159.9	159.7	159.4	159.1
102.5°	199.0	199.2	199.2	198.9	198.7	198.4	198.2
105°	257.1	257.6	257.9	257.9	257.9	257.9	257.9
107.5°	319.1	319.3	318.8	317.7	316.5	315.3	314.1
110°	361.3	361.3	360.9	360.1	359.3	358.5	357.8



TEST NUMBER: P331700

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	403.1	402.5	401.9	401.3	400.7	400.2	399.6
115°	468.5	468.2	467.7	467.0	466.2	465.4	464.6
117.5°	531.1	530.5	529.8	529.0	528.2	527.4	526.7
120°	573.8	573.8	573.4	572.7	571.9	571.1	570.3
122.5°	616.6	615.9	615.4	614.8	614.2	613.7	613.1
125°	680.7	679.9	679.4	679.1	678.9	678.6	678.4
127.5°	742.9	742.0	741.1	740.3	739.5	738.7	737.8
130°	786.0	785.5	784.7	783.7	782.6	781.6	780.6
132.5°	826.9	825.8	824.8	824.0	823.1	822.3	821.5
135°	889.0	888.7	888.2	887.4	886.7	885.9	885.1
137.5°	947.7	947.5	946.9	945.8	944.8	943.8	942.7
140°	987.3	987.3	986.8	985.8	984.8	983.7	982.7
142.5°	1023.3	1023.5	1023.1	1022.0	1021.0	1020.0	1018.9
145°	1077.6	1077.8	1077.4	1076.4	1075.4	1074.3	1073.3
147.5°	1125.4	1126.0	1125.8	1124.8	1123.8	1122.8	1121.9
150°	1155.8	1156.6	1156.6	1155.8	1155.0	1154.2	1153.5
152.5°	1186.1	1187.1	1187.1	1186.1	1185.2	1184.2	1183.2
155°	1224.7	1226.0	1226.2	1225.5	1224.7	1223.9	1223.1
157.5°	1260.5	1262.2	1262.5	1261.2	1260.0	1258.8	1257.5
160°	1281.2	1282.8	1283.0	1282.0	1281.0	1279.9	1278.9
162.5°	1300.4	1302.2	1302.4	1301.2	1300.0	1298.7	1297.5
165°	1325.0	1326.8	1327.0	1325.8	1324.5	1323.2	1321.9
167.5°	1345.2	1347.0	1347.2	1345.9	1344.5	1343.2	1341.9
170°	1356.3	1358.1	1358.3	1356.7	1355.2	1353.6	1352.1
172.5°	1364.7	1366.5	1366.6	1365.1	1363.5	1362.0	1360.4
175°	1373.8	1375.6	1375.7	1374.2	1372.6	1371.1	1369.5
177.5°	1377.4	1378.6	1378.6	1377.4	1376.2	1374.9	1373.7
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5

(END OF REPORT)