

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331621-935

Luminaire Tested: **SA2XXRDIP-C290D530U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P331621-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2794.1 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot



TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35		
1	95	91	87	84	86	82	79	77	66	64	62	52	50	49	38	37	37	30		
2	87	80	74	70	78	73	68	64	59	55	53	46	44	42	34	33	32	26		
3	80	71	64	59	72	64	59	54	52	48	45	41	38	36	31	29	28	23		
4	73	63	56	50	66	57	51	46	47	42	39	37	34	31	28	26	24	20		
5	67	56	49	43	61	51	45	40	42	37	34	34	30	28	26	23	22	18		
6	62	51	43	38	56	46	40	35	38	33	30	31	27	24	23	21	19	16		
7	58	46	38	33	52	42	36	31	35	30	26	28	24	22	22	19	17	15		
8	53	42	35	29	48	38	32	27	32	27	24	26	22	20	20	18	16	13		
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	19	16	14	12		
10	47	35	28	24	42	32	26	22	27	22	19	22	19	16	17	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.9
10°-20°	148.7	5.3
20°-30°	191.6	6.9
30°-40°	182.1	6.5
40°-50°	156.0	5.6
50°-60°	118.8	4.3
60°-70°	75.1	2.7
70°-80°	37.5	1.3
80°-90°	11.3	0.4
90°-100°	20.7	0.7
100°-110°	76.0	2.7
110°-120°	203.0	7.3
120°-130°	335.2	12.0
130°-140°	356.5	12.8
140°-150°	331.3	11.9
150°-160°	266.4	9.5
160°-170°	171.7	6.1
170°-180°	59.1	2.1
0°-30°	393.6	14.1
0°-40°	575.7	20.6
0°-60°	850.4	30.4
0°-90°	974.3	34.9
90°-120°	299.7	10.7
90°-150°	1322.7	47.3
90°-180°	1820.0	65.1
0°-180°	2794.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	12	0	12	0	12	6
95°	19	29	19	29	19	18
105°	34	137	34	137	34	36
115°	37	258	37	258	37	92
125°	384	365	384	365	384	332
135°	467	452	467	452	467	360
145°	532	524	532	524	532	333
155°	578	577	578	577	578	267
165°	607	608	607	608	607	171
175°	619	622	619	622	619	59
180°	621	621	621	621	621	

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	4.9	5.1	5.0	5.0	4.9	4.8	4.7	4.8	4.6	4.6	4.3
90°	12.1	12.0	11.7	11.5	11.4	11.0	10.5	10.0	9.5	9.0	8.2
92.5°	12.1	12.1	11.9	11.8	11.6	11.5	11.2	10.9	10.7	10.4	10.0
95°	19.3	19.5	19.5	19.6	19.7	19.5	19.0	18.5	18.0	17.6	16.8
97.5°	25.8	25.7	25.6	25.4	25.3	25.1	24.6	24.3	23.8	23.4	21.9
100°	30.1	29.9	29.7	29.5	29.3	28.8	28.0	27.2	26.4	25.6	23.9
102.5°	32.3	31.9	31.7	31.4	31.2	30.5	29.4	28.4	27.4	26.3	40.6
105°	34.2	33.8	33.3	33.0	32.5	31.8	30.7	29.6	28.5	27.4	54.7
107.5°	35.1	34.7	34.4	33.9	33.6	33.9	35.0	36.2	37.3	38.4	71.0
110°	35.5	35.1	34.7	34.3	33.9	38.7	48.6	58.6	68.6	78.6	107.5



TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	35.8	35.6	35.2	34.9	34.6	52.6	89.0	125.4	161.9	198.4	205.4
115°	36.9	44.0	51.2	58.4	65.6	92.3	138.5	184.8	231.0	277.2	274.7
117.5°	150.4	174.1	197.7	221.3	245.0	262.3	273.5	284.7	295.9	307.0	305.4
120°	274.1	287.6	301.1	314.5	328.0	334.2	332.9	331.7	330.5	329.3	327.5
122.5°	342.0	344.7	347.2	349.9	352.5	353.4	352.8	352.0	351.3	350.6	348.6
125°	384.2	383.9	383.6	383.3	383.0	382.5	381.8	381.1	380.4	379.7	377.8
127.5°	410.8	410.7	410.7	410.6	410.5	410.0	409.0	407.9	406.9	406.0	404.5
130°	427.3	427.4	427.5	427.6	427.7	427.2	426.1	425.0	424.0	422.8	421.7
132.5°	443.5	443.6	443.7	443.8	443.8	443.5	442.6	441.6	440.7	439.7	438.6
135°	466.8	467.1	467.3	467.4	467.7	467.3	466.2	465.3	464.3	463.2	462.4
137.5°	488.2	488.5	488.8	489.1	489.5	489.2	488.2	487.2	486.3	485.3	484.2
140°	501.4	502.0	502.5	502.9	503.4	503.3	502.3	501.4	500.6	499.6	498.5
142.5°	514.4	514.9	515.4	515.9	516.4	516.3	515.4	514.6	513.8	513.0	511.7
145°	532.4	533.0	533.5	534.0	534.4	534.3	533.6	533.0	532.3	531.6	529.9
147.5°	548.4	548.8	549.2	549.7	550.0	550.0	549.5	549.0	548.5	547.9	546.2
150°	558.1	558.5	559.0	559.6	560.1	560.0	559.4	558.8	558.2	557.6	556.0
152.5°	566.4	567.0	567.7	568.3	568.9	569.0	568.4	567.8	567.2	566.6	565.1
155°	577.8	578.7	579.5	580.2	581.0	581.2	580.6	580.0	579.4	578.8	577.6
157.5°	588.3	589.1	589.9	590.6	591.5	591.5	590.8	590.1	589.4	588.8	588.0
160°	594.4	595.1	595.9	596.6	597.3	597.3	596.7	596.1	595.6	595.0	594.3
162.5°	599.5	600.4	601.2	602.1	603.0	603.0	602.4	601.7	601.0	600.3	599.8
165°	607.0	607.8	608.5	609.2	609.8	609.8	609.2	608.5	607.8	607.0	606.7
167.5°	611.8	612.7	613.6	614.5	615.4	615.5	614.8	614.1	613.4	612.7	612.4
170°	614.7	615.6	616.5	617.3	618.3	618.4	617.7	617.0	616.3	615.6	615.4
172.5°	616.8	617.8	618.6	619.6	620.4	620.5	619.8	619.1	618.5	617.8	617.5
175°	618.7	619.7	620.7	621.7	622.8	622.8	622.2	621.5	620.8	620.1	619.8
177.5°	619.9	620.6	621.3	622.1	622.8	622.8	622.3	621.7	621.2	620.6	620.5
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	4.1	4.1	4.0	3.6	3.5	3.5	4.0	4.6	4.2	4.0	3.9
90°	7.4	6.6	5.8	4.8	3.7	2.7	1.5	0.4	1.5	2.7	3.7
92.5°	9.6	9.2	8.9	8.7	8.8	8.9	9.0	9.0	9.0	8.9	8.8
95°	16.1	15.4	14.7	16.0	19.3	22.6	25.9	29.2	25.9	22.6	19.3
97.5°	20.2	18.6	17.0	20.8	30.1	39.4	48.6	57.9	48.6	39.4	30.1
100°	22.2	20.5	18.9	24.8	38.5	52.2	65.9	79.6	65.9	52.2	38.5
102.5°	54.8	69.0	83.1	91.7	94.5	97.5	100.4	103.2	100.4	97.5	94.5
105°	82.0	109.2	136.5	148.6	145.6	142.6	139.6	136.6	139.6	142.6	145.6
107.5°	103.8	136.5	169.1	184.3	181.8	179.4	177.0	174.6	177.0	179.4	181.8
110°	136.4	165.2	194.1	207.4	205.3	203.3	201.1	199.1	201.1	203.3	205.3



TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	212.6	219.7	226.9	229.5	227.6	225.8	223.9	222.1	223.9	225.8	227.6
115°	272.2	269.8	267.3	265.2	263.5	261.7	260.0	258.4	260.0	261.7	263.5
117.5°	303.7	302.0	300.2	298.4	296.5	294.6	292.7	290.8	292.7	294.6	296.5
120°	325.8	324.0	322.2	320.6	319.0	317.5	316.0	314.5	316.0	317.5	319.0
122.5°	346.6	344.7	342.8	341.0	339.4	337.9	336.2	334.7	336.2	337.9	339.4
125°	375.9	374.0	372.1	370.5	369.2	367.9	366.6	365.3	366.6	367.9	369.2
127.5°	403.1	401.7	400.3	398.8	397.4	396.0	394.5	393.0	394.5	396.0	397.4
130°	420.6	419.6	418.4	417.1	415.5	413.9	412.2	410.7	412.2	413.9	415.5
132.5°	437.6	436.4	435.3	434.1	432.7	431.4	430.0	428.7	430.0	431.4	432.7
135°	461.5	460.5	459.7	458.4	456.8	455.2	453.7	452.0	453.7	455.2	456.8
137.5°	483.3	482.2	481.2	480.1	479.0	477.9	476.7	475.7	476.7	477.9	479.0
140°	497.5	496.4	495.2	494.3	493.5	492.8	491.9	491.1	491.9	492.8	493.5
142.5°	510.4	509.2	507.9	507.0	506.2	505.5	504.8	504.0	504.8	505.5	506.2
145°	528.1	526.5	524.8	524.0	524.1	524.2	524.3	524.3	524.3	524.2	524.1
147.5°	544.6	542.9	541.2	540.5	541.0	541.3	541.7	542.1	541.7	541.3	541.0
150°	554.4	552.8	551.2	550.8	551.5	552.2	552.8	553.5	552.8	552.2	551.5
152.5°	563.6	562.1	560.5	560.2	560.9	561.7	562.5	563.3	562.5	561.7	560.9
155°	576.4	575.1	573.9	573.8	574.7	575.6	576.5	577.4	576.5	575.6	574.7
157.5°	587.1	586.3	585.5	585.4	586.2	586.9	587.7	588.4	587.7	586.9	586.2
160°	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	594.3	593.7	593.1
162.5°	599.3	598.7	598.2	598.3	598.8	599.4	600.0	600.6	600.0	599.4	598.8
165°	606.4	606.1	605.9	606.0	606.6	607.2	607.8	608.4	607.8	607.2	606.6
167.5°	612.2	611.8	611.6	611.7	612.3	612.9	613.5	614.2	613.5	612.9	612.3
170°	615.2	615.0	614.8	615.0	615.6	616.2	616.8	617.3	616.8	616.2	615.6
172.5°	617.3	617.2	616.9	617.2	617.8	618.4	619.0	619.6	619.0	618.4	617.8
175°	619.7	619.5	619.3	619.5	620.3	621.0	621.6	622.3	621.6	621.0	620.3
177.5°	620.4	620.4	620.3	620.5	621.1	621.6	622.2	622.8	622.2	621.6	621.1
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	4.0	4.0	3.8	4.0	4.1	4.1	4.2	4.2	4.3	4.4	4.3
90°	4.8	5.8	6.6	7.4	8.2	9.0	9.5	10.0	10.5	11.0	11.4
92.5°	8.7	8.9	9.2	9.6	10.0	10.4	10.7	10.9	11.2	11.5	11.6
95°	16.0	14.7	15.4	16.1	16.8	17.6	18.0	18.5	19.0	19.5	19.7
97.5°	20.8	17.0	18.6	20.2	21.9	23.4	23.8	24.3	24.6	25.1	25.3
100°	24.8	18.9	20.5	22.2	23.9	25.6	26.4	27.2	28.0	28.8	29.3
102.5°	91.7	83.1	69.0	54.8	40.6	26.3	27.4	28.4	29.4	30.5	31.2
105°	148.6	136.5	109.2	82.0	54.7	27.4	28.5	29.6	30.7	31.8	32.5
107.5°	184.3	169.1	136.5	103.8	71.0	38.4	37.3	36.2	35.0	33.9	33.6
110°	207.4	194.1	165.2	136.4	107.5	78.6	68.6	58.6	48.6	38.7	33.9

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	229.5	226.9	219.7	212.6	205.4	198.4	161.9	125.4	89.0	52.6	34.6
115°	265.2	267.3	269.8	272.2	274.7	277.2	231.0	184.8	138.5	92.3	65.6
117.5°	298.4	300.2	302.0	303.7	305.4	307.0	295.9	284.7	273.5	262.3	245.0
120°	320.6	322.2	324.0	325.8	327.5	329.3	330.5	331.7	332.9	334.2	328.0
122.5°	341.0	342.8	344.7	346.6	348.6	350.6	351.3	352.0	352.8	353.4	352.5
125°	370.5	372.1	374.0	375.9	377.8	379.7	380.4	381.1	381.8	382.5	383.0
127.5°	398.8	400.3	401.7	403.1	404.5	406.0	406.9	407.9	409.0	410.0	410.5
130°	417.1	418.4	419.6	420.6	421.7	422.8	424.0	425.0	426.1	427.2	427.7
132.5°	434.1	435.3	436.4	437.6	438.6	439.7	440.7	441.6	442.6	443.5	443.8
135°	458.4	459.7	460.5	461.5	462.4	463.2	464.3	465.3	466.2	467.3	467.7
137.5°	480.1	481.2	482.2	483.3	484.2	485.3	486.3	487.2	488.2	489.2	489.5
140°	494.3	495.2	496.4	497.5	498.5	499.6	500.6	501.4	502.3	503.3	503.4
142.5°	507.0	507.9	509.2	510.4	511.7	513.0	513.8	514.6	515.4	516.3	516.4
145°	524.0	524.8	526.5	528.1	529.9	531.6	532.3	533.0	533.6	534.3	534.4
147.5°	540.5	541.2	542.9	544.6	546.2	547.9	548.5	549.0	549.5	550.0	550.0
150°	550.8	551.2	552.8	554.4	556.0	557.6	558.2	558.8	559.4	560.0	560.1
152.5°	560.2	560.5	562.1	563.6	565.1	566.6	567.2	567.8	568.4	569.0	568.9
155°	573.8	573.9	575.1	576.4	577.6	578.8	579.4	580.0	580.6	581.2	581.0
157.5°	585.4	585.5	586.3	587.1	588.0	588.8	589.4	590.1	590.8	591.5	591.5
160°	592.5	592.5	593.1	593.7	594.3	595.0	595.6	596.1	596.7	597.3	597.3
162.5°	598.3	598.2	598.7	599.3	599.8	600.3	601.0	601.7	602.4	603.0	603.0
165°	606.0	605.9	606.1	606.4	606.7	607.0	607.8	608.5	609.2	609.8	609.8
167.5°	611.7	611.6	611.8	612.2	612.4	612.7	613.4	614.1	614.8	615.5	615.4
170°	615.0	614.8	615.0	615.2	615.4	615.6	616.3	617.0	617.7	618.4	618.3
172.5°	617.2	616.9	617.2	617.3	617.5	617.8	618.5	619.1	619.8	620.5	620.4
175°	619.5	619.3	619.5	619.7	619.8	620.1	620.8	621.5	622.2	622.8	622.8
177.5°	620.5	620.3	620.4	620.4	620.5	620.6	621.2	621.7	622.3	622.8	622.8
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	4.3	4.2	4.4	4.3	4.4	4.2	4.3	4.3	4.4	4.3	4.2
90°	11.5	11.7	12.0	12.1	12.0	11.7	11.5	11.4	11.0	10.5	10.0
92.5°	11.8	11.9	12.1	12.1	12.1	11.9	11.8	11.6	11.5	11.2	10.9
95°	19.6	19.5	19.5	19.3	19.5	19.5	19.6	19.7	19.5	19.0	18.5
97.5°	25.4	25.6	25.7	25.8	25.7	25.6	25.4	25.3	25.1	24.6	24.3
100°	29.5	29.7	29.9	30.1	29.9	29.7	29.5	29.3	28.8	28.0	27.2
102.5°	31.4	31.7	31.9	32.3	31.9	31.7	31.4	31.2	30.5	29.4	28.4
105°	33.0	33.3	33.8	34.2	33.8	33.3	33.0	32.5	31.8	30.7	29.6
107.5°	33.9	34.4	34.7	35.1	34.7	34.4	33.9	33.6	33.9	35.0	36.2
110°	34.3	34.7	35.1	35.5	35.1	34.7	34.3	33.9	38.7	48.6	58.6

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	34.9	35.2	35.6	35.8	35.6	35.2	34.9	34.6	52.6	89.0	125.4
115°	58.4	51.2	44.0	36.9	44.0	51.2	58.4	65.6	92.3	138.5	184.8
117.5°	221.3	197.7	174.1	150.4	174.1	197.7	221.3	245.0	262.3	273.5	284.7
120°	314.5	301.1	287.6	274.1	287.6	301.1	314.5	328.0	334.2	332.9	331.7
122.5°	349.9	347.2	344.7	342.0	344.7	347.2	349.9	352.5	353.4	352.8	352.0
125°	383.3	383.6	383.9	384.2	383.9	383.6	383.3	383.0	382.5	381.8	381.1
127.5°	410.6	410.7	410.7	410.8	410.7	410.7	410.6	410.5	410.0	409.0	407.9
130°	427.6	427.5	427.4	427.3	427.4	427.5	427.6	427.7	427.2	426.1	425.0
132.5°	443.8	443.7	443.6	443.5	443.6	443.7	443.8	443.8	443.5	442.6	441.6
135°	467.4	467.3	467.1	466.8	467.1	467.3	467.4	467.7	467.3	466.2	465.3
137.5°	489.1	488.8	488.5	488.2	488.5	488.8	489.1	489.5	489.2	488.2	487.2
140°	502.9	502.5	502.0	501.4	502.0	502.5	502.9	503.4	503.3	502.3	501.4
142.5°	515.9	515.4	514.9	514.4	514.9	515.4	515.9	516.4	516.3	515.4	514.6
145°	534.0	533.5	533.0	532.4	533.0	533.5	534.0	534.4	534.3	533.6	533.0
147.5°	549.7	549.2	548.8	548.4	548.8	549.2	549.7	550.0	550.0	549.5	549.0
150°	559.6	559.0	558.5	558.1	558.5	559.0	559.6	560.1	560.0	559.4	558.8
152.5°	568.3	567.7	567.0	566.4	567.0	567.7	568.3	568.9	569.0	568.4	567.8
155°	580.2	579.5	578.7	577.8	578.7	579.5	580.2	581.0	581.2	580.6	580.0
157.5°	590.6	589.9	589.1	588.3	589.1	589.9	590.6	591.5	591.5	590.8	590.1
160°	596.6	595.9	595.1	594.4	595.1	595.9	596.6	597.3	597.3	596.7	596.1
162.5°	602.1	601.2	600.4	599.5	600.4	601.2	602.1	603.0	603.0	602.4	601.7
165°	609.2	608.5	607.8	607.0	607.8	608.5	609.2	609.8	609.8	609.2	608.5
167.5°	614.5	613.6	612.7	611.8	612.7	613.6	614.5	615.4	615.5	614.8	614.1
170°	617.3	616.5	615.6	614.7	615.6	616.5	617.3	618.3	618.4	617.7	617.0
172.5°	619.6	618.6	617.8	616.8	617.8	618.6	619.6	620.4	620.5	619.8	619.1
175°	621.7	620.7	619.7	618.7	619.7	620.7	621.7	622.8	622.8	622.2	621.5
177.5°	622.1	621.3	620.6	619.9	620.6	621.3	622.1	622.8	622.8	622.3	621.7
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	4.2	4.1	4.1	4.0	3.8	4.0	4.0	3.9	4.0	4.2	4.6
90°	9.5	9.0	8.2	7.4	6.6	5.8	4.8	3.7	2.7	1.5	0.4
92.5°	10.7	10.4	10.0	9.6	9.2	8.9	8.7	8.8	8.9	9.0	9.0
95°	18.0	17.6	16.8	16.1	15.4	14.7	16.0	19.3	22.6	25.9	29.2
97.5°	23.8	23.4	21.9	20.2	18.6	17.0	20.8	30.1	39.4	48.6	57.9
100°	26.4	25.6	23.9	22.2	20.5	18.9	24.8	38.5	52.2	65.9	79.6
102.5°	27.4	26.3	40.6	54.8	69.0	83.1	91.7	94.5	97.5	100.4	103.2
105°	28.5	27.4	54.7	82.0	109.2	136.5	148.6	145.6	142.6	139.6	136.6
107.5°	37.3	38.4	71.0	103.8	136.5	169.1	184.3	181.8	179.4	177.0	174.6
110°	68.6	78.6	107.5	136.4	165.2	194.1	207.4	205.3	203.3	201.1	199.1

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	161.9	198.4	205.4	212.6	219.7	226.9	229.5	227.6	225.8	223.9	222.1
115°	231.0	277.2	274.7	272.2	269.8	267.3	265.2	263.5	261.7	260.0	258.4
117.5°	295.9	307.0	305.4	303.7	302.0	300.2	298.4	296.5	294.6	292.7	290.8
120°	330.5	329.3	327.5	325.8	324.0	322.2	320.6	319.0	317.5	316.0	314.5
122.5°	351.3	350.6	348.6	346.6	344.7	342.8	341.0	339.4	337.9	336.2	334.7
125°	380.4	379.7	377.8	375.9	374.0	372.1	370.5	369.2	367.9	366.6	365.3
127.5°	406.9	406.0	404.5	403.1	401.7	400.3	398.8	397.4	396.0	394.5	393.0
130°	424.0	422.8	421.7	420.6	419.6	418.4	417.1	415.5	413.9	412.2	410.7
132.5°	440.7	439.7	438.6	437.6	436.4	435.3	434.1	432.7	431.4	430.0	428.7
135°	464.3	463.2	462.4	461.5	460.5	459.7	458.4	456.8	455.2	453.7	452.0
137.5°	486.3	485.3	484.2	483.3	482.2	481.2	480.1	479.0	477.9	476.7	475.7
140°	500.6	499.6	498.5	497.5	496.4	495.2	494.3	493.5	492.8	491.9	491.1
142.5°	513.8	513.0	511.7	510.4	509.2	507.9	507.0	506.2	505.5	504.8	504.0
145°	532.3	531.6	529.9	528.1	526.5	524.8	524.0	524.1	524.2	524.3	524.3
147.5°	548.5	547.9	546.2	544.6	542.9	541.2	540.5	541.0	541.3	541.7	542.1
150°	558.2	557.6	556.0	554.4	552.8	551.2	550.8	551.5	552.2	552.8	553.5
152.5°	567.2	566.6	565.1	563.6	562.1	560.5	560.2	560.9	561.7	562.5	563.3
155°	579.4	578.8	577.6	576.4	575.1	573.9	573.8	574.7	575.6	576.5	577.4
157.5°	589.4	588.8	588.0	587.1	586.3	585.5	585.4	586.2	586.9	587.7	588.4
160°	595.6	595.0	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0
162.5°	601.0	600.3	599.8	599.3	598.7	598.2	598.3	598.8	599.4	600.0	600.6
165°	607.8	607.0	606.7	606.4	606.1	605.9	606.0	606.6	607.2	607.8	608.4
167.5°	613.4	612.7	612.4	612.2	611.8	611.6	611.7	612.3	612.9	613.5	614.2
170°	616.3	615.6	615.4	615.2	615.0	614.8	615.0	615.6	616.2	616.8	617.3
172.5°	618.5	617.8	617.5	617.3	617.2	616.9	617.2	617.8	618.4	619.0	619.6
175°	620.8	620.1	619.8	619.7	619.5	619.3	619.5	620.3	621.0	621.6	622.3
177.5°	621.2	620.6	620.5	620.4	620.4	620.3	620.5	621.1	621.6	622.2	622.8
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.0	3.5	3.5	3.6	4.0	4.1	4.1	4.3	4.6	4.6	4.8
90°	1.5	2.7	3.7	4.8	5.8	6.6	7.4	8.2	9.0	9.5	10.0
92.5°	9.0	8.9	8.8	8.7	8.9	9.2	9.6	10.0	10.4	10.7	10.9
95°	25.9	22.6	19.3	16.0	14.7	15.4	16.1	16.8	17.6	18.0	18.5
97.5°	48.6	39.4	30.1	20.8	17.0	18.6	20.2	21.9	23.4	23.8	24.3
100°	65.9	52.2	38.5	24.8	18.9	20.5	22.2	23.9	25.6	26.4	27.2
102.5°	100.4	97.5	94.5	91.7	83.1	69.0	54.8	40.6	26.3	27.4	28.4
105°	139.6	142.6	145.6	148.6	136.5	109.2	82.0	54.7	27.4	28.5	29.6
107.5°	177.0	179.4	181.8	184.3	169.1	136.5	103.8	71.0	38.4	37.3	36.2
110°	201.1	203.3	205.3	207.4	194.1	165.2	136.4	107.5	78.6	68.6	58.6

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	223.9	225.8	227.6	229.5	226.9	219.7	212.6	205.4	198.4	161.9	125.4
115°	260.0	261.7	263.5	265.2	267.3	269.8	272.2	274.7	277.2	231.0	184.8
117.5°	292.7	294.6	296.5	298.4	300.2	302.0	303.7	305.4	307.0	295.9	284.7
120°	316.0	317.5	319.0	320.6	322.2	324.0	325.8	327.5	329.3	330.5	331.7
122.5°	336.2	337.9	339.4	341.0	342.8	344.7	346.6	348.6	350.6	351.3	352.0
125°	366.6	367.9	369.2	370.5	372.1	374.0	375.9	377.8	379.7	380.4	381.1
127.5°	394.5	396.0	397.4	398.8	400.3	401.7	403.1	404.5	406.0	406.9	407.9
130°	412.2	413.9	415.5	417.1	418.4	419.6	420.6	421.7	422.8	424.0	425.0
132.5°	430.0	431.4	432.7	434.1	435.3	436.4	437.6	438.6	439.7	440.7	441.6
135°	453.7	455.2	456.8	458.4	459.7	460.5	461.5	462.4	463.2	464.3	465.3
137.5°	476.7	477.9	479.0	480.1	481.2	482.2	483.3	484.2	485.3	486.3	487.2
140°	491.9	492.8	493.5	494.3	495.2	496.4	497.5	498.5	499.6	500.6	501.4
142.5°	504.8	505.5	506.2	507.0	507.9	509.2	510.4	511.7	513.0	513.8	514.6
145°	524.3	524.2	524.1	524.0	524.8	526.5	528.1	529.9	531.6	532.3	533.0
147.5°	541.7	541.3	541.0	540.5	541.2	542.9	544.6	546.2	547.9	548.5	549.0
150°	552.8	552.2	551.5	550.8	551.2	552.8	554.4	556.0	557.6	558.2	558.8
152.5°	562.5	561.7	560.9	560.2	560.5	562.1	563.6	565.1	566.6	567.2	567.8
155°	576.5	575.6	574.7	573.8	573.9	575.1	576.4	577.6	578.8	579.4	580.0
157.5°	587.7	586.9	586.2	585.4	585.5	586.3	587.1	588.0	588.8	589.4	590.1
160°	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	595.6	596.1
162.5°	600.0	599.4	598.8	598.3	598.2	598.7	599.3	599.8	600.3	601.0	601.7
165°	607.8	607.2	606.6	606.0	605.9	606.1	606.4	606.7	607.0	607.8	608.5
167.5°	613.5	612.9	612.3	611.7	611.6	611.8	612.2	612.4	612.7	613.4	614.1
170°	616.8	616.2	615.6	615.0	614.8	615.0	615.2	615.4	615.6	616.3	617.0
172.5°	619.0	618.4	617.8	617.2	616.9	617.2	617.3	617.5	617.8	618.5	619.1
175°	621.6	621.0	620.3	619.5	619.3	619.5	619.7	619.8	620.1	620.8	621.5
177.5°	622.2	621.6	621.1	620.5	620.3	620.4	620.4	620.5	620.6	621.2	621.7
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	4.7	4.8	4.9	5.0	5.0	5.1	4.9
90°	10.5	11.0	11.4	11.5	11.7	12.0	12.1
92.5°	11.2	11.5	11.6	11.8	11.9	12.1	12.1
95°	19.0	19.5	19.7	19.6	19.5	19.5	19.3
97.5°	24.6	25.1	25.3	25.4	25.6	25.7	25.8
100°	28.0	28.8	29.3	29.5	29.7	29.9	30.1
102.5°	29.4	30.5	31.2	31.4	31.7	31.9	32.3
105°	30.7	31.8	32.5	33.0	33.3	33.8	34.2
107.5°	35.0	33.9	33.6	33.9	34.4	34.7	35.1
110°	48.6	38.7	33.9	34.3	34.7	35.1	35.5

TEST NUMBER: P331621-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	89.0	52.6	34.6	34.9	35.2	35.6	35.8
115°	138.5	92.3	65.6	58.4	51.2	44.0	36.9
117.5°	273.5	262.3	245.0	221.3	197.7	174.1	150.4
120°	332.9	334.2	328.0	314.5	301.1	287.6	274.1
122.5°	352.8	353.4	352.5	349.9	347.2	344.7	342.0
125°	381.8	382.5	383.0	383.3	383.6	383.9	384.2
127.5°	409.0	410.0	410.5	410.6	410.7	410.7	410.8
130°	426.1	427.2	427.7	427.6	427.5	427.4	427.3
132.5°	442.6	443.5	443.8	443.8	443.7	443.6	443.5
135°	466.2	467.3	467.7	467.4	467.3	467.1	466.8
137.5°	488.2	489.2	489.5	489.1	488.8	488.5	488.2
140°	502.3	503.3	503.4	502.9	502.5	502.0	501.4
142.5°	515.4	516.3	516.4	515.9	515.4	514.9	514.4
145°	533.6	534.3	534.4	534.0	533.5	533.0	532.4
147.5°	549.5	550.0	550.0	549.7	549.2	548.8	548.4
150°	559.4	560.0	560.1	559.6	559.0	558.5	558.1
152.5°	568.4	569.0	568.9	568.3	567.7	567.0	566.4
155°	580.6	581.2	581.0	580.2	579.5	578.7	577.8
157.5°	590.8	591.5	591.5	590.6	589.9	589.1	588.3
160°	596.7	597.3	597.3	596.6	595.9	595.1	594.4
162.5°	602.4	603.0	603.0	602.1	601.2	600.4	599.5
165°	609.2	609.8	609.8	609.2	608.5	607.8	607.0
167.5°	614.8	615.5	615.4	614.5	613.6	612.7	611.8
170°	617.7	618.4	618.3	617.3	616.5	615.6	614.7
172.5°	619.8	620.5	620.4	619.6	618.6	617.8	616.8
175°	622.2	622.8	622.8	621.7	620.7	619.7	618.7
177.5°	622.3	622.8	622.8	622.1	621.3	620.6	619.9
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0

(END OF REPORT)