

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331662-935

Luminaire Tested: **SA2XXRDIP-C485D725U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331662-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D725U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3900.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331662-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot



TEST NUMBER: P331662-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11472	11472	11472
5°	11515	11329	11391
10°	11429	11144	11049
15°	11296	10813	10502
20°	11115	10340	9821
25°	10929	9805	9164
30°	10670	9257	8321
35°	10419	8657	7579
40°	10163	8037	6721
45°	9866	7341	5948
50°	9560	6636	5184
55°	9250	5883	4453
60°	8887	5089	3694
65°	8478	4271	3366
70°	7983	3522	3097
75°	7380	3206	2888
80°	6518	2864	2631
85°	5113	2260	2260

TEST NUMBER: P331662-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.7
10°-20°	182.6	4.7
20°-30°	256.4	6.6
30°-40°	279.6	7.2
40°-50°	257.1	6.6
50°-60°	201.9	5.2
60°-70°	131.7	3.4
70°-80°	67.9	1.7
80°-90°	20.8	0.5
90°-100°	139.9	3.6
100°-110°	474.9	12.2
110°-120°	504.5	12.9
120°-130°	415.3	10.6
130°-140°	333.5	8.6
140°-150°	252.0	6.5
150°-160°	177.1	4.5
160°-170°	104.3	2.7
170°-180°	33.9	0.9
0°-30°	505.6	13.0
0°-40°	785.2	20.1
0°-60°	1244.3	31.9
0°-90°	1464.6	37.6
90°-120°	1119.3	28.7
90°-150°	2120.1	54.4
90°-180°	2435.0	62.4
0°-180°	3900.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	710	710	710	710	710	
5°	710	707	699	704	703	67
15°	676	668	647	635	628	190
25°	614	592	550	525	514	282
35°	529	494	439	400	384	331
45°	432	388	322	278	260	334
55°	329	277	209	172	158	293
65°	222	169	112	91	88	220
75°	118	75	51	47	46	125
85°	28	15	12	12	12	33
90°	1	9	23	22	22	2
95°	24	58	264	100	77	25
105°	82	124	499	892	758	87
115°	145	183	417	861	998	143
125°	202	239	401	698	810	179
135°	237	283	396	586	671	183
145°	270	311	394	490	536	170
155°	308	332	383	433	450	141
165°	335	345	367	389	395	94
175°	349	350	353	357	356	33
180°	350	350	350	350	350	

TEST NUMBER: P331662-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	713.1	712.6	712.0	711.4	710.8	709.9	708.7	707.4	706.1	704.9	706.0
5°	710.5	709.8	709.1	708.4	707.7	706.4	704.6	702.7	700.9	699.0	700.3
7.5°	703.2	702.3	701.5	700.5	699.6	698.1	695.9	693.8	691.6	689.5	689.8
10°	697.1	696.0	695.0	694.1	693.0	691.1	688.3	685.4	682.5	679.7	679.2
12.5°	689.3	688.1	686.8	685.6	684.4	682.0	678.3	674.7	671.0	667.4	666.6
15°	675.8	674.2	672.7	671.1	669.5	666.3	661.4	656.6	651.8	646.9	644.2
17.5°	659.3	656.9	654.4	652.0	649.6	645.3	639.1	632.8	626.6	620.4	617.2
20°	646.9	644.0	641.2	638.3	635.4	630.4	623.3	616.1	609.0	601.8	598.3
22.5°	633.5	630.3	627.1	623.9	620.7	615.1	607.0	598.9	590.9	582.8	578.2
25°	613.5	608.9	604.3	599.7	595.1	588.1	578.7	569.3	559.8	550.4	544.6
27.5°	589.3	584.3	579.3	574.4	569.4	561.5	551.0	540.3	529.7	519.0	512.2
30°	572.3	566.9	561.5	556.0	550.6	542.2	530.7	519.3	507.8	496.5	489.1
32.5°	555.9	549.5	543.1	536.8	530.5	521.4	509.8	498.1	486.5	474.8	466.5
35°	528.6	521.2	514.0	506.7	499.4	489.5	476.9	464.3	451.8	439.2	430.2
37.5°	501.3	493.3	485.3	477.3	469.3	458.6	445.2	431.8	418.4	405.0	395.0
40°	482.2	473.7	465.1	456.6	448.0	436.8	422.9	409.1	395.2	381.3	371.2
42.5°	462.7	453.7	444.6	435.7	426.6	414.9	400.6	386.2	372.0	357.7	347.2
45°	432.1	422.6	412.9	403.4	393.8	381.5	366.5	351.5	336.5	321.5	311.3
47.5°	402.3	392.1	382.0	371.9	361.7	348.9	333.4	317.9	302.4	286.9	276.8
50°	380.6	370.5	360.4	350.3	340.1	327.2	311.4	295.8	280.0	264.2	254.4
52.5°	359.6	349.0	338.4	327.8	317.2	304.2	288.8	273.5	258.0	242.7	233.2
55°	328.6	317.5	306.3	295.2	284.0	270.7	255.3	239.9	224.4	209.0	200.4
57.5°	296.8	285.4	274.0	262.5	251.1	238.0	223.2	208.3	193.5	178.7	170.7
60°	275.2	263.8	252.4	240.9	229.5	216.5	201.7	187.0	172.3	157.6	150.2
62.5°	254.1	242.7	231.3	219.8	208.4	195.7	181.7	167.6	153.6	139.6	132.6
65°	221.9	210.3	198.7	187.1	175.6	163.3	150.5	137.6	124.8	111.8	107.0
67.5°	190.7	179.3	167.7	156.3	144.7	133.2	121.7	110.1	98.5	87.0	84.7
70°	169.1	158.0	146.8	135.7	124.5	114.0	104.2	94.3	84.5	74.6	73.2
72.5°	148.5	137.8	127.2	116.5	105.8	96.5	88.6	80.7	72.8	64.8	63.6
75°	118.3	108.3	98.3	88.3	78.3	70.9	66.0	61.1	56.3	51.4	50.5
77.5°	88.6	79.8	71.0	62.3	53.6	48.0	45.6	43.3	40.9	38.6	38.0
80°	70.1	62.8	55.5	48.2	40.9	36.6	35.1	33.8	32.3	30.8	30.3
82.5°	53.1	47.4	41.8	36.1	30.4	27.0	26.1	25.1	24.1	23.2	22.8
85°	27.6	24.6	21.6	18.7	15.7	13.9	13.5	13.1	12.7	12.2	12.2
87.5°	8.4	7.8	7.5	6.8	6.2	6.1	6.8	7.7	8.5	8.7	8.4
90°	0.7	2.7	5.4	6.7	8.1	10.1	13.4	18.2	22.2	22.9	22.2
92.5°	8.2	11.9	16.7	19.6	24.2	30.6	45.8	67.2	86.3	87.5	73.9
95°	23.6	26.3	33.0	39.0	49.8	66.0	96.9	155.5	233.6	263.8	230.8
97.5°	38.4	42.0	49.2	58.3	70.7	88.9	127.9	209.5	339.2	450.4	472.5
100°	51.8	53.8	59.9	70.7	84.1	103.0	138.6	220.8	366.1	531.7	628.6
102.5°	64.2	65.7	71.7	82.5	96.5	115.4	148.4	221.3	355.9	534.4	686.7
105°	82.1	84.8	89.5	99.6	114.4	133.3	164.9	224.8	335.9	498.7	677.8
107.5°	101.5	103.7	108.2	117.5	132.2	151.2	181.8	234.1	325.9	460.5	618.6
110°	114.4	117.1	121.1	129.9	144.0	163.6	193.1	241.6	323.7	442.2	581.5

TEST NUMBER: P331662-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.2	129.0	133.5	141.7	155.3	175.4	204.0	249.7	324.3	430.3	555.7
115°	144.7	148.1	152.1	160.1	173.7	191.8	220.8	261.8	327.1	417.3	523.7
117.5°	163.8	166.5	170.6	177.7	190.6	209.5	236.3	274.7	331.9	411.0	503.4
120°	175.6	178.4	182.4	188.5	201.9	220.8	247.0	283.4	335.2	407.2	492.7
122.5°	187.0	189.2	193.1	199.8	213.2	232.6	257.3	290.9	339.0	405.0	483.5
125°	201.9	204.0	207.9	216.0	229.5	248.3	272.6	302.9	344.6	401.1	470.5
127.5°	213.8	216.5	222.1	231.0	243.9	263.3	286.9	314.0	350.4	398.8	458.3
130°	220.8	223.4	230.1	239.6	253.0	271.9	295.5	321.1	354.7	397.8	450.3
132.5°	227.2	230.5	237.7	247.7	261.7	280.5	303.0	328.0	359.0	397.3	443.8
135°	236.9	239.6	247.7	257.8	273.3	292.1	313.7	337.2	364.1	396.4	434.8
137.5°	246.1	249.3	257.4	268.1	283.5	301.0	322.3	344.2	368.7	396.3	428.4
140°	253.0	255.7	263.8	274.6	289.4	306.9	327.1	347.9	370.8	395.7	424.7
142.5°	260.0	262.3	269.8	280.5	294.8	311.3	330.9	351.2	372.5	395.7	420.9
145°	270.5	273.3	280.0	290.1	303.5	318.3	336.6	355.3	374.2	394.4	415.9
147.5°	281.9	283.9	290.3	299.6	310.8	324.0	341.1	357.7	374.8	392.0	410.9
150°	289.4	291.4	296.8	305.6	315.6	327.8	343.3	358.7	374.2	390.4	406.5
152.5°	297.0	297.9	303.2	310.9	320.5	331.6	345.4	359.3	373.2	387.7	402.8
155°	307.5	308.2	312.3	319.7	327.1	337.2	348.6	360.1	371.5	383.0	395.7
157.5°	316.5	317.1	320.4	326.8	332.8	341.2	350.9	360.1	368.4	378.2	389.2
160°	322.4	323.0	325.7	331.1	336.6	343.9	352.0	360.1	366.8	374.9	384.4
162.5°	328.3	327.9	330.6	334.9	339.8	345.5	352.6	359.6	365.2	372.2	380.0
165°	335.2	334.5	335.9	339.9	343.3	347.3	353.4	358.1	362.1	366.8	372.9
167.5°	340.9	340.0	341.2	343.8	346.2	348.8	353.2	357.1	359.0	362.1	365.8
170°	344.6	343.3	343.9	345.9	347.3	349.3	352.7	356.0	357.4	359.4	362.1
172.5°	346.7	345.9	345.5	347.6	348.4	349.8	352.1	354.4	355.2	356.2	358.3
175°	349.3	348.6	347.9	349.3	349.3	350.0	351.3	352.7	352.0	352.7	353.4
177.5°	350.5	349.5	348.9	350.0	350.0	350.0	350.5	351.6	350.5	350.0	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0

TEST NUMBER: P331662-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	707.1	708.3	709.5	709.9	709.7	709.5	709.2	709.0
5°	701.5	702.8	704.1	704.6	704.1	703.7	703.3	702.8
7.5°	690.2	690.5	691.0	690.8	690.0	689.2	688.5	687.8
10°	678.8	678.4	678.0	677.3	676.5	675.6	674.8	673.9
12.5°	665.8	665.0	664.3	663.1	661.7	660.3	658.8	657.5
15°	641.4	638.8	636.0	634.0	632.5	631.1	629.6	628.3
17.5°	613.9	610.7	607.4	604.6	602.2	599.7	597.3	594.8
20°	594.7	591.2	587.5	584.2	581.1	577.9	574.8	571.6
22.5°	573.6	569.0	564.5	560.9	558.6	556.3	554.0	551.6
25°	538.7	532.9	527.0	523.0	520.8	518.7	516.6	514.4
27.5°	505.4	498.5	491.7	486.6	483.2	479.8	476.4	473.0
30°	481.8	474.6	467.3	461.7	457.8	454.0	450.1	446.3
32.5°	458.1	449.9	441.5	435.6	432.0	428.3	424.6	421.0
35°	421.2	412.2	403.2	397.1	394.0	390.8	387.7	384.5
37.5°	385.1	375.2	365.3	358.5	355.0	351.4	347.8	344.1
40°	361.0	350.9	340.7	333.8	330.1	326.4	322.6	318.9
42.5°	336.7	326.1	315.7	308.7	305.1	301.4	297.8	294.2
45°	301.2	291.1	280.9	274.1	270.7	267.3	263.8	260.5
47.5°	266.7	256.7	246.6	240.0	236.9	233.8	230.6	227.5
50°	244.5	234.7	224.8	218.4	215.4	212.4	209.4	206.4
52.5°	223.6	214.1	204.6	198.5	195.7	193.0	190.1	187.4
55°	191.8	183.2	174.7	169.0	166.3	163.6	160.9	158.2
57.5°	162.9	155.1	147.2	142.2	139.8	137.6	135.3	132.9
60°	142.9	135.7	128.4	123.6	121.3	119.0	116.8	114.4
62.5°	125.6	118.7	111.8	107.6	106.2	104.9	103.5	102.1
65°	102.2	97.3	92.5	89.8	89.4	88.9	88.5	88.1
67.5°	82.5	80.2	78.0	76.7	76.2	75.8	75.3	74.8
70°	71.7	70.3	68.9	67.8	67.3	66.7	66.1	65.6
72.5°	62.4	61.2	60.0	59.2	58.9	58.5	58.2	57.9
75°	49.4	48.5	47.4	46.8	46.8	46.6	46.4	46.3
77.5°	37.5	36.9	36.3	35.9	35.6	35.5	35.2	35.0
80°	29.7	29.2	28.6	28.3	28.3	28.3	28.3	28.3
82.5°	22.5	22.1	21.8	21.6	21.6	21.6	21.6	21.6
85°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
87.5°	8.2	7.8	8.0	8.0	8.0	8.0	8.0	8.0
90°	21.5	20.2	21.5	22.2	22.2	22.2	22.2	22.2
92.5°	58.7	50.4	44.7	40.6	40.0	37.8	38.4	37.3
95°	176.3	135.3	107.0	92.2	83.4	78.1	76.0	76.7
97.5°	411.5	336.7	263.8	215.2	183.0	166.5	156.7	151.0
100°	614.5	531.1	438.9	357.4	301.5	272.6	253.0	240.9
102.5°	747.5	728.7	661.2	574.9	514.2	464.8	440.4	424.0
105°	817.8	893.8	902.6	880.4	838.6	796.9	767.9	758.5
107.5°	767.2	881.7	951.7	984.3	989.5	987.2	981.5	968.9
110°	723.5	844.0	930.1	985.3	1014.3	1027.1	1033.1	1032.4

TEST NUMBER: P331662-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	683.7	799.3	891.4	954.7	994.9	1016.3	1027.8	1031.4
115°	634.6	738.3	826.5	895.8	943.6	974.6	992.0	998.2
117.5°	597.8	688.8	768.8	833.8	882.5	915.2	933.7	938.7
120°	579.5	663.0	734.3	795.6	842.7	874.3	893.8	900.5
122.5°	565.0	641.4	708.9	764.3	806.6	837.7	855.1	860.7
125°	543.8	613.1	672.4	722.8	761.9	787.5	804.3	809.7
127.5°	523.0	585.7	641.5	688.1	722.2	746.1	760.7	765.0
130°	509.5	567.4	620.5	665.0	697.9	720.8	734.3	739.7
132.5°	496.5	550.2	599.0	640.8	673.2	696.0	708.4	713.3
135°	478.5	523.0	567.4	605.0	634.0	656.3	668.3	671.1
137.5°	464.2	501.3	536.6	569.4	595.8	614.9	625.5	629.6
140°	455.0	487.3	518.2	547.9	569.4	586.9	597.0	601.1
142.5°	447.5	474.9	501.5	526.3	546.8	562.7	571.7	572.5
145°	436.8	459.0	479.9	499.4	515.6	527.0	533.7	535.7
147.5°	428.6	446.1	462.4	476.6	490.0	499.1	503.7	504.9
150°	422.7	437.5	451.6	463.7	473.8	481.9	485.9	486.6
152.5°	416.7	430.5	442.5	453.0	460.9	467.9	470.9	471.0
155°	408.5	419.3	429.4	436.8	444.2	448.9	451.6	450.3
157.5°	399.0	408.0	416.5	422.2	427.5	431.4	432.7	432.7
160°	393.0	400.5	407.9	412.6	417.3	420.7	421.3	421.3
162.5°	387.1	393.5	399.8	403.5	408.1	410.4	411.1	410.5
165°	378.2	383.0	387.7	390.4	393.0	395.7	395.7	395.1
167.5°	369.8	373.4	376.6	379.1	380.3	381.8	381.6	380.8
170°	365.5	367.5	370.1	371.5	372.2	374.2	373.5	372.2
172.5°	360.6	362.1	364.3	365.1	365.8	366.7	366.0	365.2
175°	355.3	356.0	356.7	357.4	357.4	358.1	357.4	356.0
177.5°	351.6	351.6	352.1	352.1	352.1	352.1	351.6	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0

(END OF REPORT)