

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332705

Luminaire Tested: **SA4XXDIP-C1195D1035U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332705
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D1035U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8812.3 lumens
Efficiency: N/A
Efficacy: 131.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332705
CATALOG NUMBER: SA4XXDIP-C1195D1035U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332705

CATALOG NUMBER: SA4XXDIP-C1195D1035U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58																			
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54	49																			
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	47	45	41																			
3	83	73	66	60	77	68	62	56	60	54	50	51	47	44	44	41	38	35																			
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33	30																			
5	70	58	49	43	65	54	47	41	47	41	37	41	36	33	35	32	29	26																			
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25	23																			
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20																			
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18																			
9	51	39	31	26	48	37	30	25	32	27	23	29	24	21	25	21	18	16																			
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332705

CATALOG NUMBER: SA4XXDIP-C1195D1035U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	2.1
10°-20°	528.8	6.0
20°-30°	778.3	8.8
30°-40°	904.8	10.3
40°-50°	904.8	10.3
50°-60°	791.5	9.0
60°-70°	587.8	6.7
70°-80°	333.9	3.8
80°-90°	99.2	1.1
90°-100°	367.0	4.2
100°-110°	763.9	8.7
110°-120°	684.2	7.8
120°-130°	575.5	6.5
130°-140°	479.9	5.4
140°-150°	366.6	4.2
150°-160°	257.7	2.9
160°-170°	151.6	1.7
170°-180°	49.3	0.6
0°-30°	1494.7	17.0
0°-40°	2399.5	27.2
0°-60°	4095.8	46.5
0°-90°	5116.7	58.1
90°-120°	1815.1	20.6
90°-150°	3237.1	36.7
90°-180°	3696.0	41.9
0°-180°	8812.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	1	8	18	20	21	6
95°	33	104	814	403	244	37
105°	117	169	655	1410	1405	125
115°	206	258	584	1122	1349	204
125°	286	340	581	955	1076	255
135°	340	405	576	848	962	263
145°	392	449	573	715	786	246
155°	446	482	557	631	658	206
165°	486	501	534	566	574	137
175°	507	508	512	519	517	48
180°	508	508	508	508	508	



TEST NUMBER: P332705

CATALOG NUMBER: SA4XXDIP-C1195D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.4	33.5	33.8	33.8	33.7	33.4	34.3	34.0	34.1	34.3	34.1
90°	1.0	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0
92.5°	11.4	16.6	26.0	38.1	52.7	73.5	124.2	201.7	277.1	316.7	263.8
95°	32.9	35.9	45.9	58.9	82.9	124.8	211.6	375.4	614.0	813.6	836.6
97.5°	59.1	59.1	67.7	79.7	100.2	135.4	202.3	337.4	574.6	856.9	1051.0
100°	75.9	75.9	82.9	94.8	113.8	145.8	204.7	317.5	521.1	802.6	1058.2
102.5°	91.8	93.4	99.6	110.8	129.0	159.3	212.6	311.9	485.2	734.8	998.3
105°	116.8	119.8	124.8	136.8	154.7	183.7	231.6	314.5	454.2	654.9	889.5
107.5°	144.4	146.4	151.3	164.1	181.3	209.8	253.8	329.2	448.6	610.2	801.6
110°	162.7	164.7	169.7	181.7	199.7	226.6	270.5	340.4	450.2	595.0	757.7



TEST NUMBER: P332705

CATALOG NUMBER: SA4XXDIP-C1195D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	180.3	182.3	188.1	199.3	217.2	244.2	286.5	352.4	455.0	587.8	733.0
115°	205.7	208.6	215.6	225.6	244.6	271.5	311.5	371.4	464.2	584.0	709.8
117.5°	232.0	234.8	241.0	252.0	269.7	297.7	335.6	390.7	474.0	583.0	699.4
120°	249.6	251.6	258.6	269.5	286.5	314.5	352.4	404.3	481.2	583.0	693.8
122.5°	265.6	267.5	274.5	284.7	303.3	330.4	368.4	417.1	488.4	582.2	687.4
125°	286.5	290.5	296.5	307.5	326.4	354.4	390.3	436.3	499.2	581.0	676.9
127.5°	305.1	308.3	315.5	328.0	347.8	376.0	410.7	452.8	507.7	578.8	662.7
130°	315.5	319.5	327.4	342.4	361.4	390.3	424.3	463.2	514.1	578.0	653.9
132.5°	325.8	329.0	339.4	353.6	374.2	401.5	435.5	473.6	519.7	577.2	645.9
135°	340.4	344.4	354.4	371.4	392.3	418.3	451.2	487.2	528.1	576.0	633.9
137.5°	355.0	358.8	369.8	385.9	407.7	432.5	463.2	496.8	533.1	575.8	623.5
140°	365.4	368.4	379.4	396.3	417.3	441.3	471.2	503.1	537.1	575.0	618.0
142.5°	376.6	379.6	389.7	405.9	426.1	449.2	478.4	507.9	540.3	575.0	613.2
145°	392.3	395.3	405.3	419.3	438.3	460.2	486.2	513.1	542.1	573.0	605.0
147.5°	410.1	411.1	419.9	434.3	450.0	469.8	494.2	517.7	543.1	569.4	597.6
150°	421.3	422.3	430.3	442.3	457.2	476.2	498.2	520.1	543.1	567.0	592.0
152.5°	431.7	431.9	439.9	451.0	464.4	481.8	501.4	521.7	541.5	563.0	585.6
155°	446.2	447.2	453.2	463.2	474.2	489.2	506.1	523.1	539.1	557.1	576.0
157.5°	460.4	460.4	466.0	473.8	483.4	495.2	509.5	523.1	536.5	550.9	566.2
160°	469.2	469.2	473.2	480.2	488.2	499.2	511.1	523.1	534.1	546.1	559.1
162.5°	477.2	476.4	479.6	485.8	493.0	501.6	512.7	523.1	531.7	541.3	552.7
165°	486.2	486.2	488.2	493.2	498.2	504.1	513.1	521.1	527.1	534.1	542.1
167.5°	495.2	494.2	495.2	499.0	501.8	506.3	512.9	518.7	522.3	526.9	532.5
170°	499.2	498.2	499.2	502.2	504.1	507.1	512.1	517.1	519.1	522.1	526.1
172.5°	503.1	502.2	502.3	504.5	505.7	507.9	511.3	515.5	515.9	517.3	520.5
175°	507.1	506.1	506.1	507.1	508.1	508.1	510.1	513.1	512.1	512.1	514.1
177.5°	508.9	508.1	507.3	508.1	508.1	508.1	508.9	510.5	508.9	508.9	509.7
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332705

CATALOG NUMBER: SA4XXDIP-C1195D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	34.3	34.5	34.7	34.7	34.9	35.1	34.9	34.9
90°	18.0	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	196.1	147.6	117.4	97.4	85.7	80.3	76.9	76.9
95°	739.7	585.0	451.2	354.4	305.5	274.5	256.6	243.6
97.5°	1093.0	1035.4	937.8	833.6	761.9	701.8	671.9	651.1
100°	1204.0	1223.9	1175.0	1101.1	1014.3	953.4	923.4	915.5
102.5°	1198.4	1297.4	1311.6	1280.8	1227.5	1183.4	1151.9	1145.5
105°	1118.1	1290.8	1389.6	1430.6	1432.6	1424.6	1410.6	1404.6
107.5°	1004.1	1188.0	1327.2	1416.2	1465.5	1488.3	1498.3	1500.9
110°	935.4	1108.1	1252.9	1362.7	1433.6	1475.5	1493.5	1502.5



TEST NUMBER: P332705

CATALOG NUMBER: SA4XXDIP-C1195D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	885.1	1037.8	1174.6	1284.4	1364.9	1415.6	1440.8	1455.3
115°	834.6	957.4	1074.2	1170.0	1248.9	1308.8	1340.7	1348.7
117.5°	809.8	911.5	1003.3	1084.6	1151.9	1202.2	1234.5	1240.7
120°	798.6	891.5	971.4	1042.2	1099.1	1143.1	1169.0	1180.0
122.5°	789.1	878.7	951.4	1013.5	1061.6	1099.1	1121.1	1132.1
125°	772.7	858.5	927.4	982.3	1022.3	1051.2	1070.2	1076.2
127.5°	752.7	834.8	903.5	955.6	995.7	1021.5	1037.4	1043.4
130°	736.8	815.6	883.5	936.4	977.3	1002.3	1018.3	1024.3
132.5°	720.0	794.1	860.3	913.3	953.4	981.5	996.7	1002.7
135°	696.8	761.7	822.6	872.5	912.5	940.4	956.4	962.4
137.5°	675.9	730.8	782.1	827.2	864.5	892.1	905.3	912.5
140°	663.9	710.8	755.7	797.6	832.6	854.6	868.5	876.5
142.5°	652.7	694.0	732.6	768.9	799.8	820.2	832.6	838.2
145°	636.9	670.9	700.8	728.8	753.7	770.7	780.7	785.7
147.5°	623.9	650.9	674.9	696.8	715.2	729.8	737.4	739.1
150°	616.0	638.9	658.9	676.9	692.8	705.8	711.8	712.8
152.5°	607.2	626.9	645.3	660.1	673.7	684.2	687.8	688.8
155°	594.0	610.0	624.9	636.9	646.9	654.9	657.9	657.9
157.5°	579.8	593.2	605.8	615.4	622.9	628.9	630.7	630.7
160°	571.0	582.0	593.0	601.0	607.0	613.0	614.0	614.0
162.5°	562.2	571.6	580.2	587.4	591.8	597.8	598.8	598.0
165°	550.1	556.1	563.0	568.0	572.0	576.0	575.0	574.0
167.5°	538.3	542.9	548.5	551.5	553.5	556.1	555.9	555.1
170°	531.1	534.1	538.1	541.1	543.1	544.1	543.1	543.1
172.5°	524.7	526.9	529.3	531.5	532.7	533.7	532.7	531.1
175°	516.1	517.1	519.1	519.1	519.1	521.1	519.1	517.1
177.5°	510.5	511.3	511.3	512.1	511.3	512.1	510.5	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1

(END OF REPORT)