

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904878

Luminaire Tested: DFN2DIP-4P2F0-030D020US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904878
REPORT IS A COMBINATION OF REPORTS P899013 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-030D020US835-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4740.0 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 43.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904878

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904878

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2923	2923	2923
5°	2922	2875	2897
10°	2892	2829	2853
15°	2844	2775	2787
20°	2781	2703	2719
25°	2717	2618	2642
30°	2640	2539	2545
35°	2566	2446	2443
40°	2476	2353	2345
45°	2385	2259	2245
50°	2287	2159	2130
55°	2183	2045	2022
60°	2065	1911	1899
65°	1935	1770	1754
70°	1771	1599	1597
75°	1545	1393	1445
80°	1272	1131	1170
85°	852	707	728

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2385 cd/sqm

TEST NUMBER: P904878

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	2.3
10°-20°	309.1	6.5
20°-30°	454.3	9.6
30°-40°	527.6	11.1
40°-50°	527.0	11.1
50°-60°	459.5	9.7
60°-70°	339.7	7.2
70°-80°	192.2	4.1
80°-90°	52.5	1.1
90°-100°	39.1	0.8
100°-110°	124.4	2.6
110°-120°	212.8	4.5
120°-130°	279.9	5.9
130°-140°	314.2	6.6
140°-150°	308.1	6.5
150°-160°	258.4	5.5
160°-170°	171.4	3.6
170°-180°	59.9	1.3
0°-30°	873.3	18.4
0°-40°	1400.9	29.6
0°-60°	2387.4	50.4
0°-90°	2971.8	62.7
90°-120°	376.3	7.9
90°-150°	1278.5	27.0
90°-180°	1768.0	37.3
0°-180°	4740.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1167	1167	1167	1167	1167	
5°	1167	1163	1150	1160	1157	111
15°	1111	1105	1090	1094	1089	313
25°	1006	997	978	980	978	463
35°	868	856	838	832	826	542
45°	706	698	681	669	664	545
55°	534	528	514	501	495	478
65°	360	354	342	332	327	356
75°	188	186	181	174	176	201
85°	46	45	44	40	39	51
90°	1	7	19	18	18	5
95°	28	33	34	34	33	31
105°	115	116	118	118	118	121
115°	214	217	216	215	214	211
125°	311	315	314	312	312	278
135°	402	408	409	408	407	311
145°	488	492	495	495	493	305
155°	558	559	561	564	562	257
165°	607	606	606	610	607	171
175°	631	630	629	632	629	60
180°	632	632	632	632	632	

TEST NUMBER: P904878

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1167.3	1167.3	1167.3	1167.3	1167.3
2.5°	1174.1	1168.5	1156.1	1167.3	1165.2
5°	1167.3	1162.9	1150.5	1159.5	1157.3
7.5°	1159.5	1152.8	1140.4	1149.5	1147.2
10°	1147.2	1139.3	1125.9	1134.8	1131.5
12.5°	1130.3	1123.6	1110.2	1115.7	1113.5
15°	1111.2	1104.6	1089.9	1094.4	1088.8
17.5°	1087.6	1081.0	1066.3	1071.9	1066.3
20°	1061.8	1055.1	1039.4	1042.7	1038.3
22.5°	1036.1	1026.0	1011.3	1011.3	1009.0
25°	1005.7	996.8	977.7	979.9	977.7
27.5°	972.0	964.1	949.6	946.3	940.7
30°	938.4	929.4	912.6	909.2	904.7
32.5°	902.5	895.8	877.8	871.0	866.5
35°	867.7	856.5	838.5	831.7	826.1
37.5°	828.4	818.3	800.3	792.4	786.8
40°	788.0	779.0	761.0	751.0	746.5
42.5°	748.7	739.7	721.8	710.5	703.8
45°	706.1	698.2	681.3	669.0	664.5
47.5°	664.5	656.7	638.7	626.3	619.6
50°	620.7	615.1	599.4	583.7	578.1
52.5°	578.1	570.2	555.7	543.3	535.4
55°	534.4	527.6	514.1	500.7	495.1
57.5°	490.5	484.9	470.3	456.8	452.3
60°	446.7	442.3	426.6	414.2	410.9
62.5°	404.1	396.2	385.0	373.8	369.3
65°	360.4	353.6	342.4	332.3	326.7
67.5°	315.5	309.8	299.7	291.9	287.4
70°	273.9	269.4	259.3	251.4	247.0
72.5°	231.3	226.7	221.1	213.3	210.0
75°	188.5	186.4	180.7	174.0	176.3
77.5°	150.4	145.9	143.6	140.3	137.0
80°	112.3	111.1	108.8	105.5	103.3
82.5°	76.3	76.3	75.3	70.7	70.7
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	0.6	6.9	18.7	17.5	18.1
92.5°	11.8	16.0	16.6	17.2	17.2
95°	27.8	33.2	34.1	34.1	33.2
97.5°	46.3	51.3	53.4	53.4	53.4
100°	67.7	72.1	73.6	73.6	73.0
102.5°	90.2	93.4	95.5	96.1	95.5
105°	114.8	116.3	117.5	118.4	118.4
107.5°	139.2	141.5	141.5	141.9	139.2
110°	162.9	165.9	165.9	165.9	164.4

TEST NUMBER: P904878

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.4	191.6	191.1	189.5	188.4
115°	213.6	216.6	215.7	215.1	213.6
117.5°	238.6	242.8	240.1	238.6	237.0
120°	263.7	267.9	263.7	263.7	262.0
122.5°	286.6	291.9	289.3	287.8	286.6
125°	310.6	315.4	313.9	312.2	311.6
127.5°	334.1	340.0	337.9	335.6	334.1
130°	356.0	362.9	361.9	360.8	358.7
132.5°	380.6	386.0	386.3	383.7	382.1
135°	401.8	407.7	408.8	408.3	406.7
137.5°	425.4	430.2	431.2	430.8	428.5
140°	446.2	451.0	453.7	453.7	451.6
142.5°	467.6	472.3	473.9	474.4	472.3
145°	487.8	491.6	494.7	495.2	493.1
147.5°	505.9	510.7	513.0	513.9	511.8
150°	524.6	527.8	529.9	531.6	529.9
152.5°	541.2	544.4	547.1	549.2	547.1
155°	557.8	559.3	561.0	563.7	562.0
157.5°	572.1	573.2	574.2	578.0	575.3
160°	584.9	586.0	586.6	589.8	587.5
162.5°	596.7	596.7	597.2	600.9	598.2
165°	606.8	606.2	606.2	610.0	607.4
167.5°	615.9	614.2	614.2	618.0	615.4
170°	622.8	621.3	620.7	624.5	621.3
172.5°	627.6	626.0	625.5	629.3	626.0
175°	631.4	629.9	628.7	632.5	629.3
177.5°	633.5	632.0	630.8	634.0	630.8
180°	632.5	632.5	632.5	632.5	632.5

TEST NUMBER: P904878

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.96	12.95	12.80	13.81	14.89	11.51	12.50	12.35	13.36	14.44
	3H	13.61	14.49	14.46	15.36	16.47	13.12	14.00	13.97	14.87	15.98
	4H	14.18	15.02	15.05	15.90	17.02	13.69	14.53	14.56	15.41	16.52
	6H	14.57	15.35	15.45	16.23	17.36	14.07	14.85	14.95	15.73	16.86
	8H	14.67	15.41	15.56	16.31	17.44	14.17	14.91	15.06	15.81	16.94
	12H	14.72	15.42	15.61	16.32	17.47	14.21	14.91	15.10	15.81	16.96
4H	2H	12.42	13.26	13.30	14.14	15.25	12.07	12.90	12.94	13.78	14.90
	3H	14.27	14.97	15.16	15.88	17.01	13.86	14.56	14.75	15.48	16.61
	4H	14.97	15.61	15.87	16.52	17.68	14.55	15.19	15.45	16.10	17.25
	6H	15.47	16.03	16.39	16.96	18.11	15.04	15.59	15.95	16.53	17.68
	8H	15.62	16.13	16.53	17.06	18.23	15.18	15.69	16.09	16.62	17.79
	12H	15.68	16.15	16.62	17.09	18.27	15.24	15.70	16.17	16.65	17.82
8H	4H	15.17	15.68	16.08	16.61	17.78	14.79	15.30	15.70	16.23	17.40
	6H	15.78	16.20	16.72	17.17	18.34	15.39	15.82	16.33	16.78	17.96
	8H	15.98	16.36	16.93	17.32	18.51	15.59	15.97	16.54	16.92	18.11
	12H	16.10	16.44	17.06	17.39	18.63	15.70	16.03	16.65	16.98	18.22
12H	4H	15.16	15.62	16.09	16.56	17.74	14.79	15.25	15.72	16.19	17.37
	6H	15.80	16.18	16.75	17.14	18.33	15.43	15.81	16.38	16.76	17.95
	8H	16.03	16.36	16.99	17.31	18.55	15.65	15.98	16.60	16.93	18.17