

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907594

Luminaire Tested: DFN2DIP-4P2F0-020D020US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907594
REPORT IS A COMBINATION OF REPORTS P899011 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D020US840-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3787.0 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907594

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907594

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1968	1968	1968
5°	1967	1935	1950
10°	1947	1904	1920
15°	1915	1868	1876
20°	1872	1819	1830
25°	1830	1762	1779
30°	1777	1709	1713
35°	1727	1647	1644
40°	1667	1584	1579
45°	1606	1521	1511
50°	1539	1454	1434
55°	1469	1377	1361
60°	1390	1286	1278
65°	1303	1192	1181
70°	1192	1076	1075
75°	1040	938	973
80°	856	762	787
85°	572	476	491

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1606 cd/sqm

TEST NUMBER: P907594

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.0	2.0
10°-20°	208.1	5.5
20°-30°	305.8	8.1
30°-40°	355.2	9.4
40°-50°	354.8	9.4
50°-60°	309.4	8.2
60°-70°	228.7	6.0
70°-80°	129.4	3.4
80°-90°	36.0	1.0
90°-100°	39.5	1.0
100°-110°	125.6	3.3
110°-120°	214.9	5.7
120°-130°	282.7	7.5
130°-140°	317.3	8.4
140°-150°	311.1	8.2
150°-160°	261.0	6.9
160°-170°	173.1	4.6
170°-180°	60.5	1.6
0°-30°	587.9	15.5
0°-40°	943.2	24.9
0°-60°	1607.3	42.4
0°-90°	2001.4	52.8
90°-120°	380.0	10.0
90°-150°	1291.1	34.1
90°-180°	1786.0	47.2
0°-180°	3787.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	786	786	786	786	786	
5°	786	783	775	781	779	75
15°	748	744	734	737	733	211
25°	677	671	658	660	658	312
35°	584	577	564	560	556	365
45°	475	470	459	450	447	367
55°	360	355	346	337	333	322
65°	243	238	231	224	220	240
75°	127	126	122	117	119	135
85°	31	30	30	27	26	35
90°	1	7	19	18	18	4
95°	28	34	34	34	34	31
105°	116	117	119	120	120	122
115°	216	219	218	217	216	213
125°	314	318	317	315	315	280
135°	406	412	413	412	411	314
145°	493	496	500	500	498	308
155°	563	565	566	569	568	259
165°	613	612	612	616	613	173
175°	638	636	635	639	636	61
180°	639	639	639	639	639	

TEST NUMBER: P907594

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	785.9	785.9	785.9	785.9	785.9
2.5°	790.4	786.7	778.3	785.9	784.5
5°	785.9	782.9	774.6	780.6	779.1
7.5°	780.6	776.1	767.8	773.9	772.3
10°	772.3	767.1	758.0	764.0	761.7
12.5°	760.9	756.5	747.4	751.1	749.6
15°	748.1	743.7	733.8	736.8	733.1
17.5°	732.3	727.8	717.9	721.6	717.9
20°	714.9	710.3	699.7	702.1	699.0
22.5°	697.5	690.7	680.9	680.9	679.3
25°	677.1	671.1	658.2	659.6	658.2
27.5°	654.4	649.1	639.3	637.1	633.3
30°	631.8	625.7	614.4	612.2	609.0
32.5°	607.5	603.1	591.0	586.4	583.4
35°	584.2	576.6	564.5	560.0	556.1
37.5°	557.7	550.9	538.8	533.5	529.7
40°	530.5	524.4	512.3	505.6	502.5
42.5°	504.0	498.0	485.9	478.4	473.8
45°	475.3	470.1	458.7	450.4	447.4
47.5°	447.4	442.1	430.0	421.6	417.2
50°	417.9	414.1	403.5	392.9	389.2
52.5°	389.2	383.8	374.1	365.8	360.5
55°	359.7	355.2	346.1	337.1	333.3
57.5°	330.2	326.5	316.6	307.6	304.5
60°	300.7	297.8	287.2	278.8	276.6
62.5°	272.1	266.7	259.2	251.7	248.6
65°	242.6	238.0	230.6	223.7	219.9
67.5°	212.4	208.5	201.8	196.5	193.5
70°	184.4	181.4	174.5	169.3	166.3
72.5°	155.7	152.7	148.9	143.6	141.4
75°	126.9	125.5	121.6	117.1	118.7
77.5°	101.3	98.3	96.6	94.4	92.2
80°	75.6	74.8	73.3	71.0	69.5
82.5°	51.4	51.4	50.7	47.7	47.7
85°	30.9	30.2	29.5	27.2	26.5
87.5°	13.6	12.1	10.6	8.4	7.6
90°	0.6	7.0	18.9	17.7	18.3
92.5°	11.9	16.2	16.8	17.4	17.4
95°	28.1	33.5	34.4	34.4	33.5
97.5°	46.8	51.8	53.9	53.9	53.9
100°	68.4	72.8	74.3	74.3	73.7
102.5°	91.1	94.3	96.4	97.0	96.4
105°	115.9	117.4	118.7	119.6	119.6
107.5°	140.6	142.9	142.9	143.3	140.6
110°	164.5	167.5	167.5	167.5	166.0

TEST NUMBER: P907594

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	190.3	193.5	193.0	191.4	190.3
115°	215.7	218.7	217.8	217.2	215.7
117.5°	241.0	245.2	242.5	241.0	239.3
120°	266.3	270.5	266.3	266.3	264.6
122.5°	289.4	294.8	292.2	290.6	289.4
125°	313.7	318.5	317.0	315.3	314.7
127.5°	337.4	343.4	341.2	338.9	337.4
130°	359.5	366.5	365.5	364.4	362.2
132.5°	384.4	389.8	390.1	387.5	385.9
135°	405.8	411.7	412.8	412.3	410.7
137.5°	429.6	434.4	435.5	435.1	432.7
140°	450.6	455.4	458.2	458.2	456.1
142.5°	472.2	477.0	478.6	479.1	477.0
145°	492.6	496.4	499.6	500.1	498.0
147.5°	510.9	515.7	518.1	519.0	516.8
150°	529.8	533.0	535.1	536.8	535.1
152.5°	546.5	549.8	552.5	554.6	552.5
155°	563.3	564.8	566.5	569.3	567.5
157.5°	577.7	578.9	579.9	583.7	581.0
160°	590.7	591.8	592.4	595.6	593.3
162.5°	602.6	602.6	603.1	606.8	604.1
165°	612.8	612.2	612.2	616.0	613.4
167.5°	622.0	620.3	620.3	624.1	621.5
170°	628.9	627.4	626.8	630.7	627.4
172.5°	633.8	632.2	631.7	635.5	632.2
175°	637.6	636.1	634.9	638.7	635.5
177.5°	639.7	638.2	637.0	640.3	637.0
180°	638.7	638.7	638.7	638.7	638.7



TEST NUMBER: P907594

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.75	10.64	10.68	11.59	12.82	9.30	10.19	10.24	11.14	12.37
	3H	11.39	12.18	12.33	13.14	14.40	10.90	11.69	11.84	12.65	13.91
	4H	11.96	12.71	12.92	13.68	14.94	11.47	12.22	12.43	13.18	14.45
	6H	12.35	13.04	13.31	14.01	15.28	11.85	12.54	12.81	13.51	14.78
	8H	12.44	13.10	13.42	14.09	15.36	11.94	12.60	12.92	13.59	14.86
	12H	12.48	13.11	13.46	14.09	15.39	11.97	12.60	12.96	13.58	14.88
4H	2H	10.20	10.95	11.16	11.92	13.18	9.84	10.60	10.81	11.56	12.82
	3H	12.04	12.67	13.01	13.66	14.94	11.63	12.26	12.61	13.26	14.53
	4H	12.74	13.31	13.72	14.30	15.60	12.31	12.89	13.30	13.88	15.18
	6H	13.23	13.73	14.23	14.74	16.04	12.80	13.30	13.80	14.31	15.60
	8H	13.37	13.84	14.37	14.84	16.15	12.94	13.40	13.93	14.40	15.72
	12H	13.44	13.85	14.45	14.87	16.19	12.99	13.41	14.00	14.43	15.74
8H	4H	12.92	13.39	13.92	14.39	15.70	12.55	13.01	13.54	14.01	15.33
	6H	13.53	13.91	14.55	14.96	16.27	13.14	13.53	14.16	14.57	15.88
	8H	13.73	14.07	14.76	15.10	16.43	13.34	13.68	14.37	14.71	16.04
	12H	13.85	14.15	14.88	15.17	16.55	13.44	13.74	14.47	14.77	16.14
12H	4H	12.91	13.33	13.92	14.35	15.66	12.54	12.96	13.55	13.98	15.29
	6H	13.55	13.89	14.58	14.92	16.25	13.18	13.52	14.21	14.55	15.88
	8H	13.78	14.08	14.81	15.10	16.48	13.40	13.69	14.43	14.72	16.09