

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915808

Luminaire Tested: DFN2DIP-4P2F0-040D030US930-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915808
REPORT IS A COMBINATION OF REPORTS P899022 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-040D030US930-RLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4936.6 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 63.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915808

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P915808

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		62	62	62
1	100	96	92	88		93	89	86	83		77	75	72		66	64	63		55	54	53
2	91	84	78	73		85	79	73	69		68	64	61		58	56	53		49	47	46
3	84	74	67	62		78	70	63	58		61	56	52		52	49	46		44	42	40
4	77	66	59	53		71	62	55	50		54	49	45		47	43	40		40	37	35
5	71	59	51	46		66	56	49	43		49	43	39		42	38	35		36	33	30
6	65	53	46	40		61	50	43	38		44	38	34		38	34	31		33	30	27
7	61	48	41	35		56	46	39	34		40	35	30		35	31	27		30	27	24
8	56	44	37	31		52	42	35	30		37	31	27		32	28	25		28	25	22
9	53	41	33	28		49	38	32	27		34	28	25		30	25	22		26	23	20
10	49	37	30	25		46	35	29	24		31	26	22		28	23	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3375	3375	3375
5°	3374	3313	3337
10°	3334	3239	3223
15°	3281	3124	3050
20°	3213	2969	2839
25°	3144	2796	2636
30°	3054	2619	2381
35°	2965	2431	2157
40°	2874	2236	1901
45°	2769	2022	1669
50°	2660	1806	1443
55°	2546	1577	1226
60°	2413	1338	1004
65°	2260	1097	897
70°	2074	872	804
75°	1840	753	721
80°	1505	608	608
85°	970	375	430

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2769 cd/sqm

TEST NUMBER: P915808

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.6
10°-20°	346.8	7.0
20°-30°	486.9	9.9
30°-40°	530.7	10.8
40°-50°	487.8	9.9
50°-60°	383.1	7.8
60°-70°	249.3	5.1
70°-80°	128.4	2.6
80°-90°	35.0	0.7
90°-100°	47.9	1.0
100°-110°	152.1	3.1
110°-120°	260.3	5.3
120°-130°	342.3	6.9
130°-140°	384.2	7.8
140°-150°	376.8	7.6
150°-160°	316.1	6.4
160°-170°	209.6	4.2
170°-180°	73.3	1.5
0°-30°	960.0	19.4
0°-40°	1490.7	30.2
0°-60°	2361.5	47.8
0°-90°	2774.2	56.2
90°-120°	460.2	9.3
90°-150°	1563.5	31.7
90°-180°	2162.0	43.8
0°-180°	4936.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1348	1342	1326	1337	1333	128
15°	1282	1268	1227	1204	1192	361
25°	1164	1125	1044	994	976	535
35°	1003	940	833	756	729	628
45°	820	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	1	8	23	21	22	5
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	

TEST NUMBER: P915808

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.9	1347.9	1347.9	1347.9	1347.9
2.5°	1354.0	1347.9	1334.4	1346.7	1344.2
5°	1347.9	1341.7	1325.8	1336.8	1333.3
7.5°	1336.8	1329.6	1312.5	1317.3	1311.2
10°	1322.3	1313.7	1289.3	1285.6	1278.4
12.5°	1304.0	1293.0	1260.0	1252.7	1239.3
15°	1282.0	1268.5	1227.1	1204.0	1191.8
17.5°	1256.4	1236.8	1185.5	1158.8	1139.2
20°	1227.1	1202.6	1141.7	1111.3	1084.3
22.5°	1195.4	1167.3	1096.5	1055.1	1036.9
25°	1163.7	1124.6	1044.1	994.2	975.7
27.5°	1125.9	1084.3	995.3	938.0	909.9
30°	1085.7	1039.2	941.6	879.5	846.5
32.5°	1046.6	990.4	890.5	817.3	786.7
35°	1002.7	940.4	833.2	756.3	729.4
37.5°	960.0	892.8	779.4	695.2	664.8
40°	914.8	841.7	723.3	636.7	605.0
42.5°	868.5	790.4	667.2	576.9	546.5
45°	819.7	737.9	609.9	523.3	494.0
47.5°	773.4	686.8	555.1	468.4	441.6
50°	722.1	635.5	501.3	417.1	391.6
52.5°	672.1	580.6	450.1	369.6	346.4
55°	623.3	528.2	396.4	323.3	300.1
57.5°	573.3	475.7	348.9	280.5	261.1
60°	522.0	424.4	298.8	236.7	217.2
62.5°	472.1	374.5	256.1	197.6	187.9
65°	420.9	322.0	212.2	170.8	167.1
67.5°	372.1	273.2	170.8	150.0	146.3
70°	320.8	225.7	141.5	129.3	124.3
72.5°	272.1	181.7	118.3	108.6	106.2
75°	224.4	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.5
80°	132.9	70.8	58.5	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.2	23.2	23.2
87.5°	19.6	9.7	9.7	8.6	8.6
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1

TEST NUMBER: P915808

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6

TEST NUMBER: P915808

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.80	12.68	12.71	13.60	14.79	7.76	8.64	8.67	9.56	10.75
	3H	13.46	14.25	14.38	15.18	16.39	8.93	9.72	9.85	10.65	11.86
	4H	14.05	14.80	14.99	15.74	16.95	9.37	10.11	10.30	11.05	12.27
	6H	14.46	15.14	15.41	16.09	17.32	9.67	10.36	10.62	11.30	12.53
	8H	14.58	15.23	15.53	16.19	17.42	9.75	10.41	10.71	11.37	12.60
	12H	14.63	15.25	15.59	16.21	17.46	9.79	10.41	10.75	11.37	12.62
4H	2H	11.82	12.56	12.76	13.50	14.72	8.35	9.09	9.29	10.03	11.25
	3H	13.62	14.24	14.58	15.21	16.44	9.68	10.30	10.63	11.27	12.50
	4H	14.30	14.87	15.26	15.83	17.08	10.21	10.78	11.17	11.74	12.99
	6H	14.80	15.28	15.77	16.27	17.52	10.61	11.10	11.58	12.08	13.34
	8H	14.96	15.41	15.94	16.39	17.66	10.73	11.18	11.70	12.16	13.43
	12H	15.05	15.45	16.04	16.45	17.72	10.78	11.19	11.78	12.19	13.46
8H	4H	14.27	14.72	15.24	15.70	16.97	10.48	10.93	11.46	11.91	13.18
	6H	14.81	15.19	15.81	16.21	17.47	10.97	11.35	11.97	12.37	13.64
	8H	15.01	15.34	16.02	16.35	17.64	11.15	11.48	12.16	12.49	13.77
	12H	15.14	15.43	16.15	16.43	17.76	11.25	11.54	12.26	12.55	13.88
12H	4H	14.22	14.63	15.21	15.63	16.90	10.48	10.89	11.48	11.89	13.16
	6H	14.78	15.11	15.79	16.12	17.41	11.02	11.35	12.03	12.36	13.64
	8H	14.99	15.28	16.00	16.28	17.62	11.21	11.50	12.22	12.50	13.84