

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921244

Luminaire Tested: DFN2DIP-4P2F0-020D040US940-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921244
REPORT IS A COMBINATION OF REPORTS P899024 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D040US940-RLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4672.6 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 49.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921244

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921244

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1846	1846	1846
5°	1845	1812	1825
10°	1823	1771	1763
15°	1794	1708	1668
20°	1757	1624	1553
25°	1720	1529	1442
30°	1670	1433	1302
35°	1621	1329	1180
40°	1571	1223	1039
45°	1514	1106	912
50°	1455	988	789
55°	1392	862	670
60°	1320	732	549
65°	1236	600	491
70°	1134	477	440
75°	1006	411	394
80°	823	333	332
85°	530	205	235

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1677 cd/sqm

TEST NUMBER: P921244

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	1.5
10°-20°	189.6	4.1
20°-30°	266.3	5.7
30°-40°	290.2	6.2
40°-50°	266.8	5.7
50°-60°	209.5	4.5
60°-70°	136.4	2.9
70°-80°	70.2	1.5
80°-90°	21.1	0.5
90°-100°	69.8	1.5
100°-110°	221.8	4.7
110°-120°	379.5	8.1
120°-130°	499.2	10.7
130°-140°	560.3	12.0
140°-150°	549.4	11.8
150°-160°	460.9	9.9
160°-170°	305.7	6.5
170°-180°	106.8	2.3
0°-30°	525.0	11.2
0°-40°	815.2	17.4
0°-60°	1291.4	27.6
0°-90°	1519.1	32.5
90°-120°	671.2	14.4
90°-150°	2280.1	48.8
90°-180°	3153.0	67.5
0°-180°	4672.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	737	734	725	731	729	70
15°	701	694	671	658	652	198
25°	636	615	571	544	534	293
35°	548	514	456	414	399	343
45°	448	404	334	286	270	346
55°	341	289	217	177	164	305
65°	230	176	116	94	91	228
75°	123	76	53	49	48	130
85°	29	15	13	13	13	33
90°	1	12	33	31	32	5
95°	50	59	61	61	59	55
105°	205	207	210	211	211	216
115°	381	386	385	384	381	377
125°	554	562	560	557	556	495
135°	717	727	729	728	725	554
145°	870	877	882	883	880	544
155°	995	998	1000	1005	1002	458
165°	1082	1081	1081	1088	1083	305
175°	1126	1123	1121	1128	1122	107
180°	1128	1128	1128	1128	1128	

TEST NUMBER: P921244

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	737.1	737.1	737.1	737.1	737.1
2.5°	740.4	737.1	729.7	736.5	735.1
5°	737.1	733.8	725.0	731.1	729.1
7.5°	731.1	727.1	717.7	720.4	717.0
10°	723.1	718.4	705.1	703.0	699.1
12.5°	713.1	707.0	689.0	685.1	677.7
15°	701.1	693.7	671.0	658.3	651.8
17.5°	687.1	676.4	648.4	633.6	623.0
20°	671.0	657.6	624.4	607.7	593.0
22.5°	653.7	638.4	599.7	577.0	567.0
25°	636.4	615.0	571.0	543.7	533.6
27.5°	615.7	593.0	544.3	512.9	497.6
30°	593.7	568.3	515.0	481.0	462.9
32.5°	572.3	541.6	487.0	446.9	430.3
35°	548.3	514.3	455.7	413.6	398.9
37.5°	524.9	488.2	426.2	380.2	363.6
40°	500.2	460.3	395.6	348.2	330.8
42.5°	474.9	432.3	364.9	315.5	298.9
45°	448.3	403.5	333.6	286.1	270.1
47.5°	422.9	375.6	303.5	256.1	241.5
50°	394.9	347.6	274.2	228.1	214.2
52.5°	367.5	317.4	246.1	202.2	189.5
55°	340.8	288.8	216.8	176.8	164.1
57.5°	313.5	260.1	190.8	153.5	142.8
60°	285.5	232.1	163.5	129.5	118.8
62.5°	258.2	204.8	140.1	108.1	102.7
65°	230.2	176.1	116.1	93.5	91.4
67.5°	203.5	149.4	93.5	82.0	80.1
70°	175.4	123.4	77.3	70.7	68.0
72.5°	148.7	99.3	64.6	59.4	58.1
75°	122.7	76.0	53.3	48.7	48.1
77.5°	96.8	54.0	42.0	39.3	38.0
80°	72.7	38.7	32.0	29.3	29.3
82.5°	50.6	26.0	22.0	20.7	20.7
85°	28.6	14.6	12.7	12.7	12.7
87.5°	10.7	5.4	5.4	4.6	4.6
90°	1.0	12.2	33.3	31.3	32.3
92.5°	21.0	28.5	29.6	30.6	30.6
95°	49.7	59.2	60.9	60.9	59.2
97.5°	82.7	91.5	95.2	95.2	95.2
100°	120.7	128.6	131.3	131.3	130.3
102.5°	160.9	166.7	170.4	171.4	170.4
105°	204.7	207.4	209.5	211.2	211.2
107.5°	248.3	252.4	252.4	253.0	248.3
110°	290.4	295.9	295.9	295.9	293.2

TEST NUMBER: P921244

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	336.0	341.8	340.7	338.0	336.0
115°	380.8	386.4	384.6	383.6	380.8
117.5°	425.4	432.9	428.2	425.4	422.8
120°	470.4	477.8	470.4	470.4	467.3
122.5°	511.1	520.7	515.9	513.2	511.1
125°	554.0	562.5	559.8	556.7	555.7
127.5°	595.8	606.4	602.6	598.5	595.8
130°	634.9	647.2	645.5	643.5	639.7
132.5°	678.8	688.3	689.0	684.2	681.5
135°	716.6	727.1	729.2	728.1	725.4
137.5°	758.8	767.2	768.9	768.2	764.2
140°	795.8	804.3	809.0	809.0	805.3
142.5°	833.9	842.4	845.1	846.1	842.4
145°	870.0	876.7	882.2	883.2	879.5
147.5°	902.2	910.7	914.8	916.5	912.8
150°	935.6	941.4	945.1	948.2	945.1
152.5°	965.2	970.9	975.7	979.5	975.7
155°	994.7	997.5	1000.5	1005.3	1002.2
157.5°	1020.3	1022.3	1024.0	1030.8	1026.0
160°	1043.0	1045.1	1046.1	1051.9	1047.8
162.5°	1064.1	1064.1	1065.1	1071.6	1066.8
165°	1082.2	1081.1	1081.1	1087.9	1083.2
167.5°	1098.5	1095.4	1095.4	1102.2	1097.4
170°	1110.7	1108.0	1107.0	1113.7	1108.0
172.5°	1119.2	1116.5	1115.4	1122.3	1116.5
175°	1126.1	1123.3	1121.2	1128.0	1122.3
177.5°	1129.8	1127.0	1125.0	1130.8	1125.0
180°	1128.0	1128.0	1128.0	1128.0	1128.0

TEST NUMBER: P921244

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.24	7.95	8.34	9.04	10.54	3.20	3.91	4.30	5.00	6.51
	3H	8.88	9.52	9.99	10.62	12.14	4.36	4.99	5.47	6.09	7.61
	4H	9.47	10.07	10.59	11.17	12.70	4.79	5.39	5.91	6.49	8.02
	6H	9.87	10.42	11.00	11.52	13.06	5.09	5.64	6.21	6.74	8.28
	8H	9.98	10.50	11.11	11.63	13.16	5.16	5.69	6.29	6.81	8.34
	12H	10.03	10.53	11.16	11.64	13.19	5.19	5.69	6.33	6.80	8.36
4H	2H	7.24	7.84	8.36	8.94	10.46	3.77	4.37	4.90	5.47	7.00
	3H	9.03	9.53	10.16	10.65	12.19	5.08	5.58	6.22	6.71	8.25
	4H	9.70	10.15	10.83	11.27	12.83	5.61	6.07	6.74	7.19	8.74
	6H	10.18	10.58	11.32	11.72	13.27	6.00	6.39	7.14	7.53	9.08
	8H	10.34	10.71	11.48	11.84	13.41	6.11	6.48	7.25	7.61	9.18
	12H	10.42	10.75	11.58	11.90	13.47	6.16	6.49	7.32	7.64	9.21
8H	4H	9.65	10.02	10.79	11.15	12.71	5.87	6.23	7.01	7.36	8.93
	6H	10.19	10.49	11.35	11.66	13.23	6.35	6.65	7.51	7.83	9.39
	8H	10.39	10.65	11.55	11.80	13.39	6.53	6.79	7.69	7.94	9.53
	12H	10.50	10.74	11.67	11.89	13.50	6.62	6.85	7.79	8.01	9.62
12H	4H	9.60	9.93	10.75	11.07	12.64	5.86	6.19	7.02	7.34	8.91
	6H	10.16	10.42	11.33	11.58	13.16	6.39	6.66	7.56	7.81	9.39
	8H	10.36	10.59	11.53	11.74	13.36	6.58	6.81	7.75	7.96	9.58

END OF REPORT