

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644846

Luminaire Tested: OMN4DIP-SR4F0-50D100U830-FLLOOB-1DUDD-WW

Issue Date: 2/16/2023



**Test Information**

Test Method: LM-79-2019  
Report Number: P644846  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-50D100U830-FLLOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE  
DOWNLIGHT - FLAT FROSTED LENS - 500 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6000.1 lumens  
Efficiency: N/A  
Efficacy: 138.6 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.13 / 1.26  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 43.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P644846

CATALOG NUMBER: OMN4DIP-SR4F0-50D100U830-FLLOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P644846

CATALOG NUMBER: OMN4DIP-SR4F0-50D100U830-FLLOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	66	62	57	53	50	44	42	40	32	31	29	24
3	78	69	62	56	70	63	57	52	50	46	42	39	36	34	28	27	25	20
4	72	61	53	48	64	55	49	44	45	40	36	35	31	29	25	23	22	18
5	66	54	47	41	59	49	43	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	18	17	13
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13417	13417	13417
5°	13267	13358	13451
10°	13162	13218	13309
15°	12985	12985	13060
20°	12802	12704	12667
25°	12469	12367	12207
30°	12100	11930	11699
35°	11722	11432	11166
40°	11272	10939	10557
45°	10894	10481	9965
50°	10422	9970	9457
55°	10027	9517	8943
60°	9565	9055	8289
65°	9070	8424	7775
70°	8592	7794	7260
75°	8041	7124	6769
80°	7355	6518	6202
85°	6910	6076	5650

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10894 cd/sqm



TEST NUMBER: P644846

CATALOG NUMBER: OMN4DIP-SR4F0-50D100U830-FLLOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.2	1.3
10°-20°	219.4	3.7
20°-30°	319.0	5.3
30°-40°	362.8	6.0
40°-50°	353.8	5.9
50°-60°	302.0	5.0
60°-70°	219.4	3.7
70°-80°	124.1	2.1
80°-90°	39.9	0.7
90°-100°	95.7	1.6
100°-110°	650.4	10.8
110°-120°	881.0	14.7
120°-130°	716.7	11.9
130°-140°	575.7	9.6
140°-150°	453.8	7.6
150°-160°	331.8	5.5
160°-170°	206.1	3.4
170°-180°	70.3	1.2
0°-30°	616.5	10.3
0°-40°	979.3	16.3
0°-60°	1635.1	27.3
0°-90°	2018.5	33.6
90°-120°	1627.1	27.1
90°-150°	3373.4	56.2
90°-180°	3982.0	66.4
0°-180°	6000.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	831	831	831	831	831	
5°	819	831	824	823	830	78
15°	777	787	777	776	781	219
25°	700	706	694	682	685	322
35°	595	597	580	566	566	371
45°	477	475	459	443	436	367
55°	356	355	338	322	318	318
65°	237	235	220	207	204	236
75°	129	124	114	110	108	137
85°	37	33	33	32	30	40
90°	4	10	16	20	20	6
95°	46	74	41	45	53	48
105°	150	225	844	1076	711	158
115°	259	313	726	1508	1762	258
125°	370	420	685	1195	1414	328
135°	456	506	688	984	1130	351
145°	539	585	693	858	949	339
155°	632	655	707	777	814	290
165°	702	711	725	744	758	197
175°	739	744	739	735	730	70
180°	739	739	739	739	739	



TEST NUMBER: P644846

CATALOG NUMBER: OMN4DIP-SR4F0-50D100U830-FLLOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	831.0	831.0	831.0	831.0	831.0
2.5°	823.8	834.4	828.3	828.4	831.9
5°	818.6	830.7	824.2	823.3	829.9
7.5°	810.0	821.9	814.3	813.1	821.8
10°	802.8	813.8	806.2	804.1	811.8
12.5°	792.8	803.9	796.2	793.2	800.9
15°	776.8	786.7	776.8	775.7	781.3
17.5°	758.7	767.3	755.7	752.0	756.2
20°	745.1	752.8	739.4	733.9	737.2
22.5°	727.9	735.6	721.4	713.1	717.3
25°	699.9	706.5	694.2	681.9	685.2
27.5°	669.8	674.9	662.6	649.9	651.0
30°	649.0	652.3	639.9	626.4	627.5
32.5°	627.3	629.7	616.4	602.0	602.2
35°	594.7	596.9	580.0	566.5	566.5
37.5°	560.1	561.4	543.4	528.7	527.1
40°	534.8	537.0	519.0	504.2	500.9
42.5°	511.3	511.7	495.4	480.7	476.5
45°	477.1	474.9	459.0	443.1	436.4
47.5°	440.3	440.3	422.2	406.2	400.0
50°	414.9	414.9	396.9	380.9	376.5
52.5°	391.4	390.5	373.3	357.4	351.2
55°	356.2	355.0	338.1	322.1	317.7
57.5°	318.8	318.8	303.0	285.9	281.1
60°	296.2	296.2	280.4	263.3	256.7
62.5°	271.8	270.9	255.1	239.8	235.9
65°	237.4	235.2	220.5	206.8	203.5
67.5°	204.6	202.4	186.8	175.9	173.7
70°	182.0	179.8	165.1	156.0	153.8
72.5°	160.3	157.2	144.3	137.0	134.8
75°	128.9	124.5	114.2	109.6	108.5
77.5°	99.0	91.5	87.3	84.1	83.0
80°	79.1	72.5	70.1	67.8	66.7
82.5°	62.0	55.3	54.7	53.3	52.2
85°	37.3	32.9	32.8	31.6	30.5
87.5°	16.3	14.8	15.9	16.6	16.6
90°	4.5	10.2	16.1	19.6	19.6
92.5°	19.3	21.4	25.4	33.6	36.4
95°	46.2	73.6	40.6	45.4	53.4
97.5°	73.9	137.0	276.6	82.7	70.9
100°	96.3	170.2	550.9	162.6	108.1
102.5°	117.7	195.3	744.4	427.3	233.6
105°	149.8	224.9	843.9	1076.2	711.4
107.5°	183.1	239.3	805.8	1565.8	1465.6
110°	204.5	257.9	783.4	1645.3	1766.9



TEST NUMBER: P644846

CATALOG NUMBER: OMN4DIP-SR4F0-50D100U830-FLLOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	226.8	280.2	761.1	1598.8	1804.1
115°	259.1	312.6	726.5	1507.7	1762.3
117.5°	293.5	346.1	718.1	1410.2	1672.1
120°	319.6	368.5	703.3	1336.0	1608.8
122.5°	337.3	390.7	684.7	1272.3	1523.3
125°	369.6	419.6	684.7	1195.3	1413.5
127.5°	395.4	447.2	685.6	1106.0	1321.5
130°	410.3	464.9	689.3	1046.2	1250.8
132.5°	428.0	482.6	688.4	1019.3	1187.6
135°	455.7	505.7	688.2	984.4	1129.9
137.5°	478.9	532.6	688.2	945.8	1070.4
140°	497.5	547.5	688.2	923.2	1036.9
142.5°	516.1	562.5	691.9	897.0	1003.4
145°	539.4	584.8	692.8	857.6	948.6
147.5°	567.3	607.3	698.4	829.3	899.3
150°	585.9	622.3	702.1	810.4	869.5
152.5°	604.5	637.2	702.1	795.3	843.5
155°	632.4	655.1	706.8	777.3	813.7
157.5°	654.7	676.5	712.4	766.0	792.3
160°	669.6	687.8	716.1	758.4	781.2
162.5°	680.7	698.9	719.8	754.6	770.0
165°	702.1	711.2	725.4	744.3	757.9
167.5°	714.2	722.4	730.0	739.5	747.7
170°	725.4	729.9	730.0	739.4	744.0
172.5°	729.1	737.3	733.7	735.7	740.3
175°	739.3	743.9	739.3	734.6	730.0
177.5°	739.3	743.0	739.3	739.2	735.6
180°	739.3	739.3	739.3	739.3	739.3

(END OF REPORT)