

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644615

Luminaire Tested: OMN4DIP-SR4F0-100D50U930-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P644615
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-100D50U930-BBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 1000 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5497.7 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 52.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644615

CATALOG NUMBER: OMN4DIP-SR4F0-100D50U930-BBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644615

CATALOG NUMBER: OMN4DIP-SR4F0-100D50U930-BBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	74	74	74	70		
1	105	102	99	96	99	96	94	91	87	85	83	78	77	75	70	69	68	68	68	68	68	68	68	64		
2	98	92	87	83	93	88	84	80	80	76	74	72	70	68	65	63	62	62	62	62	62	62	62	59		
3	91	84	78	73	87	80	75	71	73	69	66	67	63	61	61	58	56	56	56	56	56	56	56	53		
4	85	76	70	65	81	73	67	63	67	62	59	61	58	55	56	53	51	51	51	51	51	51	51	48		
5	80	70	63	58	76	67	61	56	62	57	53	57	53	50	52	49	47	47	47	47	47	47	47	44		
6	74	64	57	52	71	61	55	51	57	52	48	52	48	45	48	45	43	43	43	43	43	43	43	40		
7	70	59	52	47	66	57	50	46	52	47	43	49	44	41	45	42	39	39	39	39	39	39	39	37		
8	65	54	47	43	62	52	46	42	49	43	40	45	41	38	42	38	36	36	36	36	36	36	36	34		
9	61	50	43	39	58	48	42	38	45	40	36	42	38	35	39	36	33	33	33	33	33	33	33	31		
10	58	47	40	36	55	45	39	35	42	37	33	39	35	32	37	33	31	31	31	31	31	31	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	32270	32270	32270
5°	31837	32520	33026
10°	32385	33203	33561
15°	33278	33773	33825
20°	33430	33805	33243
25°	32660	33021	32298
30°	30922	31271	30368
35°	28109	28109	27524
40°	23119	22888	22394
45°	13823	16245	13181
50°	4467	9053	4194
55°	1581	3031	1581
60°	101	858	52
65°	61	61	0
70°	76	0	0
75°	0	0	0
80°	0	0	0
85°	296	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 16245 cd/sqm



TEST NUMBER: P644615

CATALOG NUMBER: OMN4DIP-SR4F0-100D50U930-BBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.3	4.4
10°-20°	711.2	12.9
20°-30°	1052.5	19.1
30°-40°	1087.9	19.8
40°-50°	633.0	11.5
50°-60°	107.2	2.0
60°-70°	4.2	0.1
70°-80°	0.6	0.0
80°-90°	1.3	0.0
90°-100°	38.0	0.7
100°-110°	270.7	4.9
110°-120°	367.5	6.7
120°-130°	299.1	5.4
130°-140°	240.5	4.4
140°-150°	189.6	3.4
150°-160°	138.7	2.5
160°-170°	86.1	1.6
170°-180°	29.4	0.5
0°-30°	2004.0	36.5
0°-40°	3091.9	56.2
0°-60°	3832.1	69.7
0°-90°	3838.3	69.8
90°-120°	676.1	12.3
90°-150°	1405.3	25.6
90°-180°	1659.0	30.2
0°-180°	5497.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2498	2498	2498	2498	2498	
5°	2455	2520	2508	2515	2547	235
15°	2489	2576	2526	2512	2530	700
25°	2292	2368	2317	2247	2266	1047
35°	1783	1811	1783	1738	1746	1092
45°	757	881	889	859	722	585
55°	70	82	135	76	70	77
65°	2	2	2	0	0	2
75°	0	2	0	0	0	1
85°	2	2	0	0	0	1
90°	0	2	4	6	6	1
95°	16	29	16	18	21	17
105°	60	92	352	449	297	63
115°	107	130	303	630	736	106
125°	154	174	286	500	591	136
135°	190	211	288	411	472	146
145°	225	244	290	358	396	142
155°	264	274	295	325	340	121
165°	293	297	303	311	317	82
175°	309	311	309	307	305	29
180°	309	309	309	309	309	

TEST NUMBER: P644615

CATALOG NUMBER: OMN4DIP-SR4F0-100D50U930-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2498.3	2498.3	2498.3	2498.3	2498.3
2.5°	2465.6	2514.4	2496.8	2498.6	2510.8
5°	2455.4	2520.2	2508.1	2514.7	2547.1
7.5°	2462.8	2528.4	2526.8	2528.7	2560.3
10°	2469.1	2537.7	2531.5	2530.2	2558.8
12.5°	2481.5	2556.3	2531.5	2528.5	2552.5
15°	2488.6	2576.3	2525.6	2512.4	2529.5
17.5°	2464.8	2562.4	2493.6	2458.3	2465.2
20°	2432.0	2531.2	2459.3	2406.9	2418.4
22.5°	2380.5	2475.1	2410.9	2346.1	2360.6
25°	2291.6	2367.9	2316.9	2247.2	2266.2
27.5°	2165.2	2225.5	2193.3	2125.7	2137.5
30°	2073.2	2122.7	2096.6	2030.4	2036.1
32.5°	1967.1	2009.0	1981.1	1924.1	1923.8
35°	1782.6	1811.2	1782.6	1737.9	1745.5
37.5°	1541.1	1562.9	1533.7	1506.9	1510.7
40°	1371.1	1388.2	1357.4	1332.0	1328.1
42.5°	1158.9	1206.5	1176.4	1141.8	1147.2
45°	756.7	880.7	889.3	858.9	721.6
47.5°	381.5	516.9	619.0	469.7	336.6
50°	222.3	304.3	450.5	248.7	208.7
52.5°	145.9	180.6	314.8	157.2	138.5
55°	70.2	81.7	134.6	75.9	70.2
57.5°	24.2	37.2	59.7	38.0	26.9
60°	3.9	15.3	33.2	11.5	2.0
62.5°	2.3	4.6	20.7	2.3	0.4
65°	2.0	2.0	2.0	0.0	0.0
67.5°	2.0	2.0	0.0	0.0	0.0
70°	2.0	2.0	0.0	0.0	0.0
72.5°	2.0	2.0	0.0	0.0	0.0
75°	0.0	1.9	0.0	0.0	0.0
77.5°	0.0	1.9	0.0	0.0	0.0
80°	0.0	1.9	0.0	0.0	0.0
82.5°	0.0	1.9	0.0	0.0	0.0
85°	2.0	2.0	0.0	0.0	0.0
87.5°	1.6	1.9	0.8	1.2	1.2
90°	0.0	1.9	3.9	5.8	5.8
92.5°	4.7	6.6	8.5	12.1	13.6
95°	15.5	28.8	15.5	17.6	21.4
97.5°	27.6	55.3	114.2	33.7	29.1
100°	36.9	69.2	229.3	67.5	44.7
102.5°	46.2	80.1	310.1	178.1	97.5
105°	60.2	92.5	351.7	449.3	297.3
107.5°	74.2	98.5	335.7	653.8	612.4
110°	83.5	106.3	326.4	687.0	738.3



TEST NUMBER: P644615

CATALOG NUMBER: OMN4DIP-SR4F0-100D50U930-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	92.9	115.7	317.1	667.6	753.9
115°	106.9	129.7	303.1	630.0	736.4
117.5°	121.2	143.7	299.6	589.3	698.7
120°	132.1	153.0	293.4	558.3	672.3
122.5°	139.9	162.3	285.6	531.6	636.5
125°	153.5	174.4	285.6	499.5	590.7
127.5°	164.8	186.0	286.0	462.1	552.2
130°	171.0	193.8	287.6	437.2	522.7
132.5°	178.8	201.5	287.6	425.9	496.2
135°	190.4	211.3	287.6	411.3	472.1
137.5°	200.1	222.5	287.6	395.2	447.3
140°	207.9	228.8	287.6	385.8	433.3
142.5°	215.7	235.0	289.1	374.8	419.3
145°	225.4	244.4	289.5	358.4	396.4
147.5°	237.0	253.8	291.8	346.5	375.8
150°	244.8	260.0	293.4	338.6	363.3
152.5°	252.6	266.3	293.4	332.3	352.5
155°	264.2	273.7	295.3	324.8	340.0
157.5°	273.6	282.7	297.7	320.1	331.1
160°	279.8	287.4	299.2	316.9	326.4
162.5°	284.4	292.0	300.8	315.3	321.8
165°	293.4	297.2	303.1	311.0	316.7
167.5°	298.4	301.9	305.0	309.0	312.4
170°	303.1	305.0	305.0	309.0	310.9
172.5°	304.7	308.1	306.6	307.4	309.3
175°	308.9	310.8	308.9	306.9	305.0
177.5°	308.9	310.4	308.9	308.9	307.4
180°	308.9	308.9	308.9	308.9	308.9

(END OF REPORT)