

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907956

Luminaire Tested: DFN2DIP-HX2F0-060D020US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907956
REPORT IS A COMBINATION OF REPORTS P899160 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D020US840-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6937.8 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907956

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907956

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US840-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44
5	74	63	54	48	70	60	53	47	55	49	44	51	45	42	46	42	39
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35
7	64	51	43	38	61	49	42	37	46	39	35	42	37	33	39	34	31
8	59	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5900	5900	5900
5°	5901	5793	5833
10°	5833	5665	5632
15°	5743	5464	5329
20°	5627	5193	4961
25°	5509	4892	4605
30°	5353	4584	4158
35°	5200	4255	3765
40°	5044	3915	3317
45°	4863	3541	2912
50°	4675	3164	2516
55°	4478	2764	2137
60°	4250	2347	1749
65°	3987	1925	1562
70°	3667	1531	1399
75°	3265	1323	1252
80°	2687	1072	1054
85°	1758	661	738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4863 cd/sqm

TEST NUMBER: P907956

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	3.4
10°-20°	644.3	9.3
20°-30°	904.6	13.0
30°-40°	986.1	14.2
40°-50°	906.3	13.1
50°-60°	711.7	10.3
60°-70°	463.3	6.7
70°-80°	238.5	3.4
80°-90°	62.7	0.9
90°-100°	39.5	0.6
100°-110°	125.6	1.8
110°-120°	214.9	3.1
120°-130°	282.7	4.1
130°-140°	317.3	4.6
140°-150°	311.1	4.5
150°-160°	261.0	3.8
160°-170°	173.1	2.5
170°-180°	60.5	0.9
0°-30°	1783.6	25.7
0°-40°	2769.6	39.9
0°-60°	4387.7	63.2
0°-90°	5152.1	74.3
90°-120°	380.0	5.5
90°-150°	1291.1	18.6
90°-180°	1786.0	25.7
0°-180°	6937.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2504	2504	2504	2504	2504	
5°	2504	2493	2463	2484	2477	237
15°	2382	2357	2280	2237	2214	671
25°	2162	2090	1940	1847	1813	994
35°	1863	1747	1548	1405	1355	1166
45°	1523	1371	1133	972	918	1176
55°	1158	981	736	601	558	1035
65°	782	598	394	317	310	775
75°	417	258	181	165	163	441
85°	97	50	43	43	43	112
90°	1	7	19	18	18	7
95°	28	34	34	34	34	31
105°	116	117	119	120	120	122
115°	216	219	218	217	216	213
125°	314	318	317	315	315	280
135°	406	412	413	412	411	314
145°	493	496	500	500	498	308
155°	563	565	566	569	568	259
165°	613	612	612	616	613	173
175°	638	636	635	639	636	61
180°	639	639	639	639	639	

TEST NUMBER: P907956

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2504.3	2504.3	2504.3	2504.3	2504.3
2.5°	2515.6	2504.3	2479.2	2502.0	2497.5
5°	2504.3	2493.0	2463.4	2483.9	2477.1
7.5°	2483.9	2470.3	2438.6	2447.5	2436.2
10°	2456.6	2440.7	2395.6	2388.6	2375.1
12.5°	2422.8	2402.3	2341.0	2327.5	2302.5
15°	2381.9	2356.8	2279.9	2236.9	2214.2
17.5°	2334.3	2297.9	2202.7	2152.9	2116.7
20°	2279.9	2234.4	2121.2	2064.7	2014.7
22.5°	2221.0	2168.8	2037.3	1960.4	1926.4
25°	2162.1	2089.5	1940.0	1847.1	1813.0
27.5°	2091.9	2014.7	1849.3	1742.7	1690.6
30°	2017.1	1930.8	1749.5	1634.1	1572.8
32.5°	1944.5	1840.2	1654.6	1518.4	1461.7
35°	1863.0	1747.4	1548.0	1405.1	1355.1
37.5°	1783.6	1658.8	1448.2	1291.7	1235.2
40°	1699.7	1563.9	1343.8	1183.0	1124.1
42.5°	1613.7	1468.6	1239.7	1071.9	1015.4
45°	1523.0	1371.0	1133.3	972.1	917.8
47.5°	1436.9	1276.1	1031.3	870.2	820.4
50°	1341.7	1180.8	931.5	775.0	727.6
52.5°	1248.6	1078.6	836.3	686.7	643.7
55°	1158.0	981.3	736.5	600.7	557.5
57.5°	1065.2	883.8	648.2	521.3	484.9
60°	970.0	788.7	555.2	439.8	403.4
62.5°	877.2	695.9	475.8	367.2	349.1
65°	781.9	598.2	394.4	317.4	310.4
67.5°	691.3	507.6	317.4	278.7	272.0
70°	596.0	419.3	262.8	240.2	231.1
72.5°	505.4	337.6	219.7	201.8	197.1
75°	417.0	258.2	181.3	165.4	163.3
77.5°	328.7	183.5	142.8	133.7	129.2
80°	246.9	131.5	108.7	99.8	99.8
82.5°	172.2	88.5	74.7	70.2	70.2
85°	97.4	49.8	43.0	43.0	43.0
87.5°	36.4	18.1	18.1	15.9	15.9
90°	0.6	7.0	18.9	17.7	18.3
92.5°	11.9	16.2	16.8	17.4	17.4
95°	28.1	33.5	34.4	34.4	33.5
97.5°	46.8	51.8	53.9	53.9	53.9
100°	68.4	72.8	74.3	74.3	73.7
102.5°	91.1	94.3	96.4	97.0	96.4
105°	115.9	117.4	118.7	119.6	119.6
107.5°	140.6	142.9	142.9	143.3	140.6
110°	164.5	167.5	167.5	167.5	166.0

TEST NUMBER: P907956

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	190.3	193.5	193.0	191.4	190.3
115°	215.7	218.7	217.8	217.2	215.7
117.5°	241.0	245.2	242.5	241.0	239.3
120°	266.3	270.5	266.3	266.3	264.6
122.5°	289.4	294.8	292.2	290.6	289.4
125°	313.7	318.5	317.0	315.3	314.7
127.5°	337.4	343.4	341.2	338.9	337.4
130°	359.5	366.5	365.5	364.4	362.2
132.5°	384.4	389.8	390.1	387.5	385.9
135°	405.8	411.7	412.8	412.3	410.7
137.5°	429.6	434.4	435.5	435.1	432.7
140°	450.6	455.4	458.2	458.2	456.1
142.5°	472.2	477.0	478.6	479.1	477.0
145°	492.6	496.4	499.6	500.1	498.0
147.5°	510.9	515.7	518.1	519.0	516.8
150°	529.8	533.0	535.1	536.8	535.1
152.5°	546.5	549.8	552.5	554.6	552.5
155°	563.3	564.8	566.5	569.3	567.5
157.5°	577.7	578.9	579.9	583.7	581.0
160°	590.7	591.8	592.4	595.6	593.3
162.5°	602.6	602.6	603.1	606.8	604.1
165°	612.8	612.2	612.2	616.0	613.4
167.5°	622.0	620.3	620.3	624.1	621.5
170°	628.9	627.4	626.8	630.7	627.4
172.5°	633.8	632.2	631.7	635.5	632.2
175°	637.6	636.1	634.9	638.7	635.5
177.5°	639.7	638.2	637.0	640.3	637.0
180°	638.7	638.7	638.7	638.7	638.7

TEST NUMBER: P907956

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.20	16.27	15.92	17.01	17.89	11.18	12.26	11.90	13.00	13.87
	3H	16.87	17.83	17.61	18.58	19.49	12.37	13.33	13.11	14.08	15.00
	4H	17.47	18.38	18.23	19.14	20.06	12.82	13.73	13.58	14.49	15.41
	6H	17.88	18.72	18.65	19.49	20.43	13.14	13.98	13.91	14.74	15.68
	8H	18.01	18.80	18.79	19.59	20.53	13.23	14.02	14.01	14.81	15.75
	12H	18.07	18.82	18.85	19.60	20.57	13.27	14.03	14.06	14.81	15.78
4H	2H	15.24	16.15	16.00	16.91	17.83	11.79	12.70	12.55	13.46	14.38
	3H	17.06	17.82	17.84	18.61	19.55	13.14	13.90	13.91	14.69	15.63
	4H	17.75	18.43	18.53	19.22	20.19	13.69	14.37	14.47	15.16	16.13
	6H	18.25	18.84	19.05	19.66	20.64	14.10	14.69	14.90	15.51	16.49
	8H	18.42	18.97	19.22	19.78	20.77	14.22	14.78	15.03	15.59	16.58
	12H	18.51	19.00	19.34	19.84	20.83	14.29	14.79	15.12	15.62	16.62
8H	4H	17.73	18.28	18.53	19.09	20.08	13.97	14.52	14.78	15.34	16.32
	6H	18.28	18.73	19.11	19.59	20.58	14.47	14.93	15.31	15.79	16.78
	8H	18.48	18.88	19.32	19.74	20.74	14.65	15.06	15.50	15.91	16.92
	12H	18.61	18.97	19.46	19.81	20.87	14.77	15.12	15.62	15.97	17.03
12H	4H	17.69	18.18	18.52	19.02	20.01	13.98	14.48	14.81	15.31	16.31
	6H	18.25	18.65	19.10	19.51	20.51	14.52	14.92	15.36	15.78	16.78
	8H	18.46	18.82	19.31	19.66	20.73	14.72	15.08	15.57	15.92	16.99