

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913412

Luminaire Tested: DFN2DIP-HX2F0-060D020US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913412
REPORT IS A COMBINATION OF REPORTS P899160 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D020US927-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5442.3 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913412

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913412

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US927-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44
5	74	63	54	48	70	60	53	47	55	49	44	51	45	42	46	42	39
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35
7	64	51	43	38	61	49	42	37	46	39	35	42	37	33	39	34	31
8	59	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4629	4629	4629
5°	4629	4544	4576
10°	4575	4444	4418
15°	4505	4286	4180
20°	4414	4074	3891
25°	4322	3838	3613
30°	4199	3596	3262
35°	4079	3338	2954
40°	3956	3071	2602
45°	3815	2778	2284
50°	3668	2482	1974
55°	3513	2168	1676
60°	3334	1841	1372
65°	3128	1510	1225
70°	2876	1201	1097
75°	2561	1038	982
80°	2108	840	827
85°	1379	518	579

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3815 cd/sqm

TEST NUMBER: P913412

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	3.4
10°-20°	505.4	9.3
20°-30°	709.6	13.0
30°-40°	773.5	14.2
40°-50°	710.9	13.1
50°-60°	558.3	10.3
60°-70°	363.4	6.7
70°-80°	187.1	3.4
80°-90°	49.2	0.9
90°-100°	31.0	0.6
100°-110°	98.5	1.8
110°-120°	168.6	3.1
120°-130°	221.7	4.1
130°-140°	248.9	4.6
140°-150°	244.1	4.5
150°-160°	204.7	3.8
160°-170°	135.8	2.5
170°-180°	47.5	0.9
0°-30°	1399.1	25.7
0°-40°	2172.6	39.9
0°-60°	3441.9	63.2
0°-90°	4041.5	74.3
90°-120°	298.1	5.5
90°-150°	1012.8	18.6
90°-180°	1401.0	25.7
0°-180°	5442.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1956	1932	1948	1943	186
15°	1868	1849	1788	1755	1737	527
25°	1696	1639	1522	1449	1422	780
35°	1461	1371	1214	1102	1063	915
45°	1195	1076	889	763	720	923
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	203	142	130	128	346
85°	76	39	34	34	34	88
90°	0	6	15	14	14	5
95°	22	26	27	27	26	25
105°	91	92	93	94	94	96
115°	169	172	171	170	169	167
125°	246	250	249	247	247	220
135°	318	323	324	323	322	246
145°	386	389	392	392	391	241
155°	442	443	444	447	445	203
165°	481	480	480	483	481	136
175°	500	499	498	501	498	48
180°	501	501	501	501	501	

TEST NUMBER: P913412

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.5	1964.5	1964.5	1964.5	1964.5
2.5°	1973.3	1964.5	1944.8	1962.7	1959.1
5°	1964.5	1955.6	1932.4	1948.4	1943.1
7.5°	1948.4	1937.8	1913.0	1919.9	1911.1
10°	1927.1	1914.6	1879.2	1873.7	1863.1
12.5°	1900.5	1884.4	1836.4	1825.8	1806.2
15°	1868.4	1848.8	1788.4	1754.7	1736.9
17.5°	1831.1	1802.6	1727.9	1688.9	1660.4
20°	1788.4	1752.8	1664.0	1619.6	1580.4
22.5°	1742.2	1701.3	1598.1	1537.8	1511.2
25°	1696.1	1639.1	1521.8	1449.0	1422.2
27.5°	1641.0	1580.4	1450.6	1367.1	1326.2
30°	1582.3	1514.6	1372.4	1281.8	1233.7
32.5°	1525.3	1443.5	1297.9	1191.1	1146.6
35°	1461.4	1370.7	1214.3	1102.2	1063.0
37.5°	1399.2	1301.2	1136.1	1013.3	968.9
40°	1333.3	1226.8	1054.2	928.0	881.8
42.5°	1265.8	1152.1	972.5	840.8	796.5
45°	1194.7	1075.5	889.0	762.6	719.9
47.5°	1127.2	1001.0	809.0	682.6	643.6
50°	1052.5	926.3	730.7	607.9	570.8
52.5°	979.5	846.1	656.0	538.7	504.9
55°	908.4	769.8	577.7	471.2	437.4
57.5°	835.6	693.3	508.5	408.9	380.4
60°	760.9	618.7	435.5	345.0	316.5
62.5°	688.1	545.9	373.3	288.0	273.9
65°	613.4	469.3	309.3	249.0	243.5
67.5°	542.2	398.2	249.0	218.6	213.3
70°	467.5	328.9	206.1	188.5	181.3
72.5°	396.5	264.8	172.4	158.3	154.6
75°	327.1	202.6	142.2	129.8	128.1
77.5°	257.9	143.9	112.0	104.9	101.3
80°	193.7	103.1	85.2	78.3	78.3
82.5°	135.1	69.4	58.6	55.1	55.1
85°	76.4	39.1	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	0.5	5.5	14.8	13.9	14.3
92.5°	9.3	12.7	13.2	13.6	13.6
95°	22.0	26.3	27.0	27.0	26.3
97.5°	36.7	40.6	42.3	42.3	42.3
100°	53.6	57.1	58.3	58.3	57.8
102.5°	71.5	74.0	75.7	76.1	75.7
105°	90.9	92.1	93.1	93.8	93.8
107.5°	110.3	112.1	112.1	112.4	110.3
110°	129.0	131.4	131.4	131.4	130.2



TEST NUMBER: P913412

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	149.2	151.8	151.4	150.1	149.2
115°	169.2	171.6	170.9	170.4	169.2
117.5°	189.0	192.3	190.2	189.0	187.7
120°	208.9	212.2	208.9	208.9	207.6
122.5°	227.0	231.2	229.2	228.0	227.0
125°	246.1	249.9	248.7	247.3	246.8
127.5°	264.7	269.3	267.7	265.9	264.7
130°	282.0	287.5	286.7	285.8	284.2
132.5°	301.5	305.8	306.0	304.0	302.7
135°	318.3	323.0	323.8	323.4	322.2
137.5°	337.0	340.8	341.6	341.3	339.4
140°	353.5	357.3	359.4	359.4	357.7
142.5°	370.4	374.1	375.4	375.8	374.1
145°	386.4	389.4	391.9	392.3	390.6
147.5°	400.8	404.6	406.4	407.1	405.4
150°	415.6	418.1	419.8	421.1	419.8
152.5°	428.7	431.3	433.4	435.1	433.4
155°	441.9	443.1	444.4	446.6	445.2
157.5°	453.2	454.1	454.9	457.9	455.7
160°	463.3	464.2	464.7	467.2	465.4
162.5°	472.7	472.7	473.1	476.0	473.9
165°	480.7	480.2	480.2	483.2	481.2
167.5°	487.9	486.6	486.6	489.6	487.5
170°	493.4	492.2	491.7	494.7	492.2
172.5°	497.2	495.9	495.5	498.5	495.9
175°	500.2	499.0	498.0	501.1	498.5
177.5°	501.8	500.7	499.7	502.2	499.7
180°	501.1	501.1	501.1	501.1	501.1

TEST NUMBER: P913412

CATALOG NUMBER: DFN2DIP-HX2F0-060D020US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.35	15.43	15.08	16.17	17.05	10.34	11.41	11.06	12.15	13.03
	3H	16.02	16.99	16.76	17.74	18.65	11.53	12.49	12.26	13.24	14.15
	4H	16.63	17.53	17.38	18.29	19.22	11.98	12.88	12.73	13.64	14.57
	6H	17.04	17.88	17.81	18.65	19.58	12.30	13.13	13.06	13.90	14.84
	8H	17.16	17.96	17.94	18.75	19.69	12.38	13.18	13.16	13.97	14.91
	12H	17.22	17.98	18.01	18.76	19.73	12.43	13.19	13.21	13.97	14.93
4H	2H	14.40	15.31	15.16	16.06	16.99	10.95	11.85	11.71	12.61	13.54
	3H	16.22	16.97	16.99	17.77	18.71	12.30	13.05	13.07	13.85	14.79
	4H	16.90	17.59	17.69	18.38	19.35	12.84	13.53	13.63	14.32	15.29
	6H	17.41	18.00	18.21	18.82	19.79	13.26	13.85	14.06	14.67	15.64
	8H	17.57	18.12	18.38	18.94	19.93	13.38	13.93	14.19	14.75	15.74
	12H	17.67	18.16	18.49	19.00	19.99	13.45	13.94	14.27	14.78	15.77
8H	4H	16.88	17.44	17.69	18.25	19.24	13.13	13.68	13.93	14.49	15.48
	6H	17.43	17.89	18.27	18.74	19.73	13.63	14.09	14.47	14.94	15.93
	8H	17.63	18.04	18.48	18.89	19.90	13.81	14.21	14.66	15.07	16.07
	12H	17.76	18.12	18.61	18.97	20.03	13.92	14.28	14.77	15.13	16.19
12H	4H	16.85	17.34	17.67	18.18	19.17	13.14	13.63	13.97	14.47	15.46
	6H	17.41	17.81	18.25	18.67	19.67	13.67	14.08	14.52	14.93	15.94
	8H	17.62	17.98	18.47	18.82	19.88	13.88	14.24	14.73	15.08	16.14