

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645065

Luminaire Tested: OMN4DIP-SR4F0-75D125U930-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



**Test Information**

Test Method: LM-79-2019  
Report Number: P645065  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-75D125U930-BBMOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE  
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 750 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7220.6 lumens  
Efficiency: N/A  
Efficacy: 109.2 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.18  
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P645065

CATALOG NUMBER: OMN4DIP-SR4F0-75D125U930-BBMOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P645065

CATALOG NUMBER: OMN4DIP-SR4F0-75D125U930-BBMOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40								
1	97	93	90	87	88	85	83	80	70	69	67	57	56	54	44	43	43	37								
2	90	84	78	74	82	77	72	69	64	61	58	52	50	48	41	40	39	34								
3	83	75	69	64	76	69	64	59	58	54	51	47	45	43	38	36	35	31								
4	77	67	61	55	70	62	56	52	52	48	45	43	40	38	35	33	32	28								
5	71	61	54	49	65	56	50	46	48	43	40	40	37	34	32	30	29	25								
6	66	55	48	43	60	51	45	41	44	39	36	37	33	31	30	28	26	23								
7	61	50	43	38	56	47	41	36	40	35	32	34	30	28	28	25	24	21								
8	57	46	39	34	53	43	37	33	37	32	29	31	28	25	26	23	22	19								
9	53	42	36	31	49	40	34	29	34	29	26	29	26	23	24	22	20	18								
10	50	39	32	28	46	36	31	27	32	27	24	27	24	21	22	20	18	17								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24327	24327	24327
5°	24000	24515	24896
10°	24413	25031	25299
15°	25087	25460	25500
20°	25201	25484	25060
25°	24620	24893	24348
30°	23311	23573	22893
35°	21190	21190	20750
40°	17428	17254	16882
45°	10419	12246	9937
50°	3368	6824	3161
55°	1191	2283	1191
60°	75	646	39
65°	46	46	0
70°	57	0	0
75°	0	0	0
80°	0	0	0
85°	222	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 12246 cd/sqm



TEST NUMBER: P645065

CATALOG NUMBER: OMN4DIP-SR4F0-75D125U930-BBMOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	181.2	2.5
10°-20°	536.1	7.4
20°-30°	793.4	11.0
30°-40°	820.1	11.4
40°-50°	477.2	6.6
50°-60°	80.8	1.1
60°-70°	3.2	0.0
70°-80°	0.5	0.0
80°-90°	2.2	0.0
90°-100°	99.0	1.4
100°-110°	705.5	9.8
110°-120°	957.8	13.3
120°-130°	779.6	10.8
130°-140°	627.0	8.7
140°-150°	494.3	6.8
150°-160°	361.4	5.0
160°-170°	224.5	3.1
170°-180°	76.6	1.1
0°-30°	1510.7	20.9
0°-40°	2330.9	32.3
0°-60°	2888.9	40.0
0°-90°	2894.7	40.1
90°-120°	1762.4	24.4
90°-150°	3663.3	50.7
90°-180°	4326.0	59.9
0°-180°	7220.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1883	1883	1883	1883	1883	
5°	1851	1900	1891	1896	1920	177
15°	1876	1942	1904	1894	1907	528
25°	1728	1785	1747	1694	1708	789
35°	1344	1365	1344	1310	1316	823
45°	570	664	670	648	544	441
55°	53	62	101	57	53	58
65°	2	2	2	0	0	2
75°	0	1	0	0	0	1
85°	2	2	0	0	0	1
90°	0	5	10	15	15	2
95°	40	75	40	46	56	45
105°	157	241	917	1171	775	166
115°	279	338	790	1642	1920	277
125°	400	455	744	1302	1540	356
135°	496	551	750	1072	1231	382
145°	588	637	755	934	1033	369
155°	689	714	770	847	886	316
165°	765	775	790	811	826	215
175°	805	810	805	800	795	76
180°	805	805	805	805	805	

TEST NUMBER: P645065

CATALOG NUMBER: OMN4DIP-SR4F0-75D125U930-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1883.4	1883.4	1883.4	1883.4	1883.4
2.5°	1858.7	1895.5	1882.2	1883.6	1892.8
5°	1851.0	1899.9	1890.7	1895.7	1920.1
7.5°	1856.6	1906.1	1904.8	1906.3	1930.1
10°	1861.3	1913.1	1908.4	1907.4	1928.9
12.5°	1870.7	1927.1	1908.4	1906.1	1924.2
15°	1876.0	1942.1	1903.9	1893.9	1906.9
17.5°	1858.1	1931.7	1879.8	1853.2	1858.4
20°	1833.4	1908.1	1854.0	1814.5	1823.1
22.5°	1794.6	1865.9	1817.5	1768.6	1779.6
25°	1727.5	1785.0	1746.6	1694.0	1708.4
27.5°	1632.2	1677.7	1653.4	1602.5	1611.4
30°	1562.9	1600.2	1580.5	1530.6	1534.9
32.5°	1482.9	1514.5	1493.5	1450.5	1450.2
35°	1343.8	1365.4	1343.8	1310.1	1315.9
37.5°	1161.8	1178.2	1156.2	1136.0	1138.8
40°	1033.6	1046.5	1023.3	1004.1	1001.2
42.5°	873.6	909.5	886.8	860.8	864.8
45°	570.4	663.9	670.4	647.5	544.0
47.5°	287.6	389.6	466.7	354.1	253.8
50°	167.6	229.4	339.6	187.5	157.3
52.5°	110.0	136.1	237.3	118.5	104.4
55°	52.9	61.6	101.4	57.2	52.9
57.5°	18.2	28.0	45.0	28.6	20.3
60°	2.9	11.6	25.0	8.7	1.5
62.5°	1.8	3.5	15.6	1.7	0.3
65°	1.5	1.5	1.5	0.0	0.0
67.5°	1.5	1.5	0.0	0.0	0.0
70°	1.5	1.5	0.0	0.0	0.0
72.5°	1.5	1.5	0.0	0.0	0.0
75°	0.0	1.4	0.0	0.0	0.0
77.5°	0.0	1.4	0.0	0.0	0.0
80°	0.0	1.4	0.0	0.0	0.0
82.5°	0.0	1.4	0.0	0.0	0.0
85°	1.5	1.5	0.0	0.0	0.0
87.5°	1.2	2.2	2.0	3.0	3.0
90°	0.0	5.0	10.1	15.2	15.2
92.5°	12.2	17.1	22.3	31.5	35.5
95°	40.5	75.2	40.5	45.8	55.7
97.5°	71.9	144.2	297.8	87.9	76.0
100°	96.2	180.4	597.6	175.9	116.5
102.5°	120.5	208.7	808.3	464.2	254.2
105°	157.0	241.2	916.7	1171.1	774.9
107.5°	193.5	256.9	875.2	1704.4	1596.4
110°	217.8	277.2	850.9	1790.9	1924.6



TEST NUMBER: P645065

CATALOG NUMBER: OMN4DIP-SR4F0-75D125U930-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	242.1	301.5	826.6	1740.3	1965.1
115°	278.6	338.0	790.1	1642.2	1919.5
117.5°	316.0	374.5	781.0	1536.0	1821.3
120°	344.4	398.9	764.8	1455.3	1752.4
122.5°	364.7	423.1	744.5	1385.8	1659.2
125°	400.1	454.6	744.5	1302.0	1539.7
127.5°	429.5	485.0	745.5	1204.7	1439.4
130°	445.7	505.1	749.6	1139.6	1362.4
132.5°	466.0	525.4	749.6	1110.3	1293.5
135°	496.3	550.8	749.6	1072.3	1230.7
137.5°	521.7	580.1	749.6	1030.2	1165.9
140°	541.9	596.4	749.6	1005.6	1129.4
142.5°	562.2	612.7	753.6	977.1	1093.0
145°	587.5	637.0	754.6	934.2	1033.2
147.5°	617.9	661.5	760.7	903.3	979.5
150°	638.2	677.8	764.8	882.7	947.1
152.5°	658.4	694.1	764.8	866.2	918.7
155°	688.8	713.6	769.8	846.7	886.3
157.5°	713.1	736.9	775.9	834.3	863.0
160°	729.3	749.1	780.0	826.1	850.9
162.5°	741.5	761.3	784.0	821.9	838.7
165°	764.8	774.7	790.1	810.7	825.6
167.5°	777.9	786.9	795.2	805.5	814.4
170°	790.1	795.1	795.2	805.4	810.4
172.5°	794.2	803.1	799.2	801.4	806.3
175°	805.3	810.2	805.3	800.1	795.2
177.5°	805.3	809.3	805.3	805.2	801.2
180°	805.3	805.3	805.3	805.3	805.3

(END OF REPORT)