

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645190

Luminaire Tested: OMN4DIP-SR4F0-75D75U930-WBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P645190
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-27)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-75D75U930-WBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - WHITE BAFFLE WITH MEDIUM OPTIC - 750 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5672.7 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.21 / 1.19
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 48.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P645190

CATALOG NUMBER: OMN4DIP-SR4F0-75D75U930-WBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P645190

CATALOG NUMBER: OMN4DIP-SR4F0-75D75U930-WBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									70									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																			
1	101	97	94	91	94	91	88	86	79	77	75	67	66	65	57	56	55	51																			
2	94	87	82	78	87	82	77	74	71	68	65	62	59	57	53	51	50	46																			
3	87	79	73	68	81	74	69	64	65	61	58	57	54	51	49	47	45	41																			
4	81	71	65	59	75	67	61	57	59	55	51	52	49	46	45	43	41	37																			
5	75	65	58	52	70	61	55	50	54	49	46	48	44	41	42	39	37	34																			
6	70	59	52	47	65	56	49	45	50	45	41	44	40	37	39	36	34	31																			
7	65	54	47	42	61	51	45	40	46	41	37	41	37	34	36	33	31	28																			
8	61	50	43	38	57	47	41	36	42	37	34	38	34	31	33	30	28	26																			
9	57	46	39	34	53	43	37	33	39	34	31	35	31	28	31	28	26	24																			
10	53	42	36	31	50	40	34	30	36	31	28	33	29	26	29	26	24	22																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25220	25220	25220
5°	25030	25373	25869
10°	25435	25937	26360
15°	26069	26424	26600
20°	26212	26454	26151
25°	25711	25773	25458
30°	24581	24516	23924
35°	22442	22256	21792
40°	18642	18369	18023
45°	11709	13320	11172
50°	4491	7889	4166
55°	2119	3310	2153
60°	1026	1671	912
65°	944	987	853
70°	944	944	835
75°	953	953	808
80°	982	878	766
85°	1097	874	652

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 13320 cd/sqm



TEST NUMBER: P645190

CATALOG NUMBER: OMN4DIP-SR4F0-75D75U930-WBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.1	3.3
10°-20°	556.2	9.8
20°-30°	826.3	14.6
30°-40°	864.8	15.2
40°-50°	523.8	9.2
50°-60°	120.9	2.1
60°-70°	33.2	0.6
70°-80°	19.4	0.3
80°-90°	7.8	0.1
90°-100°	57.9	1.0
100°-110°	413.0	7.3
110°-120°	560.7	9.9
120°-130°	456.3	8.0
130°-140°	367.0	6.5
140°-150°	289.3	5.1
150°-160°	211.6	3.7
160°-170°	131.4	2.3
170°-180°	44.8	0.8
0°-30°	1570.6	27.7
0°-40°	2435.4	42.9
0°-60°	3080.2	54.3
0°-90°	3140.6	55.4
90°-120°	1031.6	18.2
90°-150°	2144.3	37.8
90°-180°	2532.0	44.6
0°-180°	5672.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1952	1952	1952	1952	1952	
5°	1930	1975	1957	1965	1995	185
15°	1950	2008	1976	1960	1989	549
25°	1804	1857	1808	1762	1786	826
35°	1423	1445	1411	1379	1382	875
45°	641	729	729	704	612	492
55°	94	107	147	101	96	98
65°	31	32	32	29	28	31
75°	19	19	19	18	16	20
85°	7	7	6	6	4	7
90°	0	3	6	9	9	1
95°	24	44	24	27	33	27
105°	92	141	537	686	454	97
115°	163	198	462	961	1124	162
125°	234	266	436	762	901	208
135°	290	322	439	628	720	224
145°	344	373	442	547	605	216
155°	403	418	451	496	519	185
165°	448	454	462	474	483	126
175°	471	474	471	468	465	45
180°	471	471	471	471	471	



TEST NUMBER: P645190

CATALOG NUMBER: OMN4DIP-SR4F0-75D75U930-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1952.5	1952.5	1952.5	1952.5	1952.5
2.5°	1933.6	1968.1	1948.9	1950.5	1966.6
5°	1930.4	1975.0	1956.9	1964.9	1995.1
7.5°	1935.7	1982.3	1971.6	1974.4	2007.4
10°	1939.2	1988.1	1977.5	1976.7	2009.8
12.5°	1947.5	1998.6	1978.6	1974.4	2006.3
15°	1949.5	2008.5	1976.0	1960.5	1989.2
17.5°	1930.4	1995.4	1951.6	1919.5	1942.5
20°	1906.9	1973.0	1924.5	1879.5	1902.5
22.5°	1870.4	1935.4	1883.4	1834.8	1859.0
25°	1804.0	1857.2	1808.4	1761.9	1786.3
27.5°	1719.9	1757.2	1715.5	1671.4	1685.2
30°	1648.1	1685.5	1643.7	1598.3	1604.0
32.5°	1568.1	1599.8	1559.0	1518.3	1522.9
35°	1423.2	1444.7	1411.4	1379.1	1382.0
37.5°	1246.8	1249.6	1227.0	1197.7	1198.2
40°	1105.6	1114.2	1089.4	1066.0	1068.9
42.5°	937.4	971.3	947.1	926.0	926.5
45°	641.0	728.7	729.2	703.6	611.6
47.5°	354.0	455.5	520.8	403.8	304.9
50°	223.5	288.2	392.6	236.1	207.3
52.5°	160.0	189.0	286.7	167.0	152.0
55°	94.1	107.0	147.0	101.3	95.6
57.5°	57.3	68.6	85.9	67.7	57.6
60°	39.7	49.8	64.7	45.3	35.3
62.5°	35.0	38.2	50.6	36.1	32.9
65°	30.9	32.3	32.3	29.4	27.9
67.5°	27.3	28.8	27.3	25.8	24.4
70°	25.0	26.4	25.0	23.5	22.1
72.5°	22.6	24.1	22.6	21.1	19.7
75°	19.1	19.1	19.1	17.6	16.2
77.5°	15.6	15.6	15.3	14.1	12.6
80°	13.2	13.2	11.8	11.7	10.3
82.5°	10.9	10.9	9.4	9.4	7.9
85°	7.4	7.4	5.9	5.8	4.4
87.5°	3.5	4.1	3.5	4.1	3.0
90°	0.0	2.9	5.9	8.9	8.9
92.5°	7.1	10.0	13.0	18.4	20.8
95°	23.7	44.0	23.7	26.8	32.6
97.5°	42.1	84.4	174.3	51.4	44.5
100°	56.3	105.6	349.8	103.0	68.2
102.5°	70.6	122.2	473.2	271.7	148.8
105°	91.9	141.2	536.6	685.5	453.6
107.5°	113.2	150.4	512.3	997.6	934.5
110°	127.5	162.3	498.1	1048.3	1126.6



TEST NUMBER: P645190

CATALOG NUMBER: OMN4DIP-SR4F0-75D75U930-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	176.5	483.8	1018.7	1150.3
115°	163.1	197.8	462.5	961.3	1123.6
117.5°	185.0	219.2	457.1	899.1	1066.1
120°	201.6	233.5	447.7	851.8	1025.8
122.5°	213.5	247.7	435.8	811.2	971.2
125°	234.2	266.1	435.8	762.1	901.2
127.5°	251.4	283.9	436.4	705.1	842.5
130°	260.9	295.7	438.8	667.0	797.5
132.5°	272.7	307.5	438.8	649.9	757.2
135°	290.5	322.4	438.8	627.6	720.4
137.5°	305.4	339.6	438.8	603.0	682.5
140°	317.2	349.1	438.8	588.6	661.1
142.5°	329.1	358.6	441.1	571.9	639.8
145°	343.9	372.9	441.7	546.8	604.8
147.5°	361.7	387.2	445.3	528.7	573.4
150°	373.5	396.7	447.7	516.7	554.4
152.5°	385.4	406.3	447.7	507.1	537.8
155°	403.2	417.7	450.6	495.6	518.8
157.5°	417.4	431.3	454.2	488.4	505.2
160°	426.9	438.5	456.6	483.6	498.1
162.5°	434.0	445.6	458.9	481.1	490.9
165°	447.7	453.5	462.5	474.5	483.2
167.5°	455.4	460.6	465.4	471.5	476.7
170°	462.5	465.4	465.4	471.4	474.3
172.5°	464.9	470.1	467.8	469.1	472.0
175°	471.4	474.3	471.4	468.3	465.4
177.5°	471.4	473.7	471.4	471.3	469.0
180°	471.4	471.4	471.4	471.4	471.4

(END OF REPORT)