

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644501

Luminaire Tested: OMN4DIP-SR4F0-100D100U935-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



**Test Information**

Test Method: LM-79-2019  
Report Number: P644501  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-100D100U935-BBMOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE  
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 1000 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1000 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7295.1 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18  
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 67.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P644501

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-BBMOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P644501

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-BBMOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				
1	101	97	94	91	93	90	88	85	78	76	74	66	65	64	55	55	54	49				
2	93	87	82	78	87	82	77	74	71	68	65	61	59	57	52	50	49	45				
3	87	79	73	68	81	74	69	64	65	61	57	56	53	51	48	46	44	41				
4	81	71	65	60	75	67	61	57	59	55	51	51	48	46	44	42	40	37				
5	75	65	58	53	70	61	55	50	54	49	46	47	44	41	41	39	37	34				
6	70	59	52	47	65	56	50	45	50	45	41	44	40	37	38	35	33	31				
7	65	54	47	42	61	51	45	40	46	41	37	40	37	34	35	33	31	28				
8	61	50	43	38	57	47	41	37	42	37	34	37	34	31	33	30	28	26				
9	57	46	39	34	53	43	37	33	39	34	31	35	31	28	31	28	26	24				
10	53	42	36	31	50	40	34	30	36	31	28	32	29	26	29	26	24	22				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	32686	32686	32686
5°	32248	32939	33451
10°	32802	33631	33994
15°	33706	34209	34261
20°	33861	34241	33670
25°	33080	33447	32714
30°	31320	31673	30759
35°	28470	28470	27879
40°	23416	23183	22684
45°	14002	16455	13351
50°	4525	9169	4248
55°	1601	3069	1601
60°	103	868	52
65°	61	61	0
70°	76	0	0
75°	0	0	0
80°	0	0	0
85°	296	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 16455 cd/sqm



TEST NUMBER: P644501

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-BBMOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	243.4	3.3
10°-20°	720.4	9.9
20°-30°	1066.0	14.6
30°-40°	1101.9	15.1
40°-50°	641.1	8.8
50°-60°	108.6	1.5
60°-70°	4.3	0.1
70°-80°	0.6	0.0
80°-90°	2.0	0.0
90°-100°	78.0	1.1
100°-110°	555.6	7.6
110°-120°	754.3	10.3
120°-130°	613.9	8.4
130°-140°	493.8	6.8
140°-150°	389.3	5.3
150°-160°	284.7	3.9
160°-170°	176.8	2.4
170°-180°	60.3	0.8
0°-30°	2029.9	27.8
0°-40°	3131.8	42.9
0°-60°	3881.5	53.2
0°-90°	3888.4	53.3
90°-120°	1387.9	19.0
90°-150°	2884.9	39.5
90°-180°	3407.0	46.7
0°-180°	7295.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2530	2530	2530	2530	2530	
5°	2487	2553	2540	2547	2580	238
15°	2521	2610	2558	2545	2562	709
25°	2321	2398	2347	2276	2295	1060
35°	1806	1834	1806	1760	1768	1106
45°	766	892	901	870	731	593
55°	71	83	136	77	71	78
65°	2	2	2	0	0	2
75°	0	2	0	0	0	1
85°	2	2	0	0	0	1
90°	0	4	8	12	12	2
95°	32	59	32	36	44	36
105°	124	190	722	922	610	130
115°	219	266	622	1293	1512	218
125°	315	358	586	1025	1212	280
135°	391	434	590	844	969	301
145°	463	502	594	736	814	291
155°	542	562	606	667	698	249
165°	602	610	622	638	650	169
175°	634	638	634	630	626	60
180°	634	634	634	634	634	



TEST NUMBER: P644501

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2530.5	2530.5	2530.5	2530.5	2530.5
2.5°	2497.3	2546.8	2528.9	2530.8	2543.2
5°	2487.1	2552.7	2540.4	2547.1	2579.9
7.5°	2494.6	2561.0	2559.4	2561.3	2593.3
10°	2500.9	2570.4	2564.1	2562.8	2591.8
12.5°	2513.5	2589.2	2564.1	2561.1	2585.4
15°	2520.6	2609.5	2558.2	2544.7	2562.1
17.5°	2496.5	2595.4	2525.8	2490.0	2496.9
20°	2463.4	2563.8	2491.0	2437.9	2449.5
22.5°	2411.2	2507.0	2442.0	2376.4	2391.1
25°	2321.1	2398.4	2346.8	2276.1	2295.4
27.5°	2193.1	2254.1	2221.6	2153.1	2165.1
30°	2099.9	2150.1	2123.6	2056.5	2062.3
32.5°	1992.4	2034.9	2006.6	1948.9	1948.6
35°	1805.5	1834.5	1805.5	1760.3	1768.0
37.5°	1561.0	1583.0	1553.5	1526.3	1530.2
40°	1388.7	1406.1	1374.9	1349.1	1345.3
42.5°	1173.8	1222.1	1191.6	1156.5	1161.9
45°	766.5	892.0	900.8	870.0	730.9
47.5°	386.4	523.5	627.0	475.8	341.0
50°	225.2	308.3	456.3	251.9	211.4
52.5°	147.8	182.9	318.8	159.2	140.3
55°	71.1	82.7	136.3	76.9	71.1
57.5°	24.5	37.6	60.4	38.5	27.3
60°	4.0	15.5	33.6	11.6	2.0
62.5°	2.4	4.7	20.9	2.3	0.4
65°	2.0	2.0	2.0	0.0	0.0
67.5°	2.0	2.0	0.0	0.0	0.0
70°	2.0	2.0	0.0	0.0	0.0
72.5°	2.0	2.0	0.0	0.0	0.0
75°	0.0	1.9	0.0	0.0	0.0
77.5°	0.0	1.9	0.0	0.0	0.0
80°	0.0	1.9	0.0	0.0	0.0
82.5°	0.0	1.9	0.0	0.0	0.0
85°	2.0	2.0	0.0	0.0	0.0
87.5°	1.6	2.4	1.6	2.4	2.4
90°	0.0	3.9	8.0	12.0	12.0
92.5°	9.6	13.5	17.5	24.8	27.9
95°	31.9	59.2	31.9	36.1	43.9
97.5°	56.6	113.6	234.5	69.2	59.8
100°	75.8	142.1	470.7	138.5	91.7
102.5°	94.9	164.3	636.6	365.6	200.2
105°	123.6	189.9	721.9	922.3	610.3
107.5°	152.4	202.3	689.2	1342.2	1257.2
110°	171.5	218.3	670.1	1410.4	1515.7

TEST NUMBER: P644501

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	190.7	237.5	650.9	1370.5	1547.6
115°	219.4	266.2	622.2	1293.3	1511.7
117.5°	248.9	294.9	615.0	1209.7	1434.3
120°	271.2	314.1	602.3	1146.1	1380.1
122.5°	287.2	333.2	586.3	1091.4	1306.7
125°	315.1	358.0	586.3	1025.3	1212.5
127.5°	338.2	381.9	587.1	948.7	1133.6
130°	351.0	397.8	590.3	897.4	1072.9
132.5°	367.0	413.8	590.3	874.4	1018.7
135°	390.9	433.8	590.3	844.4	969.2
137.5°	410.8	456.8	590.3	811.3	918.2
140°	426.8	469.7	590.3	792.0	889.5
142.5°	442.7	482.5	593.5	769.5	860.7
145°	462.7	501.7	594.3	735.7	813.7
147.5°	486.6	520.9	599.1	711.3	771.4
150°	502.6	533.8	602.3	695.2	745.9
152.5°	518.5	546.6	602.3	682.2	723.5
155°	542.5	562.0	606.3	666.8	698.0
157.5°	561.6	580.3	611.1	657.0	679.7
160°	574.4	590.0	614.2	650.6	670.1
162.5°	583.9	599.5	617.4	647.3	660.5
165°	602.3	610.1	622.2	638.4	650.1
167.5°	612.7	619.7	626.2	634.4	641.4
170°	622.2	626.1	626.2	634.3	638.2
172.5°	625.4	632.4	629.4	631.1	635.0
175°	634.2	638.1	634.2	630.1	626.2
177.5°	634.2	637.3	634.2	634.1	631.0
180°	634.2	634.2	634.2	634.2	634.2

(END OF REPORT)