

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645016

Luminaire Tested: OMN4DIP-SR4F0-50D75U935-WBMOOB-1DUDD-WW

Issue Date: 9/2/2020



**Test Information**

Test Method: LM-79-2019  
Report Number: P645016  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-50D75U935-WBMOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE  
DOWNLIGHT - WHITE BAFFLE WITH MEDIUM OPTIC - 500 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 750 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4701.2 lumens  
Efficiency: N/A  
Efficacy: 120.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.21 / 1.19  
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 39  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P645016

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U935-WBMOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P645016

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U935-WBMOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				45
1	98	95	91	88	90	87	84	82	73	71	70	60	59	58	48	48	47	41				41
2	91	85	79	75	84	78	74	70	66	63	60	55	53	51	45	43	42	38				38
3	84	76	70	65	77	70	65	61	60	56	53	50	48	45	41	40	38	34				34
4	78	68	62	56	72	64	58	53	54	50	47	46	43	40	38	36	34	31				31
5	72	62	55	50	66	58	51	47	50	45	41	42	39	36	35	33	31	28				28
6	67	56	49	44	62	53	46	42	45	41	37	39	35	33	33	30	28	25				25
7	62	51	44	39	58	48	42	37	42	37	33	36	32	30	30	28	26	23				23
8	58	47	40	35	54	44	38	33	38	34	30	33	29	27	28	26	24	21				21
9	54	43	36	32	50	41	34	30	35	31	27	31	27	24	26	24	22	20				20
10	51	40	33	29	47	37	32	27	33	28	25	29	25	22	24	22	20	18				18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17153	17153	17153
5°	17024	17258	17595
10°	17300	17641	17930
15°	17732	17972	18093
20°	17828	17993	17787
25°	17487	17530	17316
30°	16720	16675	16272
35°	15264	15138	14822
40°	12680	12494	12258
45°	7964	9060	7599
50°	3054	5365	2833
55°	1441	2252	1464
60°	698	1137	620
65°	642	672	581
70°	642	642	566
75°	649	649	549
80°	669	595	521
85°	741	593	445

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 9060 cd/sqm



TEST NUMBER: P645016

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U935-WBMOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.9	2.7
10°-20°	378.3	8.0
20°-30°	562.0	12.0
30°-40°	588.2	12.5
40°-50°	356.3	7.6
50°-60°	82.2	1.7
60°-70°	22.6	0.5
70°-80°	13.2	0.3
80°-90°	5.7	0.1
90°-100°	58.7	1.2
100°-110°	418.3	8.9
110°-120°	567.9	12.1
120°-130°	462.2	9.8
130°-140°	371.7	7.9
140°-150°	293.1	6.2
150°-160°	214.3	4.6
160°-170°	133.1	2.8
170°-180°	45.4	1.0
0°-30°	1068.3	22.7
0°-40°	1656.5	35.2
0°-60°	2095.0	44.6
0°-90°	2136.5	45.4
90°-120°	1044.9	22.2
90°-150°	2171.9	46.2
90°-180°	2565.0	54.6
0°-180°	4701.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1328	1328	1328	1328	1328	
5°	1313	1343	1331	1336	1357	126
15°	1326	1366	1344	1333	1353	373
25°	1227	1263	1230	1198	1215	562
35°	968	983	960	938	940	595
45°	436	496	496	479	416	335
55°	64	73	100	69	65	66
65°	21	22	22	20	19	21
75°	13	13	13	12	11	14
85°	5	5	4	4	3	5
90°	0	3	6	9	9	1
95°	24	45	24	27	33	27
105°	93	143	544	694	459	98
115°	165	200	468	974	1138	164
125°	237	270	441	772	913	211
135°	294	327	444	636	730	226
145°	348	378	447	554	613	219
155°	408	423	456	502	526	187
165°	453	459	468	481	490	127
175°	478	480	478	474	471	45
180°	478	478	478	478	478	

TEST NUMBER: P645016

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U935-WBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1328.0	1328.0	1328.0	1328.0	1328.0
2.5°	1315.2	1338.7	1325.6	1326.6	1337.6
5°	1313.0	1343.3	1331.0	1336.5	1357.0
7.5°	1316.6	1348.3	1341.0	1342.9	1365.4
10°	1319.0	1352.2	1345.0	1344.5	1367.0
12.5°	1324.6	1359.4	1345.8	1342.9	1364.6
15°	1326.0	1366.1	1344.0	1333.4	1353.0
17.5°	1313.0	1357.2	1327.4	1305.6	1321.2
20°	1297.0	1342.0	1309.0	1278.4	1294.0
22.5°	1272.2	1316.4	1281.0	1248.0	1264.4
25°	1227.0	1263.2	1230.0	1198.4	1215.0
27.5°	1169.8	1195.2	1166.8	1136.8	1146.2
30°	1121.0	1146.4	1118.0	1087.1	1091.0
32.5°	1066.6	1088.1	1060.4	1032.7	1035.8
35°	968.0	982.7	960.0	938.0	940.0
37.5°	848.0	850.0	834.6	814.6	815.0
40°	752.0	757.9	741.0	725.0	727.0
42.5°	637.6	660.7	644.2	629.8	630.2
45°	436.0	495.6	496.0	478.6	416.0
47.5°	240.8	309.8	354.2	274.7	207.4
50°	152.0	196.0	267.0	160.6	141.0
52.5°	108.8	128.6	195.0	113.6	103.4
55°	64.0	72.8	100.0	68.9	65.0
57.5°	39.0	46.6	58.4	46.0	39.2
60°	27.0	33.8	44.0	30.8	24.0
62.5°	23.8	26.0	34.4	24.6	22.4
65°	21.0	22.0	22.0	20.0	19.0
67.5°	18.6	19.6	18.6	17.6	16.6
70°	17.0	18.0	17.0	16.0	15.0
72.5°	15.4	16.4	15.4	14.4	13.4
75°	13.0	13.0	13.0	12.0	11.0
77.5°	10.6	10.6	10.4	9.6	8.6
80°	9.0	9.0	8.0	8.0	7.0
82.5°	7.4	7.4	6.4	6.4	5.4
85°	5.0	5.0	4.0	4.0	3.0
87.5°	2.4	3.0	2.8	3.4	2.6
90°	0.0	2.9	6.0	9.0	9.0
92.5°	7.2	10.1	13.2	18.7	21.0
95°	24.0	44.6	24.0	27.2	33.0
97.5°	42.6	85.5	176.6	52.1	45.0
100°	57.1	107.0	354.3	104.3	69.1
102.5°	71.5	123.7	479.3	275.2	150.7
105°	93.1	143.0	543.5	694.3	459.4
107.5°	114.7	152.3	518.9	1010.5	946.5
110°	129.1	164.4	504.5	1061.8	1141.1



TEST NUMBER: P645016

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U935-WBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	143.5	178.8	490.1	1031.8	1165.1
115°	165.2	200.4	468.4	973.7	1138.1
117.5°	187.4	222.0	463.0	910.7	1079.8
120°	204.2	236.5	453.4	862.8	1039.0
122.5°	216.2	250.9	441.4	821.7	983.7
125°	237.2	269.5	441.4	771.9	912.9
127.5°	254.6	287.5	442.0	714.2	853.4
130°	264.3	299.5	444.4	675.6	807.8
132.5°	276.3	311.5	444.4	658.3	766.9
135°	294.3	326.6	444.4	635.7	729.7
137.5°	309.3	343.9	444.4	610.8	691.3
140°	321.3	353.6	444.4	596.2	669.6
142.5°	333.3	363.3	446.8	579.3	648.0
145°	348.3	377.7	447.4	553.9	612.6
147.5°	366.3	392.2	451.0	535.5	580.8
150°	378.4	401.8	453.4	523.4	561.5
152.5°	390.4	411.5	453.4	513.6	544.7
155°	408.4	423.1	456.4	502.0	525.5
157.5°	422.8	436.9	460.0	494.7	511.7
160°	432.4	444.2	462.4	489.8	504.5
162.5°	439.6	451.4	464.8	487.3	497.3
165°	453.4	459.3	468.4	480.7	489.5
167.5°	461.2	466.5	471.4	477.6	482.9
170°	468.4	471.4	471.4	477.5	480.5
172.5°	470.8	476.1	473.8	475.1	478.1
175°	477.5	480.4	477.5	474.4	471.4
177.5°	477.5	479.8	477.5	477.4	475.1
180°	477.5	477.5	477.5	477.5	477.5

(END OF REPORT)