

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645101

Luminaire Tested: OMN4DIP-SR4F0-75D150U935-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



**Test Information**

Test Method: LM-79-2019  
Report Number: P645101  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-75D150U935-BBMOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE  
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 750 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7931.3 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18  
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 76.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P645101

CATALOG NUMBER: OMN4DIP-SR4F0-75D150U935-BBMOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P645101

CATALOG NUMBER: OMN4DIP-SR4F0-75D150U935-BBMOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				
1	96	93	89	86	87	84	82	79	69	67	65	54	53	52	41	41	40	34				
2	89	83	77	73	81	75	71	67	62	59	56	50	48	46	38	37	36	31				
3	82	74	68	63	75	68	63	58	56	52	49	45	43	41	35	34	33	28				
4	76	67	60	54	69	61	55	51	51	47	43	41	39	36	33	31	29	26				
5	70	60	53	48	64	55	49	45	46	42	38	38	35	33	30	28	27	23				
6	65	54	47	42	59	50	44	39	42	38	34	35	32	29	28	26	24	21				
7	61	50	42	37	55	46	40	35	39	34	31	32	29	26	26	24	22	20				
8	56	45	38	34	52	42	36	32	36	31	28	30	26	24	24	22	20	18				
9	53	42	35	30	48	39	33	28	33	28	25	28	24	22	22	20	19	17				
10	49	38	32	27	45	36	30	26	30	26	23	26	22	20	21	19	17	15				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24640	24640	24640
5°	24310	24831	25218
10°	24728	25353	25626
15°	25410	25789	25829
20°	25526	25813	25383
25°	24938	25213	24662
30°	23610	23877	23188
35°	21462	21462	21016
40°	17652	17477	17099
45°	10555	12405	10065
50°	3412	6913	3201
55°	1207	2315	1207
60°	78	654	39
65°	46	46	0
70°	57	0	0
75°	0	0	0
80°	0	0	0
85°	222	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 12405 cd/sqm



TEST NUMBER: P645101

CATALOG NUMBER: OMN4DIP-SR4F0-75D150U935-BBMOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.5	2.3
10°-20°	543.1	6.8
20°-30°	803.6	10.1
30°-40°	830.7	10.5
40°-50°	483.3	6.1
50°-60°	81.9	1.0
60°-70°	3.2	0.0
70°-80°	0.5	0.0
80°-90°	2.5	0.0
90°-100°	114.4	1.4
100°-110°	815.3	10.3
110°-120°	1106.9	14.0
120°-130°	900.9	11.4
130°-140°	724.6	9.1
140°-150°	571.2	7.2
150°-160°	417.7	5.3
160°-170°	259.4	3.3
170°-180°	88.5	1.1
0°-30°	1530.2	19.3
0°-40°	2360.9	29.8
0°-60°	2926.1	36.9
0°-90°	2932.3	37.0
90°-120°	2036.7	25.7
90°-150°	4233.4	53.4
90°-180°	4999.0	63.0
0°-180°	7931.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1908	1908	1908	1908	1908	
5°	1875	1924	1915	1920	1945	180
15°	1900	1967	1928	1918	1932	535
25°	1750	1808	1769	1716	1730	799
35°	1361	1383	1361	1327	1333	834
45°	578	672	679	656	551	447
55°	54	62	103	58	54	59
65°	2	2	2	0	0	2
75°	0	2	0	0	0	1
85°	2	2	0	0	0	1
90°	0	6	12	18	18	2
95°	47	87	47	53	64	52
105°	181	279	1059	1353	896	191
115°	322	391	913	1898	2218	320
125°	462	525	860	1505	1779	411
135°	574	636	866	1239	1422	441
145°	679	736	872	1080	1194	426
155°	796	825	890	978	1024	365
165°	884	895	913	937	954	248
175°	931	936	931	925	919	88
180°	931	931	931	931	931	



TEST NUMBER: P645101

CATALOG NUMBER: OMN4DIP-SR4F0-75D150U935-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1907.6	1907.6	1907.6	1907.6	1907.6
2.5°	1882.6	1919.9	1906.4	1907.8	1917.2
5°	1874.9	1924.4	1915.1	1920.1	1944.9
7.5°	1880.5	1930.6	1929.4	1930.8	1955.0
10°	1885.3	1937.7	1933.0	1932.0	1953.8
12.5°	1894.8	1951.9	1933.0	1930.7	1949.0
15°	1900.2	1967.2	1928.5	1918.4	1931.5
17.5°	1882.0	1956.6	1904.1	1877.1	1882.3
20°	1857.0	1932.7	1877.9	1837.8	1846.6
22.5°	1817.7	1889.9	1840.9	1791.4	1802.5
25°	1749.8	1808.0	1769.1	1715.9	1730.4
27.5°	1653.3	1699.3	1674.7	1623.1	1632.1
30°	1583.0	1620.9	1600.9	1550.3	1554.7
32.5°	1502.0	1534.0	1512.7	1469.2	1468.9
35°	1361.1	1382.9	1361.1	1327.0	1332.8
37.5°	1176.7	1193.3	1171.1	1150.6	1153.5
40°	1046.9	1060.0	1036.5	1017.0	1014.1
42.5°	884.9	921.3	898.3	871.9	875.9
45°	577.8	672.4	679.1	655.8	551.0
47.5°	291.3	394.7	472.7	358.7	257.0
50°	169.8	232.4	344.0	189.9	159.3
52.5°	111.4	137.9	240.4	120.0	105.7
55°	53.6	62.3	102.8	58.0	53.6
57.5°	18.5	28.4	45.6	29.0	20.6
60°	3.0	11.7	25.3	8.8	1.5
62.5°	1.8	3.5	15.8	1.8	0.3
65°	1.5	1.5	1.5	0.0	0.0
67.5°	1.5	1.5	0.0	0.0	0.0
70°	1.5	1.5	0.0	0.0	0.0
72.5°	1.5	1.5	0.0	0.0	0.0
75°	0.0	1.5	0.0	0.0	0.0
77.5°	0.0	1.5	0.0	0.0	0.0
80°	0.0	1.5	0.0	0.0	0.0
82.5°	0.0	1.5	0.0	0.0	0.0
85°	1.5	1.5	0.0	0.0	0.0
87.5°	1.2	2.3	2.3	3.5	3.5
90°	0.0	5.7	11.7	17.6	17.6
92.5°	14.0	19.8	25.8	36.4	41.0
95°	46.8	86.9	46.8	52.9	64.4
97.5°	83.1	166.7	344.2	101.5	87.8
100°	111.2	208.5	690.6	203.3	134.6
102.5°	139.3	241.2	934.1	536.5	293.8
105°	181.4	278.7	1059.4	1353.3	895.5
107.5°	223.6	296.8	1011.4	1969.6	1844.8
110°	251.7	320.4	983.3	2069.6	2224.1



TEST NUMBER: P645101

CATALOG NUMBER: OMN4DIP-SR4F0-75D150U935-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	279.8	348.4	955.2	2011.1	2270.9
115°	321.9	390.6	913.1	1897.8	2218.3
117.5°	365.2	432.8	902.5	1775.1	2104.7
120°	398.0	461.0	883.8	1681.7	2025.1
122.5°	421.4	488.9	860.4	1601.5	1917.4
125°	462.4	525.3	860.4	1504.6	1779.3
127.5°	496.3	560.4	861.6	1392.1	1663.4
130°	515.1	583.7	866.2	1316.9	1574.4
132.5°	538.5	607.1	866.2	1283.1	1494.8
135°	573.6	636.5	866.2	1239.1	1422.3
137.5°	602.9	670.4	866.2	1190.5	1347.3
140°	626.3	689.2	866.2	1162.1	1305.2
142.5°	649.7	708.0	870.9	1129.1	1263.1
145°	678.9	736.2	872.1	1079.5	1194.0
147.5°	714.1	764.4	879.1	1043.8	1132.0
150°	737.5	783.3	883.8	1020.1	1094.5
152.5°	760.9	802.1	883.8	1001.1	1061.7
155°	796.0	824.6	889.6	978.5	1024.3
157.5°	824.1	851.6	896.7	964.1	997.3
160°	842.8	865.7	901.4	954.7	983.3
162.5°	856.9	879.8	906.0	949.8	969.2
165°	883.8	895.2	913.1	936.9	954.0
167.5°	899.0	909.3	918.9	930.9	941.2
170°	913.1	918.8	918.9	930.7	936.5
172.5°	917.7	928.0	923.6	926.1	931.8
175°	930.6	936.3	930.6	924.6	918.9
177.5°	930.6	935.2	930.6	930.5	925.9
180°	930.6	930.6	930.6	930.6	930.6

(END OF REPORT)