

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645034

Luminaire Tested: OMN4DIP-SR4F0-75D100U840-FLLOOB-1DUDD-WW

Issue Date: 2/16/2023



**Test Information**

Test Method: LM-79-2019  
Report Number: P645034  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-75D100U840-FLLOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE  
DOWNLIGHT - FLAT FROSTED LENS - 750 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1000 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7191.1 lumens  
Efficiency: N/A  
Efficacy: 141.6 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.13 / 1.26  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 50.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P645034

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U840-FLLOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P645034

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U840-FLLOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	68	64	61	57	54	49	47	45	39	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	41	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	20	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20492	20492	20492
5°	20263	20404	20543
10°	20102	20185	20328
15°	19829	19829	19945
20°	19553	19405	19345
25°	19042	18889	18643
30°	18480	18222	17868
35°	17903	17461	17051
40°	17216	16706	16124
45°	16639	16009	15221
50°	15918	15224	14443
55°	15313	14534	13658
60°	14609	13831	12658
65°	13853	12863	11874
70°	13124	11901	11084
75°	12283	10880	10343
80°	11241	9958	9475
85°	10559	9281	8633

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16639 cd/sqm



TEST NUMBER: P645034

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U840-FLLOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.4	1.7
10°-20°	335.0	4.7
20°-30°	487.2	6.8
30°-40°	554.2	7.7
40°-50°	540.3	7.5
50°-60°	461.2	6.4
60°-70°	335.2	4.7
70°-80°	189.5	2.6
80°-90°	60.1	0.8
90°-100°	101.1	1.4
100°-110°	671.7	9.3
110°-120°	908.9	12.6
120°-130°	739.2	10.3
130°-140°	593.5	8.3
140°-150°	467.8	6.5
150°-160°	342.0	4.8
160°-170°	212.4	3.0
170°-180°	72.4	1.0
0°-30°	941.6	13.1
0°-40°	1495.7	20.8
0°-60°	2497.3	34.7
0°-90°	3082.0	42.9
90°-120°	1681.7	23.4
90°-150°	3482.2	48.4
90°-180°	4109.0	57.1
0°-180°	7191.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1250	1269	1259	1257	1268	119
15°	1186	1202	1186	1185	1193	334
25°	1069	1079	1060	1041	1046	492
35°	908	912	886	865	865	567
45°	729	725	701	677	667	561
55°	544	542	516	492	485	485
65°	363	359	337	316	311	360
75°	197	190	174	168	166	209
85°	57	50	50	48	47	61
90°	7	13	20	23	23	9
95°	52	78	44	48	56	53
105°	157	234	871	1110	733	167
115°	269	323	749	1554	1816	267
125°	382	434	706	1232	1457	339
135°	470	521	709	1015	1165	362
145°	556	603	714	884	978	349
155°	652	675	728	801	839	299
165°	724	733	748	767	781	203
175°	762	767	762	757	752	72
180°	762	762	762	762	762	



TEST NUMBER: P645034

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U840-FLLOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1269.2	1269.2	1269.2	1269.2	1269.2
2.5°	1258.2	1274.4	1265.1	1265.2	1270.6
5°	1250.2	1268.8	1258.9	1257.4	1267.5
7.5°	1237.1	1255.3	1243.7	1241.9	1255.1
10°	1226.1	1242.9	1231.2	1228.0	1239.9
12.5°	1210.9	1227.7	1216.0	1211.5	1223.3
15°	1186.3	1201.5	1186.3	1184.8	1193.2
17.5°	1158.7	1171.9	1154.2	1148.5	1154.9
20°	1138.0	1149.8	1129.4	1120.8	1125.9
22.5°	1111.7	1123.6	1101.7	1089.1	1095.5
25°	1068.9	1079.0	1060.3	1041.4	1046.5
27.5°	1023.0	1030.7	1011.9	992.6	994.3
30°	991.2	996.3	977.4	956.7	958.4
32.5°	958.0	961.8	941.5	919.4	919.7
35°	908.3	911.7	885.9	865.1	865.1
37.5°	855.5	857.5	829.9	807.4	805.1
40°	816.8	820.2	792.6	770.1	765.0
42.5°	780.9	781.6	756.7	734.1	727.7
45°	728.7	725.3	701.1	676.7	666.6
47.5°	672.4	672.4	644.8	620.4	611.0
50°	633.7	633.7	606.1	581.8	575.0
52.5°	597.8	596.5	570.2	545.8	536.4
55°	544.0	542.3	516.3	492.0	485.2
57.5°	487.0	487.0	462.8	436.7	429.3
60°	452.4	452.4	428.3	402.1	392.0
62.5°	415.1	413.8	389.6	366.3	360.2
65°	362.6	359.3	336.7	315.9	310.8
67.5°	312.6	309.2	285.3	268.6	265.2
70°	278.0	274.6	252.1	238.2	234.8
72.5°	244.9	240.1	220.3	209.2	205.8
75°	196.9	190.1	174.4	167.5	165.8
77.5°	151.3	139.8	133.3	128.4	126.7
80°	120.9	110.7	107.1	103.6	101.9
82.5°	94.6	84.5	83.6	81.5	79.8
85°	57.0	50.2	50.1	48.3	46.6
87.5°	24.9	22.1	23.3	23.9	23.9
90°	6.9	13.3	19.9	23.0	23.0
92.5°	23.9	24.9	28.7	37.0	39.4
95°	52.2	78.2	43.5	48.5	56.2
97.5°	80.1	143.5	286.7	86.2	73.6
100°	103.2	177.8	569.0	168.2	112.0
102.5°	124.8	203.1	768.4	441.0	240.9
105°	157.2	233.5	870.9	1109.9	733.3
107.5°	191.4	248.3	831.6	1614.5	1510.7
110°	213.0	267.5	808.6	1696.4	1821.3



TEST NUMBER: P645034

CATALOG NUMBER: OMN4DIP-SR4F0-75D100U840-FLLOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	236.0	290.5	785.6	1648.5	1859.6
115°	268.8	323.3	749.4	1554.0	1816.5
117.5°	304.2	357.9	740.8	1453.6	1723.5
120°	331.1	380.9	725.4	1377.1	1658.3
122.5°	348.9	403.8	706.3	1311.4	1570.1
125°	382.1	433.6	706.3	1232.1	1457.0
127.5°	408.2	462.0	707.2	1140.0	1362.1
130°	423.5	479.7	711.1	1078.4	1289.3
132.5°	441.3	497.5	709.7	1050.7	1224.1
135°	469.7	521.2	709.3	1014.7	1164.6
137.5°	493.7	549.0	709.3	974.9	1103.3
140°	512.8	564.4	709.3	951.6	1068.8
142.5°	532.0	579.8	713.2	924.6	1034.3
145°	556.0	602.8	714.1	884.0	977.7
147.5°	584.7	626.0	719.9	854.8	926.9
150°	603.9	641.4	723.7	835.3	896.2
152.5°	623.1	656.8	723.7	819.7	869.4
155°	651.8	675.2	728.5	801.2	838.7
157.5°	674.8	697.3	734.3	789.5	816.7
160°	690.2	708.9	738.1	781.8	805.2
162.5°	701.7	720.4	741.9	777.7	793.7
165°	723.7	733.1	747.7	767.2	781.2
167.5°	736.2	744.6	752.5	762.2	770.7
170°	747.7	752.4	752.5	762.2	766.8
172.5°	751.5	759.9	756.3	758.3	763.0
175°	762.1	766.7	762.1	757.2	752.5
177.5°	762.1	765.8	762.1	762.0	758.2
180°	762.1	762.1	762.1	762.1	762.1

(END OF REPORT)