

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644512

Luminaire Tested: OMN4DIP-SR4F0-100D100U940-WBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P644512
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-27)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-100D100U940-WBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - WHITE BAFFLE WITH MEDIUM OPTIC - 1000 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7841.8 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.21 / 1.19
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 67.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644512

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-WBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644512

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-WBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	101	97	94	91	94	91	88	86	79	77	75	67	66	65	57	56	55	51				
2	94	87	82	78	87	82	77	74	71	68	65	62	59	57	53	51	50	46				
3	87	79	73	68	81	74	69	64	65	61	58	57	54	51	49	47	45	41				
4	81	71	64	59	75	67	61	57	59	55	51	52	49	46	45	43	41	37				
5	75	65	58	52	70	61	55	50	54	49	46	48	44	41	42	39	37	34				
6	70	59	52	47	65	56	49	45	50	45	41	44	40	37	39	36	34	31				
7	65	54	47	42	61	51	45	40	46	41	37	41	37	34	36	33	31	28				
8	61	50	43	38	57	47	41	36	42	37	34	38	34	31	33	30	28	26				
9	57	46	39	34	53	43	37	33	39	34	31	35	31	28	31	28	26	24				
10	53	42	36	31	50	40	34	30	36	31	28	33	29	26	29	26	24	22				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	34842	34842	34842
5°	34580	35054	35738
10°	35140	35833	36419
15°	36017	36505	36750
20°	36213	36547	36129
25°	35520	35607	35173
30°	33961	33870	33052
35°	31004	30748	30107
40°	25756	25378	24899
45°	16177	18404	15436
50°	6203	10897	5755
55°	2928	4574	2973
60°	1416	2310	1258
65°	1305	1366	1180
70°	1303	1303	1152
75°	1318	1318	1113
80°	1361	1205	1056
85°	1512	1200	904

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 18404 cd/sqm



TEST NUMBER: P644512

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-WBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.8	3.3
10°-20°	768.5	9.8
20°-30°	1141.6	14.6
30°-40°	1194.8	15.2
40°-50°	723.7	9.2
50°-60°	167.0	2.1
60°-70°	45.9	0.6
70°-80°	26.9	0.3
80°-90°	10.8	0.1
90°-100°	80.2	1.0
100°-110°	571.3	7.3
110°-120°	775.6	9.9
120°-130°	631.3	8.1
130°-140°	507.7	6.5
140°-150°	400.3	5.1
150°-160°	292.7	3.7
160°-170°	181.8	2.3
170°-180°	62.0	0.8
0°-30°	2169.9	27.7
0°-40°	3364.7	42.9
0°-60°	4255.4	54.3
0°-90°	4338.9	55.3
90°-120°	1427.1	18.2
90°-150°	2966.4	37.8
90°-180°	3503.0	44.7
0°-180°	7841.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2697	2697	2697	2697	2697	
5°	2667	2728	2704	2715	2756	255
15°	2693	2775	2730	2708	2748	758
25°	2492	2566	2498	2434	2468	1141
35°	1966	1996	1950	1905	1909	1208
45°	886	1007	1008	972	845	680
55°	130	148	203	140	132	135
65°	43	45	45	41	39	43
75°	26	26	26	24	22	28
85°	10	10	8	8	6	10
90°	0	4	8	12	12	2
95°	33	61	33	37	45	37
105°	127	195	742	948	628	134
115°	226	274	640	1330	1554	224
125°	324	368	603	1054	1247	288
135°	402	446	607	868	997	309
145°	476	516	611	756	837	299
155°	558	578	623	686	718	256
165°	619	627	640	656	668	174
175°	652	656	652	648	644	62
180°	652	652	652	652	652	



TEST NUMBER: P644512

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2697.4	2697.4	2697.4	2697.4	2697.4
2.5°	2671.4	2719.1	2692.6	2694.7	2716.9
5°	2667.0	2728.5	2703.5	2714.6	2756.3
7.5°	2674.3	2738.6	2723.8	2727.7	2773.4
10°	2679.2	2746.7	2732.0	2731.0	2776.7
12.5°	2690.5	2761.2	2733.6	2727.7	2771.8
15°	2693.4	2774.8	2729.9	2708.5	2748.2
17.5°	2667.0	2756.7	2696.2	2651.8	2683.6
20°	2634.5	2725.8	2658.8	2596.6	2628.4
22.5°	2584.1	2673.9	2602.0	2534.9	2568.3
25°	2492.3	2565.8	2498.4	2434.1	2467.9
27.5°	2376.1	2427.7	2370.0	2309.1	2328.2
30°	2277.0	2328.6	2270.9	2208.1	2216.0
32.5°	2166.5	2210.2	2153.9	2097.6	2103.9
35°	1966.2	1996.0	1950.0	1905.4	1909.3
37.5°	1722.5	1726.4	1695.2	1654.6	1655.4
40°	1527.5	1539.4	1505.1	1472.7	1476.7
42.5°	1295.1	1342.0	1308.5	1279.3	1280.1
45°	885.6	1006.8	1007.5	972.1	845.0
47.5°	489.1	629.3	719.5	557.9	421.3
50°	308.7	398.1	542.3	326.1	286.4
52.5°	221.0	261.1	396.1	230.7	210.0
55°	130.0	147.9	203.1	140.0	132.0
57.5°	79.2	94.7	118.6	93.5	79.6
60°	54.8	68.7	89.4	62.7	48.7
62.5°	48.3	52.7	69.9	49.9	45.5
65°	42.7	44.6	44.7	40.6	38.6
67.5°	37.8	39.8	37.8	35.7	33.7
70°	34.5	36.5	34.5	32.5	30.5
72.5°	31.3	33.3	31.3	29.2	27.2
75°	26.4	26.4	26.4	24.3	22.3
77.5°	21.5	21.5	21.1	19.5	17.5
80°	18.3	18.3	16.2	16.2	14.2
82.5°	15.0	15.0	13.0	13.0	11.0
85°	10.2	10.2	8.1	8.1	6.1
87.5°	4.9	5.7	4.9	5.7	4.1
90°	0.0	4.0	8.2	12.3	12.3
92.5°	9.8	13.9	18.0	25.5	28.7
95°	32.8	60.9	32.8	37.1	45.1
97.5°	58.2	116.8	241.2	71.1	61.5
100°	77.9	146.1	483.9	142.5	94.3
102.5°	97.6	169.0	654.6	375.9	205.9
105°	127.1	195.3	742.3	948.3	627.5
107.5°	156.7	208.0	708.7	1380.1	1292.7
110°	176.4	224.5	689.0	1450.2	1558.5



TEST NUMBER: P644512

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U940-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	196.0	244.2	669.3	1409.2	1591.3
115°	225.6	273.7	639.8	1329.8	1554.4
117.5°	255.9	303.2	632.4	1243.8	1474.8
120°	278.9	323.0	619.3	1178.4	1419.0
122.5°	295.3	342.6	602.9	1122.2	1343.6
125°	324.0	368.1	602.9	1054.3	1246.8
127.5°	347.8	392.7	603.7	975.5	1165.6
130°	360.9	409.0	607.0	922.8	1103.2
132.5°	377.3	425.4	607.0	899.1	1047.5
135°	401.9	446.0	607.0	868.3	996.6
137.5°	422.4	469.7	607.0	834.2	944.1
140°	438.8	482.9	607.0	814.3	914.6
142.5°	455.2	496.1	610.3	791.2	885.1
145°	475.7	515.8	611.1	756.5	836.7
147.5°	500.4	535.6	616.0	731.4	793.2
150°	516.8	548.8	619.3	714.8	766.9
152.5°	533.2	562.0	619.3	701.5	744.0
155°	557.8	577.8	623.4	685.6	717.7
157.5°	577.5	596.7	628.3	675.6	698.9
160°	590.6	606.6	631.6	669.0	689.0
162.5°	600.4	616.5	634.9	665.5	679.2
165°	619.3	627.3	639.8	656.5	668.5
167.5°	630.0	637.2	643.9	652.3	659.5
170°	639.8	643.8	643.9	652.2	656.2
172.5°	643.1	650.3	647.2	648.9	652.9
175°	652.1	656.1	652.1	647.9	643.9
177.5°	652.1	655.3	652.1	652.0	648.8
180°	652.1	652.1	652.1	652.1	652.1

(END OF REPORT)