

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645142

Luminaire Tested: OMN4DIP-SR4F0-75D25U940-WBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P645142
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-27)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-75D25U940-WBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - WHITE BAFFLE WITH MEDIUM OPTIC - 750 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4174.1 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.21 / 1.19
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P645142

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-WBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P645142

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-WBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	82	82	82	78	
1	107	103	100	98	102	99	97	94	91	89	87	84	82	81	77	76	75	75	75	75	72	
2	100	94	89	85	95	90	86	82	83	80	77	77	75	72	71	69	68	68	68	68	65	
3	93	85	79	75	89	82	77	73	76	72	69	71	68	65	66	63	61	61	61	61	59	
4	87	78	71	66	83	75	69	65	70	65	61	66	62	58	61	58	56	56	56	56	53	
5	81	71	64	59	78	69	63	58	65	59	55	60	56	53	57	53	50	50	50	50	48	
6	76	65	58	53	73	63	57	52	59	54	50	56	51	48	53	49	46	46	46	46	44	
7	71	60	53	48	68	58	52	47	55	49	45	52	47	44	49	45	42	42	42	42	40	
8	67	55	48	44	64	54	47	43	51	45	41	48	43	40	46	42	39	39	39	39	37	
9	63	51	45	40	60	50	44	39	47	42	38	45	40	37	43	38	36	36	36	36	34	
10	59	48	41	37	57	46	40	36	44	39	35	42	37	34	40	36	33	33	33	33	31	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26266	26266	26266
5°	26068	26426	26942
10°	26490	27012	27454
15°	27151	27520	27705
20°	27299	27552	27236
25°	26777	26842	26514
30°	25601	25533	24917
35°	23372	23180	22697
40°	19416	19131	18770
45°	12195	13874	11636
50°	4676	8215	4338
55°	2207	3448	2241
60°	1067	1741	948
65°	984	1030	889
70°	982	982	869
75°	993	993	838
80°	1027	907	796
85°	1141	904	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 13874 cd/sqm



TEST NUMBER: P645142

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-WBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	4.7
10°-20°	579.3	13.9
20°-30°	860.6	20.6
30°-40°	900.7	21.6
40°-50°	545.6	13.1
50°-60°	125.9	3.0
60°-70°	34.6	0.8
70°-80°	20.3	0.5
80°-90°	7.4	0.2
90°-100°	20.7	0.5
100°-110°	147.4	3.5
110°-120°	200.2	4.8
120°-130°	162.9	3.9
130°-140°	131.0	3.1
140°-150°	103.3	2.5
150°-160°	75.5	1.8
160°-170°	46.9	1.1
170°-180°	16.0	0.4
0°-30°	1635.8	39.2
0°-40°	2536.5	60.8
0°-60°	3207.9	76.9
0°-90°	3270.2	78.3
90°-120°	368.3	8.8
90°-150°	765.5	18.3
90°-180°	904.0	21.7
0°-180°	4174.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2034	2034	2034	2034	2034	
5°	2010	2057	2038	2046	2078	192
15°	2030	2092	2058	2042	2072	572
25°	1879	1934	1883	1835	1860	860
35°	1482	1505	1470	1436	1439	911
45°	668	759	760	733	637	513
55°	98	112	153	106	100	102
65°	32	34	34	31	29	32
75°	20	20	20	18	17	21
85°	8	8	6	6	5	8
90°	0	1	2	3	3	1
95°	8	16	8	10	12	9
105°	33	50	192	245	162	35
115°	58	71	165	343	401	58
125°	84	95	156	272	322	74
135°	104	115	157	224	257	80
145°	123	133	158	195	216	77
155°	144	149	161	177	185	66
165°	160	162	165	169	172	45
175°	168	169	168	167	166	16
180°	168	168	168	168	168	



TEST NUMBER: P645142

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2033.5	2033.5	2033.5	2033.5	2033.5
2.5°	2013.9	2049.8	2029.8	2031.4	2048.2
5°	2010.5	2056.9	2038.1	2046.4	2077.9
7.5°	2016.0	2064.5	2053.4	2056.3	2090.7
10°	2019.7	2070.6	2059.5	2058.8	2093.2
12.5°	2028.3	2081.6	2060.7	2056.3	2089.5
15°	2030.4	2091.8	2058.0	2041.8	2071.8
17.5°	2010.5	2078.2	2032.6	1999.1	2023.1
20°	1986.0	2054.9	2004.4	1957.5	1981.4
22.5°	1948.0	2015.7	1961.5	1910.9	1936.1
25°	1878.8	1934.2	1883.4	1835.0	1860.4
27.5°	1791.2	1830.2	1786.6	1740.7	1755.1
30°	1716.5	1755.4	1711.9	1664.6	1670.6
32.5°	1633.2	1666.1	1623.7	1581.3	1586.0
35°	1482.2	1504.7	1470.0	1436.4	1439.4
37.5°	1298.5	1301.5	1278.0	1247.4	1248.0
40°	1151.5	1160.5	1134.6	1110.2	1113.2
42.5°	976.3	1011.6	986.4	964.4	965.0
45°	667.6	758.9	759.5	732.8	637.0
47.5°	368.7	474.4	542.4	420.6	317.6
50°	232.7	300.1	408.8	245.8	215.9
52.5°	166.6	196.8	298.6	173.9	158.3
55°	98.0	111.5	153.1	105.5	99.5
57.5°	59.7	71.4	89.4	70.5	60.0
60°	41.3	51.8	67.4	47.2	36.7
62.5°	36.4	39.7	52.7	37.6	34.3
65°	32.2	33.7	33.7	30.6	29.1
67.5°	28.5	30.0	28.5	26.9	25.4
70°	26.0	27.5	26.0	24.5	23.0
72.5°	23.6	25.1	23.6	22.0	20.5
75°	19.9	19.9	19.9	18.3	16.8
77.5°	16.2	16.2	15.9	14.7	13.2
80°	13.8	13.8	12.2	12.2	10.7
82.5°	11.3	11.3	9.8	9.8	8.3
85°	7.7	7.7	6.1	6.1	4.6
87.5°	3.7	3.9	2.9	3.1	1.9
90°	0.0	1.0	2.1	3.2	3.2
92.5°	2.5	3.6	4.7	6.6	7.4
95°	8.5	15.7	8.5	9.6	11.6
97.5°	15.0	30.1	62.2	18.4	15.9
100°	20.1	37.7	124.9	36.8	24.3
102.5°	25.2	43.6	168.9	97.0	53.1
105°	32.8	50.4	191.6	244.7	161.9
107.5°	40.4	53.7	182.9	356.2	333.6
110°	45.5	57.9	177.8	374.3	402.2



TEST NUMBER: P645142

CATALOG NUMBER: OMN4DIP-SR4F0-75D25U940-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	50.6	63.0	172.7	363.7	410.7
115°	58.2	70.6	165.1	343.2	401.1
117.5°	66.0	78.3	163.2	321.0	380.6
120°	72.0	83.4	159.8	304.1	366.2
122.5°	76.2	88.4	155.6	289.6	346.7
125°	83.6	95.0	155.6	272.1	321.8
127.5°	89.8	101.3	155.8	251.7	300.8
130°	93.1	105.6	156.6	238.1	284.7
132.5°	97.4	109.8	156.6	232.0	270.3
135°	103.7	115.1	156.6	224.1	257.2
137.5°	109.0	121.2	156.6	215.3	243.6
140°	113.2	124.6	156.6	210.2	236.0
142.5°	117.5	128.0	157.5	204.2	228.4
145°	122.8	133.1	157.7	195.2	215.9
147.5°	129.1	138.2	159.0	188.8	204.7
150°	133.4	141.6	159.8	184.5	197.9
152.5°	137.6	145.0	159.8	181.0	192.0
155°	143.9	149.1	160.9	176.9	185.2
157.5°	149.0	154.0	162.1	174.3	180.4
160°	152.4	156.5	163.0	172.6	177.8
162.5°	155.0	159.1	163.8	171.8	175.3
165°	159.8	161.9	165.1	169.4	172.5
167.5°	162.6	164.4	166.2	168.3	170.2
170°	165.1	166.1	166.2	168.3	169.3
172.5°	166.0	167.8	167.0	167.5	168.5
175°	168.3	169.3	168.3	167.2	166.2
177.5°	168.3	169.1	168.3	168.3	167.4
180°	168.3	168.3	168.3	168.3	168.3

(END OF REPORT)