

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645235

Luminaire Tested: OMN4DP-SR4F0-125D940-BBM-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P645235
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-689-23)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DP-SR4F0-125D940-BBM-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5056.3 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 49.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P645235
CATALOG NUMBER: OMN4DP-SR4F0-125D940-BBM-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P645235

CATALOG NUMBER: OMN4DP-SR4F0-125D940-BBM-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	103	102	100	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84				84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58				58
7	78	67	60	56	76	66	60	55	65	59	55	64	59	55	63	58	54	53				53
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	49				49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45				45
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41				41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	42519	42519	42519
5°	41949	42848	43514
10°	42669	43748	44219
15°	43847	44501	44569
20°	44047	44542	43799
25°	43033	43509	42557
30°	40742	41201	40014
35°	37035	37035	36266
40°	30460	30157	29508
45°	18212	21405	17368
50°	5886	11928	5526
55°	2083	3993	2083
60°	132	1129	67
65°	79	79	0
70°	98	0	0
75°	0	0	0
80°	0	0	0
85°	385	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 21405 cd/sqm



TEST NUMBER: P645235

CATALOG NUMBER: OMN4DP-SR4F0-125D940-BBM-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	316.7	6.3
10°-20°	937.1	18.5
20°-30°	1386.8	27.4
30°-40°	1433.4	28.3
40°-50°	834.0	16.5
50°-60°	141.3	2.8
60°-70°	5.6	0.1
70°-80°	0.8	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2640.5	52.2
0°-40°	4073.9	80.6
0°-60°	5049.2	99.9
0°-90°	5056.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5056.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3292	3292	3292	3292	3292	
5°	3235	3321	3305	3313	3356	310
15°	3279	3394	3328	3310	3333	922
25°	3019	3120	3053	2961	2986	1379
35°	2349	2386	2349	2290	2300	1439
45°	997	1160	1172	1132	951	771
55°	92	108	177	100	92	102
65°	3	3	3	0	0	3
75°	0	2	0	0	0	1
85°	3	3	0	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P645235

CATALOG NUMBER: OMN4DP-SR4F0-125D940-BBM-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3291.8	3291.8	3291.8	3291.8	3291.8
2.5°	3248.6	3312.9	3289.7	3292.2	3308.2
5°	3235.3	3320.7	3304.6	3313.3	3356.0
7.5°	3245.0	3331.5	3329.3	3331.8	3373.5
10°	3253.2	3343.7	3335.5	3333.8	3371.4
12.5°	3269.7	3368.2	3335.5	3331.6	3363.2
15°	3278.9	3394.5	3327.8	3310.3	3332.9
17.5°	3247.6	3376.2	3285.6	3239.1	3248.1
20°	3204.4	3335.1	3240.4	3171.4	3186.4
22.5°	3136.6	3261.2	3176.7	3091.3	3110.4
25°	3019.4	3119.9	3052.8	2960.9	2986.0
27.5°	2852.9	2932.3	2889.9	2800.8	2816.4
30°	2731.6	2796.9	2762.4	2675.2	2682.8
32.5°	2591.8	2647.1	2610.3	2535.3	2534.8
35°	2348.7	2386.4	2348.7	2289.8	2299.9
37.5°	2030.6	2059.2	2020.8	1985.5	1990.5
40°	1806.5	1829.1	1788.5	1755.0	1750.0
42.5°	1526.9	1589.7	1550.0	1504.5	1511.5
45°	997.0	1160.4	1171.8	1131.7	950.8
47.5°	502.6	681.0	815.6	618.9	443.5
50°	292.9	401.0	593.6	327.7	275.0
52.5°	192.2	237.9	414.7	207.1	182.4
55°	92.5	107.6	177.3	100.0	92.5
57.5°	31.9	48.9	78.6	50.0	35.5
60°	5.1	20.2	43.7	15.1	2.6
62.5°	3.1	6.1	27.2	3.0	0.5
65°	2.6	2.6	2.6	0.0	0.0
67.5°	2.6	2.6	0.0	0.0	0.0
70°	2.6	2.6	0.0	0.0	0.0
72.5°	2.6	2.6	0.0	0.0	0.0
75°	0.0	2.5	0.0	0.0	0.0
77.5°	0.0	2.5	0.0	0.0	0.0
80°	0.0	2.5	0.0	0.0	0.0
82.5°	0.0	2.5	0.0	0.0	0.0
85°	2.6	2.6	0.0	0.0	0.0
87.5°	2.1	2.1	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)