

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645255

Luminaire Tested: OMN4DP-SR4F0-50D940-FLL-1DUDD-WW

Issue Date: 2/16/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P645255  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-689-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DP-SR4F0-50D940-FLL-1DUDD-WW  
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE  
DOWNLIGHT - FLAT FROSTED LENS - 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1875.0 lumens  
Efficiency: N/A  
Efficacy: 131.1 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.13 / 1.26  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P645255  
CATALOG NUMBER: OMN4DP-SR4F0-50D940-FLL-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P645255

CATALOG NUMBER: OMN4DP-SR4F0-50D940-FLL-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	99																				
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84																				
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71																				
3	91	81	73	67	89	79	72	66	76	70	65	73	68	63	71	66	62	60																				
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	63	58	54	52																				
5	77	65	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45																				
6	71	58	50	43	69	57	49	43	55	48	43	54	47	42	52	46	42	40																				
7	66	53	44	38	65	52	44	38	51	43	38	49	43	38	48	42	37	35																				
8	62	49	40	34	60	48	40	34	46	39	34	45	39	34	44	38	34	32																				
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29																				
10	54	41	34	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12411	12411	12411
5°	12272	12357	12443
10°	12175	12226	12311
15°	12010	12010	12080
20°	11842	11753	11716
25°	11533	11441	11291
30°	11192	11037	10821
35°	10843	10575	10328
40°	10427	10117	9765
45°	10076	9695	9218
50°	9640	9221	8749
55°	9272	8802	8273
60°	8848	8376	7666
65°	8390	7790	7194
70°	7950	7209	6713
75°	7436	6588	6263
80°	6806	6025	5737
85°	6391	5613	5224

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10076 cd/sqm



TEST NUMBER: P645255

CATALOG NUMBER: OMN4DP-SR4F0-50D940-FLL-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.3	3.9
10°-20°	202.9	10.8
20°-30°	295.1	15.7
30°-40°	335.6	17.9
40°-50°	327.2	17.5
50°-60°	279.3	14.9
60°-70°	203.0	10.8
70°-80°	114.8	6.1
80°-90°	35.3	1.9
90°-100°	4.5	0.2
100°-110°	2.5	0.1
110°-120°	1.5	0.1
120°-130°	0.9	0.0
130°-140°	0.1	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	570.3	30.4
0°-40°	905.9	48.3
0°-60°	1512.4	80.7
0°-90°	1865.6	99.5
90°-120°	8.5	0.5
90°-150°	9.4	0.5
90°-180°	9.0	0.5
0°-180°	1875.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	757	768	762	762	768	72
15°	718	728	718	718	723	203
25°	647	654	642	631	634	298
35°	550	552	536	524	524	343
45°	441	439	425	410	404	340
55°	329	328	313	298	294	294
65°	220	218	204	191	188	218
75°	119	115	106	101	100	127
85°	34	30	30	29	28	37
90°	4	5	6	5	5	4
95°	8	4	3	3	2	6
105°	5	3	2	1	0	6
115°	3	2	1	0	0	3
125°	2	2	1	0	0	2
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P645255

CATALOG NUMBER: OMN4DP-SR4F0-50D940-FLL-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	768.7	768.7	768.7	768.7	768.7
2.5°	762.0	771.8	766.2	766.3	769.5
5°	757.2	768.4	762.4	761.5	767.7
7.5°	749.2	760.3	753.2	752.1	760.1
10°	742.6	752.8	745.7	743.8	750.9
12.5°	733.4	743.6	736.5	733.7	740.9
15°	718.5	727.7	718.5	717.6	722.7
17.5°	701.8	709.7	699.0	695.6	699.5
20°	689.2	696.4	684.0	678.8	681.9
22.5°	673.3	680.5	667.3	659.6	663.5
25°	647.4	653.5	642.2	630.7	633.8
27.5°	619.6	624.3	612.9	601.2	602.2
30°	600.3	603.4	592.0	579.4	580.4
32.5°	580.2	582.5	570.2	556.8	557.0
35°	550.1	552.2	536.5	524.0	524.0
37.5°	518.1	519.3	502.6	489.0	487.6
40°	494.7	496.7	480.0	466.4	463.3
42.5°	472.9	473.3	458.3	444.6	440.7
45°	441.3	439.3	424.6	409.8	403.7
47.5°	407.3	407.3	390.5	375.7	370.0
50°	383.8	383.8	367.1	352.4	348.3
52.5°	362.1	361.3	345.3	330.6	324.8
55°	329.4	328.4	312.7	298.0	293.9
57.5°	294.9	294.9	280.3	264.5	260.0
60°	274.0	274.0	259.4	243.5	237.4
62.5°	251.4	250.6	235.9	221.8	218.2
65°	219.6	217.6	203.9	191.3	188.3
67.5°	189.3	187.3	172.8	162.7	160.6
70°	168.4	166.3	152.7	144.3	142.2
72.5°	148.3	145.4	133.5	126.7	124.7
75°	119.2	115.1	105.6	101.4	100.4
77.5°	91.6	84.7	80.7	77.8	76.8
80°	73.2	67.1	64.8	62.7	61.7
82.5°	57.3	51.2	50.6	49.3	48.3
85°	34.5	30.4	30.3	29.3	28.2
87.5°	15.1	12.8	13.0	12.8	12.8
90°	4.2	5.2	6.3	5.2	5.2
92.5°	7.5	5.3	4.6	4.4	3.6
95°	8.4	4.3	3.1	3.1	2.1
97.5°	7.3	4.3	2.9	1.9	1.0
100°	7.3	4.3	2.1	1.0	1.0
102.5°	6.5	3.4	2.1	1.0	0.2
105°	5.2	3.2	2.1	1.0	0.0
107.5°	5.0	3.2	2.1	1.0	0.0
110°	4.2	3.2	2.1	1.0	0.0



TEST NUMBER: P645255

CATALOG NUMBER: OMN4DP-SR4F0-50D940-FLL-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	4.2	3.2	2.1	1.0	0.0
115°	3.1	2.1	1.0	0.0	0.0
117.5°	3.1	2.1	1.0	0.0	0.0
120°	3.1	2.1	1.0	0.0	0.0
122.5°	2.3	2.1	1.0	0.0	0.0
125°	2.1	2.1	1.0	0.0	0.0
127.5°	1.0	1.9	1.0	0.0	0.0
130°	1.0	1.0	1.0	0.0	0.0
132.5°	0.2	0.2	0.2	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)