

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P77757

Luminaire Tested: **DFN2DIP-RG2F0-050D040US940-FLL-OOB-1DUDD-W**

Issue Date: 02/20/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P77757  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2401-290-9&G3-2401-290-1)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 02/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-RG2F0-050D040US940-FLL-OOB-1DUDD-W  
Description: Define Geo Ring 2ft Diameter Direct/Indirect Fixture w/ Frosted Lens  
for Downlight and Bat-Wing Lens for UPLIGHT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8799.7 lumens  
Efficiency: N/A  
Efficacy: 75.7 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.21  
Luminous Opening: Circular (Dia: 2' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 116.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P77757  
CATALOG NUMBER: DFN2DIP-RG2F0-050D040US940-FLL-OOB-1DUDD-W

### Luminous Intensity Polar Plot





TEST NUMBER: P77757

CATALOG NUMBER: DFN2DIP-RG2F0-050D040US940-FLL-OOB-1DUDD-W

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20 |    |    | 20 |    |    | 20 |    |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50 |    |    | 30 |    |    | 10 |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0  |
| RCR |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |
| 0   | 109 | 109 | 109 | 109 | 101 | 101 | 101 | 101 | 87 | 87 | 87 | 74 | 74 | 74 | 62 | 62 | 62 | 57 |
| 1   | 99  | 95  | 91  | 88  | 92  | 89  | 85  | 82  | 77 | 74 | 72 | 66 | 64 | 62 | 55 | 54 | 53 | 48 |
| 2   | 91  | 83  | 77  | 72  | 84  | 78  | 72  | 68  | 67 | 63 | 60 | 58 | 55 | 52 | 49 | 47 | 45 | 40 |
| 3   | 83  | 73  | 66  | 60  | 77  | 69  | 62  | 57  | 60 | 55 | 50 | 51 | 47 | 44 | 43 | 41 | 38 | 35 |
| 4   | 76  | 65  | 57  | 51  | 70  | 61  | 54  | 48  | 53 | 48 | 43 | 46 | 42 | 38 | 39 | 36 | 33 | 30 |
| 5   | 70  | 58  | 50  | 44  | 65  | 55  | 47  | 42  | 48 | 42 | 37 | 41 | 37 | 33 | 35 | 32 | 29 | 26 |
| 6   | 64  | 52  | 44  | 38  | 60  | 49  | 42  | 36  | 43 | 37 | 33 | 37 | 33 | 29 | 32 | 29 | 26 | 23 |
| 7   | 60  | 47  | 39  | 34  | 55  | 45  | 37  | 32  | 39 | 33 | 29 | 34 | 29 | 26 | 29 | 26 | 23 | 21 |
| 8   | 55  | 43  | 35  | 30  | 52  | 41  | 34  | 29  | 36 | 30 | 26 | 31 | 27 | 23 | 27 | 23 | 21 | 18 |
| 9   | 52  | 39  | 32  | 27  | 48  | 37  | 30  | 26  | 33 | 27 | 23 | 29 | 24 | 21 | 25 | 21 | 19 | 17 |
| 10  | 48  | 36  | 29  | 24  | 45  | 34  | 28  | 23  | 30 | 25 | 21 | 27 | 22 | 19 | 23 | 20 | 17 | 15 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |      |
|-----|------|
|     | 0°   |
| 0°  | 7488 |
| 5°  | 7466 |
| 10° | 7357 |
| 15° | 7163 |
| 20° | 6919 |
| 25° | 6620 |
| 30° | 6291 |
| 35° | 5968 |
| 40° | 5651 |
| 45° | 5354 |
| 50° | 5084 |
| 55° | 4822 |
| 60° | 4613 |
| 65° | 4410 |
| 70° | 4227 |
| 75° | 4036 |
| 80° | 3705 |
| 85° | 2878 |



TEST NUMBER: P77757  
 CATALOG NUMBER: DFN2DIP-RG2F0-050D040US940-FLL-OOB-1DUDD-W

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 205.4  | 2.3       |
| 10°-20°   | 568.0  | 6.5       |
| 20°-30°   | 805.6  | 9.2       |
| 30°-40°   | 892.7  | 10.1      |
| 40°-50°   | 853.6  | 9.7       |
| 50°-60°   | 724.9  | 8.2       |
| 60°-70°   | 539.8  | 6.1       |
| 70°-80°   | 321.6  | 3.7       |
| 80°-90°   | 88.6   | 1.0       |
| 90°-100°  | 75.1   | 0.9       |
| 100°-110° | 242.3  | 2.8       |
| 110°-120° | 559.4  | 6.4       |
| 120°-130° | 813.0  | 9.2       |
| 130°-140° | 780.7  | 8.9       |
| 140°-150° | 614.2  | 7.0       |
| 150°-160° | 414.0  | 4.7       |
| 160°-170° | 229.0  | 2.6       |
| 170°-180° | 71.8   | 0.8       |
| 0°-30°    | 1579.0 | 17.9      |
| 0°-40°    | 2471.7 | 28.1      |
| 0°-60°    | 4050.2 | 46.0      |
| 0°-90°    | 5000.2 | 56.8      |
| 90°-120°  | 876.8  | 10.0      |
| 90°-150°  | 3084.6 | 35.1      |
| 90°-180°  | 3799.0 | 43.2      |
| 0°-180°   | 8799.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | Flux |
|------|------|------|
| 0°   | 2185 |      |
| 5°   | 2171 | 205  |
| 15°  | 2020 | 568  |
| 25°  | 1751 | 806  |
| 35°  | 1427 | 893  |
| 45°  | 1105 | 854  |
| 55°  | 807  | 725  |
| 65°  | 544  | 540  |
| 75°  | 305  | 322  |
| 85°  | 73   | 84   |
| 90°  | 5    | 10   |
| 95°  | 71   | 70   |
| 105° | 219  | 242  |
| 115° | 564  | 559  |
| 125° | 922  | 813  |
| 135° | 1013 | 781  |
| 145° | 979  | 614  |
| 155° | 892  | 414  |
| 165° | 803  | 229  |
| 175° | 744  | 72   |
| 180° | 734  |      |



TEST NUMBER: P77757

CATALOG NUMBER: DFN2DIP-RG2F0-050D040US940-FLL-OOB-1DUDD-W

**CANDELA DISTRIBUTION (FULL):**

| 0°     |        |
|--------|--------|
| 0°     | 2185.4 |
| 2.5°   | 2182.9 |
| 5°     | 2170.7 |
| 7.5°   | 2148.8 |
| 10°    | 2114.6 |
| 12.5°  | 2073.2 |
| 15°    | 2019.5 |
| 17.5°  | 1961.0 |
| 20°    | 1897.6 |
| 22.5°  | 1826.8 |
| 25°    | 1751.2 |
| 27.5°  | 1675.6 |
| 30°    | 1590.2 |
| 32.5°  | 1512.2 |
| 35°    | 1426.8 |
| 37.5°  | 1343.9 |
| 40°    | 1263.4 |
| 42.5°  | 1182.9 |
| 45°    | 1104.9 |
| 47.5°  | 1029.3 |
| 50°    | 953.7  |
| 52.5°  | 880.5  |
| 55°    | 807.3  |
| 57.5°  | 741.5  |
| 60°    | 673.2  |
| 62.5°  | 607.3  |
| 65°    | 543.9  |
| 67.5°  | 482.9  |
| 70°    | 422.0  |
| 72.5°  | 363.4  |
| 75°    | 304.9  |
| 77.5°  | 246.3  |
| 80°    | 187.8  |
| 82.5°  | 129.3  |
| 85°    | 73.2   |
| 87.5°  | 26.8   |
| 90°    | 5.0    |
| 92.5°  | 35.3   |
| 95°    | 70.7   |
| 97.5°  | 101.0  |
| 100°   | 132.9  |
| 102.5° | 171.6  |
| 105°   | 218.7  |
| 107.5° | 282.7  |
| 110°   | 360.1  |



TEST NUMBER: P77757  
CATALOG NUMBER: DFN2DIP-RG2F0-050D040US940-FLL-OOB-1DUDD-W

**CANDELA DISTRIBUTION (continued):**

|        | 0°     |
|--------|--------|
| 112.5° | 457.7  |
| 115°   | 563.7  |
| 117.5° | 674.7  |
| 120°   | 777.4  |
| 122.5° | 859.8  |
| 125°   | 922.1  |
| 127.5° | 965.8  |
| 130°   | 992.7  |
| 132.5° | 1007.9 |
| 135°   | 1012.9 |
| 137.5° | 1012.9 |
| 140°   | 1006.2 |
| 142.5° | 994.4  |
| 145°   | 979.3  |
| 147.5° | 959.1  |
| 150°   | 938.9  |
| 152.5° | 915.3  |
| 155°   | 891.8  |
| 157.5° | 868.2  |
| 160°   | 844.7  |
| 162.5° | 822.8  |
| 165°   | 802.6  |
| 167.5° | 784.1  |
| 170°   | 767.3  |
| 172.5° | 755.5  |
| 175°   | 743.7  |
| 177.5° | 737.0  |
| 180°   | 733.6  |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

NEO-RAY

Report Number: SP1-2401-290-4

Test Date: 01/19/2024

Luminaire Tested: RNG2DIP-RG2F0-020D020US940-FLL-FLL-1-D-UDD-W

Data in this report applies to families of products including RNG2DIP-RG2F0-020D020US940-FLL-FLL-1-D-UDD-W.



**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2401-290-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 01/19/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: NEO-RAY  
 Catalog Number: **RNG2DIP-RG2F0-020D020US940-FLL-FLL-1-D-UDD-W**  
 Description: 2' RING DIRECT/INDIRECT FIXTURE WITH FROSTED LIGHT LEVEL 1

**Spectral Parameters**

CCT (K): 3758  
 CIE u': 0.2291  
 CIE v': 0.5077  
 Duv: 0.0012  
 CIE x: 0.3927  
 CIE y: 0.3866  
 CIE z: 0.2207  
 Peak Wavelength (nm): 622  
 Dominant Wavelength (nm): 579  
 Purity: 34

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 94.5 |      |      |
| R1:       | 96.0 | R9:  | 76.6 |
| R2:       | 99.4 | R10: | 97.1 |
| R3:       | 98.5 | R11: | 92.7 |
| R4:       | 91.3 | R12: | 73.3 |
| R5:       | 93.7 | R13: | 97.5 |
| R6:       | 96.5 | R14: | 99.6 |
| R7:       | 92.4 |      |      |
| R8:       | 88.3 |      |      |

Rf: 89  
 Rg: 95.5



**Test Conditions**

Stabilization Time: 24M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.6/27%  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2401-290-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 8/9/2023         | 2/9/2024             |
| Power Meter                    | XITRON 2801 IN0071    | 10/23/2023       | 10/23/2024           |
| AC Power Source                | CHROMA 61603 IN0063   | 10/24/2023       | 10/24/2024           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | ONSET IN0085          | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | ONSET IN0046          | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2401-290-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP1-2401-290-4

**Photopic Flux vs. Wavelength**



#####

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 1835                                 | NR                             | 490               | 33863                                | NR                             | 620               | 68794                                | NR                             | 750               | 6489                                 | NR                             | 880               | 1195                                 | NR                             |
| 365               | 1756                                 | NR                             | 495               | 36543                                | NR                             | 625               | 68963                                | NR                             | 755               | 5711                                 | NR                             | 885               | 1624                                 | NR                             |
| 370               | 1802                                 | NR                             | 500               | 39024                                | NR                             | 630               | 68221                                | NR                             | 760               | 5217                                 | NR                             | 890               | 1275                                 | NR                             |
| 375               | 1845                                 | NR                             | 505               | 41399                                | NR                             | 635               | 66761                                | NR                             | 765               | 4671                                 | NR                             | 895               | 1184                                 | NR                             |
| 380               | 1842                                 | NR                             | 510               | 43372                                | NR                             | 640               | 65207                                | NR                             | 770               | 4277                                 | NR                             | 900               | 1288                                 | NR                             |
| 385               | 1553                                 | NR                             | 515               | 45125                                | NR                             | 645               | 62607                                | NR                             | 775               | 3684                                 | NR                             | 905               | 1449                                 | NR                             |
| 390               | 1519                                 | NR                             | 520               | 46728                                | NR                             | 650               | 59420                                | NR                             | 780               | 3015                                 | NR                             | 910               | 1184                                 | NR                             |
| 395               | 1452                                 | NR                             | 525               | 48116                                | NR                             | 655               | 56103                                | NR                             | 785               | 2857                                 | NR                             | 915               | 1999                                 | NR                             |
| 400               | 1256                                 | NR                             | 530               | 49751                                | NR                             | 660               | 52566                                | NR                             | 790               | 2657                                 | NR                             | 920               | 1299                                 | NR                             |
| 405               | 1033                                 | NR                             | 535               | 51317                                | NR                             | 665               | 48489                                | NR                             | 795               | 2474                                 | NR                             | 925               | 1312                                 | NR                             |
| 410               | 1023                                 | NR                             | 540               | 52637                                | NR                             | 670               | 44555                                | NR                             | 800               | 2413                                 | NR                             | 930               | 1526                                 | NR                             |
| 415               | 1228                                 | NR                             | 545               | 54148                                | NR                             | 675               | 40405                                | NR                             | 805               | 2307                                 | NR                             | 935               | 1577                                 | NR                             |
| 420               | 1723                                 | NR                             | 550               | 55654                                | NR                             | 680               | 36707                                | NR                             | 810               | 1935                                 | NR                             | 940               | 1108                                 | NR                             |
| 425               | 2748                                 | NR                             | 555               | 56944                                | NR                             | 685               | 32841                                | NR                             | 815               | 1648                                 | NR                             | 945               | 1728                                 | NR                             |
| 430               | 4401                                 | NR                             | 560               | 57653                                | NR                             | 690               | 29037                                | NR                             | 820               | 1582                                 | NR                             | 950               | 1356                                 | NR                             |
| 435               | 7516                                 | NR                             | 565               | 58559                                | NR                             | 695               | 25745                                | NR                             | 825               | 1937                                 | NR                             | 955               | 564                                  | NR                             |
| 440               | 12984                                | NR                             | 570               | 59300                                | NR                             | 700               | 22850                                | NR                             | 830               | 1558                                 | NR                             | 960               | 1914                                 | NR                             |
| 445               | 22972                                | NR                             | 575               | 59941                                | NR                             | 705               | 20102                                | NR                             | 835               | 1584                                 | NR                             | 965               | 994                                  | NR                             |
| 450               | 42364                                | NR                             | 580               | 60752                                | NR                             | 710               | 17680                                | NR                             | 840               | 1621                                 | NR                             | 970               | 757                                  | NR                             |
| 455               | 64528                                | NR                             | 585               | 61417                                | NR                             | 715               | 15746                                | NR                             | 845               | 1333                                 | NR                             | 975               | 758                                  | NR                             |
| 460               | 65971                                | NR                             | 590               | 62430                                | NR                             | 720               | 13934                                | NR                             | 850               | 1406                                 | NR                             | 980               | 1163                                 | NR                             |
| 465               | 51026                                | NR                             | 595               | 63801                                | NR                             | 725               | 12285                                | NR                             | 855               | 1655                                 | NR                             | 985               | 952                                  | NR                             |
| 470               | 43331                                | NR                             | 600               | 64806                                | NR                             | 730               | 10834                                | NR                             | 860               | 1737                                 | NR                             | 990               | 1604                                 | NR                             |
| 475               | 38626                                | NR                             | 605               | 66352                                | NR                             | 735               | 9292                                 | NR                             | 865               | 1841                                 | NR                             | 995               | 1145                                 | NR                             |
| 480               | 33315                                | NR                             | 610               | 67770                                | NR                             | 740               | 8312                                 | NR                             | 870               | 1490                                 | NR                             | 1000              | 0                                    | NR                             |
| 485               | 31961                                | NR                             | 615               | 68560                                | NR                             | 745               | 7359                                 | NR                             | 875               | 1559                                 | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2401-290-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 7174.5

S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1835          | NR            | 490    | 33863         | NR            | 620    | 68794         | NR            | 750    | 6489          | NR            | 880    | 1195          | NR            |
| 365    | 1756          | NR            | 495    | 36543         | NR            | 625    | 68963         | NR            | 755    | 5711          | NR            | 885    | 1624          | NR            |
| 370    | 1802          | NR            | 500    | 39024         | NR            | 630    | 68221         | NR            | 760    | 5217          | NR            | 890    | 1275          | NR            |
| 375    | 1845          | NR            | 505    | 41399         | NR            | 635    | 66761         | NR            | 765    | 4671          | NR            | 895    | 1184          | NR            |
| 380    | 1842          | NR            | 510    | 43372         | NR            | 640    | 65207         | NR            | 770    | 4277          | NR            | 900    | 1288          | NR            |
| 385    | 1553          | NR            | 515    | 45125         | NR            | 645    | 62607         | NR            | 775    | 3684          | NR            | 905    | 1449          | NR            |
| 390    | 1519          | NR            | 520    | 46728         | NR            | 650    | 59420         | NR            | 780    | 3015          | NR            | 910    | 1184          | NR            |
| 395    | 1452          | NR            | 525    | 48116         | NR            | 655    | 56103         | NR            | 785    | 2857          | NR            | 915    | 1999          | NR            |
| 400    | 1256          | NR            | 530    | 49751         | NR            | 660    | 52566         | NR            | 790    | 2657          | NR            | 920    | 1299          | NR            |
| 405    | 1033          | NR            | 535    | 51317         | NR            | 665    | 48489         | NR            | 795    | 2474          | NR            | 925    | 1312          | NR            |
| 410    | 1023          | NR            | 540    | 52637         | NR            | 670    | 44555         | NR            | 800    | 2413          | NR            | 930    | 1526          | NR            |
| 415    | 1228          | NR            | 545    | 54148         | NR            | 675    | 40405         | NR            | 805    | 2307          | NR            | 935    | 1577          | NR            |
| 420    | 1723          | NR            | 550    | 55654         | NR            | 680    | 36707         | NR            | 810    | 1935          | NR            | 940    | 1108          | NR            |
| 425    | 2748          | NR            | 555    | 56944         | NR            | 685    | 32841         | NR            | 815    | 1648          | NR            | 945    | 1728          | NR            |
| 430    | 4401          | NR            | 560    | 57653         | NR            | 690    | 29037         | NR            | 820    | 1582          | NR            | 950    | 1356          | NR            |
| 435    | 7516          | NR            | 565    | 58559         | NR            | 695    | 25745         | NR            | 825    | 1937          | NR            | 955    | 564           | NR            |
| 440    | 12984         | NR            | 570    | 59300         | NR            | 700    | 22850         | NR            | 830    | 1558          | NR            | 960    | 1914          | NR            |
| 445    | 22972         | NR            | 575    | 59941         | NR            | 705    | 20102         | NR            | 835    | 1584          | NR            | 965    | 994           | NR            |
| 450    | 42364         | NR            | 580    | 60752         | NR            | 710    | 17680         | NR            | 840    | 1621          | NR            | 970    | 757           | NR            |
| 455    | 64528         | NR            | 585    | 61417         | NR            | 715    | 15746         | NR            | 845    | 1333          | NR            | 975    | 758           | NR            |
| 460    | 65971         | NR            | 590    | 62430         | NR            | 720    | 13934         | NR            | 850    | 1406          | NR            | 980    | 1163          | NR            |
| 465    | 51026         | NR            | 595    | 63801         | NR            | 725    | 12285         | NR            | 855    | 1655          | NR            | 985    | 952           | NR            |
| 470    | 43331         | NR            | 600    | 64806         | NR            | 730    | 10834         | NR            | 860    | 1737          | NR            | 990    | 1604          | NR            |
| 475    | 38626         | NR            | 605    | 66352         | NR            | 735    | 9292          | NR            | 865    | 1841          | NR            | 995    | 1145          | NR            |
| 480    | 33315         | NR            | 610    | 67770         | NR            | 740    | 8312          | NR            | 870    | 1490          | NR            | 1000   | 0             | NR            |
| 485    | 31961         | NR            | 615    | 68560         | NR            | 745    | 7359          | NR            | 875    | 1559          | NR            |        |               |               |

REPORT NUMBER: SP1-2401-290-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2971.3 M/P: 0.73

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1835          | NR            | 490    | 33863         | NR            | 620    | 68794         | NR            | 750    | 6489          | NR            | 880    | 1195          | NR            |
| 365    | 1756          | NR            | 495    | 36543         | NR            | 625    | 68963         | NR            | 755    | 5711          | NR            | 885    | 1624          | NR            |
| 370    | 1802          | NR            | 500    | 39024         | NR            | 630    | 68221         | NR            | 760    | 5217          | NR            | 890    | 1275          | NR            |
| 375    | 1845          | NR            | 505    | 41399         | NR            | 635    | 66761         | NR            | 765    | 4671          | NR            | 895    | 1184          | NR            |
| 380    | 1842          | NR            | 510    | 43372         | NR            | 640    | 65207         | NR            | 770    | 4277          | NR            | 900    | 1288          | NR            |
| 385    | 1553          | NR            | 515    | 45125         | NR            | 645    | 62607         | NR            | 775    | 3684          | NR            | 905    | 1449          | NR            |
| 390    | 1519          | NR            | 520    | 46728         | NR            | 650    | 59420         | NR            | 780    | 3015          | NR            | 910    | 1184          | NR            |
| 395    | 1452          | NR            | 525    | 48116         | NR            | 655    | 56103         | NR            | 785    | 2857          | NR            | 915    | 1999          | NR            |
| 400    | 1256          | NR            | 530    | 49751         | NR            | 660    | 52566         | NR            | 790    | 2657          | NR            | 920    | 1299          | NR            |
| 405    | 1033          | NR            | 535    | 51317         | NR            | 665    | 48489         | NR            | 795    | 2474          | NR            | 925    | 1312          | NR            |
| 410    | 1023          | NR            | 540    | 52637         | NR            | 670    | 44555         | NR            | 800    | 2413          | NR            | 930    | 1526          | NR            |
| 415    | 1228          | NR            | 545    | 54148         | NR            | 675    | 40405         | NR            | 805    | 2307          | NR            | 935    | 1577          | NR            |
| 420    | 1723          | NR            | 550    | 55654         | NR            | 680    | 36707         | NR            | 810    | 1935          | NR            | 940    | 1108          | NR            |
| 425    | 2748          | NR            | 555    | 56944         | NR            | 685    | 32841         | NR            | 815    | 1648          | NR            | 945    | 1728          | NR            |
| 430    | 4401          | NR            | 560    | 57653         | NR            | 690    | 29037         | NR            | 820    | 1582          | NR            | 950    | 1356          | NR            |
| 435    | 7516          | NR            | 565    | 58559         | NR            | 695    | 25745         | NR            | 825    | 1937          | NR            | 955    | 564           | NR            |
| 440    | 12984         | NR            | 570    | 59300         | NR            | 700    | 22850         | NR            | 830    | 1558          | NR            | 960    | 1914          | NR            |
| 445    | 22972         | NR            | 575    | 59941         | NR            | 705    | 20102         | NR            | 835    | 1584          | NR            | 965    | 994           | NR            |
| 450    | 42364         | NR            | 580    | 60752         | NR            | 710    | 17680         | NR            | 840    | 1621          | NR            | 970    | 757           | NR            |
| 455    | 64528         | NR            | 585    | 61417         | NR            | 715    | 15746         | NR            | 845    | 1333          | NR            | 975    | 758           | NR            |
| 460    | 65971         | NR            | 590    | 62430         | NR            | 720    | 13934         | NR            | 850    | 1406          | NR            | 980    | 1163          | NR            |
| 465    | 51026         | NR            | 595    | 63801         | NR            | 725    | 12285         | NR            | 855    | 1655          | NR            | 985    | 952           | NR            |
| 470    | 43331         | NR            | 600    | 64806         | NR            | 730    | 10834         | NR            | 860    | 1737          | NR            | 990    | 1604          | NR            |
| 475    | 38626         | NR            | 605    | 66352         | NR            | 735    | 9292          | NR            | 865    | 1841          | NR            | 995    | 1145          | NR            |
| 480    | 33315         | NR            | 610    | 67770         | NR            | 740    | 8312          | NR            | 870    | 1490          | NR            | 1000   | 0             | NR            |
| 485    | 31961         | NR            | 615    | 68560         | NR            | 745    | 7359          | NR            | 875    | 1559          | NR            |        |               |               |

REPORT NUMBER: SP1-2401-290-4

TM-30-18

**Summary**

$R_f = 89$   
 $R_g = 95.5$   
 CIE  $R_a = 94.5$   
 $R_9 = 76.6$



**Color Vector Graphics**



REPORT NUMBER: SP1-2401-290-4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 86 | CES26 = 95  | CES51 = 89 | CES76 = 94 |
| CES02 = 62 | CES27 = 84  | CES52 = 94 | CES77 = 90 |
| CES03 = 31 | CES28 = 100 | CES53 = 89 | CES78 = 91 |
| CES04 = 69 | CES29 = 83  | CES54 = 85 | CES79 = 94 |
| CES05 = 49 | CES30 = 71  | CES55 = 82 | CES80 = 93 |
| CES06 = 51 | CES31 = 85  | CES56 = 84 | CES81 = 84 |
| CES07 = 42 | CES32 = 93  | CES57 = 81 | CES82 = 97 |
| CES08 = 41 | CES33 = 82  | CES58 = 82 | CES83 = 93 |
| CES09 = 29 | CES34 = 97  | CES59 = 95 | CES84 = 94 |
| CES10 = 74 | CES35 = 99  | CES60 = 87 | CES85 = 82 |
| CES11 = 57 | CES36 = 70  | CES61 = 89 | CES86 = 87 |
| CES12 = 63 | CES37 = 97  | CES62 = 72 | CES87 = 93 |
| CES13 = 43 | CES38 = 67  | CES63 = 86 | CES88 = 92 |
| CES14 = 74 | CES39 = 95  | CES64 = 82 | CES89 = 89 |
| CES15 = 71 | CES40 = 94  | CES65 = 86 | CES90 = 87 |
| CES16 = 47 | CES41 = 87  | CES66 = 80 | CES91 = 67 |
| CES17 = 49 | CES42 = 96  | CES67 = 80 | CES92 = 81 |
| CES18 = 56 | CES43 = 93  | CES68 = 86 | CES93 = 87 |
| CES19 = 71 | CES44 = 99  | CES69 = 87 | CES94 = 86 |
| CES20 = 66 | CES45 = 93  | CES70 = 87 | CES95 = 84 |
| CES21 = 85 | CES46 = 90  | CES71 = 77 | CES96 = 95 |
| CES22 = 78 | CES47 = 84  | CES72 = 93 | CES97 = 94 |
| CES23 = 91 | CES48 = 76  | CES73 = 85 | CES98 = 91 |
| CES24 = 90 | CES49 = 92  | CES74 = 87 | CES99 = 90 |
| CES25 = 71 | CES50 = 90  | CES75 = 82 |            |





REPORT NUMBER: SP1-2401-290-4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2401-290-4

TM-30-18

Measure Comparisons



(END OF REPORT)