

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925314

Luminaire Tested: DFN2DIP-SQ2F0-030D080US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925314
REPORT IS A COMBINATION OF REPORTS P899832 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D080US950-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9187.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925314

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925314

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	30
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22
4	71	61	53	48	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2601	2601	2601
5°	2601	2554	2572
10°	2570	2498	2485
15°	2531	2410	2352
20°	2479	2291	2191
25°	2427	2159	2035
30°	2358	2024	1838
35°	2290	1878	1666
40°	2220	1729	1469
45°	2140	1565	1290
50°	2057	1399	1115
55°	1969	1222	949
60°	1868	1039	777
65°	1752	852	695
70°	1610	679	624
75°	1431	588	560
80°	1176	477	475
85°	765	296	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3367 cd/sqm

TEST NUMBER: P925314

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	1.2
10°-20°	304.3	3.3
20°-30°	427.3	4.7
30°-40°	465.7	5.1
40°-50°	428.1	4.7
50°-60°	336.2	3.7
60°-70°	218.8	2.4
70°-80°	112.6	1.2
80°-90°	35.6	0.4
90°-100°	149.4	1.6
100°-110°	474.6	5.2
110°-120°	812.1	8.8
120°-130°	1068.1	11.6
130°-140°	1198.9	13.0
140°-150°	1175.6	12.8
150°-160°	986.2	10.7
160°-170°	654.0	7.1
170°-180°	228.6	2.5
0°-30°	842.5	9.2
0°-40°	1308.2	14.2
0°-60°	2072.5	22.6
0°-90°	2439.5	26.6
90°-120°	1436.1	15.6
90°-150°	4878.6	53.1
90°-180°	6747.0	73.4
0°-180°	9187.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1183	1183	1183	1183	1183	
5°	1183	1178	1164	1173	1170	112
15°	1125	1113	1077	1057	1046	317
25°	1021	987	916	872	856	470
35°	880	825	731	664	640	551
45°	719	648	535	459	434	556
55°	547	464	348	284	263	489
65°	369	283	186	150	147	366
75°	197	122	86	78	77	208
85°	46	24	20	20	20	53
90°	2	26	71	67	69	9
95°	106	127	130	130	127	118
105°	438	444	448	452	452	462
115°	815	827	823	821	815	806
125°	1185	1204	1198	1191	1189	1059
135°	1533	1556	1560	1558	1552	1185
145°	1861	1876	1888	1890	1882	1163
155°	2128	2134	2141	2151	2144	980
165°	2316	2313	2313	2328	2318	653
175°	2409	2404	2399	2414	2401	229
180°	2414	2414	2414	2414	2414	

TEST NUMBER: P925314

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1182.9	1182.9	1182.9	1182.9	1182.9
2.5°	1188.2	1182.9	1171.0	1181.8	1179.7
5°	1182.9	1177.5	1163.6	1173.2	1170.0
7.5°	1173.2	1166.8	1151.9	1156.1	1150.7
10°	1160.4	1152.9	1131.5	1128.2	1121.9
12.5°	1144.3	1134.7	1105.8	1099.4	1087.6
15°	1125.1	1113.2	1076.9	1056.6	1045.9
17.5°	1102.5	1085.5	1040.4	1017.0	999.8
20°	1076.9	1055.4	1001.9	975.3	951.6
22.5°	1049.1	1024.4	962.3	926.0	909.9
25°	1021.3	986.9	916.3	872.4	856.3
27.5°	988.1	951.6	873.5	823.2	798.5
30°	952.8	912.0	826.4	771.9	742.9
32.5°	918.4	869.2	781.5	717.2	690.4
35°	880.0	825.3	731.1	663.7	640.1
37.5°	842.5	783.5	684.0	610.1	583.5
40°	802.9	738.7	634.8	558.8	531.0
42.5°	762.2	693.7	585.6	506.3	479.6
45°	719.4	647.6	535.3	459.2	433.5
47.5°	678.7	602.7	487.1	411.0	387.5
50°	633.7	557.7	440.0	366.0	343.6
52.5°	589.8	509.5	395.1	324.4	304.0
55°	546.9	463.5	347.8	283.7	263.4
57.5°	503.1	417.5	306.2	246.2	229.1
60°	458.1	372.5	262.3	207.7	190.6
62.5°	414.3	328.7	224.8	173.4	164.9
65°	369.3	282.6	186.2	149.9	146.6
67.5°	326.6	239.7	149.9	131.7	128.4
70°	281.5	198.1	124.1	113.4	109.1
72.5°	238.7	159.4	103.8	95.3	93.1
75°	196.9	122.0	85.7	78.1	77.1
77.5°	155.2	86.6	67.4	63.2	61.0
80°	116.7	62.1	51.3	47.1	47.1
82.5°	81.3	41.8	35.3	33.2	33.2
85°	46.0	23.5	20.3	20.3	20.3
87.5°	17.2	8.5	8.5	7.5	7.5
90°	2.2	26.2	71.4	67.0	69.2
92.5°	45.1	61.2	63.3	65.4	65.4
95°	106.3	126.6	130.2	130.2	126.6
97.5°	176.9	195.8	203.8	203.8	203.8
100°	258.3	275.0	280.9	280.9	278.7
102.5°	344.2	356.6	364.5	366.7	364.5
105°	438.1	443.9	448.3	451.9	451.9
107.5°	531.2	540.0	540.0	541.4	531.2
110°	621.4	633.1	633.1	633.1	627.3

TEST NUMBER: P925314

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	718.9	731.3	729.1	723.3	718.9
115°	815.0	826.6	823.0	820.8	815.0
117.5°	910.3	926.3	916.1	910.3	904.5
120°	1006.4	1022.4	1006.4	1006.4	999.8
122.5°	1093.7	1114.1	1103.9	1098.1	1093.7
125°	1185.3	1203.6	1197.7	1191.2	1189.1
127.5°	1274.9	1297.4	1289.4	1280.7	1274.9
130°	1358.6	1384.7	1381.1	1376.8	1368.8
132.5°	1452.5	1472.8	1474.3	1464.1	1458.3
135°	1533.2	1555.8	1560.2	1558.0	1552.2
137.5°	1623.4	1641.6	1645.3	1643.8	1635.1
140°	1702.8	1720.9	1731.1	1731.1	1723.1
142.5°	1784.3	1802.5	1808.3	1810.5	1802.5
145°	1861.4	1875.9	1887.6	1889.8	1881.8
147.5°	1930.5	1948.7	1957.4	1961.1	1953.1
150°	2001.9	2014.2	2022.2	2028.8	2022.2
152.5°	2065.1	2077.5	2087.7	2095.7	2087.7
155°	2128.5	2134.3	2140.9	2151.0	2144.5
157.5°	2183.0	2187.4	2191.1	2205.6	2195.4
160°	2231.8	2236.2	2238.4	2250.7	2242.0
162.5°	2276.9	2276.9	2279.1	2292.9	2282.7
165°	2315.5	2313.3	2313.3	2327.9	2317.6
167.5°	2350.4	2343.9	2343.9	2358.4	2348.2
170°	2376.6	2370.8	2368.6	2383.2	2370.8
172.5°	2394.8	2389.0	2386.8	2401.3	2389.0
175°	2409.3	2403.5	2399.1	2413.7	2401.3
177.5°	2417.3	2411.5	2407.1	2419.5	2407.1
180°	2413.7	2413.7	2413.7	2413.7	2413.7

TEST NUMBER: P925314

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.62	8.29	8.76	9.42	10.99	3.58	4.25	4.72	5.38	6.95
	3H	9.27	9.86	10.41	11.00	12.59	4.74	5.34	5.89	6.47	8.06
	4H	9.85	10.42	11.01	11.56	13.15	5.17	5.74	6.32	6.87	8.46
	6H	10.25	10.77	11.41	11.91	13.52	5.46	5.99	6.63	7.12	8.73
	8H	10.36	10.86	11.53	12.01	13.61	5.54	6.04	6.71	7.19	8.79
	12H	10.41	10.88	11.58	12.03	13.65	5.57	6.04	6.74	7.19	8.81
4H	2H	7.61	8.18	8.78	9.32	10.91	4.14	4.71	5.31	5.85	7.44
	3H	9.40	9.88	10.57	11.04	12.64	5.46	5.93	6.63	7.09	8.70
	4H	10.08	10.51	11.25	11.66	13.28	5.98	6.42	7.15	7.57	9.19
	6H	10.56	10.93	11.74	12.11	13.72	6.38	6.75	7.55	7.92	9.53
	8H	10.72	11.07	11.90	12.23	13.87	6.49	6.84	7.67	8.00	9.63
	12H	10.80	11.12	11.99	12.29	13.93	6.54	6.85	7.73	8.03	9.66
8H	4H	10.03	10.37	11.20	11.54	13.17	6.24	6.59	7.42	7.75	9.38
	6H	10.56	10.85	11.76	12.06	13.68	6.73	7.02	7.92	8.22	9.85
	8H	10.77	11.02	11.97	12.20	13.85	6.91	7.15	8.10	8.34	9.99
	12H	10.89	11.10	12.09	12.29	13.97	7.00	7.22	8.21	8.40	10.08
12H	4H	9.97	10.29	11.16	11.46	13.10	6.24	6.55	7.43	7.73	9.36
	6H	10.54	10.79	11.74	11.97	13.62	6.77	7.02	7.97	8.21	9.85
	8H	10.74	10.96	11.94	12.14	13.82	6.96	7.18	8.16	8.36	10.04