

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P79122

Luminaire Tested: **DFN2DIP-RG4F0-040D100US930-FLL-FLL-1DUDD-W**

Issue Date: 02/20/2024



Test Information

Test Method: LM-79-08
Report Number: P79122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA
Test Lab: INNOVATION CENTER(G3)
Issue Date: 02/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: DFN2DIP-RG4F0-040D100US930-FLL-FLL-1DUDD-W
Description: Define Geo Ring 4ft Diameter Direct/Indirect Fixture w/ Frosted Lens
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13141.7 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.21
Luminous Opening: Circular (Dia: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 164
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P79122
CATALOG NUMBER: DFN2DIP-RG4F0-040D100US930-FLL-FLL-1DUDD-W

Luminous Intensity Polar Plot





TEST NUMBER: P79122

CATALOG NUMBER: DFN2DIP-RG4F0-040D100US930-FLL-FLL-1DUDD-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 102 | 102 | 102 | 102 | 91 | 91 | 91 | 91 | 71 | 71 | 71 | 53 | 53 | 53 | 36 | 36 | 36 | 28 | | | 28 |
| 1 | 93 | 89 | 85 | 82 | 83 | 79 | 76 | 73 | 62 | 60 | 58 | 46 | 45 | 44 | 32 | 31 | 30 | 23 | | | 23 |
| 2 | 85 | 77 | 72 | 67 | 75 | 69 | 65 | 60 | 54 | 51 | 48 | 41 | 38 | 37 | 28 | 27 | 25 | 20 | | | 20 |
| 3 | 77 | 68 | 61 | 56 | 69 | 61 | 55 | 50 | 48 | 44 | 41 | 36 | 33 | 31 | 25 | 23 | 22 | 17 | | | 17 |
| 4 | 71 | 60 | 53 | 47 | 63 | 54 | 48 | 43 | 43 | 38 | 35 | 32 | 29 | 27 | 22 | 20 | 19 | 15 | | | 15 |
| 5 | 65 | 54 | 46 | 40 | 58 | 48 | 42 | 37 | 38 | 33 | 30 | 29 | 26 | 23 | 20 | 18 | 16 | 13 | | | 13 |
| 6 | 59 | 48 | 40 | 35 | 53 | 43 | 37 | 32 | 34 | 29 | 26 | 26 | 23 | 20 | 18 | 16 | 15 | 11 | | | 11 |
| 7 | 55 | 43 | 36 | 30 | 49 | 39 | 32 | 28 | 31 | 26 | 23 | 24 | 20 | 18 | 17 | 15 | 13 | 10 | | | 10 |
| 8 | 51 | 39 | 32 | 27 | 45 | 35 | 29 | 24 | 28 | 23 | 20 | 22 | 18 | 16 | 15 | 13 | 12 | 9 | | | 9 |
| 9 | 47 | 36 | 28 | 24 | 42 | 32 | 26 | 22 | 26 | 21 | 18 | 20 | 17 | 14 | 14 | 12 | 10 | 8 | | | 8 |
| 10 | 44 | 33 | 26 | 21 | 39 | 30 | 23 | 19 | 24 | 19 | 16 | 18 | 15 | 13 | 13 | 11 | 10 | 7 | | | 7 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|------|
| | 0° |
| 0° | 1364 |
| 5° | 1359 |
| 10° | 1338 |
| 15° | 1308 |
| 20° | 1262 |
| 25° | 1210 |
| 30° | 1150 |
| 35° | 1088 |
| 40° | 1028 |
| 45° | 972 |
| 50° | 919 |
| 55° | 874 |
| 60° | 834 |
| 65° | 799 |
| 70° | 767 |
| 75° | 735 |
| 80° | 690 |
| 85° | 567 |



TEST NUMBER: P79122
 CATALOG NUMBER: DFN2DIP-RG4F0-040D100US930-FLL-FLL-1DUDD-W

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 149.6 | 1.1 |
| 10°-20° | 414.4 | 3.2 |
| 20°-30° | 588.2 | 4.5 |
| 30°-40° | 651.3 | 5.0 |
| 40°-50° | 619.9 | 4.7 |
| 50°-60° | 524.6 | 4.0 |
| 60°-70° | 390.9 | 3.0 |
| 70°-80° | 235.1 | 1.8 |
| 80°-90° | 68.5 | 0.5 |
| 90°-100° | 153.8 | 1.2 |
| 100°-110° | 630.5 | 4.8 |
| 110°-120° | 1103.6 | 8.4 |
| 120°-130° | 1455.6 | 11.1 |
| 130°-140° | 1675.2 | 12.7 |
| 140°-150° | 1694.6 | 12.9 |
| 150°-160° | 1455.1 | 11.1 |
| 160°-170° | 983.7 | 7.5 |
| 170°-180° | 347.1 | 2.6 |
| 0°-30° | 1152.1 | 8.8 |
| 0°-40° | 1803.4 | 13.7 |
| 0°-60° | 2947.9 | 22.4 |
| 0°-90° | 3642.4 | 27.7 |
| 90°-120° | 1888.0 | 14.4 |
| 90°-150° | 6713.4 | 51.1 |
| 90°-180° | 9499.0 | 72.3 |
| 0°-180° | 13141.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|------|------|------|
| 0° | 1593 | |
| 5° | 1580 | 150 |
| 15° | 1474 | 414 |
| 25° | 1280 | 588 |
| 35° | 1041 | 651 |
| 45° | 802 | 620 |
| 55° | 585 | 525 |
| 65° | 394 | 391 |
| 75° | 222 | 235 |
| 85° | 58 | 65 |
| 90° | 5 | 11 |
| 95° | 123 | 146 |
| 105° | 597 | 631 |
| 115° | 1117 | 1104 |
| 125° | 1627 | 1456 |
| 135° | 2170 | 1675 |
| 145° | 2712 | 1695 |
| 155° | 3159 | 1455 |
| 165° | 3488 | 984 |
| 175° | 3654 | 347 |
| 180° | 3674 | |



TEST NUMBER: P79122

CATALOG NUMBER: DFN2DIP-RG4F0-040D100US930-FLL-FLL-1DUDD-W

CANDELA DISTRIBUTION (FULL):

| 0° | |
|--------|--------|
| 0° | 1592.7 |
| 2.5° | 1590.8 |
| 5° | 1580.4 |
| 7.5° | 1564.3 |
| 10° | 1538.8 |
| 12.5° | 1510.4 |
| 15° | 1474.5 |
| 17.5° | 1432.0 |
| 20° | 1384.7 |
| 22.5° | 1333.7 |
| 25° | 1279.8 |
| 27.5° | 1222.1 |
| 30° | 1162.6 |
| 32.5° | 1103.0 |
| 35° | 1040.7 |
| 37.5° | 981.1 |
| 40° | 919.7 |
| 42.5° | 861.1 |
| 45° | 802.5 |
| 47.5° | 745.8 |
| 50° | 690.0 |
| 52.5° | 637.1 |
| 55° | 585.1 |
| 57.5° | 535.9 |
| 60° | 486.8 |
| 62.5° | 439.5 |
| 65° | 394.1 |
| 67.5° | 349.7 |
| 70° | 306.2 |
| 72.5° | 264.7 |
| 75° | 222.1 |
| 77.5° | 181.5 |
| 80° | 139.9 |
| 82.5° | 99.2 |
| 85° | 57.7 |
| 87.5° | 22.7 |
| 90° | 4.8 |
| 92.5° | 50.8 |
| 95° | 123.3 |
| 97.5° | 219.9 |
| 100° | 338.4 |
| 102.5° | 466.5 |
| 105° | 597.0 |
| 107.5° | 729.9 |
| 110° | 858.0 |



TEST NUMBER: P79122
CATALOG NUMBER: DFN2DIP-RG4F0-040D100US930-FLL-FLL-1DUDD-W

CANDELA DISTRIBUTION (continued):

| | 0° |
|--------|--------|
| 112.5° | 986.1 |
| 115° | 1116.6 |
| 117.5° | 1244.7 |
| 120° | 1368.0 |
| 122.5° | 1493.7 |
| 125° | 1626.6 |
| 127.5° | 1759.6 |
| 130° | 1892.5 |
| 132.5° | 2030.3 |
| 135° | 2170.4 |
| 137.5° | 2310.6 |
| 140° | 2450.8 |
| 142.5° | 2583.8 |
| 145° | 2711.9 |
| 147.5° | 2832.7 |
| 150° | 2951.1 |
| 152.5° | 3055.1 |
| 155° | 3159.0 |
| 157.5° | 3258.1 |
| 160° | 3347.5 |
| 162.5° | 3422.4 |
| 165° | 3487.7 |
| 167.5° | 3550.5 |
| 170° | 3594.1 |
| 172.5° | 3632.7 |
| 175° | 3654.5 |
| 177.5° | 3671.4 |
| 180° | 3673.8 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

NEO-RAY

Report Number: SP1-2401-290-2

Test Date: 01/18/2024

Luminaire Tested: RNG2DIP-RG2F0-020D020US930-FLL-FLL-1-D-UDD-W

Data in this report applies to families of products including RNG2DIP-RG2F0-020D020US930-FLL-FLL-1-D-UDD-W.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2401-290-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/19/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: **RNG2DIP-RG2F0-020D020US930-FLL-FLL-1-D-UDD-W**
 Description: 2' RING DIRECT/INDIRECT FIXTURE WITH FROSTED LIGHT LEVEL 1

Spectral Parameters

CCT (K): 2931
 CIE u': 0.2524
 CIE v': 0.5253
 Duv: 0.0018
 CIE x: 0.4446
 CIE y: 0.4112
 CIE z: 0.1443
 Peak Wavelength (nm): 629
 Dominant Wavelength (nm): 582
 Purity: 57.1

CRI (Ra): 94.7
 R1: 95.1
 R2: 96.3
 R3: 96.3
 R4: 95.9
 R5: 94.4
 R6: 95.6
 R7: 95.7
 R8: 88.4

R9: 72.1
 R10: 90.5
 R11: 96.7
 R12: 82.6
 R13: 95.3
 R14: 97.1

Rf: 93.8
 Rg: 99.3



Test Conditions

Stabilization Time: 28M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.6/15%
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2401-290-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | 76INCH SPHERE IN0058 | 8/9/2023 | 2/9/2024 |
| Power Meter | XITRON 2801 IN0071 | 10/23/2023 | 10/23/2024 |
| AC Power Source | CHROMA 61603 IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | AGILENT E3634A IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | ONSET IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | ONSET IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2401-290-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 7-step quadrangle

REPORT NUMBER: SP1-2401-290-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1461 | NR | 490 | 21821 | NR | 620 | 77901 | NR | 750 | 8179 | NR | 880 | 1643 | NR |
| 365 | 1400 | NR | 495 | 25627 | NR | 625 | 79163 | NR | 755 | 7299 | NR | 885 | 1703 | NR |
| 370 | 1570 | NR | 500 | 29501 | NR | 630 | 79015 | NR | 760 | 6398 | NR | 890 | 1343 | NR |
| 375 | 1768 | NR | 505 | 32566 | NR | 635 | 78215 | NR | 765 | 5779 | NR | 895 | 1272 | NR |
| 380 | 1653 | NR | 510 | 34919 | NR | 640 | 77002 | NR | 770 | 4957 | NR | 900 | 1388 | NR |
| 385 | 1519 | NR | 515 | 37015 | NR | 645 | 74220 | NR | 775 | 4366 | NR | 905 | 1205 | NR |
| 390 | 1495 | NR | 520 | 39034 | NR | 650 | 71542 | NR | 780 | 3858 | NR | 910 | 1298 | NR |
| 395 | 1377 | NR | 525 | 40568 | NR | 655 | 67792 | NR | 785 | 3408 | NR | 915 | 1337 | NR |
| 400 | 1116 | NR | 530 | 42614 | NR | 660 | 63857 | NR | 790 | 3251 | NR | 920 | 1680 | NR |
| 405 | 1027 | NR | 535 | 44347 | NR | 665 | 59357 | NR | 795 | 3012 | NR | 925 | 1293 | NR |
| 410 | 1056 | NR | 540 | 46106 | NR | 670 | 54656 | NR | 800 | 2808 | NR | 930 | 1369 | NR |
| 415 | 1393 | NR | 545 | 48203 | NR | 675 | 49862 | NR | 805 | 2550 | NR | 935 | 1382 | NR |
| 420 | 2045 | NR | 550 | 50008 | NR | 680 | 45198 | NR | 810 | 2478 | NR | 940 | 1295 | NR |
| 425 | 3225 | NR | 555 | 51782 | NR | 685 | 40716 | NR | 815 | 2341 | NR | 945 | 1425 | NR |
| 430 | 5118 | NR | 560 | 53082 | NR | 690 | 36247 | NR | 820 | 2409 | NR | 950 | 1783 | NR |
| 435 | 8200 | NR | 565 | 54447 | NR | 695 | 32175 | NR | 825 | 2301 | NR | 955 | 1148 | NR |
| 440 | 13442 | NR | 570 | 56050 | NR | 700 | 28460 | NR | 830 | 2205 | NR | 960 | 1184 | NR |
| 445 | 23157 | NR | 575 | 57513 | NR | 705 | 25105 | NR | 835 | 1768 | NR | 965 | 1637 | NR |
| 450 | 33968 | NR | 580 | 59394 | NR | 710 | 22282 | NR | 840 | 1774 | NR | 970 | 1795 | NR |
| 455 | 31939 | NR | 585 | 61139 | NR | 715 | 19778 | NR | 845 | 1483 | NR | 975 | 2363 | NR |
| 460 | 23216 | NR | 590 | 63214 | NR | 720 | 17396 | NR | 850 | 1630 | NR | 980 | 1601 | NR |
| 465 | 19706 | NR | 595 | 66121 | NR | 725 | 15186 | NR | 855 | 1763 | NR | 985 | 1282 | NR |
| 470 | 17657 | NR | 600 | 68559 | NR | 730 | 13540 | NR | 860 | 1852 | NR | 990 | 2177 | NR |
| 475 | 15359 | NR | 605 | 71420 | NR | 735 | 11700 | NR | 865 | 1735 | NR | 995 | 970 | NR |
| 480 | 15859 | NR | 610 | 74391 | NR | 740 | 10401 | NR | 870 | 2047 | NR | 1000 | 2032 | NR |
| 485 | 18528 | NR | 615 | 76685 | NR | 745 | 9147 | NR | 875 | 1930 | NR | | | |

REPORT NUMBER: SP1-2401-290-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5310.4

S/P: 1.38

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1461 | NR | 490 | 21821 | NR | 620 | 77901 | NR | 750 | 8179 | NR | 880 | 1643 | NR |
| 365 | 1400 | NR | 495 | 25627 | NR | 625 | 79163 | NR | 755 | 7299 | NR | 885 | 1703 | NR |
| 370 | 1570 | NR | 500 | 29501 | NR | 630 | 79015 | NR | 760 | 6398 | NR | 890 | 1343 | NR |
| 375 | 1768 | NR | 505 | 32566 | NR | 635 | 78215 | NR | 765 | 5779 | NR | 895 | 1272 | NR |
| 380 | 1653 | NR | 510 | 34919 | NR | 640 | 77002 | NR | 770 | 4957 | NR | 900 | 1388 | NR |
| 385 | 1519 | NR | 515 | 37015 | NR | 645 | 74220 | NR | 775 | 4366 | NR | 905 | 1205 | NR |
| 390 | 1495 | NR | 520 | 39034 | NR | 650 | 71542 | NR | 780 | 3858 | NR | 910 | 1298 | NR |
| 395 | 1377 | NR | 525 | 40568 | NR | 655 | 67792 | NR | 785 | 3408 | NR | 915 | 1337 | NR |
| 400 | 1116 | NR | 530 | 42614 | NR | 660 | 63857 | NR | 790 | 3251 | NR | 920 | 1680 | NR |
| 405 | 1027 | NR | 535 | 44347 | NR | 665 | 59357 | NR | 795 | 3012 | NR | 925 | 1293 | NR |
| 410 | 1056 | NR | 540 | 46106 | NR | 670 | 54656 | NR | 800 | 2808 | NR | 930 | 1369 | NR |
| 415 | 1393 | NR | 545 | 48203 | NR | 675 | 49862 | NR | 805 | 2550 | NR | 935 | 1382 | NR |
| 420 | 2045 | NR | 550 | 50008 | NR | 680 | 45198 | NR | 810 | 2478 | NR | 940 | 1295 | NR |
| 425 | 3225 | NR | 555 | 51782 | NR | 685 | 40716 | NR | 815 | 2341 | NR | 945 | 1425 | NR |
| 430 | 5118 | NR | 560 | 53082 | NR | 690 | 36247 | NR | 820 | 2409 | NR | 950 | 1783 | NR |
| 435 | 8200 | NR | 565 | 54447 | NR | 695 | 32175 | NR | 825 | 2301 | NR | 955 | 1148 | NR |
| 440 | 13442 | NR | 570 | 56050 | NR | 700 | 28460 | NR | 830 | 2205 | NR | 960 | 1184 | NR |
| 445 | 23157 | NR | 575 | 57513 | NR | 705 | 25105 | NR | 835 | 1768 | NR | 965 | 1637 | NR |
| 450 | 33968 | NR | 580 | 59394 | NR | 710 | 22282 | NR | 840 | 1774 | NR | 970 | 1795 | NR |
| 455 | 31939 | NR | 585 | 61139 | NR | 715 | 19778 | NR | 845 | 1483 | NR | 975 | 2363 | NR |
| 460 | 23216 | NR | 590 | 63214 | NR | 720 | 17396 | NR | 850 | 1630 | NR | 980 | 1601 | NR |
| 465 | 19706 | NR | 595 | 66121 | NR | 725 | 15186 | NR | 855 | 1763 | NR | 985 | 1282 | NR |
| 470 | 17657 | NR | 600 | 68559 | NR | 730 | 13540 | NR | 860 | 1852 | NR | 990 | 2177 | NR |
| 475 | 15359 | NR | 605 | 71420 | NR | 735 | 11700 | NR | 865 | 1735 | NR | 995 | 970 | NR |
| 480 | 15859 | NR | 610 | 74391 | NR | 740 | 10401 | NR | 870 | 2047 | NR | 1000 | 2032 | NR |
| 485 | 18528 | NR | 615 | 76685 | NR | 745 | 9147 | NR | 875 | 1930 | NR | | | |

REPORT NUMBER: SP1-2401-290-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2012.9

M/P: 0.52

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1461 | NR | 490 | 21821 | NR | 620 | 77901 | NR | 750 | 8179 | NR | 880 | 1643 | NR |
| 365 | 1400 | NR | 495 | 25627 | NR | 625 | 79163 | NR | 755 | 7299 | NR | 885 | 1703 | NR |
| 370 | 1570 | NR | 500 | 29501 | NR | 630 | 79015 | NR | 760 | 6398 | NR | 890 | 1343 | NR |
| 375 | 1768 | NR | 505 | 32566 | NR | 635 | 78215 | NR | 765 | 5779 | NR | 895 | 1272 | NR |
| 380 | 1653 | NR | 510 | 34919 | NR | 640 | 77002 | NR | 770 | 4957 | NR | 900 | 1388 | NR |
| 385 | 1519 | NR | 515 | 37015 | NR | 645 | 74220 | NR | 775 | 4366 | NR | 905 | 1205 | NR |
| 390 | 1495 | NR | 520 | 39034 | NR | 650 | 71542 | NR | 780 | 3858 | NR | 910 | 1298 | NR |
| 395 | 1377 | NR | 525 | 40568 | NR | 655 | 67792 | NR | 785 | 3408 | NR | 915 | 1337 | NR |
| 400 | 1116 | NR | 530 | 42614 | NR | 660 | 63857 | NR | 790 | 3251 | NR | 920 | 1680 | NR |
| 405 | 1027 | NR | 535 | 44347 | NR | 665 | 59357 | NR | 795 | 3012 | NR | 925 | 1293 | NR |
| 410 | 1056 | NR | 540 | 46106 | NR | 670 | 54656 | NR | 800 | 2808 | NR | 930 | 1369 | NR |
| 415 | 1393 | NR | 545 | 48203 | NR | 675 | 49862 | NR | 805 | 2550 | NR | 935 | 1382 | NR |
| 420 | 2045 | NR | 550 | 50008 | NR | 680 | 45198 | NR | 810 | 2478 | NR | 940 | 1295 | NR |
| 425 | 3225 | NR | 555 | 51782 | NR | 685 | 40716 | NR | 815 | 2341 | NR | 945 | 1425 | NR |
| 430 | 5118 | NR | 560 | 53082 | NR | 690 | 36247 | NR | 820 | 2409 | NR | 950 | 1783 | NR |
| 435 | 8200 | NR | 565 | 54447 | NR | 695 | 32175 | NR | 825 | 2301 | NR | 955 | 1148 | NR |
| 440 | 13442 | NR | 570 | 56050 | NR | 700 | 28460 | NR | 830 | 2205 | NR | 960 | 1184 | NR |
| 445 | 23157 | NR | 575 | 57513 | NR | 705 | 25105 | NR | 835 | 1768 | NR | 965 | 1637 | NR |
| 450 | 33968 | NR | 580 | 59394 | NR | 710 | 22282 | NR | 840 | 1774 | NR | 970 | 1795 | NR |
| 455 | 31939 | NR | 585 | 61139 | NR | 715 | 19778 | NR | 845 | 1483 | NR | 975 | 2363 | NR |
| 460 | 23216 | NR | 590 | 63214 | NR | 720 | 17396 | NR | 850 | 1630 | NR | 980 | 1601 | NR |
| 465 | 19706 | NR | 595 | 66121 | NR | 725 | 15186 | NR | 855 | 1763 | NR | 985 | 1282 | NR |
| 470 | 17657 | NR | 600 | 68559 | NR | 730 | 13540 | NR | 860 | 1852 | NR | 990 | 2177 | NR |
| 475 | 15359 | NR | 605 | 71420 | NR | 735 | 11700 | NR | 865 | 1735 | NR | 995 | 970 | NR |
| 480 | 15859 | NR | 610 | 74391 | NR | 740 | 10401 | NR | 870 | 2047 | NR | 1000 | 2032 | NR |
| 485 | 18528 | NR | 615 | 76685 | NR | 745 | 9147 | NR | 875 | 1930 | NR | | | |

REPORT NUMBER: SP1-2401-290-2

TM-30-18

Summary

$R_f = 93.8$
 $R_g = 99.3$
 $CIE R_a = 94.7$
 $R_9 = 72.1$



Color Vector Graphics



REPORT NUMBER: SP1-2401-290-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|-------------|------------|
| CES01 = 86 | CES26 = 96 | CES51 = 98 | CES76 = 91 |
| CES02 = 63 | CES27 = 93 | CES52 = 100 | CES77 = 92 |
| CES03 = 32 | CES28 = 97 | CES53 = 98 | CES78 = 88 |
| CES04 = 70 | CES29 = 97 | CES54 = 95 | CES79 = 96 |
| CES05 = 51 | CES30 = 94 | CES55 = 94 | CES80 = 95 |
| CES06 = 51 | CES31 = 97 | CES56 = 96 | CES81 = 87 |
| CES07 = 44 | CES32 = 93 | CES57 = 95 | CES82 = 98 |
| CES08 = 43 | CES33 = 99 | CES58 = 96 | CES83 = 97 |
| CES09 = 29 | CES34 = 96 | CES59 = 98 | CES84 = 96 |
| CES10 = 76 | CES35 = 98 | CES60 = 95 | CES85 = 86 |
| CES11 = 59 | CES36 = 86 | CES61 = 94 | CES86 = 89 |
| CES12 = 65 | CES37 = 95 | CES62 = 91 | CES87 = 94 |
| CES13 = 44 | CES38 = 90 | CES63 = 95 | CES88 = 97 |
| CES14 = 74 | CES39 = 99 | CES64 = 93 | CES89 = 89 |
| CES15 = 72 | CES40 = 98 | CES65 = 92 | CES90 = 97 |
| CES16 = 48 | CES41 = 98 | CES66 = 91 | CES91 = 81 |
| CES17 = 50 | CES42 = 96 | CES67 = 91 | CES92 = 85 |
| CES18 = 57 | CES43 = 97 | CES68 = 91 | CES93 = 91 |
| CES19 = 72 | CES44 = 99 | CES69 = 92 | CES94 = 84 |
| CES20 = 67 | CES45 = 99 | CES70 = 90 | CES95 = 88 |
| CES21 = 86 | CES46 = 98 | CES71 = 87 | CES96 = 94 |
| CES22 = 79 | CES47 = 95 | CES72 = 96 | CES97 = 96 |
| CES23 = 92 | CES48 = 94 | CES73 = 86 | CES98 = 96 |
| CES24 = 91 | CES49 = 97 | CES74 = 92 | CES99 = 94 |
| CES25 = 72 | CES50 = 99 | CES75 = 88 | |



REPORT NUMBER: SP1-2401-290-2

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2401-290-2

TM-30-18

Measure Comparisons



(END OF REPORT)