

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331604-927

Luminaire Tested: **S122DIW-S1005D1240U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331604-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1240U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6893.4 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



49% Up
51% Dn



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44	44	44	44	
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37	37	37	37	
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32	32	32	32	
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28	28	28	28	
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25	25	25	25	
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22	22	22	22	
7	60	48	40	34	55	44	38	33	39	33	29	33	29	26	28	25	22	20	20	20	20	
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18	18	18	18	
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16	16	16	16	
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15	15	15	15	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25504	25504	25504	25504
5°	28593	25671	22749	25671
10°	32765	25460	19687	25460
15°	36247	24993	17392	24993
20°	35696	24493	15856	24493
25°	32186	23826	14883	23826
30°	26597	22760	14171	22760
35°	19385	21646	13665	21646
40°	15483	20331	13384	20331
45°	13531	18810	13001	18810
50°	12717	17337	12750	17337
55°	11724	15842	12408	15842
60°	10743	14250	11880	14250
65°	9788	12825	11366	12825
70°	8884	11434	10607	11434
75°	7879	9881	9395	9881
80°	6778	8182	7569	8182
85°	6076	6076	4502	6076



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.4	2.2
10°-20°	437.4	6.3
20°-30°	634.7	9.2
30°-40°	669.8	9.7
40°-50°	593.0	8.6
50°-60°	473.3	6.9
60°-70°	321.7	4.7
70°-80°	164.9	2.4
80°-90°	44.6	0.6
90°-100°	77.1	1.1
100°-110°	239.6	3.5
110°-120°	409.5	5.9
120°-130°	538.5	7.8
130°-140°	604.4	8.8
140°-150°	592.6	8.6
150°-160°	497.0	7.2
160°-170°	329.7	4.8
170°-180°	115.2	1.7
0°-30°	1222.5	17.7
0°-40°	1892.3	27.5
0°-60°	2958.6	42.9
0°-90°	3489.9	50.6
90°-120°	726.2	10.5
90°-150°	2461.6	35.7
90°-180°	3404.0	49.4
0°-180°	6893.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1580	1580	1580	1580	1580	
5°	1764	1584	1404	1584	1764	176
15°	2168	1495	1040	1495	2168	598
25°	1807	1337	835	1337	1807	817
35°	984	1098	693	1098	984	640
45°	593	824	569	824	593	466
55°	416	563	441	563	416	373
65°	256	336	298	336	256	255
75°	126	158	151	158	126	135
85°	33	33	24	33	33	37
90°	35	1	35	1	35	17
95°	64	53	64	53	64	71
105°	228	221	228	221	228	240
115°	411	411	411	411	411	406
125°	600	598	600	598	600	535
135°	783	774	783	774	783	602
145°	949	939	949	939	949	593
155°	1082	1073	1082	1073	1082	498
165°	1169	1168	1169	1168	1169	330
175°	1211	1215	1211	1215	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1652.5	1653.0	1653.9	1646.2	1645.2	1645.2	1638.4	1632.6	1625.8	1616.5	1617.6
5°	1764.2	1770.8	1773.3	1766.0	1755.1	1753.9	1743.6	1726.6	1710.8	1698.0	1688.9
7.5°	1897.5	1900.2	1894.3	1884.7	1876.5	1861.9	1842.8	1823.9	1797.6	1773.5	1755.5
10°	1998.5	2002.2	1991.9	1977.9	1966.4	1949.4	1921.4	1892.9	1858.3	1825.0	1798.2
12.5°	2075.3	2084.2	2071.0	2069.2	2049.5	2026.1	1992.8	1978.4	1929.7	1883.2	1854.6
15°	2168.5	2167.9	2169.2	2157.6	2143.0	2139.4	2104.2	2065.9	1997.3	1970.0	1922.6
17.5°	2141.6	2150.8	2155.1	2154.9	2154.6	2152.3	2141.0	2116.8	2082.4	2038.1	1983.5
20°	2077.5	2089.6	2091.4	2105.4	2113.3	2123.6	2127.9	2121.1	2099.9	2062.9	2015.5
22.5°	1978.4	1981.8	1987.5	2009.2	2026.3	2052.2	2065.7	2088.1	2080.0	2061.9	2022.4
25°	1806.7	1800.6	1821.9	1832.8	1872.2	1913.5	1943.3	1976.1	2005.3	2022.8	2011.3
27.5°	1600.5	1591.4	1623.3	1652.3	1684.3	1729.0	1775.4	1830.1	1875.7	1932.6	1952.2
30°	1426.6	1432.1	1462.4	1493.4	1542.0	1605.1	1657.3	1717.5	1782.4	1846.2	1890.5
32.5°	1239.2	1260.2	1279.4	1326.8	1369.6	1440.0	1516.5	1591.7	1672.7	1745.2	1813.8
35°	983.5	1007.7	1034.5	1069.1	1129.2	1199.0	1273.7	1375.1	1485.6	1584.5	1665.9
37.5°	827.8	823.9	839.2	864.3	912.9	969.3	1055.3	1155.4	1285.5	1401.8	1516.5
40°	734.6	732.1	743.1	766.1	803.2	844.5	919.7	1007.7	1128.5	1270.7	1407.2
42.5°	670.5	671.9	678.0	694.3	719.6	753.6	810.0	884.9	995.5	1129.3	1276.1
45°	592.6	596.8	603.5	611.3	625.9	653.9	685.4	738.9	826.2	937.9	1082.4
47.5°	536.4	536.5	543.4	550.2	558.9	574.6	600.4	633.9	695.6	786.6	910.8
50°	506.3	502.1	506.9	512.4	521.5	532.4	549.4	581.0	622.3	695.7	799.5
52.5°	469.4	469.5	473.9	475.9	484.1	495.0	510.6	532.4	569.8	627.2	712.6
55°	416.5	419.5	421.9	425.6	432.8	440.8	452.9	467.5	496.6	539.7	602.9
57.5°	366.7	367.7	370.1	377.0	381.6	388.9	400.4	413.7	432.6	464.5	512.0
60°	332.7	332.7	337.5	340.6	346.7	353.9	363.1	375.8	392.8	418.9	457.2
62.5°	301.6	301.1	303.1	308.0	312.7	319.5	328.5	339.4	355.4	378.6	410.0
65°	256.2	255.0	258.6	259.8	264.7	271.4	278.7	290.2	302.9	320.0	347.8
67.5°	212.5	214.0	215.9	218.2	220.9	227.9	232.7	240.9	251.7	265.8	284.7
70°	188.2	188.2	188.2	190.0	193.7	197.3	202.2	208.8	219.2	231.3	248.3
72.5°	161.0	163.0	164.9	163.8	168.4	170.6	176.4	180.2	190.0	197.8	212.9
75°	126.3	126.3	126.3	129.3	131.1	132.9	136.6	140.2	145.1	154.8	162.7
77.5°	94.2	94.0	94.6	95.3	97.3	99.4	100.5	103.8	108.3	112.8	119.5
80°	72.9	74.1	74.7	75.9	75.9	77.1	77.7	82.0	85.0	88.0	92.3
82.5°	56.3	56.6	56.7	57.0	57.4	58.1	59.7	61.1	62.2	64.7	68.0
85°	32.8	32.2	32.2	33.4	32.8	32.8	34.0	35.2	35.2	35.8	37.6
87.5°	19.6	19.6	20.0	19.5	19.4	20.0	20.0	19.6	20.2	20.8	20.3
90°	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0	35.5	36.0	30.9
92.5°	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9	32.7	32.6	31.4
95°	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8	65.8	65.8	65.3
97.5°	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5	110.5	110.5	109.6
100°	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7	141.7	141.7	141.1
102.5°	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8	175.6	175.5	174.6
105°	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9	226.4	226.0	225.5
107.5°	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0	281.9	281.6	281.6
110°	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0	357.5	358.1	358.2
115°	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5	414.8	414.9	415.4
117.5°	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2	470.7	471.3	472.5
120°	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4	507.4	507.4	509.2
122.5°	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8	546.3	546.8	548.1
125°	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6	603.3	604.0	604.7
127.5°	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8	658.6	659.4	660.3
130°	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5	695.9	696.4	696.9
132.5°	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2	733.2	734.2	734.1
135°	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4	786.6	786.8	786.4
137.5°	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2	838.4	838.6	838.0
140°	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1	873.1	873.1	872.0
142.5°	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7	904.5	904.4	903.6
145°	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7	952.4	952.2	950.9
147.5°	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7	994.2	993.7	992.8
150°	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0	1019.1
152.5°	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3	1045.2
155°	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9	1080.7	1079.6	1078.9
157.5°	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1	1111.5	1110.0	1109.5
160°	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6	1130.2	1128.9	1128.6
162.5°	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4	1146.8	1145.3	1145.1
165°	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1	1168.5	1166.9	1166.9
167.5°	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0	1186.4	1184.7	1184.8
170°	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8	1196.2	1194.6	1194.8
172.5°	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2	1203.6	1202.0	1202.2
175°	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2	1211.6	1210.0	1210.5
177.5°	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7	1215.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1621.0	1617.1	1614.6	1605.9	1598.1	1590.3	1587.9	1588.9	1578.2	1568.0	1563.6
5°	1684.1	1671.9	1660.4	1644.0	1624.6	1603.3	1592.4	1583.9	1562.7	1539.6	1526.2
7.5°	1740.7	1723.3	1701.1	1670.2	1642.0	1608.5	1587.3	1568.4	1537.4	1504.8	1484.9
10°	1775.1	1751.4	1722.9	1685.3	1650.7	1610.0	1581.4	1552.9	1516.5	1477.7	1453.3
12.5°	1804.7	1772.8	1744.8	1696.5	1655.5	1604.6	1570.8	1530.6	1492.2	1446.0	1422.3
15°	1875.3	1816.4	1763.0	1708.3	1658.0	1586.9	1549.3	1495.2	1444.9	1387.8	1360.5
17.5°	1929.8	1863.6	1779.5	1710.1	1651.3	1572.6	1517.3	1452.6	1393.1	1327.9	1290.7
20°	1960.9	1885.0	1794.5	1712.0	1641.6	1551.7	1491.6	1425.5	1355.7	1282.1	1242.1
22.5°	1979.3	1899.6	1810.1	1704.7	1622.2	1534.7	1459.0	1386.6	1315.8	1236.5	1194.5
25°	1985.2	1912.3	1817.7	1698.7	1597.8	1498.9	1407.9	1337.4	1251.8	1177.7	1116.4
27.5°	1956.3	1904.1	1813.0	1687.2	1569.8	1454.1	1352.6	1272.8	1182.5	1102.1	1040.5
30°	1920.8	1890.5	1801.8	1675.5	1547.4	1423.0	1311.3	1220.8	1131.0	1049.6	986.5
32.5°	1866.0	1859.4	1781.5	1659.1	1523.7	1383.7	1268.1	1176.6	1077.1	997.2	937.0
35°	1758.2	1787.2	1738.1	1622.2	1478.8	1327.7	1202.6	1098.2	995.1	918.5	862.1
37.5°	1613.7	1686.0	1673.2	1568.1	1418.4	1266.8	1128.7	1019.5	921.2	844.0	788.6
40°	1514.1	1606.4	1619.7	1526.9	1375.7	1219.6	1073.3	964.6	868.7	798.4	742.4
42.5°	1407.2	1515.0	1551.7	1477.3	1329.0	1170.1	1023.8	911.2	816.3	747.8	698.3
45°	1228.1	1370.8	1437.0	1394.5	1251.3	1088.5	937.9	823.8	737.6	673.3	635.0
47.5°	1060.7	1216.6	1305.6	1290.5	1164.7	1003.5	854.7	745.1	661.2	609.9	575.7
50°	942.2	1102.5	1209.9	1214.8	1102.5	942.8	793.4	690.2	613.1	565.2	537.3
52.5°	839.2	992.2	1109.4	1135.1	1033.0	879.6	738.6	635.9	568.0	523.9	498.9
55°	704.8	834.2	964.1	1011.4	929.5	783.8	653.2	562.8	499.0	468.7	446.8
57.5°	586.0	693.8	813.7	866.1	815.6	690.9	568.5	489.9	438.2	411.6	394.8
60°	523.3	608.3	715.2	777.7	734.0	622.9	516.0	441.3	398.9	375.2	359.4
62.5°	465.0	540.3	630.7	687.9	664.0	559.3	463.6	397.7	361.0	338.7	327.3
65°	383.7	443.1	513.0	565.8	550.0	470.5	392.2	335.7	306.6	289.0	279.9
67.5°	315.9	358.9	407.3	453.6	440.8	384.5	321.6	277.7	256.0	240.7	235.3
70°	273.2	305.9	349.1	386.1	375.8	329.6	279.9	242.2	223.4	210.6	205.2
72.5°	232.4	259.4	292.2	322.5	315.5	277.2	235.7	207.2	192.8	181.0	176.6
75°	175.5	196.1	216.1	236.1	234.3	204.6	180.3	158.4	146.9	137.8	136.0
77.5°	129.5	141.1	154.7	166.6	163.3	146.3	127.2	114.7	106.2	100.1	99.2
80°	98.9	105.6	115.3	123.8	119.6	112.3	97.1	88.0	82.0	75.9	73.4
82.5°	71.8	78.4	84.3	88.9	85.6	78.8	69.5	63.3	59.7	55.5	54.5
85°	37.6	41.3	43.7	44.9	43.7	39.5	35.2	32.8	29.8	28.0	27.3
87.5°	19.7	18.8	17.7	17.9	15.9	15.4	12.9	10.9	10.9	11.0	10.6
90°	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0	3.8	6.5	9.3
92.5°	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3	20.3	22.3	24.3
95°	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4	55.7	58.0	60.3
97.5°	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6	99.6	101.6	103.6
100°	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5	132.3	134.1	135.9
102.5°	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9	166.4	167.9	169.4
105°	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9	221.5	222.2	222.9
107.5°	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1	278.1	279.2	280.1
110°	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3	314.7	316.0	317.4



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8	354.1	355.5	356.9
115°	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9	412.3	413.6	414.9
117.5°	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8	470.6	472.5	474.3
120°	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	509.2	511.1	512.9
122.5°	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7	544.9	547.2	549.3
125°	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8	599.8	601.9	604.0
127.5°	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4	654.0	656.6	659.3
130°	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2	688.1	691.1	694.0
132.5°	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9	725.3	727.8	730.2
135°	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5	775.9	778.5	781.0
137.5°	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6	828.7	830.8	832.8
140°	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7	860.8	862.8	864.9
142.5°	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6	893.7	895.7	897.8
145°	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8	940.5	942.1	943.6
147.5°	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0	982.9	984.8	986.7
150°	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7	1011.1	1012.5	1013.8
152.5°	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2	1036.6	1037.9	1039.3
155°	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4	1074.1	1074.8	1075.5
157.5°	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0	1106.5	1107.0	1107.5
160°	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8	1126.2	1126.7	1127.2
162.5°	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8	1144.0	1144.1	1144.1
165°	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9	1167.7	1167.4	1167.2
167.5°	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0	1187.3	1186.7	1186.0
170°	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7	1198.0	1197.4	1196.7
172.5°	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1	1205.5	1204.8	1204.0
175°	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1	1214.5	1213.8	1213.1
177.5°	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9	1218.3	1217.7	1217.2
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1558.8	1555.8	1545.6	1540.3	1531.6	1523.3	1518.0	1520.4	1522.3	1521.4	1519.9
5°	1514.1	1502.5	1484.9	1469.7	1458.8	1438.8	1430.3	1426.1	1422.4	1418.2	1413.9
7.5°	1460.9	1442.7	1417.5	1395.8	1375.4	1350.5	1336.3	1327.9	1319.1	1309.5	1301.0
10°	1423.0	1397.5	1370.8	1340.5	1316.2	1293.7	1273.7	1260.3	1248.2	1236.7	1228.1
12.5°	1383.2	1353.8	1320.8	1279.3	1252.5	1220.4	1217.3	1193.8	1174.8	1167.7	1157.7
15°	1319.8	1278.5	1236.7	1187.5	1166.3	1137.1	1118.9	1100.7	1084.3	1072.7	1069.7
17.5°	1247.8	1194.4	1152.7	1117.4	1082.6	1052.7	1035.9	1021.4	1007.9	992.4	990.4
20°	1192.9	1146.8	1101.3	1070.3	1034.5	1004.1	983.5	968.9	957.4	948.2	940.4
22.5°	1141.0	1090.4	1048.8	1014.9	979.6	955.1	938.8	924.7	915.1	905.1	897.6
25°	1057.6	1018.1	972.6	934.3	905.1	889.4	876.0	863.9	857.9	851.1	842.6
27.5°	984.6	940.7	898.1	868.5	842.9	828.9	819.4	811.2	805.5	801.6	796.8
30°	933.1	888.7	855.4	826.2	805.0	791.1	785.0	780.1	773.4	771.0	768.6
32.5°	883.5	843.6	815.1	789.8	769.5	760.4	754.9	750.5	745.3	742.8	738.0
35°	813.5	780.1	752.2	738.2	721.8	713.9	709.7	703.6	698.8	696.3	695.7
37.5°	747.6	718.6	700.2	682.2	675.3	670.5	664.6	660.5	659.1	658.7	658.1
40°	704.8	681.1	664.8	650.2	647.1	639.8	635.0	631.4	631.4	632.0	631.4
42.5°	666.0	644.8	630.3	617.7	614.1	609.7	604.9	604.7	605.6	607.7	605.6
45°	607.1	591.9	581.6	575.5	568.9	564.6	564.0	565.8	566.4	567.0	568.9
47.5°	552.9	542.9	533.5	526.8	523.9	523.2	522.4	525.6	528.5	529.7	532.4
50°	520.9	509.4	501.5	497.2	494.8	493.5	494.8	498.4	500.8	503.9	505.7
52.5°	485.0	476.8	471.3	468.1	467.1	467.9	468.1	472.2	476.1	477.2	478.0
55°	435.3	429.2	428.0	422.6	424.9	424.4	427.4	429.8	433.5	437.1	437.7
57.5°	385.7	380.9	377.6	378.1	378.8	381.5	384.0	388.3	392.2	396.1	396.4
60°	352.8	350.3	348.5	348.5	349.7	353.3	356.3	360.6	363.1	365.4	367.3
62.5°	322.6	320.2	318.4	319.3	322.5	324.6	328.2	330.5	333.0	335.3	336.2
65°	275.0	273.8	275.6	276.9	277.4	280.5	284.7	286.5	289.0	290.2	294.5
67.5°	231.2	231.4	231.2	232.9	236.4	237.1	241.1	245.4	245.9	248.2	251.0
70°	201.5	202.8	204.0	205.2	208.3	209.5	212.5	214.3	216.7	218.6	220.4
72.5°	174.4	174.6	175.8	175.5	178.1	180.8	183.3	185.1	187.6	189.9	191.7
75°	134.2	134.2	135.4	136.0	139.0	142.0	141.5	142.7	145.1	147.5	148.8
77.5°	98.0	96.6	98.0	98.6	99.6	102.1	102.6	104.3	107.1	106.2	107.6
80°	74.7	72.9	74.7	75.3	75.3	78.3	78.3	79.5	81.4	79.5	81.4
82.5°	53.3	52.4	53.8	53.9	54.9	55.0	56.0	56.2	58.1	57.2	58.1
85°	26.7	26.1	26.7	26.1	26.7	27.3	27.3	26.7	26.7	28.0	26.1
87.5°	10.6	10.9	11.5	12.4	13.0	13.5	12.9	12.8	12.8	11.6	11.6
90°	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0	34.6	34.1	34.0
92.5°	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9	33.0	33.0	33.1
95°	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8	65.8	65.8	65.5
97.5°	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5	110.5	110.5	110.5
100°	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7	141.7	141.7	141.6
102.5°	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8	176.0	176.2	176.2
105°	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9	227.4	227.8	228.1
107.5°	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0	282.2	282.4	281.9
110°	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.1



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0	356.4	355.8	355.4
115°	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5	414.3	414.1	413.6
117.5°	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2	469.6	469.1	468.5
120°	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4	507.4	507.4	507.1
122.5°	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8	545.3	544.7	544.2
125°	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6	601.9	601.3	600.8
127.5°	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8	657.0	656.2	655.4
130°	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5	695.1	694.6	694.0
132.5°	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2	731.2	730.2	729.4
135°	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4	786.2	785.9	785.4
137.5°	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2	838.0	837.9	837.3
140°	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1	873.1	873.1	872.7
142.5°	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7	904.9	905.1	904.7
145°	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7	952.9	953.1	952.8
147.5°	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7	995.2	995.7	995.5
150°	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7
152.5°	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7
155°	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9	1083.0	1084.1	1084.3
157.5°	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1	1114.6	1116.2	1116.4
160°	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6	1133.0	1134.3	1134.6
162.5°	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4	1149.9	1151.5	1151.8
165°	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1	1171.6	1173.3	1173.5
167.5°	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0	1189.5	1191.1	1191.4
170°	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8	1199.4	1201.0	1201.1
172.5°	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2	1206.8	1208.4	1208.5
175°	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2	1214.8	1216.4	1216.6
177.5°	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1515.0	1514.1	1514.1	1509.7	1514.1	1514.1	1515.0	1519.9	1521.4	1522.3	1520.4
5°	1405.4	1403.6	1400.6	1403.6	1400.6	1403.6	1405.4	1413.9	1418.2	1422.4	1426.1
7.5°	1297.0	1289.7	1288.6	1281.4	1288.6	1289.7	1297.0	1301.0	1309.5	1319.1	1327.9
10°	1217.8	1213.0	1212.4	1200.8	1212.4	1213.0	1217.8	1228.1	1236.7	1248.2	1260.3
12.5°	1157.6	1146.0	1148.3	1141.5	1148.3	1146.0	1157.6	1157.7	1167.7	1174.8	1193.8
15°	1053.3	1053.3	1050.9	1040.5	1050.9	1053.3	1053.3	1069.7	1072.7	1084.3	1100.7
17.5°	978.4	977.2	971.4	974.2	971.4	977.2	978.4	990.4	992.4	1007.9	1021.4
20°	933.7	930.1	922.8	922.8	922.8	930.1	933.7	940.4	948.2	957.4	968.9
22.5°	891.4	891.2	883.4	885.9	883.4	891.2	891.4	897.6	905.1	915.1	924.7
25°	842.0	837.2	833.5	835.4	833.5	837.2	842.0	842.6	851.1	857.9	863.9
27.5°	795.2	792.5	792.3	787.3	792.3	792.5	795.2	796.8	801.6	805.5	811.2
30°	767.9	761.9	763.1	760.1	763.1	761.9	767.9	768.6	771.0	773.4	780.1
32.5°	736.9	734.7	733.5	730.9	733.5	734.7	736.9	738.0	742.8	745.3	750.5
35°	694.5	695.1	692.1	693.3	692.1	695.1	694.5	695.7	696.3	698.8	703.6
37.5°	657.5	659.4	658.0	658.3	658.0	659.4	657.5	658.1	658.7	659.1	660.5
40°	633.2	633.2	633.2	635.0	633.2	633.2	633.2	631.4	632.0	631.4	631.4
42.5°	609.9	609.0	607.9	607.8	607.9	609.0	609.9	605.6	607.7	605.6	604.7
45°	570.1	571.9	572.5	569.4	572.5	571.9	570.1	568.9	567.0	566.4	565.8
47.5°	534.0	534.2	534.0	536.7	534.0	534.2	534.0	532.4	529.7	528.5	525.6
50°	508.7	507.6	508.7	507.6	508.7	507.6	508.7	505.7	503.9	500.8	498.4
52.5°	482.0	482.3	481.6	481.3	481.6	482.3	482.0	478.0	477.2	476.1	472.2
55°	440.1	441.3	440.8	440.8	440.8	441.3	440.1	437.7	437.1	433.5	429.8
57.5°	396.8	397.9	398.7	396.1	398.7	397.9	396.8	396.4	396.1	392.2	388.3
60°	366.7	369.7	369.1	367.9	369.1	369.7	366.7	367.3	365.4	363.1	360.6
62.5°	339.0	340.1	340.0	339.8	340.0	340.1	339.0	336.2	335.3	333.0	330.5
65°	296.3	297.5	295.6	297.5	295.6	297.5	296.3	294.5	290.2	289.0	286.5
67.5°	250.3	250.6	251.9	252.8	251.9	250.6	250.3	251.0	248.2	245.9	245.4
70°	221.6	221.0	222.8	224.7	222.8	221.0	221.6	220.4	218.6	216.7	214.3
72.5°	191.5	192.8	192.2	193.5	192.2	192.8	191.5	191.7	189.9	187.6	185.1
75°	147.5	149.3	148.8	150.6	148.8	149.3	147.5	148.8	147.5	145.1	142.7
77.5°	106.6	106.9	106.6	107.6	106.6	106.9	106.6	107.6	106.2	107.1	104.3
80°	81.4	80.2	78.9	81.4	78.9	80.2	81.4	81.4	79.5	81.4	79.5
82.5°	56.6	57.3	56.1	56.1	56.1	57.3	56.6	58.1	57.2	58.1	56.2
85°	26.1	25.5	24.3	24.3	24.3	25.5	26.1	26.1	28.0	26.7	26.7
87.5°	11.7	11.2	11.3	10.9	11.3	11.2	11.7	11.6	11.6	12.8	12.8
90°	34.2	34.5	34.7	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0
92.5°	33.1	33.2	33.3	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9
95°	65.0	64.6	64.2	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8
97.5°	110.4	110.4	110.4	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5
100°	141.4	141.2	140.9	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7
102.5°	175.9	175.7	175.5	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8
105°	228.1	228.1	228.1	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9
107.5°	280.9	279.9	278.8	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0
110°	318.5	317.7	317.0	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	354.8	354.3	353.9	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0
115°	413.0	412.3	411.5	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5
117.5°	467.8	467.1	466.4	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2
120°	506.4	505.7	505.0	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4
122.5°	543.7	543.1	542.6	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8
125°	600.6	600.3	600.1	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6
127.5°	654.7	653.9	653.2	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8
130°	693.0	692.1	691.2	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5
132.5°	728.6	727.9	727.1	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2
135°	784.7	784.1	783.4	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4
137.5°	836.4	835.5	834.6	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2
140°	871.7	870.8	869.9	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1
142.5°	903.8	902.9	902.0	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7
145°	951.9	950.9	950.1	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7
147.5°	994.7	993.8	992.9	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7
150°	1022.1	1021.4	1020.6	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4
152.5°	1048.8	1048.1	1047.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1
155°	1083.7	1083.0	1082.3	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9
157.5°	1115.3	1114.2	1113.1	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1
160°	1133.7	1132.7	1131.9	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6
162.5°	1150.6	1149.5	1148.4	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4
165°	1172.4	1171.2	1170.1	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1
167.5°	1190.2	1189.0	1187.8	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0
170°	1199.8	1198.4	1197.0	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8
172.5°	1207.1	1205.8	1204.4	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2
175°	1215.1	1213.8	1212.4	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2
177.5°	1218.1	1217.0	1215.8	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1518.0	1523.3	1531.6	1540.3	1545.6	1555.8	1558.8	1563.6	1568.0	1578.2	1588.9
5°	1430.3	1438.8	1458.8	1469.7	1484.9	1502.5	1514.1	1526.2	1539.6	1562.7	1583.9
7.5°	1336.3	1350.5	1375.4	1395.8	1417.5	1442.7	1460.9	1484.9	1504.8	1537.4	1568.4
10°	1273.7	1293.7	1316.2	1340.5	1370.8	1397.5	1423.0	1453.3	1477.7	1516.5	1552.9
12.5°	1217.3	1220.4	1252.5	1279.3	1320.8	1353.8	1383.2	1422.3	1446.0	1492.2	1530.6
15°	1118.9	1137.1	1166.3	1187.5	1236.7	1278.5	1319.8	1360.5	1387.8	1444.9	1495.2
17.5°	1035.9	1052.7	1082.6	1117.4	1152.7	1194.4	1247.8	1290.7	1327.9	1393.1	1452.6
20°	983.5	1004.1	1034.5	1070.3	1101.3	1146.8	1192.9	1242.1	1282.1	1355.7	1425.5
22.5°	938.8	955.1	979.6	1014.9	1048.8	1090.4	1141.0	1194.5	1236.5	1315.8	1386.6
25°	876.0	889.4	905.1	934.3	972.6	1018.1	1057.6	1116.4	1177.7	1251.8	1337.4
27.5°	819.4	828.9	842.9	868.5	898.1	940.7	984.6	1040.5	1102.1	1182.5	1272.8
30°	785.0	791.1	805.0	826.2	855.4	888.7	933.1	986.5	1049.6	1131.0	1220.8
32.5°	754.9	760.4	769.5	789.8	815.1	843.6	883.5	937.0	997.2	1077.1	1176.6
35°	709.7	713.9	721.8	738.2	752.2	780.1	813.5	862.1	918.5	995.1	1098.2
37.5°	664.6	670.5	675.3	682.2	700.2	718.6	747.6	788.6	844.0	921.2	1019.5
40°	635.0	639.8	647.1	650.2	664.8	681.1	704.8	742.4	798.4	868.7	964.6
42.5°	604.9	609.7	614.1	617.7	630.3	644.8	666.0	698.3	747.8	816.3	911.2
45°	564.0	564.6	568.9	575.5	581.6	591.9	607.1	635.0	673.3	737.6	823.8
47.5°	522.4	523.2	523.9	526.8	533.5	542.9	552.9	575.7	609.9	661.2	745.1
50°	494.8	493.5	494.8	497.2	501.5	509.4	520.9	537.3	565.2	613.1	690.2
52.5°	468.1	467.9	467.1	468.1	471.3	476.8	485.0	498.9	523.9	568.0	635.9
55°	427.4	424.4	424.9	422.6	428.0	429.2	435.3	446.8	468.7	499.0	562.8
57.5°	384.0	381.5	378.8	378.1	377.6	380.9	385.7	394.8	411.6	438.2	489.9
60°	356.3	353.3	349.7	348.5	348.5	350.3	352.8	359.4	375.2	398.9	441.3
62.5°	328.2	324.6	322.5	319.3	318.4	320.2	322.6	327.3	338.7	361.0	397.7
65°	284.7	280.5	277.4	276.9	275.6	273.8	275.0	279.9	289.0	306.6	335.7
67.5°	241.1	237.1	236.4	232.9	231.2	231.4	231.2	235.3	240.7	256.0	277.7
70°	212.5	209.5	208.3	205.2	204.0	202.8	201.5	205.2	210.6	223.4	242.2
72.5°	183.3	180.8	178.1	175.5	175.8	174.6	174.4	176.6	181.0	192.8	207.2
75°	141.5	142.0	139.0	136.0	135.4	134.2	134.2	136.0	137.8	146.9	158.4
77.5°	102.6	102.1	99.6	98.6	98.0	96.6	98.0	99.2	100.1	106.2	114.7
80°	78.3	78.3	75.3	75.3	74.7	72.9	74.7	73.4	75.9	82.0	88.0
82.5°	56.0	55.0	54.9	53.9	53.8	52.4	53.3	54.5	55.5	59.7	63.3
85°	27.3	27.3	26.7	26.1	26.7	26.1	26.7	27.3	28.0	29.8	32.8
87.5°	12.9	13.5	13.0	12.4	11.5	10.9	10.6	10.6	11.0	10.9	10.9
90°	35.5	36.0	30.9	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0
92.5°	32.7	32.6	31.4	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3
95°	65.8	65.8	65.3	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4
97.5°	110.5	110.5	109.6	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6
100°	141.7	141.7	141.1	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5
102.5°	175.6	175.5	174.6	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9
105°	226.4	226.0	225.5	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9
107.5°	281.9	281.6	281.6	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1
110°	319.5	319.5	319.5	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	357.5	358.1	358.2	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8
115°	414.8	414.9	415.4	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9
117.5°	470.7	471.3	472.5	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8
120°	507.4	507.4	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4
122.5°	546.3	546.8	548.1	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7
125°	603.3	604.0	604.7	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8
127.5°	658.6	659.4	660.3	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4
130°	695.9	696.4	696.9	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2
132.5°	733.2	734.2	734.1	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9
135°	786.6	786.8	786.4	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5
137.5°	838.4	838.6	838.0	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6
140°	873.1	873.1	872.0	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7
142.5°	904.5	904.4	903.6	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6
145°	952.4	952.2	950.9	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8
147.5°	994.2	993.7	992.8	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0
150°	1020.6	1020.0	1019.1	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7
152.5°	1047.2	1046.3	1045.2	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2
155°	1080.7	1079.6	1078.9	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4
157.5°	1111.5	1110.0	1109.5	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0
160°	1130.2	1128.9	1128.6	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8
162.5°	1146.8	1145.3	1145.1	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8
165°	1168.5	1166.9	1166.9	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9
167.5°	1186.4	1184.7	1184.8	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0
170°	1196.2	1194.6	1194.8	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7
172.5°	1203.6	1202.0	1202.2	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1
175°	1211.6	1210.0	1210.5	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1
177.5°	1215.8	1214.7	1215.1	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1587.9	1590.3	1598.1	1605.9	1614.6	1617.1	1621.0	1617.6	1616.5	1625.8	1632.6
5°	1592.4	1603.3	1624.6	1644.0	1660.4	1671.9	1684.1	1688.9	1698.0	1710.8	1726.6
7.5°	1587.3	1608.5	1642.0	1670.2	1701.1	1723.3	1740.7	1755.5	1773.5	1797.6	1823.9
10°	1581.4	1610.0	1650.7	1685.3	1722.9	1751.4	1775.1	1798.2	1825.0	1858.3	1892.9
12.5°	1570.8	1604.6	1655.5	1696.5	1744.8	1772.8	1804.7	1854.6	1883.2	1929.7	1978.4
15°	1549.3	1586.9	1658.0	1708.3	1763.0	1816.4	1875.3	1922.6	1970.0	1997.3	2065.9
17.5°	1517.3	1572.6	1651.3	1710.1	1779.5	1863.6	1929.8	1983.5	2038.1	2082.4	2116.8
20°	1491.6	1551.7	1641.6	1712.0	1794.5	1885.0	1960.9	2015.5	2062.9	2099.9	2121.1
22.5°	1459.0	1534.7	1622.2	1704.7	1810.1	1899.6	1979.3	2022.4	2061.9	2080.0	2088.1
25°	1407.9	1498.9	1597.8	1698.7	1817.7	1912.3	1985.2	2011.3	2022.8	2005.3	1976.1
27.5°	1352.6	1454.1	1569.8	1687.2	1813.0	1904.1	1956.3	1952.2	1932.6	1875.7	1830.1
30°	1311.3	1423.0	1547.4	1675.5	1801.8	1890.5	1920.8	1890.5	1846.2	1782.4	1717.5
32.5°	1268.1	1383.7	1523.7	1659.1	1781.5	1859.4	1866.0	1813.8	1745.2	1672.7	1591.7
35°	1202.6	1327.7	1478.8	1622.2	1738.1	1787.2	1758.2	1665.9	1584.5	1485.6	1375.1
37.5°	1128.7	1266.8	1418.4	1568.1	1673.2	1686.0	1613.7	1516.5	1401.8	1285.5	1155.4
40°	1073.3	1219.6	1375.7	1526.9	1619.7	1606.4	1514.1	1407.2	1270.7	1128.5	1007.7
42.5°	1023.8	1170.1	1329.0	1477.3	1551.7	1515.0	1407.2	1276.1	1129.3	995.5	884.9
45°	937.9	1088.5	1251.3	1394.5	1437.0	1370.8	1228.1	1082.4	937.9	826.2	738.9
47.5°	854.7	1003.5	1164.7	1290.5	1305.6	1216.6	1060.7	910.8	786.6	695.6	633.9
50°	793.4	942.8	1102.5	1214.8	1209.9	1102.5	942.2	799.5	695.7	622.3	581.0
52.5°	738.6	879.6	1033.0	1135.1	1109.4	992.2	839.2	712.6	627.2	569.8	532.4
55°	653.2	783.8	929.5	1011.4	964.1	834.2	704.8	602.9	539.7	496.6	467.5
57.5°	568.5	690.9	815.6	866.1	813.7	693.8	586.0	512.0	464.5	432.6	413.7
60°	516.0	622.9	734.0	777.7	715.2	608.3	523.3	457.2	418.9	392.8	375.8
62.5°	463.6	559.3	664.0	687.9	630.7	540.3	465.0	410.0	378.6	355.4	339.4
65°	392.2	470.5	550.0	565.8	513.0	443.1	383.7	347.8	320.0	302.9	290.2
67.5°	321.6	384.5	440.8	453.6	407.3	358.9	315.9	284.7	265.8	251.7	240.9
70°	279.9	329.6	375.8	386.1	349.1	305.9	273.2	248.3	231.3	219.2	208.8
72.5°	235.7	277.2	315.5	322.5	292.2	259.4	232.4	212.9	197.8	190.0	180.2
75°	180.3	204.6	234.3	236.1	216.1	196.1	175.5	162.7	154.8	145.1	140.2
77.5°	127.2	146.3	163.3	166.6	154.7	141.1	129.5	119.5	112.8	108.3	103.8
80°	97.1	112.3	119.6	123.8	115.3	105.6	98.9	92.3	88.0	85.0	82.0
82.5°	69.5	78.8	85.6	88.9	84.3	78.4	71.8	68.0	64.7	62.2	61.1
85°	35.2	39.5	43.7	44.9	43.7	41.3	37.6	37.6	35.8	35.2	35.2
87.5°	12.9	15.4	15.9	17.9	17.7	18.8	19.7	20.3	20.8	20.2	19.6
90°	3.8	6.5	9.3	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0
92.5°	20.3	22.3	24.3	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9
95°	55.7	58.0	60.3	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8
97.5°	99.6	101.6	103.6	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5
100°	132.3	134.1	135.9	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7
102.5°	166.4	167.9	169.4	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8
105°	221.5	222.2	222.9	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9
107.5°	278.1	279.2	280.1	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0
110°	314.7	316.0	317.4	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	354.1	355.5	356.9	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0
115°	412.3	413.6	414.9	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5
117.5°	470.6	472.5	474.3	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2
120°	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4
122.5°	544.9	547.2	549.3	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8
125°	599.8	601.9	604.0	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6
127.5°	654.0	656.6	659.3	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8
130°	688.1	691.1	694.0	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5
132.5°	725.3	727.8	730.2	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2
135°	775.9	778.5	781.0	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4
137.5°	828.7	830.8	832.8	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2
140°	860.8	862.8	864.9	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1
142.5°	893.7	895.7	897.8	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7
145°	940.5	942.1	943.6	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7
147.5°	982.9	984.8	986.7	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7
150°	1011.1	1012.5	1013.8	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4
152.5°	1036.6	1037.9	1039.3	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1
155°	1074.1	1074.8	1075.5	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9
157.5°	1106.5	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1
160°	1126.2	1126.7	1127.2	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6
162.5°	1144.0	1144.1	1144.1	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4
165°	1167.7	1167.4	1167.2	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1
167.5°	1187.3	1186.7	1186.0	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0
170°	1198.0	1197.4	1196.7	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8
172.5°	1205.5	1204.8	1204.0	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2
175°	1214.5	1213.8	1213.1	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2
177.5°	1218.3	1217.7	1217.2	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1638.4	1645.2	1645.2	1646.2	1653.9	1653.0	1652.5
5°	1743.6	1753.9	1755.1	1766.0	1773.3	1770.8	1764.2
7.5°	1842.8	1861.9	1876.5	1884.7	1894.3	1900.2	1897.5
10°	1921.4	1949.4	1966.4	1977.9	1991.9	2002.2	1998.5
12.5°	1992.8	2026.1	2049.5	2069.2	2071.0	2084.2	2075.3
15°	2104.2	2139.4	2143.0	2157.6	2169.2	2167.9	2168.5
17.5°	2141.0	2152.3	2154.6	2154.9	2155.1	2150.8	2141.6
20°	2127.9	2123.6	2113.3	2105.4	2091.4	2089.6	2077.5
22.5°	2065.7	2052.2	2026.3	2009.2	1987.5	1981.8	1978.4
25°	1943.3	1913.5	1872.2	1832.8	1821.9	1800.6	1806.7
27.5°	1775.4	1729.0	1684.3	1652.3	1623.3	1591.4	1600.5
30°	1657.3	1605.1	1542.0	1493.4	1462.4	1432.1	1426.6
32.5°	1516.5	1440.0	1369.6	1326.8	1279.4	1260.2	1239.2
35°	1273.7	1199.0	1129.2	1069.1	1034.5	1007.7	983.5
37.5°	1055.3	969.3	912.9	864.3	839.2	823.9	827.8
40°	919.7	844.5	803.2	766.1	743.1	732.1	734.6
42.5°	810.0	753.6	719.6	694.3	678.0	671.9	670.5
45°	685.4	653.9	625.9	611.3	603.5	596.8	592.6
47.5°	600.4	574.6	558.9	550.2	543.4	536.5	536.4
50°	549.4	532.4	521.5	512.4	506.9	502.1	506.3
52.5°	510.6	495.0	484.1	475.9	473.9	469.5	469.4
55°	452.9	440.8	432.8	425.6	421.9	419.5	416.5
57.5°	400.4	388.9	381.6	377.0	370.1	367.7	366.7
60°	363.1	353.9	346.7	340.6	337.5	332.7	332.7
62.5°	328.5	319.5	312.7	308.0	303.1	301.1	301.6
65°	278.7	271.4	264.7	259.8	258.6	255.0	256.2
67.5°	232.7	227.9	220.9	218.2	215.9	214.0	212.5
70°	202.2	197.3	193.7	190.0	188.2	188.2	188.2
72.5°	176.4	170.6	168.4	163.8	164.9	163.0	161.0
75°	136.6	132.9	131.1	129.3	126.3	126.3	126.3
77.5°	100.5	99.4	97.3	95.3	94.6	94.0	94.2
80°	77.7	77.1	75.9	75.9	74.7	74.1	72.9
82.5°	59.7	58.1	57.4	57.0	56.7	56.6	56.3
85°	34.0	32.8	32.8	33.4	32.2	32.2	32.8
87.5°	20.0	20.0	19.4	19.5	20.0	19.6	19.6
90°	34.6	34.1	34.0	34.2	34.5	34.7	34.9
92.5°	33.0	33.0	33.1	33.1	33.2	33.3	33.3
95°	65.8	65.8	65.5	65.0	64.6	64.2	63.7
97.5°	110.5	110.5	110.5	110.4	110.4	110.4	110.4
100°	141.7	141.7	141.6	141.4	141.2	140.9	140.7
102.5°	176.0	176.2	176.2	175.9	175.7	175.5	175.2
105°	227.4	227.8	228.1	228.1	228.1	228.1	228.1
107.5°	282.2	282.4	281.9	280.9	279.9	278.8	277.7
110°	319.5	319.5	319.1	318.5	317.7	317.0	316.4



TEST NUMBER: P331604-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	356.4	355.8	355.4	354.8	354.3	353.9	353.3
115°	414.3	414.1	413.6	413.0	412.3	411.5	410.9
117.5°	469.6	469.1	468.5	467.8	467.1	466.4	465.7
120°	507.4	507.4	507.1	506.4	505.7	505.0	504.4
122.5°	545.3	544.7	544.2	543.7	543.1	542.6	542.2
125°	601.9	601.3	600.8	600.6	600.3	600.1	599.8
127.5°	657.0	656.2	655.4	654.7	653.9	653.2	652.4
130°	695.1	694.6	694.0	693.0	692.1	691.2	690.2
132.5°	731.2	730.2	729.4	728.6	727.9	727.1	726.4
135°	786.2	785.9	785.4	784.7	784.1	783.4	782.7
137.5°	838.0	837.9	837.3	836.4	835.5	834.6	833.7
140°	873.1	873.1	872.7	871.7	870.8	869.9	869.0
142.5°	904.9	905.1	904.7	903.8	902.9	902.0	901.0
145°	952.9	953.1	952.8	951.9	950.9	950.1	949.1
147.5°	995.2	995.7	995.5	994.7	993.8	992.9	992.0
150°	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0
152.5°	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3
155°	1083.0	1084.1	1084.3	1083.7	1083.0	1082.3	1081.6
157.5°	1114.6	1116.2	1116.4	1115.3	1114.2	1113.1	1112.0
160°	1133.0	1134.3	1134.6	1133.7	1132.7	1131.9	1130.9
162.5°	1149.9	1151.5	1151.8	1150.6	1149.5	1148.4	1147.4
165°	1171.6	1173.3	1173.5	1172.4	1171.2	1170.1	1168.9
167.5°	1189.5	1191.1	1191.4	1190.2	1189.0	1187.8	1186.6
170°	1199.4	1201.0	1201.1	1199.8	1198.4	1197.0	1195.6
172.5°	1206.8	1208.4	1208.5	1207.1	1205.8	1204.4	1203.0
175°	1214.8	1216.4	1216.6	1215.1	1213.8	1212.4	1211.0
177.5°	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2

(END OF REPORT)