

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331607-927

Luminaire Tested: **S122DIW-S1005D1240U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331607-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1240U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7140.2 lumens  
Efficiency: N/A  
Efficacy: 93.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331607-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331607-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	79	71	68	66	58	56	54	46	44	44	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	52	44	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331607-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.7	1.7
10°-20°	334.1	4.7
20°-30°	491.0	6.9
30°-40°	570.4	8.0
40°-50°	569.8	8.0
50°-60°	496.9	7.0
60°-70°	367.4	5.1
70°-80°	208.1	2.9
80°-90°	59.3	0.8
90°-100°	44.7	0.6
100°-110°	163.8	2.3
110°-120°	437.9	6.1
120°-130°	722.9	10.1
130°-140°	768.8	10.8
140°-150°	714.5	10.0
150°-160°	574.5	8.0
160°-170°	370.2	5.2
170°-180°	127.4	1.8
0°-30°	943.8	13.2
0°-40°	1514.2	21.2
0°-60°	2580.8	36.1
0°-90°	3215.6	45.0
90°-120°	646.4	9.1
90°-150°	2852.5	40.0
90°-180°	3925.0	55.0
0°-180°	7140.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	1	12	19	24	26	5
95°	63	33	38	42	42	77
105°	295	307	59	69	74	315
115°	557	574	598	170	80	548
125°	788	801	819	825	828	702
135°	975	990	999	1008	1007	753
145°	1131	1131	1146	1152	1148	707
155°	1245	1238	1248	1253	1246	574
165°	1312	1307	1309	1315	1309	371
175°	1342	1336	1337	1343	1334	128
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P331607-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.7	17.7	17.7	17.8	17.8	17.8	17.7	17.7	17.6	17.5	17.0
90°	1.0	3.3	5.7	8.1	10.5	12.5	14.2	15.9	17.7	19.4	20.4
92.5°	19.6	19.3	19.2	18.9	18.7	19.0	19.9	20.8	21.6	22.5	23.1
95°	63.0	55.8	48.8	41.7	34.5	31.8	33.3	34.8	36.3	37.8	38.9
97.5°	125.0	105.0	84.9	65.0	44.9	36.6	40.1	43.6	47.1	50.6	51.4
100°	171.5	142.0	112.5	83.0	53.6	40.6	44.3	47.9	51.6	55.2	57.0
102.5°	222.7	216.4	210.2	204.0	197.7	179.3	148.6	118.0	87.4	56.8	59.0
105°	294.6	301.0	307.5	313.9	320.4	294.3	235.5	176.7	117.9	59.1	61.5
107.5°	376.6	381.8	387.0	392.2	397.4	364.8	294.3	223.8	153.3	82.8	80.3
110°	429.3	433.8	438.3	442.8	447.3	418.5	356.3	294.1	231.8	169.6	148.1



TEST NUMBER: P331607-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	478.9	482.9	486.9	490.9	495.0	489.3	473.9	458.5	443.1	427.7	349.2
115°	557.2	560.9	564.5	568.2	571.9	576.4	581.8	587.2	592.6	597.9	498.2
117.5°	627.2	631.3	635.3	639.4	643.6	647.5	651.1	654.8	658.5	662.3	638.1
120°	678.3	681.6	684.8	688.0	691.3	694.8	698.7	702.6	706.5	710.3	712.9
122.5°	721.8	725.2	728.6	732.0	735.4	739.2	743.4	747.6	751.9	756.1	757.6
125°	787.8	790.6	793.4	796.2	799.0	802.5	806.6	810.6	814.8	818.9	820.4
127.5°	847.7	850.8	853.9	857.1	860.2	863.2	866.3	869.3	872.4	875.4	877.7
130°	885.7	889.1	892.6	896.0	899.5	902.4	904.8	907.1	909.5	911.9	914.3
132.5°	924.5	927.4	930.3	933.3	936.2	938.8	941.2	943.6	945.9	948.3	950.3
135°	974.9	978.3	981.8	985.2	988.6	991.3	993.2	995.2	997.1	999.1	1001.2
137.5°	1025.8	1028.3	1030.6	1033.1	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7
140°	1059.1	1060.9	1062.6	1064.3	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5
142.5°	1087.1	1088.6	1090.2	1091.7	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0
145°	1130.8	1130.7	1130.4	1130.2	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9
147.5°	1169.0	1168.2	1167.4	1166.6	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8
150°	1193.9	1192.4	1190.9	1189.3	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9
152.5°	1214.8	1213.1	1211.4	1209.7	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3
155°	1245.2	1243.3	1241.3	1239.4	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4
157.5°	1269.1	1267.4	1265.7	1264.2	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3
160°	1283.0	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3
162.5°	1295.5	1294.1	1292.8	1291.6	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1
165°	1312.1	1310.8	1309.5	1308.2	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7
167.5°	1324.5	1323.2	1321.9	1320.6	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9
170°	1331.5	1330.2	1328.9	1327.6	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1
172.5°	1336.1	1334.8	1333.6	1332.2	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7
175°	1342.1	1340.6	1339.1	1337.6	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8
177.5°	1343.1	1341.9	1340.7	1339.5	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331607-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	16.6	16.2	15.8	15.4	15.4	15.2	15.1	15.0
90°	21.5	22.6	23.7	24.5	24.9	25.3	25.7	26.1
92.5°	23.6	24.2	24.7	25.1	25.3	25.7	25.9	26.1
95°	39.9	41.0	42.1	42.5	42.3	42.1	41.9	41.7
97.5°	52.3	53.2	54.0	54.6	54.8	55.1	55.4	55.6
100°	58.7	60.4	62.1	63.2	63.6	64.1	64.5	65.0
102.5°	61.2	63.5	65.8	67.2	67.7	68.4	69.0	69.6
105°	63.8	66.2	68.6	70.2	71.1	71.9	72.8	73.7
107.5°	78.0	75.5	73.1	72.3	73.2	74.1	74.9	75.8
110°	126.5	105.0	83.4	73.1	74.0	74.9	75.7	76.5





TEST NUMBER: P331607-927

CATALOG NUMBER: S122DIW-S1005D1240U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	270.6	192.1	113.5	74.5	75.3	76.0	76.6	77.3
115°	398.5	298.8	199.1	141.5	126.0	110.5	95.0	79.5
117.5°	614.0	589.9	565.8	528.2	477.3	426.4	375.4	324.4
120°	715.5	718.0	720.6	707.4	678.3	649.3	620.2	591.1
122.5°	759.1	760.7	762.2	760.2	754.6	748.9	743.3	737.6
125°	821.9	823.4	824.9	825.9	826.6	827.3	827.9	828.5
127.5°	879.8	882.0	884.2	885.4	885.5	885.7	885.7	885.9
130°	916.6	919.0	921.3	922.4	922.2	922.0	921.8	921.5
132.5°	952.4	954.3	956.4	957.3	957.1	956.9	956.6	956.5
135°	1003.4	1005.5	1007.7	1008.5	1008.1	1007.7	1007.3	1006.9
137.5°	1050.8	1052.9	1055.0	1055.7	1054.9	1054.2	1053.5	1052.7
140°	1081.5	1083.4	1085.4	1085.8	1084.7	1083.6	1082.5	1081.5
142.5°	1109.8	1111.6	1113.3	1113.6	1112.6	1111.5	1110.4	1109.4
145°	1149.4	1150.9	1152.4	1152.6	1151.5	1150.5	1149.4	1148.3
147.5°	1183.9	1185.0	1186.1	1186.2	1185.3	1184.4	1183.5	1182.6
150°	1205.1	1206.5	1207.8	1207.8	1206.8	1205.7	1204.6	1203.6
152.5°	1224.6	1225.8	1227.2	1227.1	1225.7	1224.2	1222.8	1221.4
155°	1250.7	1252.0	1253.3	1253.1	1251.3	1249.7	1247.9	1246.2
157.5°	1272.8	1274.2	1275.7	1275.6	1273.9	1272.2	1270.6	1268.8
160°	1285.6	1286.9	1288.2	1288.1	1286.6	1285.1	1283.6	1282.1
162.5°	1297.6	1299.0	1300.5	1300.3	1298.5	1296.6	1294.7	1292.9
165°	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2
167.5°	1324.4	1325.9	1327.4	1327.2	1325.2	1323.3	1321.4	1319.5
170°	1330.6	1332.1	1333.6	1333.4	1331.5	1329.5	1327.6	1325.6
172.5°	1335.2	1336.7	1338.2	1338.1	1336.1	1334.2	1332.2	1330.3
175°	1340.3	1341.8	1343.3	1343.0	1340.8	1338.7	1336.5	1334.4
177.5°	1340.8	1342.0	1343.3	1343.1	1341.6	1340.0	1338.5	1336.9
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2

(END OF REPORT)