

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906602

Luminaire Tested: DFN2DIP-SQ3F0-110D060US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906602
REPORT IS A COMBINATION OF REPORTS P899912 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D060US835-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14660.0 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 157
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906602

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906602

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	94	90	95	92	88	85	81	78	76	71	69	67	62	61	59
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	40	37	34
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5209	5209	5209
5°	5214	5123	5158
10°	5159	5019	4988
15°	5085	4850	4727
20°	4988	4618	4407
25°	4888	4359	4099
30°	4755	4093	3708
35°	4625	3808	3364
40°	4492	3513	2971
45°	4339	3187	2615
50°	4179	2857	2266
55°	4012	2506	1932
60°	3819	2139	1589
65°	3597	1766	1428
70°	3327	1419	1290
75°	2987	1243	1170
80°	2496	1032	1009
85°	1693	672	748

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4339 cd/sqm

TEST NUMBER: P906602

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.1	2.9
10°-20°	1169.7	8.0
20°-30°	1642.2	11.2
30°-40°	1790.1	12.2
40°-50°	1645.3	11.2
50°-60°	1292.1	8.8
60°-70°	841.1	5.7
70°-80°	432.9	3.0
80°-90°	115.9	0.8
90°-100°	117.4	0.8
100°-110°	373.1	2.5
110°-120°	638.5	4.4
120°-130°	839.7	5.7
130°-140°	942.5	6.4
140°-150°	924.2	6.3
150°-160°	775.3	5.3
160°-170°	514.2	3.5
170°-180°	179.7	1.2
0°-30°	3238.0	22.1
0°-40°	5028.1	34.3
0°-60°	7965.5	54.3
0°-90°	9355.4	63.8
90°-120°	1129.0	7.7
90°-150°	3835.4	26.2
90°-180°	5305.0	36.2
0°-180°	14660.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4546	4546	4546	4546	4546	
5°	4546	4526	4472	4509	4497	431
15°	4324	4279	4139	4061	4020	1218
25°	3925	3793	3522	3353	3291	1805
35°	3382	3172	2810	2551	2460	2117
45°	2765	2489	2057	1765	1666	2135
55°	2102	1781	1337	1090	1012	1879
65°	1420	1086	716	576	564	1407
75°	757	469	329	300	296	801
85°	177	90	78	78	78	203
90°	2	21	56	53	54	14
95°	84	100	102	102	100	93
105°	344	349	352	355	355	363
115°	641	650	647	645	641	634
125°	932	946	942	936	935	833
135°	1205	1223	1226	1225	1220	932
145°	1463	1475	1484	1486	1479	914
155°	1673	1678	1683	1691	1686	770
165°	1820	1819	1819	1830	1822	514
175°	1894	1890	1886	1898	1888	180
180°	1898	1898	1898	1898	1898	

TEST NUMBER: P906602

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4546.3	4546.3	4546.3	4546.3	4546.3
2.5°	4566.8	4546.3	4500.9	4542.4	4534.1
5°	4546.3	4525.8	4472.1	4509.2	4497.0
7.5°	4509.2	4484.7	4427.1	4443.3	4422.7
10°	4459.9	4431.0	4349.0	4336.3	4311.9
12.5°	4398.3	4361.2	4249.9	4225.4	4180.0
15°	4324.1	4278.7	4139.0	4060.9	4019.8
17.5°	4237.7	4171.8	3998.9	3908.5	3842.6
20°	4139.0	4056.5	3850.9	3748.3	3657.5
22.5°	4032.1	3937.3	3698.6	3558.9	3497.3
25°	3925.1	3793.3	3521.8	3353.3	3291.3
27.5°	3797.7	3657.5	3357.2	3163.8	3069.1
30°	3661.9	3505.2	3176.1	2966.5	2855.2
32.5°	3530.1	3340.6	3003.6	2756.6	2653.6
35°	3382.1	3172.1	2810.3	2551.0	2460.2
37.5°	3238.1	3011.5	2629.1	2344.9	2242.4
40°	3085.7	2839.1	2439.7	2147.6	2040.7
42.5°	2929.4	2666.2	2250.7	1946.0	1843.4
45°	2764.9	2489.0	2057.3	1764.8	1666.2
47.5°	2608.6	2316.6	1872.2	1579.7	1489.4
50°	2435.7	2143.7	1691.1	1406.9	1320.9
52.5°	2266.8	1958.2	1518.2	1246.7	1168.5
55°	2102.2	1781.4	1337.0	1090.4	1012.3
57.5°	1933.8	1604.6	1176.8	946.4	880.4
60°	1760.9	1431.8	1007.9	798.4	732.5
62.5°	1592.4	1263.3	863.9	666.6	633.8
65°	1419.5	1086.0	715.9	576.2	563.5
67.5°	1255.0	921.5	576.2	505.9	493.7
70°	1082.1	761.3	477.1	436.1	419.5
72.5°	917.5	612.9	399.0	366.2	357.9
75°	756.9	468.8	329.1	300.3	296.4
77.5°	596.7	333.1	259.3	242.7	234.4
80°	448.3	238.8	197.3	181.2	181.2
82.5°	312.5	160.6	135.8	127.5	127.5
85°	176.8	90.4	78.1	78.1	78.1
87.5°	65.9	32.7	32.7	28.8	28.8
90°	1.7	20.6	56.1	52.6	54.3
92.5°	35.5	48.1	49.8	51.5	51.5
95°	83.5	99.5	102.4	102.4	99.5
97.5°	139.0	153.9	160.2	160.2	160.2
100°	203.1	216.2	220.8	220.8	219.1
102.5°	270.6	280.3	286.6	288.3	286.6
105°	344.4	349.0	352.4	355.3	355.3
107.5°	417.6	424.5	424.5	425.6	417.6
110°	488.6	497.7	497.7	497.7	493.1



TEST NUMBER: P906602

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.2	574.9	573.2	568.6	565.2
115°	640.7	649.9	647.0	645.3	640.7
117.5°	715.7	728.3	720.2	715.7	711.1
120°	791.2	803.8	791.2	791.2	786.0
122.5°	859.8	875.8	867.8	863.3	859.8
125°	931.9	946.2	941.6	936.5	934.8
127.5°	1002.3	1020.0	1013.7	1006.9	1002.3
130°	1068.1	1088.7	1085.8	1082.4	1076.1
132.5°	1141.9	1157.9	1159.0	1151.0	1146.4
135°	1205.4	1223.1	1226.5	1224.8	1220.2
137.5°	1276.3	1290.6	1293.5	1292.3	1285.5
140°	1338.7	1353.0	1361.0	1361.0	1354.7
142.5°	1402.7	1417.0	1421.6	1423.3	1417.0
145°	1463.4	1474.8	1484.0	1485.7	1479.4
147.5°	1517.7	1532.0	1538.9	1541.7	1535.4
150°	1573.8	1583.5	1589.8	1594.9	1589.8
152.5°	1623.5	1633.3	1641.3	1647.6	1641.3
155°	1673.3	1677.9	1683.0	1691.1	1685.9
157.5°	1716.2	1719.7	1722.5	1734.0	1726.0
160°	1754.6	1758.0	1759.7	1769.4	1762.6
162.5°	1790.0	1790.0	1791.7	1802.6	1794.6
165°	1820.3	1818.6	1818.6	1830.1	1822.1
167.5°	1847.8	1842.7	1842.7	1854.1	1846.1
170°	1868.4	1863.8	1862.1	1873.5	1863.8
172.5°	1882.7	1878.1	1876.4	1887.8	1878.1
175°	1894.1	1889.6	1886.1	1897.6	1887.8
177.5°	1900.4	1895.9	1892.4	1902.1	1892.4
180°	1897.6	1897.6	1897.6	1897.6	1897.6

TEST NUMBER: P906602

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.05	15.00	14.88	15.86	16.92	10.01	10.97	10.84	11.82	12.88
	3H	15.73	16.59	16.58	17.45	18.54	11.20	12.06	12.05	12.92	14.01
	4H	16.34	17.15	17.21	18.02	19.12	11.65	12.46	12.52	13.33	14.43
	6H	16.77	17.51	17.64	18.39	19.50	11.97	12.72	12.85	13.59	14.71
	8H	16.89	17.60	17.78	18.50	19.61	12.06	12.77	12.95	13.67	14.78
	12H	16.96	17.63	17.85	18.52	19.66	12.11	12.78	13.00	13.67	14.81
4H	2H	14.08	14.89	14.95	15.76	16.86	10.62	11.42	11.49	12.29	13.39
	3H	15.91	16.59	16.80	17.49	18.60	11.97	12.64	12.85	13.54	14.66
	4H	16.61	17.22	17.50	18.12	19.26	12.52	13.13	13.41	14.03	15.17
	6H	17.13	17.65	18.03	18.57	19.72	12.94	13.46	13.85	14.39	15.53
	8H	17.30	17.79	18.21	18.71	19.87	13.07	13.56	13.98	14.47	15.63
	12H	17.40	17.84	18.33	18.78	19.94	13.13	13.57	14.06	14.51	15.67
8H	4H	16.58	17.07	17.49	17.99	19.15	12.80	13.30	13.71	14.21	15.37
	6H	17.15	17.55	18.09	18.51	19.67	13.32	13.72	14.26	14.68	15.84
	8H	17.36	17.72	18.31	18.67	19.85	13.51	13.87	14.45	14.82	15.99
	12H	17.50	17.82	18.45	18.76	19.99	13.63	13.94	14.57	14.88	16.11
12H	4H	16.54	16.98	17.47	17.92	19.08	12.81	13.26	13.74	14.19	15.35
	6H	17.12	17.48	18.07	18.43	19.61	13.37	13.73	14.31	14.68	15.85
	8H	17.35	17.66	18.30	18.60	19.83	13.58	13.89	14.53	14.84	16.06

END OF REPORT