

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331613-927

Luminaire Tested: **S122DIW-S1005D1440U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331613-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1440U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7779.1 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331613-927

CATALOG NUMBER: S122DIW-S1005D1440U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331613-927

CATALOG NUMBER: S122DIW-S1005D1440U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	37	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	32	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331613-927

CATALOG NUMBER: S122DIW-S1005D1440U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.7	1.5
10°-20°	334.1	4.3
20°-30°	491.0	6.3
30°-40°	570.4	7.3
40°-50°	569.8	7.3
50°-60°	496.9	6.4
60°-70°	367.4	4.7
70°-80°	208.1	2.7
80°-90°	59.8	0.8
90°-100°	51.9	0.7
100°-110°	190.5	2.4
110°-120°	509.1	6.5
120°-130°	840.4	10.8
130°-140°	893.8	11.5
140°-150°	830.7	10.7
150°-160°	667.9	8.6
160°-170°	430.4	5.5
170°-180°	148.2	1.9
0°-30°	943.8	12.1
0°-40°	1514.2	19.5
0°-60°	2580.8	33.2
0°-90°	3216.1	41.3
90°-120°	751.5	9.7
90°-150°	3316.5	42.6
90°-180°	4563.0	58.7
0°-180°	7779.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	1	13	22	28	30	6
95°	73	39	44	49	48	90
105°	342	357	69	81	86	366
115°	648	668	695	198	92	638
125°	916	931	952	960	963	816
135°	1134	1151	1162	1172	1171	875
145°	1315	1315	1333	1340	1335	822
155°	1448	1439	1451	1457	1449	667
165°	1526	1519	1522	1529	1522	431
175°	1560	1553	1555	1562	1551	148
180°	1557	1557	1557	1557	1557	



TEST NUMBER: P331613-927

CATALOG NUMBER: S122DIW-S1005D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.7	17.8	18.0	18.1	18.2	18.2	18.2	18.1	18.1	18.1	17.7
90°	1.1	3.9	6.7	9.4	12.1	14.5	16.6	18.5	20.5	22.5	23.8
92.5°	22.7	22.5	22.3	22.0	21.8	22.1	23.1	24.2	25.1	26.1	26.8
95°	73.2	65.0	56.7	48.5	40.2	36.9	38.7	40.4	42.2	44.0	45.2
97.5°	145.4	122.1	98.8	75.5	52.2	42.6	46.7	50.7	54.7	58.8	59.8
100°	199.4	165.1	130.8	96.5	62.2	47.2	51.4	55.7	60.0	64.2	66.2
102.5°	258.9	251.7	244.4	237.1	229.9	208.4	172.9	137.2	101.6	66.0	68.6
105°	342.5	350.0	357.5	365.0	372.6	342.1	273.8	205.4	137.0	68.8	71.5
107.5°	437.8	443.9	450.0	456.0	462.1	424.1	342.1	260.2	178.2	96.3	93.4
110°	499.2	504.4	509.6	514.9	520.1	486.6	414.2	341.9	269.5	197.2	172.1



TEST NUMBER: P331613-927

CATALOG NUMBER: S122DIW-S1005D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	556.8	561.4	566.1	570.8	575.4	568.8	551.0	533.1	515.2	497.3	406.0
115°	647.8	652.1	656.3	660.6	664.9	670.1	676.4	682.6	688.9	695.1	579.2
117.5°	729.2	734.0	738.7	743.5	748.2	752.7	757.0	761.4	765.6	770.0	742.0
120°	788.7	792.4	796.1	799.9	803.7	807.8	812.3	816.8	821.3	825.9	828.9
122.5°	839.2	843.1	847.1	851.0	855.0	859.4	864.3	869.2	874.1	879.0	880.8
125°	916.0	919.2	922.5	925.7	929.0	933.0	937.8	942.5	947.3	952.0	953.8
127.5°	985.6	989.2	992.8	996.4	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4
130°	1029.8	1033.8	1037.8	1041.8	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0
132.5°	1074.8	1078.2	1081.6	1085.1	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9
135°	1133.5	1137.4	1141.5	1145.4	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1
137.5°	1192.7	1195.5	1198.3	1201.1	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2
140°	1231.4	1233.4	1235.5	1237.5	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1
142.5°	1263.9	1265.7	1267.5	1269.3	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2
145°	1314.9	1314.5	1314.3	1314.1	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6
147.5°	1359.2	1358.3	1357.3	1356.4	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1
150°	1388.1	1386.3	1384.6	1382.8	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7
152.5°	1412.4	1410.5	1408.5	1406.5	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2
155°	1447.8	1445.5	1443.3	1441.0	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6
157.5°	1475.5	1473.6	1471.7	1469.8	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1
160°	1491.7	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2
162.5°	1506.1	1504.7	1503.2	1501.7	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0
165°	1525.5	1524.0	1522.5	1521.0	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9
167.5°	1539.9	1538.4	1536.9	1535.4	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1
170°	1548.1	1546.6	1545.1	1543.6	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3
172.5°	1553.5	1552.0	1550.5	1549.0	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7
175°	1560.4	1558.7	1557.0	1555.2	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6
177.5°	1561.5	1560.2	1558.8	1557.4	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331613-927

CATALOG NUMBER: S122DIW-S1005D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	17.3	16.9	16.5	16.2	16.2	16.0	15.9	15.8
90°	25.0	26.3	27.6	28.4	28.9	29.4	29.9	30.4
92.5°	27.4	28.1	28.8	29.2	29.5	29.8	30.1	30.4
95°	46.4	47.7	49.0	49.4	49.2	49.0	48.7	48.5
97.5°	60.8	61.8	62.8	63.5	63.8	64.1	64.4	64.6
100°	68.2	70.3	72.2	73.5	74.0	74.5	75.0	75.5
102.5°	71.2	73.8	76.4	78.1	78.8	79.5	80.2	80.9
105°	74.2	77.0	79.8	81.6	82.6	83.7	84.6	85.6
107.5°	90.6	87.8	85.0	84.1	85.1	86.1	87.1	88.1
110°	147.1	122.1	97.0	85.0	86.0	87.0	88.0	89.0



TEST NUMBER: P331613-927

CATALOG NUMBER: S122DIW-S1005D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	314.7	223.3	132.0	86.7	87.5	88.3	89.1	89.9
115°	463.3	347.4	231.5	164.5	146.5	128.4	110.4	92.4
117.5°	713.9	685.9	657.8	614.2	554.9	495.7	436.4	377.2
120°	831.9	834.9	837.9	822.4	788.7	754.9	721.0	687.3
122.5°	882.6	884.5	886.2	883.8	877.3	870.8	864.2	857.6
125°	955.5	957.3	959.0	960.3	961.1	961.8	962.6	963.3
127.5°	1022.9	1025.5	1028.0	1029.4	1029.5	1029.7	1029.8	1030.0
130°	1065.7	1068.5	1071.2	1072.5	1072.2	1072.0	1071.7	1071.4
132.5°	1107.2	1109.6	1112.0	1113.0	1112.8	1112.5	1112.3	1112.0
135°	1166.6	1169.1	1171.6	1172.6	1172.1	1171.6	1171.1	1170.6
137.5°	1221.7	1224.2	1226.6	1227.4	1226.5	1225.7	1224.9	1224.0
140°	1257.4	1259.6	1261.9	1262.3	1261.2	1259.9	1258.6	1257.4
142.5°	1290.3	1292.4	1294.4	1294.8	1293.6	1292.3	1291.1	1289.8
145°	1336.3	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1335.1
147.5°	1376.5	1377.8	1379.1	1379.2	1378.2	1377.1	1376.0	1375.0
150°	1401.2	1402.7	1404.2	1404.3	1403.1	1401.8	1400.6	1399.3
152.5°	1423.7	1425.2	1426.7	1426.6	1425.0	1423.4	1421.7	1420.1
155°	1454.1	1455.6	1457.1	1456.9	1454.9	1452.9	1450.9	1448.9
157.5°	1479.8	1481.5	1483.2	1483.0	1481.1	1479.2	1477.2	1475.3
160°	1494.7	1496.2	1497.7	1497.6	1495.9	1494.1	1492.3	1490.6
162.5°	1508.6	1510.4	1512.0	1511.8	1509.7	1507.5	1505.4	1503.2
165°	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1
167.5°	1539.8	1541.6	1543.3	1543.1	1540.9	1538.6	1536.4	1534.1
170°	1547.1	1548.8	1550.5	1550.3	1548.1	1545.8	1543.6	1541.3
172.5°	1552.4	1554.2	1555.9	1555.7	1553.5	1551.2	1549.0	1546.7
175°	1558.3	1560.0	1561.8	1561.5	1558.9	1556.4	1553.9	1551.4
177.5°	1558.9	1560.4	1561.8	1561.5	1559.7	1558.0	1556.2	1554.3
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0

(END OF REPORT)