

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331591-927

Luminaire Tested: **S122DIW-S1005D710U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331591-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D710U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5732.9 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	66	66	66	61													
1	101	97	93	90	94	91	87	84	79	77	75	69	67	66	59	58	57	57	57	57	57	57	57	52													
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	49	49	49	49	49	49	45													
3	85	75	68	62	79	71	65	59	62	58	54	55	51	48	47	45	42	42	42	42	42	42	42	39													
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37	37	37	37	37	37	37	34													
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	33	33	33	33	33	33	30													
6	66	54	46	41	62	51	44	39	46	40	36	40	36	32	35	32	29	29	29	29	29	29	29	26													
7	61	49	41	36	57	47	40	34	42	36	32	37	32	29	33	29	26	26	26	26	26	26	26	24													
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	26	24	24	24	24	24	24	24	21													
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21	21	21	21	21	21	21	19													
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	20	20	20	20	20	20	18													

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25504	25504	25504	25504
5°	28593	25671	22749	25671
10°	32765	25460	19687	25460
15°	36247	24993	17392	24993
20°	35696	24493	15856	24493
25°	32186	23826	14883	23826
30°	26597	22760	14171	22760
35°	19385	21646	13665	21646
40°	15483	20331	13384	20331
45°	13531	18810	13001	18810
50°	12717	17337	12750	17337
55°	11724	15842	12408	15842
60°	10743	14250	11880	14250
65°	9788	12825	11366	12825
70°	8884	11434	10607	11434
75°	7879	9881	9395	9881
80°	6778	8182	7569	8182
85°	6076	6076	4502	6076



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.4	2.6
10°-20°	437.4	7.6
20°-30°	634.7	11.1
30°-40°	669.8	11.7
40°-50°	593.0	10.3
50°-60°	473.3	8.3
60°-70°	321.7	5.6
70°-80°	164.9	2.9
80°-90°	41.7	0.7
90°-100°	25.6	0.4
100°-110°	93.8	1.6
110°-120°	250.6	4.4
120°-130°	413.7	7.2
130°-140°	440.0	7.7
140°-150°	408.9	7.1
150°-160°	328.8	5.7
160°-170°	211.9	3.7
170°-180°	72.9	1.3
0°-30°	1222.5	21.3
0°-40°	1892.3	33.0
0°-60°	2958.6	51.6
0°-90°	3486.9	60.8
90°-120°	369.9	6.5
90°-150°	1632.5	28.5
90°-180°	2246.0	39.2
0°-180°	5732.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1580	1580	1580	1580	1580	
5°	1764	1584	1404	1584	1764	176
15°	2168	1495	1040	1495	2168	598
25°	1807	1337	835	1337	1807	817
35°	984	1098	693	1098	984	640
45°	593	824	569	824	593	466
55°	416	563	441	563	416	373
65°	256	336	298	336	256	255
75°	126	158	151	158	126	135
85°	33	33	24	33	33	36
90°	15	1	15	1	15	8
95°	24	36	24	36	24	22
105°	42	169	42	169	42	44
115°	46	319	46	319	46	114
125°	474	451	474	451	474	410
135°	576	558	576	558	576	444
145°	657	647	657	647	657	411
155°	713	713	713	713	713	329
165°	749	751	749	751	749	212
175°	764	768	764	768	764	73
180°	766	766	766	766	766	



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1652.5	1653.0	1653.9	1646.2	1645.2	1645.2	1638.4	1632.6	1625.8	1616.5	1617.6
5°	1764.2	1770.8	1773.3	1766.0	1755.1	1753.9	1743.6	1726.6	1710.8	1698.0	1688.9
7.5°	1897.5	1900.2	1894.3	1884.7	1876.5	1861.9	1842.8	1823.9	1797.6	1773.5	1755.5
10°	1998.5	2002.2	1991.9	1977.9	1966.4	1949.4	1921.4	1892.9	1858.3	1825.0	1798.2
12.5°	2075.3	2084.2	2071.0	2069.2	2049.5	2026.1	1992.8	1978.4	1929.7	1883.2	1854.6
15°	2168.5	2167.9	2169.2	2157.6	2143.0	2139.4	2104.2	2065.9	1997.3	1970.0	1922.6
17.5°	2141.6	2150.8	2155.1	2154.9	2154.6	2152.3	2141.0	2116.8	2082.4	2038.1	1983.5
20°	2077.5	2089.6	2091.4	2105.4	2113.3	2123.6	2127.9	2121.1	2099.9	2062.9	2015.5
22.5°	1978.4	1981.8	1987.5	2009.2	2026.3	2052.2	2065.7	2088.1	2080.0	2061.9	2022.4
25°	1806.7	1800.6	1821.9	1832.8	1872.2	1913.5	1943.3	1976.1	2005.3	2022.8	2011.3
27.5°	1600.5	1591.4	1623.3	1652.3	1684.3	1729.0	1775.4	1830.1	1875.7	1932.6	1952.2
30°	1426.6	1432.1	1462.4	1493.4	1542.0	1605.1	1657.3	1717.5	1782.4	1846.2	1890.5
32.5°	1239.2	1260.2	1279.4	1326.8	1369.6	1440.0	1516.5	1591.7	1672.7	1745.2	1813.8
35°	983.5	1007.7	1034.5	1069.1	1129.2	1199.0	1273.7	1375.1	1485.6	1584.5	1665.9
37.5°	827.8	823.9	839.2	864.3	912.9	969.3	1055.3	1155.4	1285.5	1401.8	1516.5
40°	734.6	732.1	743.1	766.1	803.2	844.5	919.7	1007.7	1128.5	1270.7	1407.2
42.5°	670.5	671.9	678.0	694.3	719.6	753.6	810.0	884.9	995.5	1129.3	1276.1
45°	592.6	596.8	603.5	611.3	625.9	653.9	685.4	738.9	826.2	937.9	1082.4
47.5°	536.4	536.5	543.4	550.2	558.9	574.6	600.4	633.9	695.6	786.6	910.8
50°	506.3	502.1	506.9	512.4	521.5	532.4	549.4	581.0	622.3	695.7	799.5
52.5°	469.4	469.5	473.9	475.9	484.1	495.0	510.6	532.4	569.8	627.2	712.6
55°	416.5	419.5	421.9	425.6	432.8	440.8	452.9	467.5	496.6	539.7	602.9
57.5°	366.7	367.7	370.1	377.0	381.6	388.9	400.4	413.7	432.6	464.5	512.0
60°	332.7	332.7	337.5	340.6	346.7	353.9	363.1	375.8	392.8	418.9	457.2
62.5°	301.6	301.1	303.1	308.0	312.7	319.5	328.5	339.4	355.4	378.6	410.0
65°	256.2	255.0	258.6	259.8	264.7	271.4	278.7	290.2	302.9	320.0	347.8
67.5°	212.5	214.0	215.9	218.2	220.9	227.9	232.7	240.9	251.7	265.8	284.7
70°	188.2	188.2	188.2	190.0	193.7	197.3	202.2	208.8	219.2	231.3	248.3
72.5°	161.0	163.0	164.9	163.8	168.4	170.6	176.4	180.2	190.0	197.8	212.9
75°	126.3	126.3	126.3	129.3	131.1	132.9	136.6	140.2	145.1	154.8	162.7
77.5°	94.2	94.0	94.6	95.3	97.3	99.4	100.5	103.8	108.3	112.8	119.5
80°	72.9	74.1	74.7	75.9	75.9	77.1	77.7	82.0	85.0	88.0	92.3
82.5°	56.3	56.6	56.7	57.0	57.4	58.1	59.7	61.1	62.2	64.7	68.0
85°	32.8	32.2	32.2	33.4	32.8	32.8	34.0	35.2	35.2	35.8	37.6
87.5°	15.6	15.6	16.0	15.4	15.4	15.8	15.7	15.1	15.4	15.8	16.1
90°	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4	11.7	11.1	10.1
92.5°	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5	13.2	12.8	12.4
95°	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9	22.3	21.6	20.8
97.5°	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9	29.5	28.9	26.9
100°	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6	32.6	31.6	29.5
102.5°	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1	33.7	32.5	50.0
105°	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5	35.2	33.8	67.5
107.5°	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6	45.9	47.4	87.7
110°	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4	84.8	97.0	132.7



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9	199.9	244.8	253.6
115°	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1	285.1	342.1	339.1
117.5°	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4	365.2	379.0	376.8
120°	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5	408.0	406.5	404.3
122.5°	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4	433.6	432.7	430.2
125°	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3	469.4	468.6	466.3
127.5°	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5	502.2	501.0	499.2
130°	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6	523.2	521.9	520.5
132.5°	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0	543.8	542.7	541.4
135°	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3	573.0	571.8	570.7
137.5°	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3	600.2	599.0	597.7
140°	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9	617.8	616.7	615.3
142.5°	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1	634.1	633.1	631.5
145°	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7	657.0	656.1	653.9
147.5°	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6	676.9	676.2	674.1
150°	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7	689.0	688.2	686.3
152.5°	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8	700.1	699.3	697.4
155°	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7	715.0	714.3	712.8
157.5°	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4	727.5	726.7	725.6
160°	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7	735.0	734.3	733.5
162.5°	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6	741.7	740.9	740.3
165°	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0	750.1	749.2	748.8
167.5°	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0	757.1	756.2	755.9
170°	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5	760.7	759.8	759.5
172.5°	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1	763.3	762.4	762.2
175°	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1	766.2	765.3	765.1
177.5°	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4	766.7	766.0	765.9
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1621.0	1617.1	1614.6	1605.9	1598.1	1590.3	1587.9	1588.9	1578.2	1568.0	1563.6
5°	1684.1	1671.9	1660.4	1644.0	1624.6	1603.3	1592.4	1583.9	1562.7	1539.6	1526.2
7.5°	1740.7	1723.3	1701.1	1670.2	1642.0	1608.5	1587.3	1568.4	1537.4	1504.8	1484.9
10°	1775.1	1751.4	1722.9	1685.3	1650.7	1610.0	1581.4	1552.9	1516.5	1477.7	1453.3
12.5°	1804.7	1772.8	1744.8	1696.5	1655.5	1604.6	1570.8	1530.6	1492.2	1446.0	1422.3
15°	1875.3	1816.4	1763.0	1708.3	1658.0	1586.9	1549.3	1495.2	1444.9	1387.8	1360.5
17.5°	1929.8	1863.6	1779.5	1710.1	1651.3	1572.6	1517.3	1452.6	1393.1	1327.9	1290.7
20°	1960.9	1885.0	1794.5	1712.0	1641.6	1551.7	1491.6	1425.5	1355.7	1282.1	1242.1
22.5°	1979.3	1899.6	1810.1	1704.7	1622.2	1534.7	1459.0	1386.6	1315.8	1236.5	1194.5
25°	1985.2	1912.3	1817.7	1698.7	1597.8	1498.9	1407.9	1337.4	1251.8	1177.7	1116.4
27.5°	1956.3	1904.1	1813.0	1687.2	1569.8	1454.1	1352.6	1272.8	1182.5	1102.1	1040.5
30°	1920.8	1890.5	1801.8	1675.5	1547.4	1423.0	1311.3	1220.8	1131.0	1049.6	986.5
32.5°	1866.0	1859.4	1781.5	1659.1	1523.7	1383.7	1268.1	1176.6	1077.1	997.2	937.0
35°	1758.2	1787.2	1738.1	1622.2	1478.8	1327.7	1202.6	1098.2	995.1	918.5	862.1
37.5°	1613.7	1686.0	1673.2	1568.1	1418.4	1266.8	1128.7	1019.5	921.2	844.0	788.6
40°	1514.1	1606.4	1619.7	1526.9	1375.7	1219.6	1073.3	964.6	868.7	798.4	742.4
42.5°	1407.2	1515.0	1551.7	1477.3	1329.0	1170.1	1023.8	911.2	816.3	747.8	698.3
45°	1228.1	1370.8	1437.0	1394.5	1251.3	1088.5	937.9	823.8	737.6	673.3	635.0
47.5°	1060.7	1216.6	1305.6	1290.5	1164.7	1003.5	854.7	745.1	661.2	609.9	575.7
50°	942.2	1102.5	1209.9	1214.8	1102.5	942.8	793.4	690.2	613.1	565.2	537.3
52.5°	839.2	992.2	1109.4	1135.1	1033.0	879.6	738.6	635.9	568.0	523.9	498.9
55°	704.8	834.2	964.1	1011.4	929.5	783.8	653.2	562.8	499.0	468.7	446.8
57.5°	586.0	693.8	813.7	866.1	815.6	690.9	568.5	489.9	438.2	411.6	394.8
60°	523.3	608.3	715.2	777.7	734.0	622.9	516.0	441.3	398.9	375.2	359.4
62.5°	465.0	540.3	630.7	687.9	664.0	559.3	463.6	397.7	361.0	338.7	327.3
65°	383.7	443.1	513.0	565.8	550.0	470.5	392.2	335.7	306.6	289.0	279.9
67.5°	315.9	358.9	407.3	453.6	440.8	384.5	321.6	277.7	256.0	240.7	235.3
70°	273.2	305.9	349.1	386.1	375.8	329.6	279.9	242.2	223.4	210.6	205.2
72.5°	232.4	259.4	292.2	322.5	315.5	277.2	235.7	207.2	192.8	181.0	176.6
75°	175.5	196.1	216.1	236.1	234.3	204.6	180.3	158.4	146.9	137.8	136.0
77.5°	129.5	141.1	154.7	166.6	163.3	146.3	127.2	114.7	106.2	100.1	99.2
80°	98.9	105.6	115.3	123.8	119.6	112.3	97.1	88.0	82.0	75.9	73.4
82.5°	71.8	78.4	84.3	88.9	85.6	78.8	69.5	63.3	59.7	55.5	54.5
85°	37.6	41.3	43.7	44.9	43.7	39.5	35.2	32.8	29.8	28.0	27.3
87.5°	16.4	16.2	16.0	16.7	15.0	14.7	12.5	10.8	10.6	10.4	9.7
90°	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6	1.9	3.2	4.6
92.5°	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2	11.1	10.9	10.9
95°	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0	32.0	27.9	23.8
97.5°	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5	60.0	48.6	37.2
100°	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2	81.3	64.4	47.5
102.5°	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5	123.9	120.3	116.7
105°	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6	172.3	176.0	179.7
107.5°	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5	218.5	221.5	224.4
110°	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7	248.3	250.9	253.4



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1	276.4	278.7	280.9
115°	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9	321.0	323.1	325.2
117.5°	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9	361.2	363.6	365.9
120°	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2	390.1	391.9	393.7
122.5°	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0	415.0	416.9	418.9
125°	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8	452.5	454.1	455.7
127.5°	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1	486.9	488.7	490.4
130°	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8	508.8	510.8	512.8
132.5°	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1	530.8	532.4	534.1
135°	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9	559.8	561.8	563.8
137.5°	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1	588.4	589.9	591.2
140°	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2	607.1	608.1	609.1
142.5°	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1	623.0	623.9	624.8
145°	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2	647.1	647.0	646.8
147.5°	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0	668.6	668.1	667.7
150°	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3	682.4	681.5	680.6
152.5°	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2	694.3	693.3	692.3
155°	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6	711.5	710.4	709.3
157.5°	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3	725.3	724.4	723.4
160°	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	733.5	732.8	732.1
162.5°	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3	740.6	739.9	739.1
165°	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9	750.1	749.4	748.7
167.5°	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0	757.2	756.5	755.7
170°	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0	761.2	760.5	759.8
172.5°	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6	763.9	763.2	762.4
175°	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1	767.2	766.4	765.5
177.5°	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7	767.9	767.2	766.6
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1558.8	1555.8	1545.6	1540.3	1531.6	1523.3	1518.0	1520.4	1522.3	1521.4	1519.9
5°	1514.1	1502.5	1484.9	1469.7	1458.8	1438.8	1430.3	1426.1	1422.4	1418.2	1413.9
7.5°	1460.9	1442.7	1417.5	1395.8	1375.4	1350.5	1336.3	1327.9	1319.1	1309.5	1301.0
10°	1423.0	1397.5	1370.8	1340.5	1316.2	1293.7	1273.7	1260.3	1248.2	1236.7	1228.1
12.5°	1383.2	1353.8	1320.8	1279.3	1252.5	1220.4	1217.3	1193.8	1174.8	1167.7	1157.7
15°	1319.8	1278.5	1236.7	1187.5	1166.3	1137.1	1118.9	1100.7	1084.3	1072.7	1069.7
17.5°	1247.8	1194.4	1152.7	1117.4	1082.6	1052.7	1035.9	1021.4	1007.9	992.4	990.4
20°	1192.9	1146.8	1101.3	1070.3	1034.5	1004.1	983.5	968.9	957.4	948.2	940.4
22.5°	1141.0	1090.4	1048.8	1014.9	979.6	955.1	938.8	924.7	915.1	905.1	897.6
25°	1057.6	1018.1	972.6	934.3	905.1	889.4	876.0	863.9	857.9	851.1	842.6
27.5°	984.6	940.7	898.1	868.5	842.9	828.9	819.4	811.2	805.5	801.6	796.8
30°	933.1	888.7	855.4	826.2	805.0	791.1	785.0	780.1	773.4	771.0	768.6
32.5°	883.5	843.6	815.1	789.8	769.5	760.4	754.9	750.5	745.3	742.8	738.0
35°	813.5	780.1	752.2	738.2	721.8	713.9	709.7	703.6	698.8	696.3	695.7
37.5°	747.6	718.6	700.2	682.2	675.3	670.5	664.6	660.5	659.1	658.7	658.1
40°	704.8	681.1	664.8	650.2	647.1	639.8	635.0	631.4	631.4	632.0	631.4
42.5°	666.0	644.8	630.3	617.7	614.1	609.7	604.9	604.7	605.6	607.7	605.6
45°	607.1	591.9	581.6	575.5	568.9	564.6	564.0	565.8	566.4	567.0	568.9
47.5°	552.9	542.9	533.5	526.8	523.9	523.2	522.4	525.6	528.5	529.7	532.4
50°	520.9	509.4	501.5	497.2	494.8	493.5	494.8	498.4	500.8	503.9	505.7
52.5°	485.0	476.8	471.3	468.1	467.1	467.9	468.1	472.2	476.1	477.2	478.0
55°	435.3	429.2	428.0	422.6	424.9	424.4	427.4	429.8	433.5	437.1	437.7
57.5°	385.7	380.9	377.6	378.1	378.8	381.5	384.0	388.3	392.2	396.1	396.4
60°	352.8	350.3	348.5	348.5	349.7	353.3	356.3	360.6	363.1	365.4	367.3
62.5°	322.6	320.2	318.4	319.3	322.5	324.6	328.2	330.5	333.0	335.3	336.2
65°	275.0	273.8	275.6	276.9	277.4	280.5	284.7	286.5	289.0	290.2	294.5
67.5°	231.2	231.4	231.2	232.9	236.4	237.1	241.1	245.4	245.9	248.2	251.0
70°	201.5	202.8	204.0	205.2	208.3	209.5	212.5	214.3	216.7	218.6	220.4
72.5°	174.4	174.6	175.8	175.5	178.1	180.8	183.3	185.1	187.6	189.9	191.7
75°	134.2	134.2	135.4	136.0	139.0	142.0	141.5	142.7	145.1	147.5	148.8
77.5°	98.0	96.6	98.0	98.6	99.6	102.1	102.6	104.3	107.1	106.2	107.6
80°	74.7	72.9	74.7	75.3	75.3	78.3	78.3	79.5	81.4	79.5	81.4
82.5°	53.3	52.4	53.8	53.9	54.9	55.0	56.0	56.2	58.1	57.2	58.1
85°	26.7	26.1	26.7	26.1	26.7	27.3	27.3	26.7	26.7	28.0	26.1
87.5°	9.4	9.2	8.9	9.1	8.8	8.6	8.2	8.3	8.4	7.6	7.7
90°	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4	12.9	13.5	14.0
92.5°	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5	13.9	14.2	14.4
95°	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9	23.4	24.1	24.3
97.5°	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9	30.4	30.9	31.2
100°	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6	34.5	35.6	36.2
102.5°	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1	36.4	37.6	38.4
105°	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5	37.9	39.2	40.2
107.5°	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6	43.3	41.8	41.4
110°	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4	60.0	47.8	41.8



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9	110.0	65.0	42.7
115°	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1	171.0	113.9	81.0
117.5°	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4	337.5	323.8	302.3
120°	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5	410.9	412.4	404.8
122.5°	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4	435.3	436.3	435.1
125°	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3	471.2	472.1	472.7
127.5°	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5	504.8	506.0	506.7
130°	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6	525.9	527.3	527.9
132.5°	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0	546.2	547.3	547.9
135°	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3	575.4	576.7	577.2
137.5°	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3	602.5	603.8	604.2
140°	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9	620.0	621.2	621.4
142.5°	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1	636.1	637.2	637.3
145°	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7	658.6	659.5	659.7
147.5°	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6	678.2	678.8	678.9
150°	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7	690.5	691.2	691.3
152.5°	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8	701.6	702.3	702.3
155°	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7	716.5	717.2	717.1
157.5°	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4	729.2	730.1	730.0
160°	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7	736.5	737.2	737.1
162.5°	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6	743.4	744.3	744.2
165°	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0	751.8	752.7	752.7
167.5°	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0	758.8	759.6	759.5
170°	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5	762.3	763.2	763.1
172.5°	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1	765.0	765.9	765.7
175°	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1	767.9	768.7	768.6
177.5°	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4	768.0	768.7	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1515.0	1514.1	1514.1	1509.7	1514.1	1514.1	1515.0	1519.9	1521.4	1522.3	1520.4
5°	1405.4	1403.6	1400.6	1403.6	1400.6	1403.6	1405.4	1413.9	1418.2	1422.4	1426.1
7.5°	1297.0	1289.7	1288.6	1281.4	1288.6	1289.7	1297.0	1301.0	1309.5	1319.1	1327.9
10°	1217.8	1213.0	1212.4	1200.8	1212.4	1213.0	1217.8	1228.1	1236.7	1248.2	1260.3
12.5°	1157.6	1146.0	1148.3	1141.5	1148.3	1146.0	1157.6	1157.7	1167.7	1174.8	1193.8
15°	1053.3	1053.3	1050.9	1040.5	1050.9	1053.3	1053.3	1069.7	1072.7	1084.3	1100.7
17.5°	978.4	977.2	971.4	974.2	971.4	977.2	978.4	990.4	992.4	1007.9	1021.4
20°	933.7	930.1	922.8	922.8	922.8	930.1	933.7	940.4	948.2	957.4	968.9
22.5°	891.4	891.2	883.4	885.9	883.4	891.2	891.4	897.6	905.1	915.1	924.7
25°	842.0	837.2	833.5	835.4	833.5	837.2	842.0	842.6	851.1	857.9	863.9
27.5°	795.2	792.5	792.3	787.3	792.3	792.5	795.2	796.8	801.6	805.5	811.2
30°	767.9	761.9	763.1	760.1	763.1	761.9	767.9	768.6	771.0	773.4	780.1
32.5°	736.9	734.7	733.5	730.9	733.5	734.7	736.9	738.0	742.8	745.3	750.5
35°	694.5	695.1	692.1	693.3	692.1	695.1	694.5	695.7	696.3	698.8	703.6
37.5°	657.5	659.4	658.0	658.3	658.0	659.4	657.5	658.1	658.7	659.1	660.5
40°	633.2	633.2	633.2	635.0	633.2	633.2	633.2	631.4	632.0	631.4	631.4
42.5°	609.9	609.0	607.9	607.8	607.9	609.0	609.9	605.6	607.7	605.6	604.7
45°	570.1	571.9	572.5	569.4	572.5	571.9	570.1	568.9	567.0	566.4	565.8
47.5°	534.0	534.2	534.0	536.7	534.0	534.2	534.0	532.4	529.7	528.5	525.6
50°	508.7	507.6	508.7	507.6	508.7	507.6	508.7	505.7	503.9	500.8	498.4
52.5°	482.0	482.3	481.6	481.3	481.6	482.3	482.0	478.0	477.2	476.1	472.2
55°	440.1	441.3	440.8	440.8	440.8	441.3	440.1	437.7	437.1	433.5	429.8
57.5°	396.8	397.9	398.7	396.1	398.7	397.9	396.8	396.4	396.1	392.2	388.3
60°	366.7	369.7	369.1	367.9	369.1	369.7	366.7	367.3	365.4	363.1	360.6
62.5°	339.0	340.1	340.0	339.8	340.0	340.1	339.0	336.2	335.3	333.0	330.5
65°	296.3	297.5	295.6	297.5	295.6	297.5	296.3	294.5	290.2	289.0	286.5
67.5°	250.3	250.6	251.9	252.8	251.9	250.6	250.3	251.0	248.2	245.9	245.4
70°	221.6	221.0	222.8	224.7	222.8	221.0	221.6	220.4	218.6	216.7	214.3
72.5°	191.5	192.8	192.2	193.5	192.2	192.8	191.5	191.7	189.9	187.6	185.1
75°	147.5	149.3	148.8	150.6	148.8	149.3	147.5	148.8	147.5	145.1	142.7
77.5°	106.6	106.9	106.6	107.6	106.6	106.9	106.6	107.6	106.2	107.1	104.3
80°	81.4	80.2	78.9	81.4	78.9	80.2	81.4	81.4	79.5	81.4	79.5
82.5°	56.6	57.3	56.1	56.1	56.1	57.3	56.6	58.1	57.2	58.1	56.2
85°	26.1	25.5	24.3	24.3	24.3	25.5	26.1	26.1	28.0	26.7	26.7
87.5°	7.7	7.3	7.3	6.9	7.3	7.3	7.7	7.7	7.6	8.4	8.3
90°	14.3	14.5	14.7	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4
92.5°	14.5	14.7	14.8	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5
95°	24.2	24.1	24.0	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9
97.5°	31.4	31.5	31.7	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9
100°	36.4	36.7	36.9	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6
102.5°	38.8	39.1	39.5	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1
105°	40.6	41.2	41.7	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5
107.5°	41.9	42.4	42.9	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6
110°	42.3	42.9	43.3	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	43.1	43.5	43.9	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9
115°	72.1	63.2	54.3	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1
117.5°	273.1	244.0	214.8	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4
120°	388.2	371.5	354.9	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5
122.5°	431.8	428.6	425.4	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4
125°	473.0	473.4	473.8	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3
127.5°	506.8	506.8	506.9	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5
130°	527.8	527.7	527.5	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6
132.5°	547.7	547.6	547.5	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0
135°	576.9	576.7	576.5	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3
137.5°	603.7	603.3	602.9	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3
140°	620.8	620.1	619.5	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9
142.5°	636.8	636.1	635.5	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1
145°	659.0	658.4	657.7	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7
147.5°	678.3	677.9	677.3	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6
150°	690.6	690.0	689.4	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7
152.5°	701.4	700.6	699.8	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8
155°	716.1	715.2	714.2	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7
157.5°	729.0	728.1	727.1	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4
160°	736.3	735.4	734.6	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7
162.5°	743.1	742.0	740.9	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6
165°	751.8	751.0	750.1	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0
167.5°	758.4	757.3	756.2	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0
170°	762.0	760.9	759.8	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5
172.5°	764.6	763.5	762.4	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1
175°	767.3	766.1	764.9	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1
177.5°	767.8	766.8	766.0	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1518.0	1523.3	1531.6	1540.3	1545.6	1555.8	1558.8	1563.6	1568.0	1578.2	1588.9
5°	1430.3	1438.8	1458.8	1469.7	1484.9	1502.5	1514.1	1526.2	1539.6	1562.7	1583.9
7.5°	1336.3	1350.5	1375.4	1395.8	1417.5	1442.7	1460.9	1484.9	1504.8	1537.4	1568.4
10°	1273.7	1293.7	1316.2	1340.5	1370.8	1397.5	1423.0	1453.3	1477.7	1516.5	1552.9
12.5°	1217.3	1220.4	1252.5	1279.3	1320.8	1353.8	1383.2	1422.3	1446.0	1492.2	1530.6
15°	1118.9	1137.1	1166.3	1187.5	1236.7	1278.5	1319.8	1360.5	1387.8	1444.9	1495.2
17.5°	1035.9	1052.7	1082.6	1117.4	1152.7	1194.4	1247.8	1290.7	1327.9	1393.1	1452.6
20°	983.5	1004.1	1034.5	1070.3	1101.3	1146.8	1192.9	1242.1	1282.1	1355.7	1425.5
22.5°	938.8	955.1	979.6	1014.9	1048.8	1090.4	1141.0	1194.5	1236.5	1315.8	1386.6
25°	876.0	889.4	905.1	934.3	972.6	1018.1	1057.6	1116.4	1177.7	1251.8	1337.4
27.5°	819.4	828.9	842.9	868.5	898.1	940.7	984.6	1040.5	1102.1	1182.5	1272.8
30°	785.0	791.1	805.0	826.2	855.4	888.7	933.1	986.5	1049.6	1131.0	1220.8
32.5°	754.9	760.4	769.5	789.8	815.1	843.6	883.5	937.0	997.2	1077.1	1176.6
35°	709.7	713.9	721.8	738.2	752.2	780.1	813.5	862.1	918.5	995.1	1098.2
37.5°	664.6	670.5	675.3	682.2	700.2	718.6	747.6	788.6	844.0	921.2	1019.5
40°	635.0	639.8	647.1	650.2	664.8	681.1	704.8	742.4	798.4	868.7	964.6
42.5°	604.9	609.7	614.1	617.7	630.3	644.8	666.0	698.3	747.8	816.3	911.2
45°	564.0	564.6	568.9	575.5	581.6	591.9	607.1	635.0	673.3	737.6	823.8
47.5°	522.4	523.2	523.9	526.8	533.5	542.9	552.9	575.7	609.9	661.2	745.1
50°	494.8	493.5	494.8	497.2	501.5	509.4	520.9	537.3	565.2	613.1	690.2
52.5°	468.1	467.9	467.1	468.1	471.3	476.8	485.0	498.9	523.9	568.0	635.9
55°	427.4	424.4	424.9	422.6	428.0	429.2	435.3	446.8	468.7	499.0	562.8
57.5°	384.0	381.5	378.8	378.1	377.6	380.9	385.7	394.8	411.6	438.2	489.9
60°	356.3	353.3	349.7	348.5	348.5	350.3	352.8	359.4	375.2	398.9	441.3
62.5°	328.2	324.6	322.5	319.3	318.4	320.2	322.6	327.3	338.7	361.0	397.7
65°	284.7	280.5	277.4	276.9	275.6	273.8	275.0	279.9	289.0	306.6	335.7
67.5°	241.1	237.1	236.4	232.9	231.2	231.4	231.2	235.3	240.7	256.0	277.7
70°	212.5	209.5	208.3	205.2	204.0	202.8	201.5	205.2	210.6	223.4	242.2
72.5°	183.3	180.8	178.1	175.5	175.8	174.6	174.4	176.6	181.0	192.8	207.2
75°	141.5	142.0	139.0	136.0	135.4	134.2	134.2	136.0	137.8	146.9	158.4
77.5°	102.6	102.1	99.6	98.6	98.0	96.6	98.0	99.2	100.1	106.2	114.7
80°	78.3	78.3	75.3	75.3	74.7	72.9	74.7	73.4	75.9	82.0	88.0
82.5°	56.0	55.0	54.9	53.9	53.8	52.4	53.3	54.5	55.5	59.7	63.3
85°	27.3	27.3	26.7	26.1	26.7	26.1	26.7	27.3	28.0	29.8	32.8
87.5°	8.2	8.6	8.8	9.1	8.9	9.2	9.4	9.7	10.4	10.6	10.8
90°	11.7	11.1	10.1	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6
92.5°	13.2	12.8	12.4	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2
95°	22.3	21.6	20.8	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0
97.5°	29.5	28.9	26.9	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5
100°	32.6	31.6	29.5	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2
102.5°	33.7	32.5	50.0	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5
105°	35.2	33.8	67.5	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6
107.5°	45.9	47.4	87.7	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5
110°	84.8	97.0	132.7	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	199.9	244.8	253.6	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1
115°	285.1	342.1	339.1	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9
117.5°	365.2	379.0	376.8	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9
120°	408.0	406.5	404.3	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2
122.5°	433.6	432.7	430.2	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0
125°	469.4	468.6	466.3	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8
127.5°	502.2	501.0	499.2	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1
130°	523.2	521.9	520.5	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8
132.5°	543.8	542.7	541.4	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1
135°	573.0	571.8	570.7	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9
137.5°	600.2	599.0	597.7	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1
140°	617.8	616.7	615.3	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2
142.5°	634.1	633.1	631.5	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1
145°	657.0	656.1	653.9	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2
147.5°	676.9	676.2	674.1	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0
150°	689.0	688.2	686.3	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3
152.5°	700.1	699.3	697.4	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2
155°	715.0	714.3	712.8	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6
157.5°	727.5	726.7	725.6	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3
160°	735.0	734.3	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3
162.5°	741.7	740.9	740.3	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3
165°	750.1	749.2	748.8	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9
167.5°	757.1	756.2	755.9	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0
170°	760.7	759.8	759.5	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0
172.5°	763.3	762.4	762.2	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6
175°	766.2	765.3	765.1	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1
177.5°	766.7	766.0	765.9	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1587.9	1590.3	1598.1	1605.9	1614.6	1617.1	1621.0	1617.6	1616.5	1625.8	1632.6
5°	1592.4	1603.3	1624.6	1644.0	1660.4	1671.9	1684.1	1688.9	1698.0	1710.8	1726.6
7.5°	1587.3	1608.5	1642.0	1670.2	1701.1	1723.3	1740.7	1755.5	1773.5	1797.6	1823.9
10°	1581.4	1610.0	1650.7	1685.3	1722.9	1751.4	1775.1	1798.2	1825.0	1858.3	1892.9
12.5°	1570.8	1604.6	1655.5	1696.5	1744.8	1772.8	1804.7	1854.6	1883.2	1929.7	1978.4
15°	1549.3	1586.9	1658.0	1708.3	1763.0	1816.4	1875.3	1922.6	1970.0	1997.3	2065.9
17.5°	1517.3	1572.6	1651.3	1710.1	1779.5	1863.6	1929.8	1983.5	2038.1	2082.4	2116.8
20°	1491.6	1551.7	1641.6	1712.0	1794.5	1885.0	1960.9	2015.5	2062.9	2099.9	2121.1
22.5°	1459.0	1534.7	1622.2	1704.7	1810.1	1899.6	1979.3	2022.4	2061.9	2080.0	2088.1
25°	1407.9	1498.9	1597.8	1698.7	1817.7	1912.3	1985.2	2011.3	2022.8	2005.3	1976.1
27.5°	1352.6	1454.1	1569.8	1687.2	1813.0	1904.1	1956.3	1952.2	1932.6	1875.7	1830.1
30°	1311.3	1423.0	1547.4	1675.5	1801.8	1890.5	1920.8	1890.5	1846.2	1782.4	1717.5
32.5°	1268.1	1383.7	1523.7	1659.1	1781.5	1859.4	1866.0	1813.8	1745.2	1672.7	1591.7
35°	1202.6	1327.7	1478.8	1622.2	1738.1	1787.2	1758.2	1665.9	1584.5	1485.6	1375.1
37.5°	1128.7	1266.8	1418.4	1568.1	1673.2	1686.0	1613.7	1516.5	1401.8	1285.5	1155.4
40°	1073.3	1219.6	1375.7	1526.9	1619.7	1606.4	1514.1	1407.2	1270.7	1128.5	1007.7
42.5°	1023.8	1170.1	1329.0	1477.3	1551.7	1515.0	1407.2	1276.1	1129.3	995.5	884.9
45°	937.9	1088.5	1251.3	1394.5	1437.0	1370.8	1228.1	1082.4	937.9	826.2	738.9
47.5°	854.7	1003.5	1164.7	1290.5	1305.6	1216.6	1060.7	910.8	786.6	695.6	633.9
50°	793.4	942.8	1102.5	1214.8	1209.9	1102.5	942.2	799.5	695.7	622.3	581.0
52.5°	738.6	879.6	1033.0	1135.1	1109.4	992.2	839.2	712.6	627.2	569.8	532.4
55°	653.2	783.8	929.5	1011.4	964.1	834.2	704.8	602.9	539.7	496.6	467.5
57.5°	568.5	690.9	815.6	866.1	813.7	693.8	586.0	512.0	464.5	432.6	413.7
60°	516.0	622.9	734.0	777.7	715.2	608.3	523.3	457.2	418.9	392.8	375.8
62.5°	463.6	559.3	664.0	687.9	630.7	540.3	465.0	410.0	378.6	355.4	339.4
65°	392.2	470.5	550.0	565.8	513.0	443.1	383.7	347.8	320.0	302.9	290.2
67.5°	321.6	384.5	440.8	453.6	407.3	358.9	315.9	284.7	265.8	251.7	240.9
70°	279.9	329.6	375.8	386.1	349.1	305.9	273.2	248.3	231.3	219.2	208.8
72.5°	235.7	277.2	315.5	322.5	292.2	259.4	232.4	212.9	197.8	190.0	180.2
75°	180.3	204.6	234.3	236.1	216.1	196.1	175.5	162.7	154.8	145.1	140.2
77.5°	127.2	146.3	163.3	166.6	154.7	141.1	129.5	119.5	112.8	108.3	103.8
80°	97.1	112.3	119.6	123.8	115.3	105.6	98.9	92.3	88.0	85.0	82.0
82.5°	69.5	78.8	85.6	88.9	84.3	78.4	71.8	68.0	64.7	62.2	61.1
85°	35.2	39.5	43.7	44.9	43.7	41.3	37.6	37.6	35.8	35.2	35.2
87.5°	12.5	14.7	15.0	16.7	16.0	16.2	16.4	16.1	15.8	15.4	15.1
90°	1.9	3.2	4.6	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4
92.5°	11.1	10.9	10.9	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5
95°	32.0	27.9	23.8	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9
97.5°	60.0	48.6	37.2	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9
100°	81.3	64.4	47.5	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6
102.5°	123.9	120.3	116.7	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1
105°	172.3	176.0	179.7	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5
107.5°	218.5	221.5	224.4	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6
110°	248.3	250.9	253.4	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.4	278.7	280.9	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9
115°	321.0	323.1	325.2	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1
117.5°	361.2	363.6	365.9	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4
120°	390.1	391.9	393.7	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5
122.5°	415.0	416.9	418.9	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4
125°	452.5	454.1	455.7	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3
127.5°	486.9	488.7	490.4	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5
130°	508.8	510.8	512.8	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6
132.5°	530.8	532.4	534.1	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0
135°	559.8	561.8	563.8	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3
137.5°	588.4	589.9	591.2	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3
140°	607.1	608.1	609.1	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9
142.5°	623.0	623.9	624.8	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1
145°	647.1	647.0	646.8	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7
147.5°	668.6	668.1	667.7	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6
150°	682.4	681.5	680.6	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7
152.5°	694.3	693.3	692.3	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8
155°	711.5	710.4	709.3	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7
157.5°	725.3	724.4	723.4	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4
160°	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7
162.5°	740.6	739.9	739.1	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6
165°	750.1	749.4	748.7	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0
167.5°	757.2	756.5	755.7	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0
170°	761.2	760.5	759.8	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5
172.5°	763.9	763.2	762.4	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1
175°	767.2	766.4	765.5	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1
177.5°	767.9	767.2	766.6	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6	1579.6
2.5°	1638.4	1645.2	1645.2	1646.2	1653.9	1653.0	1652.5
5°	1743.6	1753.9	1755.1	1766.0	1773.3	1770.8	1764.2
7.5°	1842.8	1861.9	1876.5	1884.7	1894.3	1900.2	1897.5
10°	1921.4	1949.4	1966.4	1977.9	1991.9	2002.2	1998.5
12.5°	1992.8	2026.1	2049.5	2069.2	2071.0	2084.2	2075.3
15°	2104.2	2139.4	2143.0	2157.6	2169.2	2167.9	2168.5
17.5°	2141.0	2152.3	2154.6	2154.9	2155.1	2150.8	2141.6
20°	2127.9	2123.6	2113.3	2105.4	2091.4	2089.6	2077.5
22.5°	2065.7	2052.2	2026.3	2009.2	1987.5	1981.8	1978.4
25°	1943.3	1913.5	1872.2	1832.8	1821.9	1800.6	1806.7
27.5°	1775.4	1729.0	1684.3	1652.3	1623.3	1591.4	1600.5
30°	1657.3	1605.1	1542.0	1493.4	1462.4	1432.1	1426.6
32.5°	1516.5	1440.0	1369.6	1326.8	1279.4	1260.2	1239.2
35°	1273.7	1199.0	1129.2	1069.1	1034.5	1007.7	983.5
37.5°	1055.3	969.3	912.9	864.3	839.2	823.9	827.8
40°	919.7	844.5	803.2	766.1	743.1	732.1	734.6
42.5°	810.0	753.6	719.6	694.3	678.0	671.9	670.5
45°	685.4	653.9	625.9	611.3	603.5	596.8	592.6
47.5°	600.4	574.6	558.9	550.2	543.4	536.5	536.4
50°	549.4	532.4	521.5	512.4	506.9	502.1	506.3
52.5°	510.6	495.0	484.1	475.9	473.9	469.5	469.4
55°	452.9	440.8	432.8	425.6	421.9	419.5	416.5
57.5°	400.4	388.9	381.6	377.0	370.1	367.7	366.7
60°	363.1	353.9	346.7	340.6	337.5	332.7	332.7
62.5°	328.5	319.5	312.7	308.0	303.1	301.1	301.6
65°	278.7	271.4	264.7	259.8	258.6	255.0	256.2
67.5°	232.7	227.9	220.9	218.2	215.9	214.0	212.5
70°	202.2	197.3	193.7	190.0	188.2	188.2	188.2
72.5°	176.4	170.6	168.4	163.8	164.9	163.0	161.0
75°	136.6	132.9	131.1	129.3	126.3	126.3	126.3
77.5°	100.5	99.4	97.3	95.3	94.6	94.0	94.2
80°	77.7	77.1	75.9	75.9	74.7	74.1	72.9
82.5°	59.7	58.1	57.4	57.0	56.7	56.6	56.3
85°	34.0	32.8	32.8	33.4	32.2	32.2	32.8
87.5°	15.7	15.8	15.4	15.4	16.0	15.6	15.6
90°	12.9	13.5	14.0	14.3	14.5	14.7	15.0
92.5°	13.9	14.2	14.4	14.5	14.7	14.8	15.0
95°	23.4	24.1	24.3	24.2	24.1	24.0	23.8
97.5°	30.4	30.9	31.2	31.4	31.5	31.7	31.8
100°	34.5	35.6	36.2	36.4	36.7	36.9	37.2
102.5°	36.4	37.6	38.4	38.8	39.1	39.5	39.8
105°	37.9	39.2	40.2	40.6	41.2	41.7	42.1
107.5°	43.3	41.8	41.4	41.9	42.4	42.9	43.3
110°	60.0	47.8	41.8	42.3	42.9	43.3	43.8



TEST NUMBER: P331591-927

CATALOG NUMBER: S122DIW-S1005D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	110.0	65.0	42.7	43.1	43.5	43.9	44.3
115°	171.0	113.9	81.0	72.1	63.2	54.3	45.5
117.5°	337.5	323.8	302.3	273.1	244.0	214.8	185.7
120°	410.9	412.4	404.8	388.2	371.5	354.9	338.3
122.5°	435.3	436.3	435.1	431.8	428.6	425.4	422.2
125°	471.2	472.1	472.7	473.0	473.4	473.8	474.1
127.5°	504.8	506.0	506.7	506.8	506.8	506.9	507.0
130°	525.9	527.3	527.9	527.8	527.7	527.5	527.4
132.5°	546.2	547.3	547.9	547.7	547.6	547.5	547.4
135°	575.4	576.7	577.2	576.9	576.7	576.5	576.2
137.5°	602.5	603.8	604.2	603.7	603.3	602.9	602.5
140°	620.0	621.2	621.4	620.8	620.1	619.5	618.9
142.5°	636.1	637.2	637.3	636.8	636.1	635.5	634.9
145°	658.6	659.5	659.7	659.0	658.4	657.7	657.2
147.5°	678.2	678.8	678.9	678.3	677.9	677.3	676.8
150°	690.5	691.2	691.3	690.6	690.0	689.4	688.8
152.5°	701.6	702.3	702.3	701.4	700.6	699.8	698.9
155°	716.5	717.2	717.1	716.1	715.2	714.2	713.2
157.5°	729.2	730.1	730.0	729.0	728.1	727.1	726.1
160°	736.5	737.2	737.1	736.3	735.4	734.6	733.7
162.5°	743.4	744.3	744.2	743.1	742.0	740.9	739.9
165°	751.8	752.7	752.7	751.8	751.0	750.1	749.2
167.5°	758.8	759.6	759.5	758.4	757.3	756.2	755.1
170°	762.3	763.2	763.1	762.0	760.9	759.8	758.7
172.5°	765.0	765.9	765.7	764.6	763.5	762.4	761.3
175°	767.9	768.7	768.6	767.3	766.1	764.9	763.7
177.5°	768.0	768.7	768.7	767.8	766.8	766.0	765.1
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4

(END OF REPORT)