

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331602-927

Luminaire Tested: **S122DIW-S1005D970U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331602-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5874.7 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331602-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331602-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55								
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	53	52	51	46								
2	90	83	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39								
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33								
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28								
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24								
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21								
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19								
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17								
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15								
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20386	20386	20386
5°	20464	20169	20285
10°	20341	19964	20064
15°	20090	19704	19686
20°	19734	19316	19295
25°	19379	18838	18838
30°	18921	18401	18243
35°	18496	17875	17611
40°	17962	17351	17015
45°	17438	16826	16411
50°	16865	16284	15707
55°	16268	15651	15071
60°	15603	14899	14347
65°	14888	14147	13498
70°	13983	13237	12609
75°	12726	12190	11890
80°	11288	10953	10386
85°	9207	8781	7873



TEST NUMBER: P331602-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.7	2.0
10°-20°	334.1	5.7
20°-30°	491.0	8.4
30°-40°	570.4	9.7
40°-50°	569.8	9.7
50°-60°	496.9	8.5
60°-70°	367.4	6.3
70°-80°	208.1	3.5
80°-90°	59.8	1.0
90°-100°	60.2	1.0
100°-110°	187.1	3.2
110°-120°	319.9	5.4
120°-130°	420.6	7.2
130°-140°	472.1	8.0
140°-150°	462.9	7.9
150°-160°	388.3	6.6
160°-170°	257.5	4.4
170°-180°	90.0	1.5
0°-30°	943.8	16.1
0°-40°	1514.2	25.8
0°-60°	2580.8	43.9
0°-90°	3216.0	54.7
90°-120°	567.2	9.7
90°-150°	1922.8	32.7
90°-180°	2659.0	45.3
0°-180°	5874.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1263	1257	1244	1253	1252	120
15°	1202	1194	1179	1183	1178	338
25°	1088	1078	1057	1060	1057	500
35°	938	926	907	900	894	586
45°	764	755	737	724	719	589
55°	578	570	556	542	535	517
65°	390	382	370	360	353	385
75°	204	201	195	189	191	218
85°	50	49	47	44	42	57
90°	1	11	28	27	27	5
95°	42	49	51	51	50	48
105°	172	175	176	178	178	182
115°	321	325	324	323	321	317
125°	467	474	472	470	469	417
135°	604	613	615	614	611	467
145°	733	739	744	744	741	458
155°	838	841	843	847	845	386
165°	912	912	912	917	913	257
175°	949	947	945	950	946	90
180°	951	951	951	951	951	



TEST NUMBER: P331602-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1268.4	1267.3	1266.3	1265.2	1264.1	1262.4	1260.0	1257.7	1255.3	1252.9	1255.1
5°	1262.6	1261.6	1260.4	1259.3	1258.3	1256.2	1253.3	1250.3	1247.4	1244.4	1246.6
7.5°	1251.4	1249.7	1248.1	1246.4	1244.8	1242.4	1239.4	1236.4	1233.3	1230.3	1232.5
10°	1240.7	1238.9	1237.0	1235.1	1233.2	1230.7	1227.4	1224.2	1220.9	1217.7	1219.9
12.5°	1226.2	1224.5	1222.8	1221.1	1219.5	1217.0	1213.8	1210.5	1207.4	1204.1	1205.6
15°	1201.9	1200.3	1198.7	1197.1	1195.4	1192.9	1189.4	1185.8	1182.3	1178.8	1180.0
17.5°	1170.8	1169.2	1167.6	1165.9	1164.3	1161.7	1158.2	1154.6	1151.0	1147.6	1148.7
20°	1148.5	1146.8	1145.3	1143.6	1142.0	1139.3	1135.5	1131.8	1128.0	1124.2	1125.0
22.5°	1126.2	1123.9	1121.7	1119.4	1117.1	1114.2	1110.6	1107.1	1103.5	1099.9	1100.1
25°	1087.8	1085.6	1083.5	1081.3	1079.2	1075.8	1071.2	1066.6	1062.0	1057.4	1058.0
27.5°	1044.1	1042.1	1040.2	1038.2	1036.3	1033.6	1029.9	1026.3	1022.7	1019.1	1018.3
30°	1014.9	1012.8	1010.6	1008.4	1006.3	1003.2	999.2	995.1	991.1	987.0	986.2
32.5°	983.9	982.1	980.4	978.7	976.9	974.0	969.7	965.4	961.2	956.9	955.5
35°	938.4	935.7	933.0	930.3	927.6	924.2	919.8	915.5	911.2	906.9	905.3
37.5°	887.2	884.9	882.5	880.1	877.7	874.4	870.1	865.8	861.4	857.1	855.1
40°	852.2	850.1	848.0	845.8	843.6	840.4	836.1	831.8	827.4	823.2	820.7
42.5°	818.2	816.1	814.0	811.8	809.6	806.4	802.1	797.7	793.4	789.1	786.5
45°	763.7	761.8	759.9	758.0	756.1	753.1	749.1	745.0	741.0	736.9	734.0
47.5°	709.2	707.5	705.7	703.9	702.1	699.1	694.9	690.7	686.5	682.3	679.1
50°	671.4	670.0	668.7	667.3	666.0	663.4	659.7	655.8	652.0	648.3	644.5
52.5°	634.5	632.7	630.9	629.2	627.3	624.6	621.1	617.5	614.0	610.5	607.3
55°	577.9	576.2	574.6	573.1	571.4	568.9	565.8	562.5	559.3	556.0	552.8
57.5°	521.1	519.8	518.5	517.2	515.9	513.5	509.9	506.4	502.8	499.2	496.1
60°	483.2	482.1	481.0	480.0	478.9	476.4	472.7	468.9	465.1	461.4	458.4
62.5°	446.3	444.6	442.8	441.1	439.3	437.0	434.1	431.3	428.3	425.4	422.6
65°	389.7	388.1	386.5	384.8	383.3	381.0	378.3	375.7	373.0	370.3	367.9
67.5°	332.2	330.9	329.5	328.3	327.0	325.1	322.7	320.3	317.8	315.4	313.5
70°	296.2	295.2	294.1	293.0	291.9	290.2	287.7	285.3	282.9	280.4	278.5
72.5°	259.3	258.3	257.1	256.1	255.0	253.7	252.2	250.6	249.0	247.4	245.5
75°	204.0	203.4	202.9	202.3	201.8	200.8	199.5	198.1	196.8	195.4	193.8
77.5°	154.4	153.5	152.6	151.7	150.8	150.0	149.5	148.9	148.4	147.9	147.0
80°	121.4	121.1	120.9	120.6	120.3	119.9	119.4	118.8	118.3	117.8	116.9
82.5°	90.3	90.3	90.2	90.2	90.1	89.9	89.6	89.3	89.0	88.6	87.6
85°	49.7	49.5	49.3	49.0	48.7	48.4	48.2	47.8	47.6	47.4	46.5
87.5°	17.7	17.7	17.7	17.7	17.7	17.8	18.1	18.5	18.9	19.3	18.5
90°	0.8	2.9	5.1	7.2	9.3	12.4	16.3	20.2	24.2	28.0	27.7
92.5°	14.3	15.8	17.4	19.0	20.6	21.8	22.7	23.7	24.6	25.5	25.6
95°	41.7	43.5	45.3	47.1	48.9	49.9	50.3	50.6	51.0	51.3	51.3
97.5°	76.2	77.8	79.4	81.0	82.5	83.7	84.3	85.0	85.6	86.3	86.3
100°	101.9	103.3	104.7	106.2	107.6	108.6	109.1	109.6	110.2	110.7	110.7
102.5°	128.9	130.0	131.1	132.3	133.4	134.4	135.0	135.7	136.3	137.0	137.2
105°	172.5	173.0	173.6	174.1	174.7	175.1	175.5	175.8	176.2	176.5	176.9
107.5°	216.5	217.3	218.0	218.8	219.6	220.0	220.0	220.0	220.0	220.0	220.1
110°	244.7	245.8	246.8	248.0	249.0	249.5	249.5	249.5	249.5	249.5	249.5



TEST NUMBER: P331602-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.5	276.6	277.7	278.8	279.8	280.3	280.1	280.0	279.9	279.7	279.2
115°	320.9	322.0	323.1	324.2	325.2	325.6	325.2	324.9	324.5	324.2	324.0
117.5°	366.2	367.7	369.1	370.5	371.9	372.1	371.1	370.1	369.2	368.1	367.7
120°	396.4	397.8	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4	396.4
122.5°	424.0	425.7	427.4	429.1	430.8	431.2	430.2	429.2	428.2	427.1	426.7
125°	467.0	468.6	470.2	471.8	473.4	474.0	473.4	472.9	472.3	471.8	471.3
127.5°	508.9	510.9	512.9	515.0	517.0	517.7	517.1	516.4	515.8	515.2	514.4
130°	535.2	537.5	539.8	542.2	544.5	545.4	545.1	544.7	544.4	544.0	543.7
132.5°	564.7	566.6	568.5	570.4	572.3	573.2	573.3	573.4	573.5	573.5	572.7
135°	604.2	606.2	608.1	610.1	612.0	613.1	613.5	613.9	614.3	614.6	614.4
137.5°	645.7	647.4	649.0	650.5	652.1	653.2	653.6	654.1	654.6	655.1	654.9
140°	670.7	672.4	674.0	675.6	677.2	678.4	679.4	680.2	681.1	682.0	682.0
142.5°	696.5	698.1	699.7	701.2	702.9	704.0	704.6	705.2	705.8	706.4	706.5
145°	733.3	734.6	735.9	737.1	738.4	739.5	740.6	741.6	742.8	743.8	743.9
147.5°	766.3	767.8	769.3	770.7	772.2	773.3	774.0	774.8	775.5	776.2	776.6
150°	788.7	789.8	790.8	791.9	793.0	793.9	794.6	795.4	796.1	796.8	797.3
152.5°	808.7	809.7	810.8	811.8	812.9	813.9	814.8	815.6	816.4	817.3	817.9
155°	838.4	839.0	839.6	840.1	840.6	841.1	841.7	842.2	842.7	843.3	844.1
157.5°	864.0	864.4	864.7	865.1	865.4	865.8	866.1	866.4	866.7	867.0	868.2
160°	879.4	879.7	880.1	880.4	880.8	881.1	881.3	881.5	881.6	881.8	882.9
162.5°	893.5	893.6	893.7	893.7	893.8	893.9	894.1	894.3	894.5	894.6	895.9
165°	912.3	912.1	912.0	911.7	911.6	911.5	911.5	911.5	911.5	911.5	912.8
167.5°	928.0	927.5	926.9	926.4	925.9	925.6	925.6	925.5	925.5	925.4	926.7
170°	936.4	935.8	935.3	934.8	934.2	933.9	933.7	933.5	933.3	933.2	934.4
172.5°	942.1	941.6	941.0	940.6	940.0	939.6	939.4	939.3	939.1	938.9	940.2
175°	949.2	948.6	948.2	947.6	947.1	946.6	946.3	945.9	945.5	945.2	946.4
177.5°	952.1	951.6	951.3	950.8	950.4	950.0	949.7	949.4	949.2	948.9	949.7
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331602-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6	1262.6
2.5°	1257.2	1259.3	1261.6	1262.4	1261.9	1261.6	1261.1	1260.7
5°	1248.7	1250.9	1253.0	1253.9	1253.3	1252.8	1252.2	1251.6
7.5°	1234.6	1236.8	1239.0	1239.8	1239.1	1238.6	1237.9	1237.4
10°	1222.0	1224.2	1226.3	1227.0	1226.2	1225.3	1224.6	1223.8
12.5°	1207.1	1208.6	1210.1	1210.6	1210.0	1209.4	1208.8	1208.2
15°	1181.0	1182.1	1183.1	1183.0	1181.7	1180.4	1179.0	1177.7
17.5°	1150.0	1151.3	1152.5	1152.5	1151.1	1149.9	1148.6	1147.2
20°	1125.8	1126.6	1127.4	1127.3	1126.2	1125.1	1124.1	1123.0
22.5°	1100.3	1100.4	1100.6	1100.3	1099.7	1099.1	1098.4	1097.7
25°	1058.5	1059.1	1059.6	1059.6	1059.1	1058.5	1058.0	1057.4
27.5°	1017.5	1016.6	1015.8	1014.8	1013.5	1012.2	1010.9	1009.6
30°	985.4	984.6	983.8	982.9	981.8	980.6	979.6	978.5
32.5°	954.0	952.5	951.1	949.8	948.7	947.7	946.6	945.5
35°	903.6	902.1	900.4	899.0	897.6	896.3	894.8	893.5
37.5°	853.1	851.1	849.1	847.5	846.2	844.9	843.6	842.3
40°	818.2	815.9	813.4	811.7	810.6	809.5	808.4	807.3
42.5°	783.9	781.2	778.6	776.5	775.0	773.5	772.0	770.4
45°	731.0	728.0	725.1	723.0	721.9	720.9	719.8	718.7
47.5°	676.0	672.9	669.8	667.4	665.8	664.3	662.7	661.2
50°	640.7	637.0	633.2	630.7	629.3	628.0	626.6	625.3
52.5°	604.2	601.0	597.9	595.5	593.7	591.9	590.1	588.4
55°	549.5	546.3	543.1	540.8	539.5	538.1	536.8	535.4
57.5°	492.8	489.6	486.5	484.3	483.4	482.4	481.3	480.3
60°	455.4	452.4	449.5	447.6	446.8	446.0	445.1	444.3
62.5°	419.9	417.2	414.4	412.5	411.5	410.4	409.4	408.4
65°	365.4	363.0	360.6	358.7	357.4	356.0	354.7	353.3
67.5°	311.6	309.7	307.8	306.3	305.3	304.2	303.2	302.1
70°	276.6	274.8	272.9	271.4	270.3	269.3	268.2	267.1
72.5°	243.7	241.8	239.9	238.5	237.7	236.8	235.9	235.0
75°	192.3	190.6	189.0	188.5	189.0	189.5	190.0	190.6
77.5°	146.2	145.4	144.7	143.9	143.1	142.4	141.6	140.9
80°	116.1	115.3	114.5	113.8	113.3	112.8	112.3	111.7
82.5°	86.6	85.6	84.5	84.0	83.8	83.7	83.7	83.5
85°	45.7	44.9	44.1	43.6	43.3	43.0	42.8	42.5
87.5°	17.7	17.0	16.3	15.9	15.7	15.5	15.4	15.1
90°	27.3	27.0	26.6	26.5	26.8	26.9	27.1	27.3
92.5°	25.7	25.7	25.8	25.8	25.9	25.9	26.0	26.0
95°	51.3	51.3	51.3	51.2	50.8	50.5	50.1	49.7
97.5°	86.3	86.3	86.3	86.3	86.3	86.3	86.2	86.2
100°	110.7	110.7	110.7	110.7	110.4	110.3	110.1	110.0
102.5°	137.4	137.4	137.6	137.6	137.4	137.2	137.0	136.9
105°	177.2	177.6	177.9	178.2	178.2	178.2	178.2	178.2
107.5°	220.3	220.5	220.5	220.2	219.4	218.6	217.8	217.0
110°	249.5	249.5	249.5	249.3	248.7	248.2	247.6	247.2



TEST NUMBER: P331602-927

CATALOG NUMBER: S122DIW-S1005D970U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	278.8	278.5	278.0	277.6	277.2	276.8	276.4	276.0
115°	323.8	323.6	323.4	323.1	322.6	322.0	321.5	320.9
117.5°	367.3	366.9	366.4	365.9	365.4	364.9	364.3	363.8
120°	396.4	396.4	396.4	396.1	395.5	395.1	394.5	394.0
122.5°	426.4	425.9	425.5	425.1	424.7	424.3	423.9	423.5
125°	470.7	470.2	469.7	469.3	469.1	469.0	468.7	468.6
127.5°	513.8	513.2	512.5	511.9	511.4	510.8	510.2	509.7
130°	543.3	543.0	542.6	542.0	541.3	540.6	539.9	539.2
132.5°	572.0	571.2	570.4	569.7	569.2	568.5	568.0	567.4
135°	614.3	614.1	613.9	613.5	613.0	612.4	612.0	611.4
137.5°	654.7	654.7	654.5	654.0	653.3	652.6	651.9	651.2
140°	682.0	682.0	682.0	681.7	681.0	680.2	679.5	678.8
142.5°	706.7	706.9	706.9	706.7	706.0	705.3	704.6	703.9
145°	744.2	744.3	744.5	744.3	743.5	742.8	742.1	741.4
147.5°	777.0	777.4	777.8	777.6	777.0	776.3	775.6	774.9
150°	797.8	798.4	798.9	798.9	798.4	797.8	797.3	796.8
152.5°	818.6	819.4	820.0	820.0	819.4	818.6	817.9	817.3
155°	845.1	846.0	846.8	847.0	846.5	846.0	845.4	844.9
157.5°	869.5	870.7	871.9	872.0	871.2	870.4	869.5	868.6
160°	883.9	885.0	886.1	886.3	885.6	884.9	884.2	883.4
162.5°	897.1	898.3	899.5	899.7	898.8	897.9	897.1	896.3
165°	914.0	915.2	916.5	916.6	915.8	914.9	914.0	913.1
167.5°	928.0	929.2	930.4	930.6	929.7	928.8	927.8	926.9
170°	935.6	936.9	938.2	938.3	937.2	936.1	935.0	934.0
172.5°	941.4	942.7	943.9	944.0	942.9	941.9	940.8	939.8
175°	947.7	949.0	950.1	950.3	949.2	948.2	947.1	946.0
177.5°	950.6	951.4	952.3	952.3	951.4	950.6	949.7	948.9
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8

(END OF REPORT)