

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331489-927

Luminaire Tested: **S122DIW-S290D1440U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331489-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1440U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5599.9 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	76	67	60	55	66	59	54	49	45	41	38	32	29	27	19	18	17	12
4	69	59	52	46	61	52	46	41	40	36	32	28	26	23	17	16	15	10
5	63	53	45	39	56	47	40	35	36	31	28	25	22	20	16	14	13	9
6	58	47	39	34	51	42	35	31	32	27	24	23	20	18	14	13	11	8
7	54	42	35	30	47	38	31	27	29	24	21	21	18	16	13	11	10	7
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	12	10	9	6
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	9	8	6
10	43	32	25	20	38	28	22	19	22	18	15	16	13	11	10	9	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	0.8
10°-20°	129.6	2.3
20°-30°	188.1	3.4
30°-40°	198.5	3.5
40°-50°	175.8	3.1
50°-60°	140.3	2.5
60°-70°	95.4	1.7
70°-80°	48.9	0.9
80°-90°	15.6	0.3
90°-100°	51.9	0.9
100°-110°	190.5	3.4
110°-120°	509.1	9.1
120°-130°	840.4	15.0
130°-140°	893.8	16.0
140°-150°	830.7	14.8
150°-160°	667.9	11.9
160°-170°	430.4	7.7
170°-180°	148.2	2.6
0°-30°	362.4	6.5
0°-40°	560.9	10.0
0°-60°	877.0	15.7
0°-90°	1036.9	18.5
90°-120°	751.5	13.4
90°-150°	3316.5	59.2
90°-180°	4563.0	81.5
0°-180°	5599.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	11
90°	30	1	30	1	30	14
95°	48	73	48	73	48	45
105°	86	342	86	342	86	89
115°	92	648	92	648	92	231
125°	963	916	963	916	963	834
135°	1171	1134	1171	1134	1171	902
145°	1335	1315	1335	1315	1335	835
155°	1449	1448	1449	1448	1449	669
165°	1522	1526	1522	1526	1522	430
175°	1551	1560	1551	1560	1551	148
180°	1557	1557	1557	1557	1557	



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	9.8	9.7	9.7	9.5	9.4	9.4	9.1	8.7	8.6	8.6	8.3
90°	30.4	29.9	29.4	28.9	28.4	27.6	26.3	25.0	23.8	22.5	20.5
92.5°	30.4	30.1	29.8	29.5	29.2	28.8	28.1	27.4	26.8	26.1	25.1
95°	48.5	48.7	49.0	49.2	49.4	49.0	47.7	46.4	45.2	44.0	42.2
97.5°	64.6	64.4	64.1	63.8	63.5	62.8	61.8	60.8	59.8	58.8	54.7
100°	75.5	75.0	74.5	74.0	73.5	72.2	70.3	68.2	66.2	64.2	60.0
102.5°	80.9	80.2	79.5	78.8	78.1	76.4	73.8	71.2	68.6	66.0	101.6
105°	85.6	84.6	83.7	82.6	81.6	79.8	77.0	74.2	71.5	68.8	137.0
107.5°	88.1	87.1	86.1	85.1	84.1	85.0	87.8	90.6	93.4	96.3	178.2
110°	89.0	88.0	87.0	86.0	85.0	97.0	122.1	147.1	172.1	197.2	269.5



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	89.9	89.1	88.3	87.5	86.7	132.0	223.3	314.7	406.0	497.3	515.2
115°	92.4	110.4	128.4	146.5	164.5	231.5	347.4	463.3	579.2	695.1	688.9
117.5°	377.2	436.4	495.7	554.9	614.2	657.8	685.9	713.9	742.0	770.0	765.6
120°	687.3	721.0	754.9	788.7	822.4	837.9	834.9	831.9	828.9	825.9	821.3
122.5°	857.6	864.2	870.8	877.3	883.8	886.2	884.5	882.6	880.8	879.0	874.1
125°	963.3	962.6	961.8	961.1	960.3	959.0	957.3	955.5	953.8	952.0	947.3
127.5°	1030.0	1029.8	1029.7	1029.5	1029.4	1028.0	1025.5	1022.9	1020.4	1017.9	1014.3
130°	1071.4	1071.7	1072.0	1072.2	1072.5	1071.2	1068.5	1065.7	1063.0	1060.2	1057.4
132.5°	1112.0	1112.3	1112.5	1112.8	1113.0	1112.0	1109.6	1107.2	1104.9	1102.6	1099.8
135°	1170.6	1171.1	1171.6	1172.1	1172.6	1171.6	1169.1	1166.6	1164.1	1161.6	1159.4
137.5°	1224.0	1224.9	1225.7	1226.5	1227.4	1226.6	1224.2	1221.7	1219.2	1216.8	1214.3
140°	1257.4	1258.6	1259.9	1261.2	1262.3	1261.9	1259.6	1257.4	1255.1	1252.8	1250.1
142.5°	1289.8	1291.1	1292.3	1293.6	1294.8	1294.4	1292.4	1290.3	1288.2	1286.2	1283.0
145°	1335.1	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3	1334.6	1332.8	1328.6
147.5°	1375.0	1376.0	1377.1	1378.2	1379.2	1379.1	1377.8	1376.5	1375.1	1373.9	1369.7
150°	1399.3	1400.6	1401.8	1403.1	1404.3	1404.2	1402.7	1401.2	1399.7	1398.2	1394.2
152.5°	1420.1	1421.7	1423.4	1425.0	1426.6	1426.7	1425.2	1423.7	1422.2	1420.7	1416.9
155°	1448.9	1450.9	1452.9	1454.9	1456.9	1457.1	1455.6	1454.1	1452.6	1451.1	1448.2
157.5°	1475.3	1477.2	1479.2	1481.1	1483.0	1483.2	1481.5	1479.8	1478.1	1476.4	1474.3
160°	1490.6	1492.3	1494.1	1495.9	1497.6	1497.7	1496.2	1494.7	1493.2	1491.7	1490.2
162.5°	1503.2	1505.4	1507.5	1509.7	1511.8	1512.0	1510.4	1508.6	1507.0	1505.2	1504.0
165°	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1	1521.4
167.5°	1534.1	1536.4	1538.6	1540.9	1543.1	1543.3	1541.6	1539.8	1538.1	1536.4	1535.6
170°	1541.3	1543.6	1545.8	1548.1	1550.3	1550.5	1548.8	1547.1	1545.3	1543.6	1543.0
172.5°	1546.7	1549.0	1551.2	1553.5	1555.7	1555.9	1554.2	1552.4	1550.7	1549.0	1548.5
175°	1551.4	1553.9	1556.4	1558.9	1561.5	1561.8	1560.0	1558.3	1556.6	1554.8	1554.3
177.5°	1554.3	1556.2	1558.0	1559.7	1561.5	1561.8	1560.4	1558.9	1557.6	1556.2	1555.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	8.0	7.6	7.2	7.1	6.0	5.5	4.4	3.4	3.8	4.2	4.4
90°	18.5	16.6	14.5	12.1	9.4	6.7	3.9	1.1	3.9	6.7	9.4
92.5°	24.2	23.1	22.1	21.8	22.0	22.3	22.5	22.7	22.5	22.3	22.0
95°	40.4	38.7	36.9	40.2	48.5	56.7	65.0	73.2	65.0	56.7	48.5
97.5°	50.7	46.7	42.6	52.2	75.5	98.8	122.1	145.4	122.1	98.8	75.5
100°	55.7	51.4	47.2	62.2	96.5	130.8	165.1	199.4	165.1	130.8	96.5
102.5°	137.2	172.9	208.4	229.9	237.1	244.4	251.7	258.9	251.7	244.4	237.1
105°	205.4	273.8	342.1	372.6	365.0	357.5	350.0	342.5	350.0	357.5	365.0
107.5°	260.2	342.1	424.1	462.1	456.0	450.0	443.9	437.8	443.9	450.0	456.0
110°	341.9	414.2	486.6	520.1	514.9	509.6	504.4	499.2	504.4	509.6	514.9



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	533.1	551.0	568.8	575.4	570.8	566.1	561.4	556.8	561.4	566.1	570.8
115°	682.6	676.4	670.1	664.9	660.6	656.3	652.1	647.8	652.1	656.3	660.6
117.5°	761.4	757.0	752.7	748.2	743.5	738.7	734.0	729.2	734.0	738.7	743.5
120°	816.8	812.3	807.8	803.7	799.9	796.1	792.4	788.7	792.4	796.1	799.9
122.5°	869.2	864.3	859.4	855.0	851.0	847.1	843.1	839.2	843.1	847.1	851.0
125°	942.5	937.8	933.0	929.0	925.7	922.5	919.2	916.0	919.2	922.5	925.7
127.5°	1010.7	1007.2	1003.6	1000.1	996.4	992.8	989.2	985.6	989.2	992.8	996.4
130°	1054.7	1051.9	1049.2	1045.8	1041.8	1037.8	1033.8	1029.8	1033.8	1037.8	1041.8
132.5°	1097.0	1094.3	1091.5	1088.5	1085.1	1081.6	1078.2	1074.8	1078.2	1081.6	1085.1
135°	1157.1	1154.8	1152.5	1149.5	1145.4	1141.5	1137.4	1133.5	1137.4	1141.5	1145.4
137.5°	1211.7	1209.1	1206.6	1203.9	1201.1	1198.3	1195.5	1192.7	1195.5	1198.3	1201.1
140°	1247.4	1244.6	1241.8	1239.4	1237.5	1235.5	1233.4	1231.4	1233.4	1235.5	1237.5
142.5°	1279.9	1276.8	1273.6	1271.1	1269.3	1267.5	1265.7	1263.9	1265.7	1267.5	1269.3
145°	1324.4	1320.1	1315.8	1313.8	1314.1	1314.3	1314.5	1314.9	1314.5	1314.3	1314.1
147.5°	1365.5	1361.2	1357.0	1355.4	1356.4	1357.3	1358.3	1359.2	1358.3	1357.3	1356.4
150°	1390.2	1386.2	1382.2	1381.0	1382.8	1384.6	1386.3	1388.1	1386.3	1384.6	1382.8
152.5°	1413.1	1409.3	1405.5	1404.6	1406.5	1408.5	1410.5	1412.4	1410.5	1408.5	1406.5
155°	1445.2	1442.2	1439.2	1438.8	1441.0	1443.3	1445.5	1447.8	1445.5	1443.3	1441.0
157.5°	1472.2	1470.1	1468.0	1467.9	1469.8	1471.7	1473.6	1475.5	1473.6	1471.7	1469.8
160°	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1490.2	1488.7	1487.2
162.5°	1502.6	1501.3	1500.0	1500.2	1501.7	1503.2	1504.7	1506.1	1504.7	1503.2	1501.7
165°	1520.6	1519.9	1519.2	1519.5	1521.0	1522.5	1524.0	1525.5	1524.0	1522.5	1521.0
167.5°	1534.9	1534.2	1533.5	1533.9	1535.4	1536.9	1538.4	1539.9	1538.4	1536.9	1535.4
170°	1542.5	1542.1	1541.5	1542.1	1543.6	1545.1	1546.6	1548.1	1546.6	1545.1	1543.6
172.5°	1547.9	1547.4	1547.0	1547.4	1549.0	1550.5	1552.0	1553.5	1552.0	1550.5	1549.0
175°	1553.8	1553.3	1552.8	1553.5	1555.2	1557.0	1558.7	1560.4	1558.7	1557.0	1555.2
177.5°	1555.8	1555.5	1555.4	1555.9	1557.4	1558.8	1560.2	1561.5	1560.2	1558.8	1557.4
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	4.9	5.2	5.5	5.9	6.1	6.4	6.5	6.7	7.0	7.0	7.1
90°	12.1	14.5	16.6	18.5	20.5	22.5	23.8	25.0	26.3	27.6	28.4
92.5°	21.8	22.1	23.1	24.2	25.1	26.1	26.8	27.4	28.1	28.8	29.2
95°	40.2	36.9	38.7	40.4	42.2	44.0	45.2	46.4	47.7	49.0	49.4
97.5°	52.2	42.6	46.7	50.7	54.7	58.8	59.8	60.8	61.8	62.8	63.5
100°	62.2	47.2	51.4	55.7	60.0	64.2	66.2	68.2	70.3	72.2	73.5
102.5°	229.9	208.4	172.9	137.2	101.6	66.0	68.6	71.2	73.8	76.4	78.1
105°	372.6	342.1	273.8	205.4	137.0	68.8	71.5	74.2	77.0	79.8	81.6
107.5°	462.1	424.1	342.1	260.2	178.2	96.3	93.4	90.6	87.8	85.0	84.1
110°	520.1	486.6	414.2	341.9	269.5	197.2	172.1	147.1	122.1	97.0	85.0



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	575.4	568.8	551.0	533.1	515.2	497.3	406.0	314.7	223.3	132.0	86.7
115°	664.9	670.1	676.4	682.6	688.9	695.1	579.2	463.3	347.4	231.5	164.5
117.5°	748.2	752.7	757.0	761.4	765.6	770.0	742.0	713.9	685.9	657.8	614.2
120°	803.7	807.8	812.3	816.8	821.3	825.9	828.9	831.9	834.9	837.9	822.4
122.5°	855.0	859.4	864.3	869.2	874.1	879.0	880.8	882.6	884.5	886.2	883.8
125°	929.0	933.0	937.8	942.5	947.3	952.0	953.8	955.5	957.3	959.0	960.3
127.5°	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4	1022.9	1025.5	1028.0	1029.4
130°	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0	1065.7	1068.5	1071.2	1072.5
132.5°	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9	1107.2	1109.6	1112.0	1113.0
135°	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1	1166.6	1169.1	1171.6	1172.6
137.5°	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2	1221.7	1224.2	1226.6	1227.4
140°	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1	1257.4	1259.6	1261.9	1262.3
142.5°	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2	1290.3	1292.4	1294.4	1294.8
145°	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6	1336.3	1338.1	1339.9	1340.1
147.5°	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1	1376.5	1377.8	1379.1	1379.2
150°	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7	1401.2	1402.7	1404.2	1404.3
152.5°	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2	1423.7	1425.2	1426.7	1426.6
155°	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6	1454.1	1455.6	1457.1	1456.9
157.5°	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1	1479.8	1481.5	1483.2	1483.0
160°	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2	1494.7	1496.2	1497.7	1497.6
162.5°	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0	1508.6	1510.4	1512.0	1511.8
165°	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1
167.5°	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1	1539.8	1541.6	1543.3	1543.1
170°	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3	1547.1	1548.8	1550.5	1550.3
172.5°	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7	1552.4	1554.2	1555.9	1555.7
175°	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6	1558.3	1560.0	1561.8	1561.5
177.5°	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6	1558.9	1560.4	1561.8	1561.5
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	7.2	7.2	7.3	7.2	7.3	7.2	7.2	7.1	7.0	7.0	6.7
90°	28.9	29.4	29.9	30.4	29.9	29.4	28.9	28.4	27.6	26.3	25.0
92.5°	29.5	29.8	30.1	30.4	30.1	29.8	29.5	29.2	28.8	28.1	27.4
95°	49.2	49.0	48.7	48.5	48.7	49.0	49.2	49.4	49.0	47.7	46.4
97.5°	63.8	64.1	64.4	64.6	64.4	64.1	63.8	63.5	62.8	61.8	60.8
100°	74.0	74.5	75.0	75.5	75.0	74.5	74.0	73.5	72.2	70.3	68.2
102.5°	78.8	79.5	80.2	80.9	80.2	79.5	78.8	78.1	76.4	73.8	71.2
105°	82.6	83.7	84.6	85.6	84.6	83.7	82.6	81.6	79.8	77.0	74.2
107.5°	85.1	86.1	87.1	88.1	87.1	86.1	85.1	84.1	85.0	87.8	90.6
110°	86.0	87.0	88.0	89.0	88.0	87.0	86.0	85.0	97.0	122.1	147.1



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	87.5	88.3	89.1	89.9	89.1	88.3	87.5	86.7	132.0	223.3	314.7
115°	146.5	128.4	110.4	92.4	110.4	128.4	146.5	164.5	231.5	347.4	463.3
117.5°	554.9	495.7	436.4	377.2	436.4	495.7	554.9	614.2	657.8	685.9	713.9
120°	788.7	754.9	721.0	687.3	721.0	754.9	788.7	822.4	837.9	834.9	831.9
122.5°	877.3	870.8	864.2	857.6	864.2	870.8	877.3	883.8	886.2	884.5	882.6
125°	961.1	961.8	962.6	963.3	962.6	961.8	961.1	960.3	959.0	957.3	955.5
127.5°	1029.5	1029.7	1029.8	1030.0	1029.8	1029.7	1029.5	1029.4	1028.0	1025.5	1022.9
130°	1072.2	1072.0	1071.7	1071.4	1071.7	1072.0	1072.2	1072.5	1071.2	1068.5	1065.7
132.5°	1112.8	1112.5	1112.3	1112.0	1112.3	1112.5	1112.8	1113.0	1112.0	1109.6	1107.2
135°	1172.1	1171.6	1171.1	1170.6	1171.1	1171.6	1172.1	1172.6	1171.6	1169.1	1166.6
137.5°	1226.5	1225.7	1224.9	1224.0	1224.9	1225.7	1226.5	1227.4	1226.6	1224.2	1221.7
140°	1261.2	1259.9	1258.6	1257.4	1258.6	1259.9	1261.2	1262.3	1261.9	1259.6	1257.4
142.5°	1293.6	1292.3	1291.1	1289.8	1291.1	1292.3	1293.6	1294.8	1294.4	1292.4	1290.3
145°	1338.9	1337.6	1336.3	1335.1	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3
147.5°	1378.2	1377.1	1376.0	1375.0	1376.0	1377.1	1378.2	1379.2	1379.1	1377.8	1376.5
150°	1403.1	1401.8	1400.6	1399.3	1400.6	1401.8	1403.1	1404.3	1404.2	1402.7	1401.2
152.5°	1425.0	1423.4	1421.7	1420.1	1421.7	1423.4	1425.0	1426.6	1426.7	1425.2	1423.7
155°	1454.9	1452.9	1450.9	1448.9	1450.9	1452.9	1454.9	1456.9	1457.1	1455.6	1454.1
157.5°	1481.1	1479.2	1477.2	1475.3	1477.2	1479.2	1481.1	1483.0	1483.2	1481.5	1479.8
160°	1495.9	1494.1	1492.3	1490.6	1492.3	1494.1	1495.9	1497.6	1497.7	1496.2	1494.7
162.5°	1509.7	1507.5	1505.4	1503.2	1505.4	1507.5	1509.7	1511.8	1512.0	1510.4	1508.6
165°	1527.4	1525.7	1523.9	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7
167.5°	1540.9	1538.6	1536.4	1534.1	1536.4	1538.6	1540.9	1543.1	1543.3	1541.6	1539.8
170°	1548.1	1545.8	1543.6	1541.3	1543.6	1545.8	1548.1	1550.3	1550.5	1548.8	1547.1
172.5°	1553.5	1551.2	1549.0	1546.7	1549.0	1551.2	1553.5	1555.7	1555.9	1554.2	1552.4
175°	1558.9	1556.4	1553.9	1551.4	1553.9	1556.4	1558.9	1561.5	1561.8	1560.0	1558.3
177.5°	1559.7	1558.0	1556.2	1554.3	1556.2	1558.0	1559.7	1561.5	1561.8	1560.4	1558.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	6.5	6.4	6.1	5.9	5.5	5.2	4.9	4.4	4.2	3.8	3.4
90°	23.8	22.5	20.5	18.5	16.6	14.5	12.1	9.4	6.7	3.9	1.1
92.5°	26.8	26.1	25.1	24.2	23.1	22.1	21.8	22.0	22.3	22.5	22.7
95°	45.2	44.0	42.2	40.4	38.7	36.9	40.2	48.5	56.7	65.0	73.2
97.5°	59.8	58.8	54.7	50.7	46.7	42.6	52.2	75.5	98.8	122.1	145.4
100°	66.2	64.2	60.0	55.7	51.4	47.2	62.2	96.5	130.8	165.1	199.4
102.5°	68.6	66.0	101.6	137.2	172.9	208.4	229.9	237.1	244.4	251.7	258.9
105°	71.5	68.8	137.0	205.4	273.8	342.1	372.6	365.0	357.5	350.0	342.5
107.5°	93.4	96.3	178.2	260.2	342.1	424.1	462.1	456.0	450.0	443.9	437.8
110°	172.1	197.2	269.5	341.9	414.2	486.6	520.1	514.9	509.6	504.4	499.2



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	406.0	497.3	515.2	533.1	551.0	568.8	575.4	570.8	566.1	561.4	556.8
115°	579.2	695.1	688.9	682.6	676.4	670.1	664.9	660.6	656.3	652.1	647.8
117.5°	742.0	770.0	765.6	761.4	757.0	752.7	748.2	743.5	738.7	734.0	729.2
120°	828.9	825.9	821.3	816.8	812.3	807.8	803.7	799.9	796.1	792.4	788.7
122.5°	880.8	879.0	874.1	869.2	864.3	859.4	855.0	851.0	847.1	843.1	839.2
125°	953.8	952.0	947.3	942.5	937.8	933.0	929.0	925.7	922.5	919.2	916.0
127.5°	1020.4	1017.9	1014.3	1010.7	1007.2	1003.6	1000.1	996.4	992.8	989.2	985.6
130°	1063.0	1060.2	1057.4	1054.7	1051.9	1049.2	1045.8	1041.8	1037.8	1033.8	1029.8
132.5°	1104.9	1102.6	1099.8	1097.0	1094.3	1091.5	1088.5	1085.1	1081.6	1078.2	1074.8
135°	1164.1	1161.6	1159.4	1157.1	1154.8	1152.5	1149.5	1145.4	1141.5	1137.4	1133.5
137.5°	1219.2	1216.8	1214.3	1211.7	1209.1	1206.6	1203.9	1201.1	1198.3	1195.5	1192.7
140°	1255.1	1252.8	1250.1	1247.4	1244.6	1241.8	1239.4	1237.5	1235.5	1233.4	1231.4
142.5°	1288.2	1286.2	1283.0	1279.9	1276.8	1273.6	1271.1	1269.3	1267.5	1265.7	1263.9
145°	1334.6	1332.8	1328.6	1324.4	1320.1	1315.8	1313.8	1314.1	1314.3	1314.5	1314.9
147.5°	1375.1	1373.9	1369.7	1365.5	1361.2	1357.0	1355.4	1356.4	1357.3	1358.3	1359.2
150°	1399.7	1398.2	1394.2	1390.2	1386.2	1382.2	1381.0	1382.8	1384.6	1386.3	1388.1
152.5°	1422.2	1420.7	1416.9	1413.1	1409.3	1405.5	1404.6	1406.5	1408.5	1410.5	1412.4
155°	1452.6	1451.1	1448.2	1445.2	1442.2	1439.2	1438.8	1441.0	1443.3	1445.5	1447.8
157.5°	1478.1	1476.4	1474.3	1472.2	1470.1	1468.0	1467.9	1469.8	1471.7	1473.6	1475.5
160°	1493.2	1491.7	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7
162.5°	1507.0	1505.2	1504.0	1502.6	1501.3	1500.0	1500.2	1501.7	1503.2	1504.7	1506.1
165°	1523.9	1522.1	1521.4	1520.6	1519.9	1519.2	1519.5	1521.0	1522.5	1524.0	1525.5
167.5°	1538.1	1536.4	1535.6	1534.9	1534.2	1533.5	1533.9	1535.4	1536.9	1538.4	1539.9
170°	1545.3	1543.6	1543.0	1542.5	1542.1	1541.5	1542.1	1543.6	1545.1	1546.6	1548.1
172.5°	1550.7	1549.0	1548.5	1547.9	1547.4	1547.0	1547.4	1549.0	1550.5	1552.0	1553.5
175°	1556.6	1554.8	1554.3	1553.8	1553.3	1552.8	1553.5	1555.2	1557.0	1558.7	1560.4
177.5°	1557.6	1556.2	1555.9	1555.8	1555.5	1555.4	1555.9	1557.4	1558.8	1560.2	1561.5
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.4	5.5	6.0	7.1	7.2	7.6	8.0	8.3	8.6	8.6	8.7
90°	3.9	6.7	9.4	12.1	14.5	16.6	18.5	20.5	22.5	23.8	25.0
92.5°	22.5	22.3	22.0	21.8	22.1	23.1	24.2	25.1	26.1	26.8	27.4
95°	65.0	56.7	48.5	40.2	36.9	38.7	40.4	42.2	44.0	45.2	46.4
97.5°	122.1	98.8	75.5	52.2	42.6	46.7	50.7	54.7	58.8	59.8	60.8
100°	165.1	130.8	96.5	62.2	47.2	51.4	55.7	60.0	64.2	66.2	68.2
102.5°	251.7	244.4	237.1	229.9	208.4	172.9	137.2	101.6	66.0	68.6	71.2
105°	350.0	357.5	365.0	372.6	342.1	273.8	205.4	137.0	68.8	71.5	74.2
107.5°	443.9	450.0	456.0	462.1	424.1	342.1	260.2	178.2	96.3	93.4	90.6
110°	504.4	509.6	514.9	520.1	486.6	414.2	341.9	269.5	197.2	172.1	147.1



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	561.4	566.1	570.8	575.4	568.8	551.0	533.1	515.2	497.3	406.0	314.7
115°	652.1	656.3	660.6	664.9	670.1	676.4	682.6	688.9	695.1	579.2	463.3
117.5°	734.0	738.7	743.5	748.2	752.7	757.0	761.4	765.6	770.0	742.0	713.9
120°	792.4	796.1	799.9	803.7	807.8	812.3	816.8	821.3	825.9	828.9	831.9
122.5°	843.1	847.1	851.0	855.0	859.4	864.3	869.2	874.1	879.0	880.8	882.6
125°	919.2	922.5	925.7	929.0	933.0	937.8	942.5	947.3	952.0	953.8	955.5
127.5°	989.2	992.8	996.4	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4	1022.9
130°	1033.8	1037.8	1041.8	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0	1065.7
132.5°	1078.2	1081.6	1085.1	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9	1107.2
135°	1137.4	1141.5	1145.4	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1	1166.6
137.5°	1195.5	1198.3	1201.1	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2	1221.7
140°	1233.4	1235.5	1237.5	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1	1257.4
142.5°	1265.7	1267.5	1269.3	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2	1290.3
145°	1314.5	1314.3	1314.1	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6	1336.3
147.5°	1358.3	1357.3	1356.4	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1	1376.5
150°	1386.3	1384.6	1382.8	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7	1401.2
152.5°	1410.5	1408.5	1406.5	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2	1423.7
155°	1445.5	1443.3	1441.0	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6	1454.1
157.5°	1473.6	1471.7	1469.8	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1	1479.8
160°	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2	1494.7
162.5°	1504.7	1503.2	1501.7	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0	1508.6
165°	1524.0	1522.5	1521.0	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9	1525.7
167.5°	1538.4	1536.9	1535.4	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1	1539.8
170°	1546.6	1545.1	1543.6	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3	1547.1
172.5°	1552.0	1550.5	1549.0	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7	1552.4
175°	1558.7	1557.0	1555.2	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6	1558.3
177.5°	1560.2	1558.8	1557.4	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6	1558.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	9.1	9.4	9.4	9.5	9.7	9.7	9.8
90°	26.3	27.6	28.4	28.9	29.4	29.9	30.4
92.5°	28.1	28.8	29.2	29.5	29.8	30.1	30.4
95°	47.7	49.0	49.4	49.2	49.0	48.7	48.5
97.5°	61.8	62.8	63.5	63.8	64.1	64.4	64.6
100°	70.3	72.2	73.5	74.0	74.5	75.0	75.5
102.5°	73.8	76.4	78.1	78.8	79.5	80.2	80.9
105°	77.0	79.8	81.6	82.6	83.7	84.6	85.6
107.5°	87.8	85.0	84.1	85.1	86.1	87.1	88.1
110°	122.1	97.0	85.0	86.0	87.0	88.0	89.0



TEST NUMBER: P331489-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	223.3	132.0	86.7	87.5	88.3	89.1	89.9
115°	347.4	231.5	164.5	146.5	128.4	110.4	92.4
117.5°	685.9	657.8	614.2	554.9	495.7	436.4	377.2
120°	834.9	837.9	822.4	788.7	754.9	721.0	687.3
122.5°	884.5	886.2	883.8	877.3	870.8	864.2	857.6
125°	957.3	959.0	960.3	961.1	961.8	962.6	963.3
127.5°	1025.5	1028.0	1029.4	1029.5	1029.7	1029.8	1030.0
130°	1068.5	1071.2	1072.5	1072.2	1072.0	1071.7	1071.4
132.5°	1109.6	1112.0	1113.0	1112.8	1112.5	1112.3	1112.0
135°	1169.1	1171.6	1172.6	1172.1	1171.6	1171.1	1170.6
137.5°	1224.2	1226.6	1227.4	1226.5	1225.7	1224.9	1224.0
140°	1259.6	1261.9	1262.3	1261.2	1259.9	1258.6	1257.4
142.5°	1292.4	1294.4	1294.8	1293.6	1292.3	1291.1	1289.8
145°	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1335.1
147.5°	1377.8	1379.1	1379.2	1378.2	1377.1	1376.0	1375.0
150°	1402.7	1404.2	1404.3	1403.1	1401.8	1400.6	1399.3
152.5°	1425.2	1426.7	1426.6	1425.0	1423.4	1421.7	1420.1
155°	1455.6	1457.1	1456.9	1454.9	1452.9	1450.9	1448.9
157.5°	1481.5	1483.2	1483.0	1481.1	1479.2	1477.2	1475.3
160°	1496.2	1497.7	1497.6	1495.9	1494.1	1492.3	1490.6
162.5°	1510.4	1512.0	1511.8	1509.7	1507.5	1505.4	1503.2
165°	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1
167.5°	1541.6	1543.3	1543.1	1540.9	1538.6	1536.4	1534.1
170°	1548.8	1550.5	1550.3	1548.1	1545.8	1543.6	1541.3
172.5°	1554.2	1555.9	1555.7	1553.5	1551.2	1549.0	1546.7
175°	1560.0	1561.8	1561.5	1558.9	1556.4	1553.9	1551.4
177.5°	1560.4	1561.8	1561.5	1559.7	1558.0	1556.2	1554.3
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0

(END OF REPORT)