

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331490-927

Luminaire Tested: **S122DIW-S290D1440U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331490-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1440U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4995.8 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18	13
4	70	60	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	14	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	0.9
10°-20°	129.6	2.6
20°-30°	188.1	3.8
30°-40°	198.5	4.0
40°-50°	175.8	3.5
50°-60°	140.3	2.8
60°-70°	95.4	1.9
70°-80°	48.9	1.0
80°-90°	17.4	0.3
90°-100°	89.7	1.8
100°-110°	278.5	5.6
110°-120°	476.1	9.5
120°-130°	626.1	12.5
130°-140°	702.7	14.1
140°-150°	689.0	13.8
150°-160°	577.9	11.6
160°-170°	383.3	7.7
170°-180°	134.0	2.7
0°-30°	362.4	7.3
0°-40°	560.9	11.2
0°-60°	877.0	17.6
0°-90°	1038.7	20.8
90°-120°	844.3	16.9
90°-150°	2862.0	57.3
90°-180°	3957.0	79.2
0°-180°	4995.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	12
90°	41	1	41	1	41	18
95°	74	62	74	62	74	83
105°	265	257	265	257	265	279
115°	478	478	478	478	478	472
125°	697	695	697	695	697	622
135°	910	899	910	899	910	700
145°	1104	1092	1104	1092	1104	689
155°	1258	1248	1258	1248	1258	579
165°	1359	1358	1359	1358	1359	383
175°	1408	1413	1408	1413	1408	134
180°	1415	1415	1415	1415	1415	



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	11.9	11.8	11.9	11.7	11.6	11.8	12.0	11.9	12.1	12.4	11.3
90°	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7	41.3	41.8	36.0
92.5°	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2	38.1	37.9	36.6
95°	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4	76.4	76.4	75.9
97.5°	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5	128.5	128.5	127.5
100°	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8	164.8	164.8	164.0
102.5°	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4	204.2	204.0	203.0
105°	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8	263.2	262.8	262.2
107.5°	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9	327.6	327.5	327.5
110°	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0	415.7	416.3	416.5
115°	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0	482.2	482.5	483.0
117.5°	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7	547.3	548.0	549.4
120°	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9	589.9	589.9	592.1
122.5°	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5	635.2	635.8	637.3
125°	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6	701.4	702.2	703.1
127.5°	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8	765.7	766.8	767.7
130°	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7	809.2	809.7	810.2
132.5°	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4	852.5	853.7	853.6
135°	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3	914.6	914.8	914.3
137.5°	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5	974.8	975.0	974.3
140°	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1	1015.1	1015.1	1013.8
142.5°	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9	1051.6	1051.5	1050.5
145°	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6	1107.3	1107.1	1105.5
147.5°	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5	1156.0	1155.3	1154.3
150°	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9	1184.9
152.5°	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5	1215.2
155°	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8	1256.5	1255.1	1254.3
157.5°	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1	1292.3	1290.5	1290.1
160°	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7	1314.1	1312.5	1312.2
162.5°	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2	1333.4	1331.6	1331.3
165°	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4	1358.5	1356.7	1356.7
167.5°	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2	1379.3	1377.4	1377.5
170°	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7	1390.8	1388.9	1389.2
172.5°	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2	1399.4	1397.5	1397.8
175°	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6	1408.7	1406.8	1407.4
177.5°	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3	1412.8
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	10.4	9.2	8.0	7.4	6.3	5.7	4.4	3.4	3.9	4.4	4.8
90°	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2	4.4	7.5	10.8
92.5°	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2	23.6	25.9	28.3
95°	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1	64.7	67.4	70.0
97.5°	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4	115.8	118.1	120.5
100°	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7	153.8	155.9	158.0
102.5°	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8	193.5	195.2	196.9
105°	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7	257.5	258.3	259.1
107.5°	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2	323.4	324.6	325.7
110°	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2	365.8	367.4	369.0



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1	411.7	413.3	414.9
115°	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7	479.3	480.9	482.5
117.5°	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1	547.2	549.3	551.4
120°	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	592.1	594.2	596.4
122.5°	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1	633.6	636.1	638.7
125°	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1	697.4	699.8	702.2
127.5°	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4	760.4	763.4	766.5
130°	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5	800.0	803.5	806.9
132.5°	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5	843.4	846.1	849.0
135°	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3	902.2	905.1	908.0
137.5°	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2	963.5	965.9	968.3
140°	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4	1000.8	1003.2	1005.6
142.5°	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6	1039.0	1041.4	1043.8
145°	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5	1093.4	1095.3	1097.1
147.5°	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5	1142.7	1144.9	1147.2
150°	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9	1175.5	1177.2	1178.8
152.5°	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6	1205.1	1206.7	1208.3
155°	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0	1248.8	1249.6	1250.4
157.5°	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9	1286.5	1287.1	1287.6
160°	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9	1309.5	1310.0	1310.5
162.5°	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9	1330.1	1330.2	1330.2
165°	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9	1357.6	1357.3	1357.1
167.5°	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2	1380.5	1379.7	1378.9
170°	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7	1392.9	1392.1	1391.3
172.5°	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3	1401.5	1400.7	1399.9
175°	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8	1412.0	1411.2	1410.4
177.5°	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1	1416.5	1415.9	1415.2
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	5.2	6.0	7.1	8.2	9.2	10.2	10.0	9.9	9.7	9.3	9.3
90°	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7	40.2	39.7	39.5
92.5°	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2	38.3	38.4	38.5
95°	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4	76.4	76.4	76.1
97.5°	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5	128.5	128.5	128.5
100°	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8	164.8	164.8	164.7
102.5°	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4	204.6	204.9	204.8
105°	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8	264.4	264.8	265.1
107.5°	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9	328.1	328.3	327.8
110°	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.0



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0	414.4	413.8	413.1
115°	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0	481.6	481.4	480.9
117.5°	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7	546.1	545.4	544.6
120°	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9	589.9	589.9	589.5
122.5°	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5	633.9	633.3	632.6
125°	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6	699.8	699.0	698.5
127.5°	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8	763.8	762.9	762.0
130°	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7	808.1	807.6	806.8
132.5°	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4	850.2	849.0	848.0
135°	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3	914.0	913.8	913.2
137.5°	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5	974.4	974.1	973.5
140°	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1	1015.1	1015.1	1014.6
142.5°	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9	1052.1	1052.3	1051.9
145°	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6	1107.9	1108.1	1107.7
147.5°	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5	1157.1	1157.7	1157.5
150°	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1
152.5°	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5
155°	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8	1259.2	1260.4	1260.8
157.5°	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1	1295.9	1297.8	1298.0
160°	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7	1317.2	1318.8	1319.1
162.5°	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2	1337.0	1338.8	1339.1
165°	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4	1362.2	1364.1	1364.4
167.5°	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2	1383.1	1384.9	1385.1
170°	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7	1394.5	1396.4	1396.5
172.5°	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2	1403.1	1404.9	1405.1
175°	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6	1412.4	1414.3	1414.4
177.5°	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	9.4	9.3	9.3	9.3	9.3	9.3	9.4	9.3	9.3	9.7	9.9
90°	39.8	40.1	40.3	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7
92.5°	38.5	38.6	38.7	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2
95°	75.7	75.1	74.5	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4
97.5°	128.4	128.3	128.3	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5
100°	164.4	164.1	163.9	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8
102.5°	204.5	204.3	204.0	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4
105°	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8
107.5°	326.6	325.3	324.2	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9
110°	370.2	369.4	368.6	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	412.6	412.0	411.4	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0
115°	480.1	479.3	478.5	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0
117.5°	543.8	543.0	542.2	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7
120°	588.7	588.0	587.2	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9
122.5°	632.1	631.5	630.9	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5
125°	698.2	698.0	697.8	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6
127.5°	761.1	760.3	759.5	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8
130°	805.7	804.7	803.6	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7
132.5°	847.2	846.3	845.4	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4
135°	912.4	911.6	910.9	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3
137.5°	972.5	971.4	970.3	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5
140°	1013.5	1012.5	1011.4	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1
142.5°	1050.8	1049.7	1048.7	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9
145°	1106.7	1105.6	1104.5	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6
147.5°	1156.4	1155.4	1154.4	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5
150°	1188.3	1187.5	1186.7	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5
152.5°	1219.5	1218.5	1217.5	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5
155°	1260.0	1259.2	1258.4	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8
157.5°	1296.7	1295.5	1294.2	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1
160°	1318.0	1317.0	1316.0	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7
162.5°	1337.8	1336.6	1335.3	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2
165°	1363.0	1361.8	1360.4	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4
167.5°	1383.8	1382.4	1381.0	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2
170°	1394.9	1393.3	1391.7	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7
172.5°	1403.5	1401.9	1400.3	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2
175°	1412.8	1411.2	1409.6	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6
177.5°	1416.2	1414.9	1413.6	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	10.0	10.2	9.2	8.2	7.1	6.0	5.2	4.8	4.4	3.9	3.4
90°	41.3	41.8	36.0	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2
92.5°	38.1	37.9	36.6	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2
95°	76.4	76.4	75.9	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1
97.5°	128.5	128.5	127.5	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4
100°	164.8	164.8	164.0	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7
102.5°	204.2	204.0	203.0	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8
105°	263.2	262.8	262.2	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7
107.5°	327.6	327.5	327.5	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2
110°	371.5	371.5	371.5	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.7	416.3	416.5	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1
115°	482.2	482.5	483.0	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7
117.5°	547.3	548.0	549.4	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1
120°	589.9	589.9	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9
122.5°	635.2	635.8	637.3	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1
125°	701.4	702.2	703.1	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1
127.5°	765.7	766.8	767.7	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4
130°	809.2	809.7	810.2	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5
132.5°	852.5	853.7	853.6	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5
135°	914.6	914.8	914.3	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3
137.5°	974.8	975.0	974.3	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2
140°	1015.1	1015.1	1013.8	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4
142.5°	1051.6	1051.5	1050.5	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6
145°	1107.3	1107.1	1105.5	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5
147.5°	1156.0	1155.3	1154.3	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5
150°	1186.7	1185.9	1184.9	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9
152.5°	1217.5	1216.5	1215.2	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6
155°	1256.5	1255.1	1254.3	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0
157.5°	1292.3	1290.5	1290.1	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9
160°	1314.1	1312.5	1312.2	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9
162.5°	1333.4	1331.6	1331.3	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9
165°	1358.5	1356.7	1356.7	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9
167.5°	1379.3	1377.4	1377.5	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2
170°	1390.8	1388.9	1389.2	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7
172.5°	1399.4	1397.5	1397.8	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3
175°	1408.7	1406.8	1407.4	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8
177.5°	1413.6	1412.3	1412.8	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.4	5.7	6.3	7.4	8.0	9.2	10.4	11.3	12.4	12.1	11.9
90°	4.4	7.5	10.8	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7
92.5°	23.6	25.9	28.3	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2
95°	64.7	67.4	70.0	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4
97.5°	115.8	118.1	120.5	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5
100°	153.8	155.9	158.0	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8
102.5°	193.5	195.2	196.9	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4
105°	257.5	258.3	259.1	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8
107.5°	323.4	324.6	325.7	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9
110°	365.8	367.4	369.0	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	411.7	413.3	414.9	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0
115°	479.3	480.9	482.5	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0
117.5°	547.2	549.3	551.4	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7
120°	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9
122.5°	633.6	636.1	638.7	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5
125°	697.4	699.8	702.2	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6
127.5°	760.4	763.4	766.5	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8
130°	800.0	803.5	806.9	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7
132.5°	843.4	846.1	849.0	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4
135°	902.2	905.1	908.0	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3
137.5°	963.5	965.9	968.3	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5
140°	1000.8	1003.2	1005.6	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1
142.5°	1039.0	1041.4	1043.8	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9
145°	1093.4	1095.3	1097.1	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6
147.5°	1142.7	1144.9	1147.2	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5
150°	1175.5	1177.2	1178.8	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5
152.5°	1205.1	1206.7	1208.3	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5
155°	1248.8	1249.6	1250.4	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8
157.5°	1286.5	1287.1	1287.6	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1
160°	1309.5	1310.0	1310.5	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7
162.5°	1330.1	1330.2	1330.2	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2
165°	1357.6	1357.3	1357.1	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4
167.5°	1380.5	1379.7	1378.9	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2
170°	1392.9	1392.1	1391.3	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7
172.5°	1401.5	1400.7	1399.9	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2
175°	1412.0	1411.2	1410.4	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6
177.5°	1416.5	1415.9	1415.2	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	12.0	11.8	11.6	11.7	11.9	11.8	11.9
90°	40.2	39.7	39.5	39.8	40.1	40.3	40.6
92.5°	38.3	38.4	38.5	38.5	38.6	38.7	38.7
95°	76.4	76.4	76.1	75.7	75.1	74.5	74.1
97.5°	128.5	128.5	128.5	128.4	128.3	128.3	128.3
100°	164.8	164.8	164.7	164.4	164.1	163.9	163.6
102.5°	204.6	204.9	204.8	204.5	204.3	204.0	203.7
105°	264.4	264.8	265.1	265.1	265.1	265.1	265.1
107.5°	328.1	328.3	327.8	326.6	325.3	324.2	322.9
110°	371.5	371.5	371.0	370.2	369.4	368.6	367.8



TEST NUMBER: P331490-927

CATALOG NUMBER: S122DIW-S290D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	414.4	413.8	413.1	412.6	412.0	411.4	410.8
115°	481.6	481.4	480.9	480.1	479.3	478.5	477.7
117.5°	546.1	545.4	544.6	543.8	543.0	542.2	541.5
120°	589.9	589.9	589.5	588.7	588.0	587.2	586.4
122.5°	633.9	633.3	632.6	632.1	631.5	630.9	630.3
125°	699.8	699.0	698.5	698.2	698.0	697.8	697.4
127.5°	763.8	762.9	762.0	761.1	760.3	759.5	758.6
130°	808.1	807.6	806.8	805.7	804.7	803.6	802.6
132.5°	850.2	849.0	848.0	847.2	846.3	845.4	844.5
135°	914.0	913.8	913.2	912.4	911.6	910.9	910.1
137.5°	974.4	974.1	973.5	972.5	971.4	970.3	969.2
140°	1015.1	1015.1	1014.6	1013.5	1012.5	1011.4	1010.3
142.5°	1052.1	1052.3	1051.9	1050.8	1049.7	1048.7	1047.6
145°	1107.9	1108.1	1107.7	1106.7	1105.6	1104.5	1103.5
147.5°	1157.1	1157.7	1157.5	1156.4	1155.4	1154.4	1153.4
150°	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9
152.5°	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5
155°	1259.2	1260.4	1260.8	1260.0	1259.2	1258.4	1257.6
157.5°	1295.9	1297.8	1298.0	1296.7	1295.5	1294.2	1292.9
160°	1317.2	1318.8	1319.1	1318.0	1317.0	1316.0	1314.9
162.5°	1337.0	1338.8	1339.1	1337.8	1336.6	1335.3	1334.0
165°	1362.2	1364.1	1364.4	1363.0	1361.8	1360.4	1359.1
167.5°	1383.1	1384.9	1385.1	1383.8	1382.4	1381.0	1379.6
170°	1394.5	1396.4	1396.5	1394.9	1393.3	1391.7	1390.1
172.5°	1403.1	1404.9	1405.1	1403.5	1401.9	1400.3	1398.8
175°	1412.4	1414.3	1414.4	1412.8	1411.2	1409.6	1408.0
177.5°	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2

(END OF REPORT)