

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331469-927

Luminaire Tested: **S122DIW-S290D435U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331469-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D435U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2324.6 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331469-927

CATALOG NUMBER: S122DIW-S290D435U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331469-927

CATALOG NUMBER: S122DIW-S290D435U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	42	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6042	6042	6042
5°	6065	5977	6015
10°	6030	5917	5946
15°	5954	5840	5835
20°	5849	5727	5720
25°	5744	5585	5585
30°	5610	5455	5407
35°	5483	5298	5219
40°	5324	5143	5044
45°	5167	4987	4864
50°	4999	4828	4657
55°	4822	4642	4467
60°	4624	4414	4253
65°	4413	4195	4000
70°	4145	3923	3734
75°	3768	3612	3525
80°	3347	3245	3078
85°	2723	2594	2334



TEST NUMBER: P331469-927

CATALOG NUMBER: S122DIW-S290D435U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.2	1.5
10°-20°	99.0	4.3
20°-30°	145.6	6.3
30°-40°	169.1	7.3
40°-50°	168.9	7.3
50°-60°	147.3	6.3
60°-70°	108.9	4.7
70°-80°	61.7	2.7
80°-90°	17.7	0.8
90°-100°	15.6	0.7
100°-110°	57.2	2.5
110°-120°	153.0	6.6
120°-130°	252.6	10.9
130°-140°	268.6	11.6
140°-150°	249.7	10.7
150°-160°	200.7	8.6
160°-170°	129.3	5.6
170°-180°	44.5	1.9
0°-30°	279.8	12.0
0°-40°	448.8	19.3
0°-60°	765.0	32.9
0°-90°	953.3	41.0
90°-120°	225.9	9.7
90°-150°	996.7	42.9
90°-180°	1371.0	59.0
0°-180°	2324.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	374	374	374	374	374	
5°	374	373	369	372	371	35
15°	356	354	349	351	349	100
25°	322	319	314	314	314	148
35°	278	274	269	267	265	174
45°	226	224	218	215	213	175
55°	171	169	165	161	159	153
65°	116	113	110	107	105	114
75°	60	60	58	56	56	65
85°	15	14	14	13	13	17
90°	0	4	7	8	9	2
95°	22	12	13	15	15	27
105°	103	107	21	24	26	110
115°	195	201	209	60	28	192
125°	275	280	286	288	290	245
135°	341	346	349	352	352	263
145°	395	395	400	403	401	247
155°	435	432	436	438	436	200
165°	458	457	457	460	457	129
175°	469	467	467	469	466	45
180°	468	468	468	468	468	



TEST NUMBER: P331469-927

CATALOG NUMBER: S122DIW-S290D435U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	376.0	375.7	375.3	375.0	374.7	374.2	373.5	372.8	372.1	371.4	372.0
5°	374.2	373.9	373.6	373.3	373.0	372.4	371.5	370.7	369.7	368.8	369.5
7.5°	371.0	370.4	369.9	369.5	369.0	368.3	367.4	366.5	365.6	364.7	365.4
10°	367.8	367.3	366.7	366.1	365.5	364.8	363.8	362.9	361.9	360.9	361.6
12.5°	363.5	363.0	362.5	361.9	361.5	360.8	359.8	358.9	357.9	357.0	357.4
15°	356.2	355.8	355.3	354.8	354.3	353.6	352.5	351.5	350.5	349.4	349.7
17.5°	347.1	346.6	346.1	345.6	345.2	344.4	343.3	342.2	341.2	340.2	340.5
20°	340.4	339.9	339.5	339.0	338.5	337.7	336.6	335.5	334.4	333.3	333.5
22.5°	333.8	333.1	332.5	331.8	331.1	330.3	329.2	328.1	327.1	326.1	326.1
25°	322.4	321.8	321.2	320.5	319.9	318.9	317.5	316.2	314.8	313.5	313.6
27.5°	309.5	309.0	308.3	307.8	307.2	306.3	305.3	304.2	303.2	302.1	301.8
30°	300.9	300.2	299.6	299.0	298.3	297.4	296.2	295.0	293.7	292.6	292.3
32.5°	291.6	291.1	290.7	290.1	289.6	288.7	287.4	286.2	284.9	283.7	283.2
35°	278.2	277.3	276.6	275.8	275.0	273.9	272.7	271.4	270.1	268.8	268.3
37.5°	263.0	262.3	261.6	260.9	260.2	259.2	257.9	256.7	255.3	254.1	253.5
40°	252.6	252.0	251.4	250.7	250.1	249.1	247.8	246.5	245.3	244.0	243.3
42.5°	242.6	241.9	241.3	240.7	240.0	239.0	237.7	236.5	235.2	233.9	233.1
45°	226.3	225.8	225.2	224.7	224.1	223.2	222.0	220.9	219.7	218.4	217.5
47.5°	210.2	209.7	209.2	208.7	208.1	207.2	206.0	204.8	203.5	202.2	201.3
50°	199.0	198.6	198.2	197.8	197.4	196.6	195.5	194.4	193.3	192.2	191.1
52.5°	188.1	187.5	187.0	186.5	185.9	185.1	184.1	183.1	182.0	180.9	180.0
55°	171.3	170.8	170.3	169.8	169.4	168.7	167.7	166.8	165.8	164.9	163.8
57.5°	154.5	154.1	153.7	153.3	152.9	152.2	151.1	150.1	149.0	148.0	147.0
60°	143.2	142.9	142.6	142.3	142.0	141.2	140.1	139.0	137.8	136.7	135.9
62.5°	132.3	131.7	131.3	130.8	130.2	129.5	128.7	127.9	127.0	126.1	125.2
65°	115.5	115.0	114.5	114.1	113.6	113.0	112.2	111.4	110.6	109.8	109.0
67.5°	98.5	98.1	97.7	97.3	97.0	96.4	95.6	94.9	94.2	93.5	92.9
70°	87.8	87.5	87.1	86.8	86.5	86.0	85.3	84.6	83.8	83.1	82.5
72.5°	76.8	76.5	76.2	75.9	75.6	75.2	74.7	74.3	73.8	73.4	72.8
75°	60.4	60.3	60.1	60.0	59.8	59.6	59.2	58.7	58.3	57.9	57.4
77.5°	45.8	45.5	45.2	45.0	44.7	44.4	44.3	44.1	44.0	43.8	43.6
80°	36.0	35.9	35.8	35.7	35.6	35.6	35.4	35.3	35.1	34.9	34.7
82.5°	26.8	26.8	26.8	26.7	26.7	26.6	26.5	26.5	26.4	26.3	26.0
85°	14.7	14.7	14.6	14.5	14.4	14.3	14.3	14.2	14.1	14.0	13.8
87.5°	5.2	5.3	5.3	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.3
90°	0.3	1.2	2.0	2.9	3.6	4.4	5.0	5.5	6.2	6.7	7.1
92.5°	6.8	6.7	6.7	6.6	6.6	6.7	7.0	7.3	7.5	7.8	8.1
95°	22.0	19.5	17.0	14.6	12.0	11.1	11.6	12.1	12.7	13.2	13.5
97.5°	43.6	36.7	29.7	22.7	15.7	12.8	14.0	15.2	16.5	17.7	18.0
100°	60.0	49.6	39.3	29.0	18.7	14.2	15.4	16.7	18.0	19.3	19.9
102.5°	77.8	75.7	73.4	71.3	69.1	62.7	52.0	41.3	30.6	19.8	20.6
105°	102.9	105.2	107.4	109.7	111.9	102.8	82.3	61.7	41.2	20.7	21.5
107.5°	131.6	133.4	135.2	137.0	138.9	127.5	102.8	78.2	53.6	28.9	28.0
110°	150.0	151.5	153.1	154.7	156.3	146.2	124.5	102.7	81.0	59.3	51.7



TEST NUMBER: P331469-927

CATALOG NUMBER: S122DIW-S290D435U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.3	168.7	170.2	171.5	172.9	171.0	165.6	160.2	154.8	149.5	122.0
115°	194.7	196.0	197.3	198.5	199.8	201.4	203.3	205.2	207.0	208.9	174.0
117.5°	219.1	220.5	222.0	223.4	224.8	226.2	227.5	228.8	230.1	231.4	223.0
120°	237.0	238.1	239.2	240.4	241.5	242.8	244.2	245.5	246.8	248.2	249.1
122.5°	252.2	253.3	254.5	255.7	256.9	258.3	259.8	261.2	262.7	264.2	264.7
125°	275.3	276.2	277.3	278.2	279.2	280.4	281.9	283.3	284.7	286.1	286.6
127.5°	296.2	297.3	298.3	299.4	300.6	301.6	302.7	303.7	304.8	305.9	306.7
130°	309.5	310.7	311.9	313.1	314.3	315.3	316.2	317.0	317.8	318.6	319.4
132.5°	323.1	324.0	325.0	326.1	327.1	328.0	328.8	329.7	330.5	331.4	332.1
135°	340.6	341.8	343.0	344.2	345.5	346.3	347.1	347.8	348.4	349.1	349.8
137.5°	358.5	359.3	360.1	361.0	361.8	362.6	363.4	364.2	364.9	365.7	366.4
140°	370.1	370.7	371.3	371.9	372.5	373.2	374.1	374.9	375.7	376.5	377.2
142.5°	379.9	380.4	380.9	381.4	382.0	382.8	383.7	384.6	385.6	386.5	387.1
145°	395.1	395.1	395.0	394.9	394.8	395.5	396.7	398.0	399.3	400.5	401.1
147.5°	408.4	408.2	407.9	407.7	407.3	407.8	409.1	410.4	411.6	412.9	413.3
150°	417.2	416.6	416.1	415.6	415.0	415.3	416.6	417.8	419.0	420.2	420.6
152.5°	424.5	423.9	423.3	422.7	422.1	422.4	423.5	424.7	425.8	427.0	427.4
155°	435.1	434.4	433.7	433.1	432.4	432.5	433.4	434.3	435.2	436.1	436.6
157.5°	443.4	442.8	442.3	441.7	441.2	441.2	441.8	442.4	443.1	443.7	444.2
160°	448.3	447.8	447.4	446.9	446.5	446.5	446.9	447.4	447.8	448.3	448.8
162.5°	452.7	452.2	451.7	451.3	450.8	450.8	451.1	451.5	451.9	452.3	452.9
165°	458.4	458.0	457.6	457.1	456.6	456.5	456.8	457.0	457.2	457.4	458.0
167.5°	462.8	462.3	461.9	461.4	461.0	460.9	461.1	461.3	461.5	461.7	462.2
170°	465.2	464.8	464.3	463.9	463.4	463.3	463.4	463.6	463.7	463.9	464.4
172.5°	466.8	466.4	466.0	465.5	465.0	464.9	465.0	465.2	465.3	465.5	466.0
175°	469.0	468.4	467.9	467.4	466.8	466.7	466.8	467.0	467.1	467.2	467.8
177.5°	469.3	468.9	468.4	468.0	467.6	467.4	467.5	467.5	467.6	467.6	468.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331469-927

CATALOG NUMBER: S122DIW-S290D435U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	372.6	373.3	373.9	374.2	374.1	373.9	373.8	373.7
5°	370.2	370.8	371.5	371.7	371.5	371.4	371.2	371.1
7.5°	366.0	366.6	367.3	367.5	367.3	367.1	366.9	366.8
10°	362.3	362.9	363.5	363.7	363.5	363.2	363.0	362.7
12.5°	357.8	358.2	358.7	358.9	358.7	358.5	358.3	358.1
15°	350.1	350.4	350.7	350.7	350.3	349.9	349.5	349.1
17.5°	340.9	341.3	341.6	341.6	341.2	340.9	340.5	340.1
20°	333.7	334.0	334.2	334.1	333.8	333.5	333.2	332.9
22.5°	326.1	326.2	326.2	326.1	326.0	325.7	325.6	325.4
25°	313.8	313.9	314.1	314.1	313.9	313.8	313.6	313.5
27.5°	301.6	301.3	301.1	300.8	300.4	300.0	299.7	299.3
30°	292.1	291.8	291.6	291.4	291.0	290.7	290.4	290.0
32.5°	282.8	282.3	281.9	281.5	281.2	280.9	280.6	280.3
35°	267.8	267.4	266.9	266.5	266.1	265.7	265.3	264.8
37.5°	252.9	252.3	251.7	251.2	250.8	250.4	250.1	249.7
40°	242.6	241.9	241.1	240.6	240.3	240.0	239.6	239.3
42.5°	232.3	231.6	230.8	230.1	229.7	229.3	228.9	228.4
45°	216.7	215.8	214.9	214.3	214.0	213.7	213.3	213.0
47.5°	200.4	199.5	198.5	197.8	197.4	196.9	196.5	196.0
50°	190.0	188.8	187.7	187.0	186.6	186.2	185.8	185.4
52.5°	179.1	178.2	177.2	176.5	175.9	175.5	174.9	174.4
55°	162.9	161.9	161.0	160.3	159.9	159.5	159.1	158.7
57.5°	146.1	145.1	144.2	143.5	143.3	143.0	142.7	142.4
60°	135.0	134.1	133.2	132.7	132.5	132.2	132.0	131.7
62.5°	124.5	123.7	122.9	122.3	122.0	121.7	121.4	121.0
65°	108.3	107.6	106.9	106.3	105.9	105.5	105.1	104.7
67.5°	92.4	91.8	91.3	90.8	90.5	90.2	89.8	89.5
70°	82.0	81.4	80.9	80.5	80.2	79.8	79.5	79.1
72.5°	72.2	71.7	71.1	70.7	70.4	70.2	69.9	69.6
75°	57.0	56.5	56.0	55.8	56.0	56.2	56.3	56.5
77.5°	43.3	43.1	42.9	42.6	42.4	42.2	42.0	41.7
80°	34.5	34.2	34.0	33.7	33.6	33.4	33.3	33.1
82.5°	25.7	25.3	25.0	24.9	24.9	24.8	24.8	24.8
85°	13.5	13.3	13.1	12.9	12.8	12.8	12.7	12.6
87.5°	5.1	5.1	4.9	4.8	4.8	4.8	4.8	4.7
90°	7.5	7.9	8.2	8.6	8.7	8.9	9.0	9.1
92.5°	8.2	8.5	8.6	8.8	8.9	9.0	9.0	9.1
95°	13.9	14.3	14.7	14.9	14.8	14.7	14.7	14.6
97.5°	18.3	18.6	18.9	19.1	19.2	19.3	19.3	19.4
100°	20.5	21.1	21.7	22.1	22.3	22.4	22.5	22.7
102.5°	21.4	22.2	23.0	23.4	23.7	23.9	24.1	24.3
105°	22.3	23.1	24.0	24.6	24.8	25.1	25.4	25.7
107.5°	27.3	26.4	25.5	25.3	25.6	25.9	26.1	26.5
110°	44.2	36.7	29.2	25.5	25.8	26.1	26.5	26.8





TEST NUMBER: P331469-927

CATALOG NUMBER: S122DIW-S290D435U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	94.6	67.1	39.7	26.1	26.3	26.5	26.8	27.0
115°	139.3	104.4	69.6	49.4	44.0	38.6	33.2	27.7
117.5°	214.5	206.1	197.6	184.6	166.8	148.9	131.2	113.4
120°	250.0	250.9	251.8	247.2	237.0	226.9	216.7	206.5
122.5°	265.2	265.8	266.3	265.6	263.6	261.7	259.7	257.7
125°	287.2	287.7	288.2	288.6	288.8	289.1	289.3	289.5
127.5°	307.4	308.2	309.0	309.3	309.4	309.4	309.5	309.5
130°	320.3	321.1	321.9	322.3	322.3	322.2	322.1	322.0
132.5°	332.8	333.4	334.1	334.5	334.4	334.3	334.3	334.2
135°	350.6	351.3	352.1	352.4	352.3	352.1	352.0	351.8
137.5°	367.2	367.9	368.6	368.8	368.6	368.4	368.1	367.8
140°	377.9	378.6	379.2	379.4	379.0	378.6	378.3	377.9
142.5°	387.8	388.4	389.0	389.1	388.7	388.4	388.0	387.6
145°	401.6	402.1	402.7	402.7	402.3	402.0	401.6	401.2
147.5°	413.7	414.1	414.5	414.5	414.2	413.8	413.5	413.2
150°	421.1	421.5	422.0	422.1	421.7	421.3	420.9	420.6
152.5°	427.9	428.3	428.8	428.7	428.3	427.8	427.2	426.7
155°	437.0	437.4	437.9	437.8	437.2	436.7	436.0	435.5
157.5°	444.7	445.2	445.8	445.7	445.1	444.5	443.9	443.4
160°	449.2	449.6	450.1	450.0	449.6	449.0	448.5	448.0
162.5°	453.4	453.9	454.4	454.3	453.7	453.0	452.4	451.8
165°	458.5	459.0	459.5	459.5	459.0	458.5	458.0	457.4
167.5°	462.8	463.3	463.8	463.7	463.0	462.4	461.7	461.1
170°	464.9	465.5	466.0	465.9	465.2	464.5	463.9	463.2
172.5°	466.5	467.1	467.6	467.5	466.8	466.2	465.5	464.9
175°	468.3	468.8	469.4	469.3	468.5	467.8	467.0	466.3
177.5°	468.5	468.9	469.4	469.3	468.7	468.2	467.6	467.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9

(END OF REPORT)